

## A selection of Philips winners of iF product design awards



### HD camcorder

Also winner of a gold award [China's Most Successful Design Award](#).

Easy to use movie camera with very simple UI and built in USB.



### PowerTouch Range

Fluid organic shape that gives good ergonomics for handling has been balanced with carefully defined lines and shapes.



### DesignLine Tilt TV

Elegant, clean looking lifestyle TV, simple seamless construction, of an angled glass deco plate and back cover. Ideal for small apartments or spaces.



### Avance Hand Blender

The combination of a strong motor with a food processor accessory that can cube, slice, and shred your favorite vegetables and fruits giving you the exact shape you want in seconds.



### Soundbar HomeTheater

The thinnest and slimmest soundbar including exclusive design elements which incorporates the patented angled speakers of Ambisound technology.



### LED TV 8000

Offering a fully immersive cinematic experience, with a pure and elegant design language enhancing the most lifestyle focused home; distinctive through a full front glass plate.



**DesignLine Edge TV**  
Cinematic Viewing Experience with an 'integrated architecture' language. Distinctive through a consistent and qualitative use of angled glass plate.



**LED TV GOLD 21:9**  
Optimally designed for movie content, no 'black bars', coupled with a high performance picture quality and 2 sided Ambilight.



**Headband**  
An over-ear HiFi headphone for indoor use. Utilizing new technologies and features, such as our signature 'floating cushion' construction, to deliver a superior level of comfort.



**Avance Juicer**  
A new inverted sieve system improves the experience of juicing, showing the colors and amount of juice in a much more appealing way.



**Fidelio**  
The docking speaker's architecture enhances sound performance and radiates sound quality, while the premium design will look stylish in living rooms.



**Sonicare DiamondClean**  
The most advanced electrical toothbrush from Philips Sonicare so far delivers ultimate cleaning performance for superior results.



**Lumea IPL**  
Uses Intense Pulsed Light (IPL), the latest advanced technology used by the professional beauty industry for hair removal – adapted for use at home.



**Teamaker**  
It looks like a teapot but uses the modern technology of today to get all the goodness out of each tea, offering a unique taste experience.



**Arcitone spot**  
The design of this luminaire is inspired by architecture and illustrates the advanced LED-technology and the resulting flatness of the applied LED-disc.



### **Lirio Cielo**

The design is the result of a new way of thinking around an existing archetype. The contrast between the outside shape and the high-tech, hollow inside is only possible with LED light sources.



### **Lirio Trelome**

A high end, energy saving, pendant with a design that communicates innovation through the use of LEDs. The domes; smoothly rising up out of the slim body, hint at the origin and the direction of the cast light.



### **Lirio Balanza**

A new variation on the theme of a classic, archetypal lamp shade. The design style is “deceptively simple” with its graphical, clear volumes.



### **SmartSpot LEDdisk**

Minimalist recessed products that seamlessly blend into interiors. Innovative energy saving LEDs create light accents in every home.



### **SmartSpot Bologna**

High power LED spot with a playful design. The mechanism “guides” the light through its shape and can be directed anywhere desired.



### **Ledino Lamps**

These luminaires have a clear, iconic outline and elegant construction; possible through the use of LED technology.



### **Ledino Outdoor**

The contour provides a robust shape for outdoor application and the recessed cut out is shaped as if it is made by the light coming from the hidden LED light source.



### **LivingColors Bloom**

The design of the product is organic and reduced with the focus on the projected multi coloured LED light. It can be placed virtually everywhere in a room.



### **Multi-sensorial Gastronomy**

Interactive tableware designed to extend the range of sensory experience through visual, audio, fragrance, vibration and electrical stimulus.



### **Microbial Home**

A domestic ecosystem that challenges conventional design solutions to energy, cleaning, food preservation, lighting, human waste and healthy lifestyle.



### **Moda LED monitor**

Designed for MMD. The combination of minimal dimensions, an ultra thin cast metal neck and an open base supports the monitor to blend into home interiors in an elegant and unique way.



### **Built-in Car Air Purifier**

An automotive air purifier used in-car to eliminate airborne particulates like smoke, dust and pollen, gaseous pollutants and germs.



### **Notebook PicoPix Projector**

Designed for Sagemcom, this very compact projector uses state of the art projection technology with a minimalistic, elegant and iconic design. [Read more.](#)

**iF material design  
award 2012**



**SENSEO Viva Café Eco**  
The world's first designer  
end-to-end recycled  
automatic coffee machine:  
highest content 100%  
recycled materials including  
closed loop Philips waste  
material.

**iF packaging design  
award 2012**



**Fidelio premium pack**  
Elevated pack quality by  
glorifying the product detail  
which matters, the Philips'  
sound heritage, the use of  
black color and simplicity in  
product communications.