

Philips SoundBar  
Home theater with  
Ambisound

Wi-Fi ready

HTS9140



## Superior surround sound without clutter

Bring cinema experience home

Indulge in cinema-like multi channel surround sound without speakers and wires all around you. Philips SoundBar with Ambisound incorporates a complete home theater system, including high definition Blu-Ray Disc Playback in a single unit.

### Ultimate listening experience

- Ambisound technology for surround sound from fewer speakers
- DTS-HD and Dolby TrueHD for high fidelity surround sound

### Designed to enhance your living space

- SoundBar design with optimal fit for 40" flat TV or larger
- Slim and premium design in high quality brushed aluminum


### Connect and enjoy all your entertainment

- Wireless network ready for easy access to entertainment
- DLNA Network Link to enjoy music & videos from your PC
- Net TV for popular online services on your TV

**PHILIPS**  
sense and simplicity


# Highlights

## Ambisound technology



Ambisound technology produces truly embracing multi-channel surround sound from fewer speakers. It delivers an immersive 5.1 sound experience without the constraints of sitting position, room shape or size, and without the clutter of multiple speakers and cables. Through the combined effect of psychoacoustic phenomena, array processing and precisely angled driver positioning, Ambisound delivers more sound from fewer speakers.


## DTS-HD and Dolby TrueHD



DTS-HD Advanced Digital Out and Dolby TrueHD deliver the finest sound from your

Blu-ray Discs. Audio reproduced is virtually indistinguishable from the studio master, so you hear what the creators intended for you to hear. DTS-HD Advanced Digital Out and Dolby TrueHD complete your high definition entertainment experience.

## SoundBar design (40")



The SoundBar lends an air of sophistication and grace to any living room. Though it is designed to fit a flat TV with a 40" screen or larger, it will also sit under any other flat TV like a companion - matching all your interior and your lifestyle.


## Slim and premium design

Slim and premium design in high quality brushed aluminum

## Wireless network ready

Wireless network ready for easy access to entertainment

## DLNA Network Link



The DLNA Network link provides easy access to personal photos, music, videos or movies on your PC or Home Network. It uses the Ethernet (LAN) connection with DLNA protocol that assures that DLNA certified products will work together seamlessly. By connecting your TV, home theater or Blu-ray Disc player to your home network, you will be able to access information from all DLNA certified devices. You can access your world of entertainment at a simple push of a button with the intuitive user interface, that is designed for easy browsing.



# Specifications

## Accessories

- Included accessories: Batteries for remote control, FM antenna, HDMI cable, Quick start guide, Remote Control, User Manual, World Wide Warranty leaflet
- Compatible accessories: WUB1110 Wi-Fi USB Adaptor, DCK3060 Dock for iPod, STS1300 Floor stand

## Audio Playback

- Compression format: MP3, WAV, WMA
- MP3 bit rates: 32-256 kbps and VBR
- Playback Media: Audio CD, CD-R/RW, DVD+R/+RW, DVD-R/-RW, USB flash drive, MP3-CD, WMA-CD

## Connectivity

- Front / Side connections: Hi-Speed USB, MP3 Line-in
- Rear Connections: AUX in, Component Video output, Composite video (CVBS) output, Ethernet, FM Antenna, HDMI output, Subwoofer out, Dock connector, Coaxial Digital Input, Optical Digital Input, Wi-Fi USB

## Convenience

- Multimedia: DLNA media Browser, Net TV services

## Dimensions

- Packaging dimensions (W x H x D): 1044 x 404 x 393 mm
- Set dimensions (W x H x D): 955 x 155 x 96 mm
- Subwoofer dimensions (W x H x D): 196 x 395 x 342 mm
- Subwoofer Weight: 6.03 kg

## Loudspeakers

- Loudspeaker types: Integrated with main unit
- Center speaker impedance: 4 ohm
- Satellite speaker freq range: 150 - 20k Hz
- Satellite speaker impedance: 6 ohm
- Subwoofer freq range: 20 - 150 Hz

- Subwoofer impedance: 4 ohm
- Subwoofer type: Passive

## Picture/Display

- D/A converter: 12 bit, 150MHz
- Picture enhancement: High Def (720p, 1080i, 1080p), Progressive scan, Video upscaling

## Power

- Power consumption: 115 W
- Power supply: 220-240V, 50Hz
- Standby power consumption: < 0.22 W

## Sound

- D/A converter: 24 bit, 96k Hz
- Frequency response: 20 - 20000 Hz
- Output power (RMS): 600
- Signal to noise ratio: > 65 dB
- Sound Enhancement: Class "D" Digital Amplifier, Night Mode, Dolby Virtual Speaker
- Sound System: Dolby Digital, Dolby Prologic II, DTS, Ambisound, Dolby True HD
- Equalizer settings: Action, Classic, Concert, Drama, Gaming, Jazz, News, Party, Rock, Sports

## Still Picture Playback

- Picture Compression Format: JPEG
- Picture Enhancement: Rotate, Slideshow with music playback, Zoom
- Playback Media: CD-R/RW, DVD+R/+RW, DVD-R/-RW, USB flash drive

## Tuner/Reception/Transmission

- No. of preset Audio Channels: 40
- RDS: Station Name
- Tuner Bands: FM

## Video Playback

- Compression formats: DivX Ultra, MPEG1, MPEG2, MPEG4, WMV, XviD, AVCHD, MKV, avi
- Playback Media: CD-R/CD-RW, DVD+R/+RW, DVD-R/-RW, DVD-Video, Video CD/SVCD, BD Video, BD-R/RE 2.0
- Video disc playback system: NTSC, PAL



Issue date 2010-02-26

Version: 2.2.4

12 NC: 8670 000 59454  
EAN: 87 12581 52158 5

© 2010 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips  
Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)