



PHILIPS

Automotive

LED work lights



2023

Designed
with **you**[®]
in mind

LED work light features

Light module

Boost light

Maximum light output (in lumen)

Eco/dimmed light

Light output during power save mode (in lumen)

Spotlight

Additional small light to reach confined spaces (in lumen)

Operating time

Operating time during one charging cycle

Beam angle

Angle of the main light beam

Pivoting light module

Flexibility of the work light thanks to pivoting light module

CRI

High Color Rendering Index (CRI) reveals the true colors of an object, as if seen with natural light

UV light

UV light helps identify leakages

New:
Zoom light

Change the focus of the light beam by simply turning a knob

Smart, ergonomic design

Fixture

Fixture such as clips, clamps, and hooks to enable hands-free work

Magnet

Magnet integrated into the work light to enable hands-free work

New:
Motion sensor

Switch the light on and off by moving your hand in front of the sensor

Find My Device

The remote control accessory helps retrieve lost devices up to 10 meters

Grip

Robust ABS* and soft rubber body to hold the work light securely

USB power bank

Charge other devices via a USB port included in the work light

Robustness and durability

Ingress protection

Degree of protection against intrusion from solid objects, dust, accidental contact and water

Shock protection

Degree of protection against external impacts

Grease resistance

Highly resistant to grease and workshop solvents

Power options and recharging

Charging time

Time needed to fully recharge the integrated battery

Micro USB

Battery rechargeable via a USB Type-C or Micro USB

USB-C

Charging station

Compatibility with the Multi Dock Station** accessory for cordless charging













*Acrylonitrile-butadiene-styrene copolymer
**Accessories to buy separately



Discover our Xperion 6000 LED work lights

UV Pillar	Pillar
 reddot winner 2022 DESIGN AWARD 2022	 reddot winner 2022 DESIGN AWARD 2022
<div>Boost light500 lmUp to 4.5 h</div>	<div>Boost light500 lmUp to 4.5 h</div>
<div>Eco light250 lmUp to 10 h</div>	<div>Eco light250 lmUp to 10 h</div>
<div>Spotlight180 lmUp to 12 h</div>	<div>Spotlight180 lmUp to 12 h</div>
<div>Light angle/flexibility100°90° rotatable</div>	<div>Light angle/flexibility100°90° rotatable</div>
<div>Special light featuresUV lightExcellent color rendition</div>	<div>Special light features</div>
<div>Fixture360° rotatable hook1 magnet</div>	<div>Fixture360° rotatable hook1 magnet</div>
<div>Grip/grease resistanceABS*, RubberGarage proof</div>	<div>Grip/grease resistanceABS*Garage proof</div>
<div>RobustnessIP65IK07</div>	<div>RobustnessIP65IK07</div>
<div>Lithium battery power supply<4.5 hUSB Type-C</div>	<div>Lithium battery power supply<4.5 hUSB Type-C</div>
<div>Additional accessoriesFind My DeviceMulti Dock Station**</div>	<div>Additional accessoriesFind My Device**Multi Dock Station**</div>
<div>Philips Order EntryX60UVPX1</div>	<div>Philips Order EntryX60PILLX1</div>

* Acrylonitrile-butadiene-styrene copolymer
** Accessories to buy separately, except for the Philips Xperion 6000 UV Pillar which already includes the Find My Device function

Flood Audio	Flood	Flood Mini	Pocket	Slim	Line
  <div>Up to 20 h audio via Bluetooth</div>	 	 	 <div>reddot winner 2022</div> <div>DESIGN AWARD 2022</div> 	 <div>reddot winner 2022</div> <div>DESIGN AWARD 2022</div> 	 <div>reddot winner 2022</div> <div>DESIGN AWARD 2022</div> 
<div>Boost light</div> <div>1000 lm</div> <div>Up to 3 h</div>	<div>Boost light</div> <div>1000 lm</div> <div>Up to 3 h</div>	<div>Boost light</div> <div>500 lm</div> <div>Up to 3 h</div>	<div>Boost light</div> <div>300 lm</div> <div>Up to 3.5 h</div>	<div>Boost light</div> <div>500 lm</div> <div>Up to 4.5 h</div>	<div>Boost light</div> <div>300 lm</div> <div>Up to 4.5 h</div>
<div>Eco light</div> <div>100 lm</div> <div>Up to 22 h</div>	<div>Eco light</div> <div>100 lm</div> <div>Up to 22 h</div>	<div>Eco light</div> <div>100 lm</div> <div>Up to 9 h</div>	<div>Eco light</div> <div>150 lm</div> <div>Up to 7 h</div>	<div>Eco light</div> <div>250 lm</div> <div>Up to 7 h</div>	<div>Eco light</div> <div>150 lm</div> <div>Up to 8 h</div>
<div>Spotlight</div> <div>250 lm</div> <div>Up to 9 h</div>	<div>Spotlight</div> <div>250 lm</div> <div>Up to 9 h</div>	<div>Spotlight</div> <div>250 lm</div> <div>Up to 5 h</div>	<div>Spotlight</div> <div>100 lm</div> <div>Up to 10 h</div>	<div>Spotlight</div> <div>150 lm</div> <div>Up to 9 h</div>	<div>Spotlight</div> <div>120 lm</div> <div>Up to 9 h</div>
<div>Light angle/light function</div> <div>100°</div> <div>Light setting memory</div>	<div>Light angle/light function</div> <div>100°</div> <div>Light setting memory</div>	<div>Light angle/light function</div> <div>100°</div> <div>Light setting memory</div>	<div>Light angle</div> <div>110°</div>	<div>Light angle/flexibility</div> <div>100°</div> <div>270° rotatable</div>	<div>Light angle</div> <div>110°</div>
<div>Special features</div> <div>Zoom light</div> <div>Motion detection</div>	<div>Special features</div> <div>Zoom light</div> <div>Motion detection</div>	<div>Special light features</div> <div>Zoom light</div> <div>Compact design</div>	<div>Special light features</div> <div>25 cm flexible hose, rotatable in all directions</div>	<div>Special light features</div> <div>180° foldable</div>	
<div>Fixture</div> <div>180° rotatable handle</div> <div>Magnetic handle</div>	<div>Fixture</div> <div>180° rotatable handle</div> <div>Magnetic handle</div>	<div>Fixture</div> <div>180° rotatable handle</div> <div>Magnetic handle</div>	<div>Fixture</div> <div>360° rotatable hook</div> <div>1 magnet</div>	<div>Fixture</div> <div>360° rotatable hook</div> <div>1 magnet</div>	<div>Fixture</div> <div>360° rotatable hook</div> <div>1 magnet</div>
<div>Grip/grease resistance</div> <div>ABS*</div> <div>Garage proof</div>	<div>Grip/grease resistance</div> <div>ABS*</div> <div>Garage proof</div>	<div>Grip/grease resistance</div> <div>ABS*</div> <div>Garage proof</div>	<div>Grip/grease resistance</div> <div>ABS*, Rubber</div> <div>Garage proof</div>	<div>Grip/grease resistance</div> <div>ABS*, Rubber</div> <div>Garage proof</div>	<div>Grip/grease resistance</div> <div>ABS*</div> <div>Garage proof</div>
<div>Robustness</div> <div>IP55</div> <div>IK07</div>	<div>Robustness</div> <div>IP65</div> <div>IK07</div>	<div>Robustness</div> <div>IP65</div> <div>IK07</div>	<div>Robustness</div> <div>IP65</div> <div>IK07</div>	<div>Robustness</div> <div>IP54</div> <div>IK07</div>	<div>Robustness</div> <div>IP65</div> <div>IK07</div>
<div>Lithium battery power supply</div> <div><5 h</div> <div>USB Type-C</div>	<div>Lithium battery power supply</div> <div><5 h</div> <div>USB Type-C</div>	<div>Lithium battery power supply</div> <div><3.5 h</div> <div>USB Type-C</div>	<div>Lithium battery power supply</div> <div><3.5 h</div> <div>USB Type-C</div>	<div>Lithium battery power supply</div> <div><4 h</div> <div>USB Type-C</div>	<div>Lithium battery power supply</div> <div><3.5 h</div> <div>USB Type-C</div>
<div>Charging features</div> <div>Multi Dock Station**</div> <div>USB power bank</div>	<div>Charging features</div> <div>Multi Dock Station**</div> <div>USB power bank</div>	<div>Additional accessories</div> <div>Find My Device**</div> <div>Multi Dock Station**</div>	<div>Additional accessories</div> <div>Multi Dock Station**</div>	<div>Additional accessories</div> <div>Find My Device**</div> <div>Multi Dock Station**</div>	
<div>Philips Order Entry</div> <div>X60FLAUX1</div>	<div>Philips Order Entry</div> <div>X60FLX1</div>	<div>Philips Order Entry</div> <div>X60FLMIX1</div>	<div>Philips Order Entry</div> <div>X60POCKX1</div>	<div>Philips Order Entry</div> <div>X60SLIMX1</div>	<div>Philips Order Entry</div> <div>X60LINEX1</div>

Xperion 6000 UV Pillar

Advanced lighting performance that lasts

Our premium work light, the Philips Xperion 6000 UV Pillar, is a multi-purpose work light with several powerful light sources, UV light, high CRI and long-lasting battery. Locate your work light in seconds with the Find My Device function.



Premium LED light with multiple outputs

500 lm
250 lm
180 lm

Precision light with ergonomic design and wide beam angle

90°
100°

High CRI 95 and unique UV light

95 CRI
UV



3 year warranty**

Strong magnet and 360° rotatable hook

360°
Magnet

Compatible with the Find My Device accessory (included) and the Multi Dock Station*

Find My Device
Multi Dock Station

Resistant to impacts, water and solvents

IP65
IK07

*Accessories to buy separately
**To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 UV Pillar X60UVPI	8719018014719	8719018014726	01471931	X60UVPIX1	6

Xperion 6000 Pillar

Work all day on a single charge

The Philips Xperion 6000 Pillar LED work light lasts all day on a single charge. Its bright 250 and 500 lm main light and inbuilt 180 lm spotlight will meet multiple needs. Foldable for easy carrying and adjustable lighting angles.



Premium LED light with multiple outputs

500 lm
250 lm
180 lm

Precision light with ergonomic design and wide beam angle

90°
100°

Long operating time in different light modes

<12 h



3 year warranty**

Strong magnet and 360° rotatable hook

360°
Magnet

Compatible with the Find My Device accessory and the Multi Dock Station*

Find My Device
Multi Dock Station

Resistant to impacts, water and solvents

IP65
IK07

*Accessories to buy separately
**To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Pillar X60PILL	8719018014696	8719018014702	01469631	X60PILLX1	6



Xperion 6000 Flood Audio

Audio LED projector light

With its 1000-lm flood light, 250-lm spot and variable beam, the Philips Xperion 6000 Flood audio-enabled projector gets the job done. The smart-zoom knob and motion sensor simplify control, while Bluetooth speakers are music to the ears.



3 year warranty*



*To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Flood Audio X60FLAU	8719018019110	8719018019127	01911031	X60FLAUX1	6




Xperion 6000 Flood

Multipurpose LED projector light

With its 1000-lm flood light and variable beam, the Philips Xperion 6000 Flood multipurpose projector gets the job done. The smart-zoom knob and motion sensor simplify control, while resistance to impacts and water guarantees durability.



3 year warranty*



*To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Flood X60FL	8719018019097	8719018019103	01909731	X60FLX1	6

Xperion 6000 Flood Mini

Compact LED projector light

With its 500-lm flood light and variable beam, the Philips Xperion 6000 Flood compact projector gets the job done. The smart-zoom knob simplifies control, while resistance to impacts and water guarantees durability.



Premium LED light with multiple outputs

Versatile attachments with integrated magnets

Compact and light to follow you everywhere

Glove proof smart-zoom knob for easy light control

Fully charged within 3.5 hours via USB-C and battery life indicator

Resistant to impacts, water and solvents

*To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Flood X60FLMI	8719018019134	8719018019141	01913431	X60FLMIX1	6

Xperion 6000 Pocket

The compact but powerful light

The compact, powerful Philips Xperion 6000 Pocket is perfect for confined spaces with an ultra-flexible 100 lm, 25 cm hose spotlight. Its wide-beam light up to 300 lm in Boost mode gives you the bright light you need.



Premium LED light with multiple outputs

Precision light with flexible hose spot and wide beam angle

Long operating time in different light modes

3 year warranty**

Strong magnet and 360° rotatable hook

Compatible with the Multi Dock Station*

Resistant to impacts, water and solvents

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Pocket X60POCK	8719018014658	8719018014665	01465831	X60POCKX1	6

Xperion 6000 Slim

Perfect for narrow spaces

The versatile Philips Xperion 6000 Slim is ideal for narrow spaces. Featuring 250 lm in Eco and 500 lm in Boost mode, its unique 270° rotating light module helps you direct the powerful beam where you need it.



Premium LED light with multiple outputs

500 lm
250 lm
150 lm

Unique 270° rotating light module and wide beam angle

270°
100°

Long operating time in different light modes

<9 h

3 year warranty**

Strong magnet and 360° rotatable hook

360°

Compatible with the Find My Device accessory and the Multi Dock Station*

Find My Device
Multi Dock Station

Resistant to impacts, water and solvents

IP54
IK07

*Accessories to buy separately
**To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Slim X60SLIM	8719018014672	8719018014689	01467231	X60SLIMX1	6

Xperion 6000 Line

Work on larger areas

Designed with a 110° broad beam of 150 lm in Eco and 300 lm in Boost mode, the Philips Xperion 6000 Line is ideal for lighting up larger areas. It is equipped with a 120 lm spotlight beam to direct the light where it is needed.



Premium LED light with multiple outputs

300 lm
150 lm
120 lm

Precision light with ergonomic design and wide beam angle

110°

Long operating time in different light modes

<9 h

3 year warranty*

Strong magnet and 360° rotatable hook

360°

Fully charged within 3,5 hours via USB-C

<3,5 h
USB-C

Resistant to impacts, water and solvents

IP65
IK07

*To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Line X60LINE	8719018014733	8719018014740	01473331	X60LINEX1	6

Multi Dock Station

Docking station for charging multiple devices

The Philips Multi Dock Station is a cordless accessory for the Xperion LED work lights. Placed on a table, it can cordlessly charge two devices at a time or simply act as a storage point.

- LED indicator to show charging status
- Dedicated space for the Find My Device remote control
- Compatible with Philips Xperion 6000 UV Pillar, Pillar, Pocket, Slim, Flood Audio, Flood and Flood Mini



Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Multi Dock Station ACCMUDO	8719018014757	8719018014764	01475731	ACCMUDOX1	6

Find My Device

A handy way to find misplaced devices


With the Philips Find My Device accessory, you can use the remote control to trigger an audible buzzer and a flashing light, to find lost Philips Xperion 6000 devices. It works up to 10 meters.

- Insert the plug-and-play chip into the work light's body
- Use remote control to locate your misplaced Philips Xperion 6000 UV Pillar (included), Pillar, Slim or Flood Mini (to buy separately)
- Carry the remote control on your keychain or place it on the Philips Multi Dock Station






















Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Find My Device ACCFIMD	8719018014771	8719018014788	01477131	ACCFIMDX1	6




















EcoPro LED work lights

Versatile and powerful
LED work lights for every day use

EcoPro61 Slim		
		
		
Boost light	 500 lm	 Up to 2.2 h
Eco light	 250/50 lm	 Up to 5/20 h
Spotlight	 140 lm	 Up to 8 h
Flexibility	 90°	 270° rotatable
Special features	 180° foldable	
Fixture	 360° rotatable hook	 1 magnet
Grip/grease resistance	 PC, TPE	 Garage proof
Robustness	 IP20	 IK07
Lithium battery power supply	 3.2 h	 Micro USB



















Philips Order Entry

RC620X1

EcoPro50		
		
		
Boost light	 1000 lm	 Up to 3 h
Eco light	 500 lm	 Up to 6 h
Light angle/ flexibility	 110°	 180° pivoting handle
Special features	 USB power bank	
Fixture	 Magnet*	
Grip/grease resistance	 Aluminium, PC for lens, PTU	 Garage proof
Robustness	 IP54	 IK08
Lithium battery power supply	 <5 h	 Micro USB
Additional accessory	 *Magnetic mounting accessory	
















Philips Order Entry

RC520C1

EcoPro40		
		
		
Boost light	 300 lm	 Up to 3 h
Eco light	 180 lm	 Up to 8 h
Spotlight	 100 lm	 Up to 8 h
Light angle/ flexibility	 90°	 180° pivoting base
Fixture	 360° rotatable hook	 3 magnets
Grip/grease resistance	 ABS**, Rubber	 Garage proof
Robustness	 IP20	 IK07
Lithium battery power supply	 <4 h	 Micro USB















Philips Order Entry

RC420B1

EcoPro30		
		
		
Boost light	 300 lm	 Up to 4 h
Eco light	 150 lm	 Up to 8 h
Light angle/ flexibility	 120°	
Fixture	 360° rotatable hook	 1 magnet
Grip/grease resistance	 ABS**, Rubber	 Garage proof
Robustness	 IP54	 IK07
Lithium battery power supply	 <3 h	 Micro USB











Philips Order Entry

RC220X1

EcoPro20		
		
		
Boost light	 220 lm	 Up to 3.5 h
Light angle/ flexibility	 90°	 180° pivoting base
Fixture	 360° rotatable hook	 1 magnet
Grip/grease resistance	 ABS**, Rubber	 Garage proof
Robustness	 IP20	 IK07
Lithium battery power supply	 <3 h	 Micro USB

Philips Order Entry

RC320B1

EcoPro10		
		
		
Boost light	 90 lm	 Up to 6.5 h
Spotlight	 10 lm	
Light angle/ flexibility	 35 – 44°	
Fixture	 Clip	
Robustness	 IP20	 IK07
AAA battery power supply	 3x Philips AAA included	


Philips Order Entry

RC120B1 | RC120X1

EcoPro61 Slim

Slim and foldable hand lamp


- **Ultra-slim design:** to light up narrow spaces
- **3 light modes:** 500, 250 and 50 lm
- **Very long autonomy:** up to 20 hours in Eco mode
- **Versatile and easy to use:** 360° retractable hook
- **High-precision spotlight:** 140 lm



EcoPro50

Aluminum portable projector

- **Powerful LED light:** up to 1,000 lm
- **Powerful bright white light:** 6500 K
- **Long autonomy:** up to 6 hours with battery life indicator
- **Strong impact (IK08) and water resistance (IP54)**
- **Versatile and easy to use:** strong magnetic mounting accessory
- **Power bank:** to charge other devices



Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
EcoPro 61 Slim RC620	8719018004840	8719018004857	00484031	RC620X1	6

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
EcoPro 50 RC520	8719018050717	8719018050724	05071745	RC520C1	6

EcoPro40

Rechargeable hand lamp

- **Bright LED light:** up to 300 lm (Boost mode)
- **Strong bright light:** 6500 K
- **Enhanced autonomy:** up to 8 hours
- **Handy work light:** non-slip grip and lightweight
- **Versatile for hands-free use:** strong magnets and 360° retractable hooks



Premium LED light with multiple outputs

300 lm
180 lm
100 lm

Precision light with ergonomic design and wide beam angle

180°
90°

Long operating time in different light modes

<8 h



Strong magnet and 360° rotatable hook

Magnet icon
Hook icon

Fully charged within 4 hours via micro USB

<4 h

Resistant to impacts, water and solvents

IP20
IK07

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
EcoPro 40 RC420	8719018050571	8719018050700	05057145	RC420B1	6

EcoPro30

Rechargeable slim lamp

- **Dual-mode light:** 150 and 300 lm
- **Bright natural light:** 6000 K
- **Rechargeable long-life battery:** high-energy Li-ion battery
- **Versatile for hands-free use:** large 120° beam angle, 360° rotatable hook, strong magnet
- **Enhanced autonomy:** up to 8 hours, rechargeable via micro USB
- **Strong impact (IK07) and water resistance (IP54)**



Premium LED light with multiple outputs

300 lm
150 lm

Precision light with ergonomic design and wide beam angle

Long operating time in different light modes

<8 h



Strong magnet and 360° rotatable hook

Magnet icon
Hook icon

Fully charged within 3 hours via micro USB

<3 h

Resistant to impacts, water and solvents

IP54
IK07


Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
EcoPro 30 RC220	8719018017697	8719018017703	01769731	RC220X1	6

EcoPro20

Convenient pocket lamp

- **LED light:** up to 220 lm
- **Bright comfortable light:** 6500 K
- **Good autonomy:** up to 3.5 hours
- **Versatile pocket lamp:** magnetic 180° pivoting base and 360° retractable hook
- **Power bank:** to charge other devices




Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
EcoPro 20 RC320	8719018050557	8719018050564	05055745	RC320B1	6

EcoPro10

Portable inspection tool

- **Ultra-compact design:** lightweight (less than 100 g) for everyday use
- **High-quality light:** equipped with 5 durables LEDs
- **Bright natural light:** 6000 K
- **Long autonomy:** up to 10 hours
- **Versatile pocket lamp:** spotlight, clip



Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
EcoPro 10 RC120 B1	8719018017659	8719018017666	01765940	RC120B1	6
EcoPro 10 RC120 X1	8719018017673	8719018017680	01767330	RC120X1	6



