

# Welche LED-Beleuchtung für welche Funktion?



Frontscheinwerfer	Nebelscheinwerfer	Parkleuchten vorne	Blinkerleuchten vorne	Armaturenbekleuchtung	Innenraumbeleuchtung	Handschuhfachbeleuchtung	Parkleuchten hinten	Blinkerleuchten hinten	Nebelschlussleuchten	Kofferraumbeleuchtung	Kennzeichenbeleuchtung	Drittes Bremslicht	Bremsleuchten	Rückfahrleuchten



### Ultinon Pro9000 HL

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

### X-tremeUltinon LED

SL-WHITE [≈W5W]	SL-AMBER [≈PY21W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	SL-RED [≈P21/5W]	SL-AMBER [≈PY21W]	SL-RED [≈P21W]	IL/SL-WHITE [≈W5W]	SL-WHITE [≈W5W]	SL-RED [≈P21W]	SL-RED [≈P21W], [≈P21/5W]	SL-RED [≈P21W]	SL-WHITE [≈P21W]
SL-WHITE [≈W21/5W]	SL-AMBER [≈WY21W]	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21/5W]	SL-AMBER [≈WY21W]	SL-RED [≈W21W]	SL-WHITE Fest 30/38/43 mm	SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21W]	SL-RED [≈W21W], [≈W21/5W]	SL-RED [≈W21W]	SL-WHITE [≈W21W]



### Ultinon Pro5000 HL

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

### Ultinon LED

SL-WHITE [≈W5W]	SL-AMBER [≈PY21W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	SL-RED [≈P21/5W]	SL-AMBER [≈PY21W]	SL-RED [≈P21W]	IL/SL-WHITE [≈W5W]	SL-WHITE [≈W5W]	SL-RED [≈P21W]	SL-RED [≈P21W], [≈P21/5W]	SL-RED [≈P21W]	SL-WHITE [≈P21W]
SL-WHITE [≈W21/5W]	SL-AMBER [≈WY21W]	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21/5W]	SL-AMBER [≈WY21W]	SL-RED [≈W21W]	SL-WHITE Fest 30/38/43 mm	SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21W]	SL-RED [≈W21W], [≈W21/5W]	SL-RED [≈W21W]	SL-WHITE [≈W21W]



### Ultinon Essential HL

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

### Ultinon Pro3000 SL

SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	SL-RED [≈P21/5W]	SL-RED [≈P21W]	IL/SL-WHITE [≈W5W]	SL-WHITE [≈W5W]	SL-RED [≈P21W]	SL-RED [≈P21W], [≈P21/5W]	SL-RED [≈P21W]	SL-WHITE [≈P21W]
SL-WHITE [≈W21/5W]	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21/5W]	SL-RED [≈W21W]	SL-WHITE Fest 30/38/43 mm	SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21W]	SL-RED [≈W21W], [≈W21/5W]	SL-RED [≈W21W]	SL-WHITE [≈W21W]



### LED-Adapter

CANbus adapter HL [≈H4], [≈H7]	Light Repair HL [≈H1], [≈H7]	CANbus adapter FL [≈H8/H11/H16]

### LED-Adapter

CANbus adapter SL [≈5W]	Smart CANbus SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	Smart CANbus SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]

\*21W LED CANbus-Adapter im Lieferumfang enthalten