


**PHILIPS**

LED  
integral beam


See farther down the road with  
**Philips LED integral beam.**

### Powerful cool white light

- Universal LED replacement upgrade for vehicles with H6024, H6054, H4651, H4656 applications
- More durable than a conventional sealed beam, with increased lifetime
- Wider versatility – compatible with 12V and 24V systems
- High tech look – brighter and whiter than conventional halogen lighting
- DOT compliant



See farther down the road with **Philips LED integral beam**.




Up to  
**6000K**  
cool white  
light

*Images for illustration purposes only.*

## State-of-the-art LED technology

- Easy installation – plug and play replacement for halogen and incandescent sealed beams
- Up to 6000K powerful cool white light
- Sharp cut-off point for legal beam on the road
- Safe beam performance – no glare
- 12/24V compatibility
- Available for 7" round, 5"x7" and 4"x6" rectangular sealed beam applications
- Philips LED integral beam headlights can be used for H6024, H6054, H4651, H4656



**Lumileds**  
34119 W. Twelve Mile Road, Suite 102  
Farmington Hills, MI 48331  
**Phone: 800-257-6054**  
[www.philips.com/automotive](http://www.philips.com/automotive)



For more information, please contact your Lumileds sales account manager or customer service at:  
**866-254-6989** | [philipsautoorders@lumileds.com](mailto:philipsautoorders@lumileds.com)

2020 © Lumileds Holding B.V. All rights reserved.  
The Philips trademark and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V.