

PHILIPS

Xperion


Professional work lights



2024
Designed
with **you**
in mind


LED work light features

Light module




Boost light

Maximum light output (in lumen)




Eco/dimmed light

Light output during power save mode (in lumen)




Spotlight

Additional small light to reach confined spaces (in lumen)




Operating time

Operating time during one charging cycle




Beam angle

Angle of the main light beam




Pivoting light module

Flexibility of the work light thanks to pivoting light module




CRI

High Color Rendering Index (CRI) reveals the true colors of an object, as if seen with natural light



UV light


UV light helps identify leakages



Zoom light


Change the focus of the light beam by simply turning a knob

Smart, ergonomic design




Grip

Robust ABS* and soft rubber body to hold the work light securely




Telescopic mount

Integrated telescopic hooks extendable on both sides




Motion detector

Switch the light on and off by moving your hand in front of the sensor




Find My Device

The remote control accessory helps retrieve lost devices up to 10 meters



Sliding light

Slide the light module along the mount to the area you want to illuminate



Presence sensor

Presence sensor that senses human activity within a 2.5-meter radius

Robustness and durability



Ingress protection

Degree of protection against intrusion from solid objects, dust, accidental contact and water



Shock protection


Degree of protection against external impacts



Grease resistance


Highly resistant to grease and workshop solvents

Power options and recharging




Charging time

Time needed to fully recharge the integrated battery



Micro USB


Battery rechargeable via a USB Type-C or Micro USB



Charging station

Compatibility with the Multi Dock Station** accessory for cordless charging




























































*Acrylonitrile-butadiene-styrene copolymer
**Accessories to buy separately






















Xperion 6000




















Discover our **Xperion 6000** LED work lights



UV Pillar	Pillar	Line
		
		
<div>Boost light</div> <div></div> <div>500 lmUp to 4.5 h</div>	<div>Boost light</div> <div></div> <div>500 lmUp to 4.5 h</div>	<div>Boost light</div> <div></div> <div>300 lmUp to 4.5 h</div>
<div>Eco light</div> <div></div> <div>250 lmUp to 10 h</div>	<div>Eco light</div> <div></div> <div>250 lmUp to 10 h</div>	<div>Eco light</div> <div></div> <div>150 lmUp to 8 h</div>
<div>Spotlight</div> <div></div> <div>180 lmUp to 12 h</div>	<div>Spotlight</div> <div></div> <div>180 lmUp to 12 h</div>	<div>Spotlight</div> <div></div> <div>120 lmUp to 9 h</div>
<div>Light angle/ flexibility</div> <div></div> <div>100°90° rotatable</div>	<div>Light angle/ flexibility</div> <div></div> <div>100°90° rotatable</div>	<div>Light angle</div> <div></div> <div>110°</div>
<div>Special light features</div> <div></div> <div>UV lightExcellent color rendition</div>	<div>Special light features</div> <div></div> <div></div>	<div>Special light features</div> <div></div> <div></div>
<div>Fixture</div> <div></div> <div>360° rotatable hook1 magnet</div>	<div>Fixture</div> <div></div> <div>360° rotatable hook1 magnet</div>	<div>Fixture</div> <div></div> <div>360° rotatable hook1 magnet</div>
<div>Grip/grease resistance</div> <div></div> <div>ABS*, RubberGarage proof</div>	<div>Grip/grease resistance</div> <div></div> <div>ABS*Garage proof</div>	<div>Grip/grease resistance</div> <div></div> <div>ABS*Garage proof</div>
<div>Robustness</div> <div></div> <div>IP65IK07</div>	<div>Robustness</div> <div></div> <div>IP65IK07</div>	<div>Robustness</div> <div></div> <div>IP65IK07</div>
<div>Lithium battery power supply</div> <div></div> <div><4.5 hUSB Type-C</div>	<div>Lithium battery power supply</div> <div></div> <div><4.5 hUSB Type-C</div>	<div>Lithium battery power supply</div> <div></div> <div><3.5 hUSB Type-C</div>
<div>Additional accessories</div> <div></div> <div>Find My DeviceMulti Dock Station**</div>	<div>Additional accessories</div> <div></div> <div>Find My DeviceMulti Dock Station**</div>	<div>Additional accessories</div> <div></div> <div></div>
<div>Philips Order Entry</div> <div>X60UVPIX1</div>	<div>Philips Order Entry</div> <div>X60PILLX1</div>	<div>Philips Order Entry</div> <div>X60LINEX1</div>

* Acrylonitrile-butadiene-styrene copolymer
** Accessories to buy separately, except for the Philips Xperion 6000 UV Pillar which already includes the Find My Device function

Slim		
		
		
Boost light	 500 lm	 Up to 4.5 h
Eco light	 250 lm	 Up to 7 h
Spotlight	 150 lm	 Up to 9 h
Light angle/ flexibility	 100°	 270° rotatable
Special light features	 180° foldable	
Fixture	 360° rotatable hook	 1 magnet
Grip/grease resistance	 ABS*, Rubber	 Garage proof
Robustness	 IP54	 IK07
Lithium battery power supply	 <4 h	 USB Type-C
Additional accessories	 Find My Device**	 Multi Dock Station**

Pocket		
		
		
Boost light	 300 lm	 Up to 3.5 h
Eco light	 150 lm	 Up to 7 h
Spotlight	 100 lm	 Up to 10 h
Light angle	 110°	
Special light features	 25 cm flexible hose, rotatable in all directions	
Fixture	 360° rotatable hook	 1 magnet
Grip/grease resistance	 ABS*, Rubber	 Garage proof
Robustness	 IP65	 IK07
Lithium battery power supply	 <3.5 h	 USB Type-C
Additional accessories	 Multi Dock Station**	

Penlight		
Boost light	200 lm	Up to 3 h
Eco light	100 lm	Up to 5.5 h
Spotlight	120 lm	Up to 3.5 h
Light angle	80°	
Special features	Rotating magnetic clip	
Fixture	2 magnets	
Grip/grease resistance	ABS*	Garage proof
Robustness	IP65	IK07
Lithium battery power supply	<1.6 h	USB Type-C
Philips Order Entry		
X60PENX1		

Flood Audio		
Boost light	1000 lm	Up to 3 h
Eco light	100 lm	Up to 22 h
Spotlight	250 lm	Up to 9 h
Light angle/ light function	100°	Light setting memory
Special features	Zoom light	Motion detection
Fixture	180° rotatable handle	Magnetic handle
Grip/grease resistance	ABS*	Garage proof
Robustness	IP55	IK07
Lithium battery power supply	<5 h	USB Type-C
Charging features	Multi Dock Station**	USB power bank
Philips Order Entry		
X60FLAUX1		

Flood		
Boost light	1000 lm	Up to 3 h
Eco light	100 lm	Up to 22 h
Spotlight	250 lm	Up to 9 h
Light angle/ light function	100°	Light setting memory
Special features	Zoom light	Motion detection
Fixture	180° rotatable handle	Magnetic handle
Grip/grease resistance	ABS*	Garage proof
Robustness	IP65	IK07
Lithium battery power supply	<5 h	USB Type-C
Charging features	Multi Dock Station**	USB power bank
Philips Order Entry		
X60FLX1		

Flood Mini		
Boost light	500 lm	Up to 3 h
Eco light	100 lm	Up to 9 h
Spotlight	250 lm	Up to 5 h
Light angle/ light function	100°	Light setting memory
Special light features	Zoom light	Compact design
Fixture	180° rotatable handle	Magnetic handle
Grip/grease resistance	ABS*	Garage proof
Robustness	IP65	IK07
Lithium battery power supply	<3.5 h	USB Type-C
Additional accessories	Find My Device**	Multi Dock Station**
Philips Order Entry		
X60FLMX1		

Headlight		
Boost light	300 lm	Up to 2.5 h
Eco light	150 lm	Up to 4 h
Spotlight	120 lm	Up to 4.5 h
Light angle/ flexibility	220° panoramic	60° rotatable
Special features	Motion detection	
Fixture	Adjustable headband	
Grip/grease resistance	Garage proof	
Robustness	IP65	IK07
Lithium battery power supply	<2.5 h	USB Type-C

Philips Order Entry
X60HEADX1

Under-bonnet light		
Boost light	1200 lm	Up to 3 h
Eco light	120 lm	Up to 20 h
Light angle/ feature	110°	5800 K
Special features	Presence sensor	Sliding light
Fixture	Extendable 1.1-2.1 m	360° rotatable hook
Grip/grease resistance	Rubber	Garage proof
Robustness	IP54	IK07
Lithium battery power supply	<3.5 h	USB Type-C

Philips Order Entry
X60BONNX1

Hybrid foldable Under-bonnet light		
Boost light mains powered	2400 lm	Dimming 300-2400 lm
Boost light battery powered	1400 lm	Up to 3 h
Eco light battery powered	300 lm	Up to 12 h
Light angle/ Light color	110°	6500 K
Special features	Mains and battery	Foldable
Fixture	Extendable 1.1 – 2.1 m	360° rotatable hook
Grip/grease resistance	Rubber	Garage proof
Robustness	IP54	IK07
Lithium battery power supply	<2.5 h	5-meter cable

Philips Order Entry
X61BONNX1

Xperion 6100 Under-bonnet light

Foldable and powerful LED light

Mains- or battery-powered, the Philips Xperion 6100 Under-bonnet LED light offers a seamlessly dimmable beam of up to 2100 lumens, and a telescopic mount, ideal for working on cars, vans and trucks.

3 year warranty*

Powerful, premium light dimming with multiple light outputs

Integrated telescopic hooks extendable on both sides

Foldable for easy storage

Hybrid, with a 5-meter robust cable

Battery life indicator Fully charged within 2.5 hours

360° rotatable hooks covered with soft rubber

Resistant to impacts, water and solvents

New

*To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6100 Under-bonnet light X61BONN	8719018027368	8719018027375	02736831	X61BONNX1	6

Xperion 6000 UV Pillar

Advanced lighting performance that lasts

Our premium work light, the Philips Xperion 6000 UV Pillar, is a multi-purpose work light with several powerful light sources, UV light, high CRI and long-lasting battery. Locate your work light in seconds with the Find My Device function.



Premium LED light with multiple outputs

500 lm
250 lm
180 lm

Precision light with ergonomic design and wide beam angle

90°
100°

High CRI 95 and unique UV light

95 CRI
UV

3 year warranty**

Strong magnet and 360° rotatable hook

360°

Compatible with the Find My Device accessory (included) and the Multi Dock Station*

Find My Device
Multi Dock Station

Resistant to impacts, water and solvents

IP65
IK07

*Accessories to buy separately
**To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 UV Pillar X60UVPI	8719018014719	8719018014726	01471931	X60UVPIX1	6

Xperion 6000 Pillar

Work all day on a single charge

The Philips Xperion 6000 Pillar LED work light lasts all day on a single charge. Its bright 250 and 500 lm main light and inbuilt 180 lm spotlight will meet multiple needs. Foldable for easy carrying and adjustable lighting angles.



Premium LED light with multiple outputs

500 lm
250 lm
180 lm

Precision light with ergonomic design and wide beam angle

90°
100°

Long operating time in different light modes

<12 h

3 year warranty**

Strong magnet and 360° rotatable hook

360°

Compatible with the Find My Device accessory and the Multi Dock Station*

Find My Device
Multi Dock Station

Resistant to impacts, water and solvents

IP65
IK07

*Accessories to buy separately
**To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Pillar X60PILL	8719018014696	8719018014702	01469631	X60PILLX1	6

Xperion 6000 Line

Work on larger areas

Designed with a 110° broad beam of 150 lm in Eco and 300 lm in Boost mode, the Philips Xperion 6000 Line is ideal for lighting up larger areas. It is equipped with a 120 lm spotlight beam to direct the light where it is needed.



Premium LED light with multiple outputs

300 lm
150 lm
120 lm

Precision light with ergonomic design and wide beam angle

110°

Long operating time in different light modes

<9 h

3 year warranty*

Strong magnet and 360° rotatable hook

Fully charged within 3,5 hours via USB-C

<3,5 h

Resistant to impacts, water and solvents

IP65
IK07

*To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Line X60LINE	8719018014733	8719018014740	01473331	X60LINEX1	6

Xperion 6000 Slim

Perfect for narrow spaces

The versatile Philips Xperion 6000 Slim is ideal for narrow spaces. Featuring 250 lm in Eco and 500 lm in Boost mode, its unique 270° rotating light module helps you direct the powerful beam where you need it.



Premium LED light with multiple outputs

500 lm
250 lm
150 lm

Unique 270° rotating light module and wide beam angle

270°
100°

Long operating time in different light modes

<9 h

3 year warranty**

Strong magnet and 360° rotatable hook

Compatible with the Find My Device accessory and the Multi Dock Station*

Resistant to impacts, water and solvents

IP54
IK07

*Accessories to buy separately
**To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Slim X60SLIM	8719018014672	8719018014689	01467231	X60SLIMX1	6

Xperion 6000 Pocket

The compact but powerful light

The compact, powerful Philips Xperion 6000 Pocket is perfect for confined spaces with an ultra-flexible 100 lm, 25 cm hose spotlight. Its wide-beam light up to 300 lm in Boost mode gives you the bright light you need.

Premium LED light with multiple outputs



300 lm

150 lm

100 lm

Precision light with flexible hose spot and wide beam angle



110°

Long operating time in different light modes




<10 h



3 year warranty**



Strong magnet and 360° rotatable hook



Compatible with the Multi Dock Station*



Resistant to impacts, water and solvents



IP65

IK07

*To be claimed on Philips.com/LEDworklights-warranty

Ordering information


Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Pocket X60POCK	8719018014658	8719018014665	01465831	X60POCKX1	6

Xperion 6000 Penlight

Compact LED worker’s companion

Designed with a broad beam of 200 lumens, the compact, ergonomic Philips Xperion 6000 Penlight is ideal for all inspection work. Our Penlight is equipped with a 120-lm pointer to direct the light where needed.

Multiple LED light modes



200 lm

100 lm

120 lm

Fully charged within 1.6 hours, via USB-C and battery life indicator



<1.6 h


USB-C



3 year warranty*



Smart rotatable clip, strong magnets and ergonomic body



Resistant to impacts, water and solvents



IP65

IK07

*To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Penlight X60PEN	8719018021694	8719018021700	02169431	X60PENX1	6



Xperion 6000 Flood Audio

Audio LED projector light

With its 1000-lm flood light, 250-lm spot and variable beam, the Philips Xperion 6000 Flood audio-enabled projector gets the job done. The smart-zoom knob and motion sensor simplify control, while Bluetooth speakers are music to the ears.



3 year warranty*



*To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Flood Audio X60FLAU	8719018019110	8719018019127	01911031	X60FLAUX1	6




Xperion 6000 Flood

Multipurpose LED projector light

With its 1000-lm flood light and variable beam, the Philips Xperion 6000 Flood multipurpose projector gets the job done. The smart-zoom knob and motion sensor simplify control, while resistance to impacts and water guarantees durability.



3 year warranty*



*To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Flood X60FL	8719018019097	8719018019103	01909731	X60FLX1	6

Xperion 6000 Flood Mini

Compact LED projector light

With its 500-lm flood light and variable beam, the Philips Xperion 6000 Flood compact projector gets the job done. The smart-zoom knob simplifies control, while resistance to impacts and water guarantees durability.



3 year warranty*

Premium LED light with multiple outputs

100 lm

500 lm

250 lm

Versatile attachments with integrated magnets

Fully charged within 3.5 hours via USB-C and battery life indicator

<3.5 h

Compact and light to follow you everywhere

Glove proof smart-zoom knob for easy light control

Resistant to impacts, water and solvents

*To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Flood X60FLMI	8719018019134	8719018019141	01913431	X60FLMIX1	6

Xperion 6000 Headlight

Dual-mode, motion-sensing LED light

The Philips Xperion 6000 Headlight projects a 300-lumen panoramic light beam in front of you. Its rotating 120-lumen spotlight allows you to see every detail. An additional motion-detection function makes it a versatile, hands-free tool.



3 year warranty*

Premium LED light with multiple outputs

300 lm

150 lm

120 lm

220° panoramic LED light beam

220°

Motion-detection mode for hands-free use

Anti-slip elastic headband. Comfortable and easy to adjust

Fully charged within 2.5 hours, via USB-C and battery life indicator

<2.5 h

Resistant to impacts, water and solvents

*To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Headlight X60HEAD	8719018021731	8719018021748	02173131	X60HEADX1	6



Xperion 6000 Under-bonnet light

Extendable, powerful LED light

The Philips Xperion 6000 Under-bonnet LED light offers a seamlessly dimmable beam of up to 1200 lumens, 360° rotatability, and a telescopic mount extending up to 2.08 meters. It is for working on cars, vans, and trucks.



3 year warranty*

Seamless, premium light dimming with multiple outputs



Telescopic, extendable mount up to 2.08 meters



Sliding light module along the mount



Presence sensor of human activity within a 2.5-meter radius



360° rotatable hooks covered with soft rubber



Fully charged within 3.5 hours, via USB-C and battery life indicator



Resistant to impacts, water and solvents



*To be claimed on Philips.com/LEDworklights-warranty

Ordering information


Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Under-bonnet light X60BONN	8719018021717	8719018021724	02171731	X60BONNX1	6

Multi Dock Station

Docking station for charging multiple devices

The Philips Multi Dock Station is a cordless accessory for the Xperion LED work lights. Placed on a table, it can cordlessly charge two devices at a time or simply act as a storage point.

- LED indicator to show charging status
- Dedicated space for the Find My Device remote control
- Compatible with Philips Xperion 6000 UV Pillar, Pillar, Pocket, Slim, Flood Audio, Flood and Flood Mini.



Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Multi Dock Station ACCMUDO	8719018014757	8719018014764	01475731	ACCMUDOX1	6

Find My Device

A handy way to find misplaced devices

With the Philips Find My Device accessory, you can use the remote control to trigger an audible buzzer and a flashing light, to find lost Philips Xperion 6000 devices. It works up to 10 meters.

- Insert the plug-and-play chip into the work light's body
- Use remote control to locate your misplaced Philips Xperion 6000 UV Pillar (included), Pillar, Slim or Flood Mini (to buy separately)
- Carry the remote control on your keychain or place it on the Philips Multi Dock Station



Ordering information


Product	EAN1	EAN3	GOC	Order Entry	MOQ
Find My Device ACCFIMD	8719018014771	8719018014788	01477131	ACCFIMDX1	6



Xperion 3000



Discover our **Xperion 3000** LED work lights



Pillar		
Boost light	500 lm	Up to 2.5 h
Eco light	200 lm	Up to 8 h
Spotlight	120 lm	Up to 8.5 h
Light angle	Main light 90°	Spot 30°
Flexibility	180° foldable stand	90° tiltable light module
Special features	x2 Dual hooks	
Fixture	360° rotatable hooks	3 magnets
Grip/grease resistance	Nylon, PC	Garage proof
Robustness	IP20	IK08
Lithium battery power supply	<3.5 h	USB type-C

Philips Order Entry
X30PILLX1

* Acrylonitrile-butadiene-styrene copolymer

Line		
Boost light	300 lm	Up to 4 h
Eco light	150 lm	Up to 7.5 h
Light angle	Main light 120°	
Fixture	360° rotatable hook	1 magnet
Grip/grease resistance	Robust ABS*	Garage proof
Robustness	IP54	IK07
Lithium battery power supply	<3 h	USB type-C

Philips Order Entry
X30LINEX1

Zoom		
Boost light	1000 lm	Up to 1.5 h
Eco light	600/200 lm	Up to 3/9 h
Spotlight	1000 lm	Up to 1.5 h
Flexibility	180° rotatable light module	
Special features	zoom Zoom 20° - 130°	
Fixture	1 magnet	
Grip/grease resistance	Nylon, Rubber	Garage proof
Robustness	IP54	IK07
Lithium battery power supply	<3.5 h	USB type-C

Philips Order Entry
X30ZOOMX1

Slim



Boost light		
500 lm	Up to 3 h	
Eco light		
200 lm	Up to 8 h	
Spotlight		
150 lm	Up to 8 h	
Light angle		
Main light 90°	Spot 30°	
Flexibility		
270° tiltable light module		
Fixture		
180° rotatable hook	1 magnet	
Grip/grease resistance		
PC, Rubber	Garage proof	
Robustness		
IP20	IK07	
Lithium battery power supply		
<3.5 h	USB type-C	

Philips Order Entry
X30SLIMX1

Pocket



Boost light		
300 lm	Up to 3 h	
Eco light		
100 lm	Up to 10 h	
Light angle		
Main light 90°		
Flexibility		
180° foldable stand		
Fixture		
360° rotatable hook	1 magnet	
Grip/grease resistance		
Nylon, PC	Garage proof	
Robustness		
IP20	IK08	
Lithium battery power supply		
<3.5 h	USB type-C	

Philips Order Entry
X30POCKX1

Penlight



Boost light		
100 lm	Up to 4 h	
Spotlight		
50 lm	Up to 6 h	
Light angle		
Main light 80°	Spot 30°	
Fixture		
Clip	1 magnet	
Grip		
Robust ABS*		
Robustness		
IP20	IK06	
Lithium battery power supply		
<2.2 h	USB type-C	

Philips Order Entry
X30PENX1


Pen eco



Boost light		
90 lm	Up to 6.5 h	
Spotlight		
10 lm	Up to 10 h	
Light angle		
Main light 40°	Spot 30°	
Fixture		
Clip		
Grip		
Robust ABS*		
Robustness		
IP20	IK07	
Power supply		
3x AAA incl.		

Philips Order Entry
X30PECOB1, X30PECOX1

Flood



Boost light		
1000 lm	Up to 3 h	
Eco light		
500 lm	Up to 6 h	
Spotlight		
300 lm	Up to 8 h	
Light angle		
Main light 110°	Spot 30°	
Flexibility		
180° foldable stand		
Special features		
Dual lights: spot + flood	Power bank function	
Fixture		
180° rotatable hook	Magnetic handle	
Grip/grease resistance		
Nylon, Rubber	Garage proof	
Robustness		
IP65	IK08	
Lithium battery power supply		
<5.5 h	USB type-C	

Philips Order Entry
X30FLX1

Flood mini



Boost light		
500 lm	Up to 3 h	
Eco light		
200 lm	Up to 8 h	
Spotlight		
300 lm	Up to 5 h	
Light angle		
Main light 110°	Spot 30°	
Flexibility		
180° foldable stand		
Special features		
Dual lights: spot + flood		
Fixture		
180° foldable stand	Magnetic handle	
Grip/grease resistance		
Nylon, Rubber	Garage proof	
Robustness		
IP65	IK08	
Lithium battery power supply		
<3.5 h	USB type-C	

Philips Order Entry
X30FLMIX1

Headlamp



Boost light		
	300 lm	Up to 2 h
Eco light		
	100 lm	Up to 6 h
Spotlight		
	200 lm	Up to 3 h
Light angle		
	Main light 120°	
Flexibility		
	60° tiltable light module	
Special features		
	Dual lights: spot + flood	
Fixture		
	Soft anti-slip band	
Grip/grease resistance		
	PC, Rubber	Garage proof
Robustness		
	IP65	IK07
Lithium battery power supply		
	<2.5 h	USB type-C

Philips Order Entry
X30HEADX1

Under-Bonnet



New





Boost light		
	1200 lm	Up to 3 h
Eco light		
	300/600 lm	Up to 12 h
Light angle		
	Main light 110°	
Flexibility		
	225° tiltable light module	
Special features		
	180° foldable	
Fixture		
	1 magnet	360° rotatable hooks
Grip/grease resistance		
	Garage proof	
Robustness		
	IP54	IK07
Lithium battery power supply		
	<4 h	USB type-C

Philips Order Entry
X30BONNX1



Xperion 3000 Under-bonnet light

Versatile, foldable LED under-bonnet light

The Philips Xperion 3000 Under-bonnet LED light offers a powerful, bright light of 1200 lumens, helping you spot even the smallest details so you can see what you need to get the job done quickly.



New



Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Under-bonnet light X30BONN	8719018025173	8719018025180	02517331	X30BONNX1	1


Xperion 3000 Pillar

Bright LED hand lamp

With its powerful bright light, non-slip grip, lightweight design and versatility, the Philips Xperion 3000 Pillar is an excellent cordless LED work lamp for everyday use. There’s even a handy spotlight to help you see in confined spaces.




Bright, comfortable work light



500 lm

200 lm

Handy spotlight



120 lm

Long operating time in different light modes



8.5 h



Three magnets and two 360° rotatable hooks for hands-free use



x2

x3

Flexible adjustment of the lighting module



90°

180°

Robust, shock-resistant housing



IP20

IK08

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Pillar X30PILL	8719018024961	8719018024978	02496131	X30PILLX1	6


Xperion 3000 Line

Cordless, slim professional LED lamp

The Philips Xperion 3000 Line LED hand light is ideal for quick inspection jobs and longer repairs. Its 120°-wide light beam eliminates shadows, while a 360° rotating hook and strong magnet allow hands-free working.



Bright, comfortable work light



300 lm


150 lm

Charged via USB-C



<3 h


Long operating time in different light modes



<7.5 h




Strong magnet and 360° rotatable hook



x2

x3

Wide beam angle



120°

Robust, shock-resistant housing



IP54

IK07

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Line X30LINE	8719018024947	8719018024954	02494731	X30LINEX1	6

Xperion 3000 Zoom

Powerful LED zoom light

With its powerful bright light and non-slip grip, the Philips Xperion 3000 Zoom is an excellent versatile LED work lamp. Its zoom lens allows you to adjust your light from wide flood to focused brightness easily.



Zoom from a 130° to a 20° light angle

Charged via USB-C and battery life indicator

Long operating time in different light modes



Powerful magnet for hands-free use

Flexible adjustment of the lighting module

Robust, shock-resistant housing

Xperion 3000 Slim

Slim, foldable LED hand light

The versatile, ultra-thin Philips Xperion 3000 Slim is ideal for lighting narrow spaces. Tackle any workshop task, from brief inspections to maintenance and repair work, for a full day without interruption.



Bright, comfortable work light

Handy spotlight

Long operating time in different light modes



Strong magnet and 360° rotatable hook

Ultra-slim, 270° pivoting design to light up narrow spaces

Robust, shock-resistant housing

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Zoom X30ZOOM	8719018025005	8719018025012	02500531	X30ZOOMX1	6

Ordering information


Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Slim X30SLIM	8719018024985	8719018024992	02498531	X30SLIMX1	6

Xperion 3000 Pocket

Small, handy LED pocket lamp

The Philips Xperion 3000 Pocket LED lamp is a small, rechargeable work light that slips easily into your pocket. It's perfect for quick inspection jobs and everyday use.

Pocket-sized, bright, comfortable work light




300 lm
 100 lm

Charged via USB-C



<3.5 h

Long operating time in different light modes



<10 h



Magnet and 360° rotatable hook for hands-free use



P
 G

Flexible adjustment of the lighting module



180°

Robust, shock-resistant housing



IP20
 IK08

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Pocket X30POCK	8719018024923	8719018024930	02492331	X30POCKX1	6

Xperion 3000 Penlight

Portable LED inspection tool


Compact and ergonomic, our Philips Xperion 3000 Penlight is ideal for quick inspection jobs. Featuring a natural white light, it illuminates what's in front of you and fits easily into narrow spaces.

Pocket-sized, bright, comfortable work light




100 lm

Handy spotlight



50 lm

Long operating time in different light modes



<6 h



Magnet and Clip for hands-free use



P
 G

Charged via USB-C



<2.2 h




Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Penlight X30PEN	8719018024886	8719018024893	02488631	X30PENX1	6

Xperion 3000 Pen eco

Compact worker’s companion

The ultra-compact Philips Xperion 3000 Pen eco is an everyday companion in your pocket.





Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Pen Eco X30PECOB1	8719018024848	8719018024855	02484840	X30PECOB1	10
Xperion 3000 Pen Eco X30PECOX1	8719018024862	8719018024879	02486230	X30PECOX1	10

Xperion 3000 Flood

Portable LED flood light

Small but powerful, versatile yet robust, the Philips Xperion 3000 Flood LED light provides the bright white light you need to illuminate large dark areas. Enjoy up to six hours of continuous use before charging the battery.



Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Flood X30FL	8719018025043	8719018025050	02504331	X30FLX1	6

Xperion 3000 Flood mini

Compact LED flood light

Compact and versatile, the Philips Xperion 3000 Flood mini rechargeable LED light provides the bright white light you need for everyday use. Enjoy up to eight hours of continuous use before charging the battery.



Bright, comfortable work light with Boost, Eco and spot settings

500 lm

200 lm

300 lm

Long operating time in different light modes

<8 h

Charged via USB-C

USB-C

<3.5 h

Tiltable magnetic handle and 360° hook for hands-free use

180°

Compact and light to follow you everywhere

Robust, shock-resistant housing

IP65

IK08

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Flood Mini X30FLMI	8719018025029	8719018025036	02502931	X30FLMIX1	6

Xperion 3000 Headlamp

Dual-mode LED headlight

The lightweight Philips Xperion 3000 Headlight provides bright white light wherever you need it. Two preset modes of up to 300 lumens and a comfortable headband make it a versatile, hands-free tool for everyday use.



Bright, comfortable work light with wide beam angle

120°

300 lm

100 lm

Handy spotlight

200 lm

Charged via USB-C

USB-C

<2.5 h

Anti-slip elastic headband. Comfortable and easy to adjust

Flexible adjustment of the lighting module

60°

Robust, shock-resistant housing

IP65

IK07

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Headlight X30HEAD	8719018024909	8719018024916	02490931	X30HEADX1	6

