



Philips Ultinon Pro6000
Boost HL
Car headlights bulb

H4-LED

Road-legal LED bulb
Quick and easy installation
Broad fleet compatibility

11342U60B2X2

Ultimate road-legal performance

Ultra-compact and highly performant

Discover the Philips Ultinon Pro6000 Boost series, the new benchmark in automotive road-legal LED bulbs. Explore the next generation of retrofit LED lighting and enter a new era where performance and light quality reach new heights.

Accredited LED range

- Accredited by automotive experts

Fits a wider range of vehicles

- Improved mechanical fit in the narrowest headlamps

Outstanding +300% brightness

- Up to 300% brighter on the road!

Exclusive Philips technology

- High-quality light improves on-road vision
- Long-term durability and warranty

Reliable Philips quality

- Trust Philips know-how

PHILIPS


Highlights

Road-legal LED bulb




The Philips Ultinon Pro6000 Boost range has been approved for road use in several European Union countries*, making it compliant with road-traffic regulations. As a result, Philips Ultinon Pro6000 Boost LED bulbs can safely replace traditional bulbs in a broad range of vehicles, from cars to two-wheelers, motorhomes, vans, and light trucks. Drive in confidence with our new Philips Ultinon Pro6000 Boost LED bulbs.

30% more compact design




The latest innovative generation of the Philips Ultinon Pro6000 Boost H4-LED bulb showcases a direct-fit body with an integrated IEC 60061-compliant base. The bulbs ultra-compact design makes it 30% smaller than its predecessor, improving mechanical fit in the narrowest headlights. The design simplifies lamp replacement for both high-beam and low-beam functions*, offering users improved versatility and utility. Check out our compatibility list for Philips Ultinon Pro6000 Boost at [Philips.com/roadlegalLED](https://philips.com/roadlegalLED) and get the best LED replacement for your halogen bulbs!

Unique light performance



You really can get more brightness from the same light output now. The Philips Ultinon Pro6000 Boost range features automotive industry-exclusive LEDs, combined with a revolutionary architecture that ensures unique optical performance. The result is an impressive boost in brightness on the road, up to 300% more**! Upgrade your headlights to peak LED automotive performance with our Philips Ultinon Pro6000 Boost bulbs.

Exclusive light quality



Philips Ultinon Pro6000 Boost features a brilliant white light beam achieved through a unique 5800 Kelvin color temperature. Its optimal spectrum enhances the visibility of road signs, making them more easily discernible for drivers. Philips Ultinon Pro6000 Boost bulbs are also equipped with our cutting-edge SafeBeam technology, producing a glare-free beam of light guaranteed not to dazzle oncoming drivers. With our Philips Ultinon Pro6000 Boost bulbs, enjoy clearer vision from exceptional lighting.

Long-term durability



Featuring advanced AirBoost cooling technology, the Philips Ultinon Pro6000 Boost range is designed to improve heat dissipation, providing LED bulb life of up to 3,000 hours. Its unique construction offers consistent, reliable performance, lasting six times longer than comparable halogen bulbs. For peace of mind, the Philips Ultinon Pro6000 Boost range has a full 5-year warranty, including a 2-year standard warranty and an additional 3 years of extended protection***. Benefit now from all the advantages of improved light and the assurance of long-lasting performance.

Reliable Philips quality



With our extensive expertise in building premium automotive lighting products that prioritize safety and reliability, we excel in maintaining high-quality standards. Our range of Philips LED bulbs meets the strict requirements for electromagnetic compatibility (EMI) with vehicle systems and offers stable, professional-quality lighting. Rely on the world-renowned expertise of an automotive specialist.

Specifications

Marketing specifications

- Product highlight: Up to +300% brightness, Safebeam technology, Airboost heat management
- Expected benefits: Road-legal, High brightness, Easy-to-fit

Product description

- Application: High Beam, Low Beam
- Base: P43t-38
- Color temperature: 5800K
- Designation: LED H4 11342 U60B2 12V 18W X2
- Designation LED Type: H4-LED
- Ingress protection rating (IP): IP55
- Lifespan: 3000 hours
- Light source: Automotive LED chips
- Operating Temperature: -40 to +105 °C
- Range: Ultinon Pro6000 Boost HL
- Technology: LED
- Type: H4
- Driver box -Height (mm): 83.6 mm
- Homologation ECE R37: no
- Homologation ECE R10
- Polarity free
- Homologation: National approval
- Diameter: 27.3 mm

Light characteristics

- Lumens: 1650/1000 lm

Electrical characteristics

- Wattage: 18 W
- Voltage: 12 V

Ordering information

- Order entry: 11342U60B2X2
- Ordering code: 02792431

Packaging Data

- Packaging type: Carton
- Packing: Box
- EAN1: 8719018027924
- EAN3: 8719018027931
- Packaging type: X2

Packed product information

- Length: 11.1 cm
- Width: 5 cm
- Height: 13.5 cm
- Net weight per piece: 40 g
- Net weight: 80 g
- Pack Quantity: 2 pcs
- Gross weight: 155 g

Outerpack information

- Length: 23.6 cm
- Width: 16.7 cm
- Height: 15 cm
- Quantity: 12 pcs
- Gross weight per outerpack: 1020 g



Issue date 2024-06-28

Version: 3.3.0

EAN: 87 19018 02792 4

© 2024 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* The Philips Ultinon Pro6000 LED Boost range is approved for road traffic in the respective countries where approval exists and for the listed range of vehicle models and lighting functions only. For more information about the legal requirements that apply in your country and to consult our latest compatibility list, visit Philips.com/roadlegalLED. You are responsible for complying with legal requirements applicable in your country.

** Compared to minimum legal requirement. Applies to H4, H7. May vary depending on car model & bulb type.

*** The Philips Ultinon Pro6000 LED Boost range is covered by a 2-year guarantee on purchase + 3 years' free extended warranty upon registration. Visit philips.com/auto-warranty to know more about our warranty policy. The Philips warranty covers manufacturing defects and non-commercial use only.