

Philips Ultinon Pro9200 HL  
Unrivalled LED automotive  
performance

#### LED-HL [≈H9/H11]

Up to 400% brighter light  
Broad fleet compatibility  
High-end Style and Safety

11362U92X2

# Master the light, defy the dark

## Unrivalled LED automotive performance

Defy the dark with the Philips Ultinon Pro9200, the pinnacle of LED retrofit lighting performance. Enjoy the power of cutting-edge LED technology with up to 400%\* increased brightness from one of the most compact bulbs on the market.

#### **Broad fleet compatibility**

- Ultra-compact design for broad fleet compatibility

#### **Revolutionary brightness and high-end style**

- Concentrated power – Up to 400% brighter light
- Up to 5800 Kelvin colour temperature for cool white light

#### **Best-in-class cut-off line**

- Light, just where you need it

#### **Performance made to last**

- 12 V and 24 V compatible for wider usability
- Enhanced lifetime of up to 5000 hours


#### **Automotive-grade quality**

- The durability that today's drivers demand

# PHILIPS


# Highlights

## Ultra-compact design



The Philips Ultinon Pro9200 LED range combines the power of LED technology with an ultra-compact housing to suit any lighting application. Enjoy a 30% smaller footprint than its predecessor, designed for effortless fitting even in the narrowest headlights. Retrofitting is easy, offering passionate drivers and customisers hassle-free functionality.


## Superior visibility and style



Master the light on the road. Meticulously engineered to ignite your passion for driving, our Philips Ultinon Pro9200 headlight bulbs provide unrivalled performance and the exceptional visibility you want while driving. Thanks to our unique LED selection and meticulous product refinement, you enjoy unrivalled brightness of up to 400% more than the legal minimum for halogen bulbs. See road signs better with their unique optimal

spectrum and improve your view of the road ahead. Our bulbs empower you to navigate with confidence.

## Best-in-class cut-off line



Drive safely and precisely with the Philips Ultinon Pro9200. Thanks to the precise positioning of the LED chips on our Philips Ultinon Pro9200 bulbs, you have light exactly where you need it on the road without dazzling oncoming vehicles. Our bulbs also feature our innovative Philips SafeBeam technology, producing the best usable beam and glare-free pattern. This means optimal visibility while driving.

## High-end style



Embrace your passion for driving with the Philips Ultinon Pro9200, the perfect blend of practicality and performance. With a colour temperature of up to 5800 K, endorsed by

Original Equipment Manufacturers for its ability to enhance eye comfort during night-time driving, our new bulb lets you navigate dark roads with ease and comfort. Rely on our Philips Ultinon Pro9200 for your night-time driving adventures!

## 12 V-24 V for wider usability



Philips Ultinon Pro9200 is compatible with both 12 V and 24 V electrical systems, making it suitable for most vehicle types.

## Up to 5000 hours' lifetime



Drive longer and brighter with Philips Ultinon Pro9200 headlight bulbs. Our bulbs offer bright, elegant light engineered to last. Boasting longevity-enhancing technology such as the dual AirBoost heat-management system, they last for up to 5000 hours of operation and provide constant light throughout their lifespan. The Philips Ultinon Pro9200 range is covered by a 5 year warranty, including a 2 year standard warranty and an additional 3 years of extended protection\*\*\*.

# Specifications

## Marketing specifications

- Product highlight: Up to +400% brightness, AirBoost heat management, SafeBeam technology, glare-free light beam
- Expected benefits: Brighter Lights, Better vision, Easy to fit

## Product description

- Application: High Beam, Low Beam, Running lights
- Base: PGJ19-2/5
- Designation: LED H11/H9 11362 U92 12/24 V 21 W X2
- Designation LED Type: LED-HL [≈H9/H11]
- Ingress protection rating (IP): IP55
- Lifespan: 5000 hours
- Operating Temperature: -40 to +105°C
- Range: Ultinon Pro9200 HL
- Technology: LED
- Type: H9/H11
- Voltage: 12/24 V
- Wattage: 21 W
- ECE R37 certification: No
- ECE R10 certification
- Polarity free
- Diameter: 14 mm
- Length – mm: 73 mm

## Light characteristics

- Colour temperature: 5800 K
- Lumens [lm]: 1800 lm

## Ordering information

- Order entry: 11362U92X2
- Ordering code: 2773394

## Logistic data

- Quantity in box: 2 pcs

## Packaging Data

- Packing: Set box
- EAN1: 8719018027733
- EAN3: 8719018027740
- Packaging type: Carton

## Packed product information

- Net weight per piece: 45.65 g
- Net weight per pack: 91.3 g
- Gross weight: 174.1 g
- Height [mm]: 130 mm
- Length [mm]: 111 mm
- Width [mm]: 60 mm

## Outer pack information

- Length: 230 cm
- Width: 128 cm
- Height: 140 cm
- Quantity: 8 pcs (4 sets)
- Gross weight per outer pack: 0.8014 kg



Issue date 2024-07-13

Version: 1.1.1

EAN: 87 19018 02773 3

© 2024 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)

\* Compared to minimum legal requirement. Applies to H4, H7. May vary depending on car model & bulb type.

\*\* Non-ECE compliant, not for use on public roads. You are responsible for complying with legal requirements applicable in your country.

\*\*\* The Philips Ultinon Pro9200 LED range is covered by a 2 year guarantee on purchase + 3 years' free extended warranty upon registration. Visit [philips.com/auto-warranty](http://philips.com/auto-warranty) to know more about our warranty policy. The Philips warranty covers manufacturing defects and non-commercial use only.