

Philips Xperion 3000
Under-bonnet light

1200 lm Boost/300 lm Eco

Battery life: 3 h (Eco: 12 h)
Versatile attachment options
Foldable

X30BONNX1



Quality light to get the job done

Versatile, foldable LED under-bonnet light

The Philips Xperion 3000 Under-bonnet LED light offers a 1200 lumen powerful, broad beam in a versatile, flexible under-bonnet format.

Bright, comfortable work light

- Light up your whole work area
- See every detail with a 110° wide-angle beam

Versatile for hands-free use

- Smart handle to position light for hands-free use

Handy and easy to operate

- Long-life battery
- Battery-status indicator

Sturdy lamp for daily use

- Robust aluminium and nylon housing
- Water- and dust-protected

PHILIPS

Under-bonnet light
1200 lm Boost/300 lm Eco Battery life: 3 h (Eco: 12 h), Versatile attachment options, Foldable

Specifications

Marketing specifications

- Product highlight: Versatile attachment
- Expected benefits: Quality light to get the job done

Product description

- Impact protection rating (IK): IK07
- Ingress protection rating (IP): IP54
- Magnet: Magnetic handle
- Materials and finishing: Aluminium, Nylon
- Operating Temperature: -10°C to 40°C °C
- Orientable light: 225°
- Range: Xperion 3000
- Technology: LED
- Resistant to: Grease, oil, workshop solvents
- Hook: 2 rotatable hooks
- Hands-free options: Magnetic handle, 2 hooks

Light characteristics

- Colour temperature: 6500 K
- Light intensity (boost): 1200 lumens
- Light intensity (eco): 600/300 lumens
- Beam angle: 110°

Electrical characteristics

- Battery capacity: 5200 mAh
- Battery run time (boost): Up to 3 hours
- Battery run time (eco): Up to 12 hours
- Battery type: Lithium battery

- Plug type: Plug not included
- Charging cable type: USB-C cable
- Battery charging time: Up to 4 hours
- Power Source: Battery
- Wattage: 10 W
- Voltage: 3.7 V

Ordering information

- Order entry: 2517331
- Ordering code: X30BONNX1

Packaging Data

- EAN1: 8719018025173
- EAN3: 8719018025180

Packed product information

- Length: 41,8 cm
- Width: 10,8 cm
- Height: 5,3 cm
- Pack Quantity / MOQ: 6
- Weight with batteries: 0,8 Kg g
- Cable length: 100 cm USB-C cable

Outer pack information

- Length: 46,7 cm
- Width: 23,5 cm
- Height: 17,5 cm
- Gross weight per piece: 0,8 kg g

X30BONNX1

Highlights

Bright, comfortable work light

The Philips Xperion 3000 Under-bonnet LED light offers a powerful, bright light of 1200 lumens, helping you spot even the smallest details so you can see what you need to get the job done quickly.

110° wide-angle beam

The Philips Xperion 3000 Under-bonnet LED light provides a wide-angle beam of 110°, perfect for illuminating your entire work area. This broad, bright light lets you see every little detail as you work.

Versatile attachments

The smart handle of our Under-bonnet light can be used as a support to hold the lamp up in a free-standing position, as a hook to hang the light from or attached to any metal surface with its integrated magnets. This versatility allows you to position the light easily and at the right angle, directing the beam just where you need it.

Ready for action

The Philips Xperion 3000 Under-bonnet LED light provides 3 hours of continuous use in Boost mode (1200 lm) and up to 12 hours in Eco mode (300 lm). It takes less than 4 hours to fully recharge overnight, ready to go again the next day.

Don't get left in the dark

See when the battery needs charging. The Philips Under-bonnet LED light features a battery-status indicator showing how long the work lamp can function before the battery drains entirely. Never run out of power again in the middle of a job. The indicator also displays the time remaining until the battery is fully charged.

Designed for durability

Complying with international impact-resistance standard IK07, the robust aluminium and nylon housing of the Philips Under-bonnet LED light is designed to withstand tough working environments. Because we know that even the most careful workers sometimes drop their tools.

Designed for durability

The Philips Under-bonnet LED light conforms to the IP54 international splash- and dust-resistance rating. Built to rigorous manufacturing standards with multiple sealing processes, your lamp is resistant to splashed water and protected from dust.



Issue date 2024-02-03

Version: 3.3.1

EAN: 87 19018 02517 3

© 2024 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com