


Philips Xperion 6100
Under-bonnet light

Dual power: cable and battery

Up to 2400 lumen dimming light
Extendable up to 2.1 metres
Foldable for easy storage

X61BONNX1



Designed with you in mind

Corded and cordless powerful LED Under-bonnet lamp

Mains- or battery-powered, the Philips Xperion 6100 Under-bonnet LED lamp offers a seamlessly dimmable beam of up to 2400 lumens, with a telescopic mount that can extend up to 2.1 metres on both sides, ideal for working on cars, vans and trucks.

Powerful, bright LED lamp

- Powerful dimming beam

Long-lasting performance

- 5-metre robust cable
- Long-life battery

Enhanced versatility

- Telescopic, extendable mount
- Foldable for easy storage

Superior durability

- Robust, water- and dust-protected

Extended warranty

- Extend your warranty online to 3 years

PHILIPS

Under-bonnet light

Dual power: cable and battery Up to 2400 lumen dimming light, Extendable up to 2.1 metres, Foldable for easy storage

Specifications

Marketing specifications

- Product highlight: Extendable up to 2.1 m
- Expected benefits: Designed with you in mind

Product description

- Impact protection rating (IK): IK07
- Ingress protection rating (IP): IP54
- Magnet: No
- Materials and finishing: Aluminium
- Operating Temperature: -10°C to 40°C
- Range: Xperion 6000
- Resistant to: grease, oil, workshop solvents
- Technology: LED
- Hook: Rotatable, 2 sides extendable
- Hands-free options: Large rotating hooks

Light characteristics

- Colour temperature: 6500 K
- Light intensity (boost): Up to 2400 lumens
- Light intensity (eco): 300 lumens
- Beam angle: 110°

Electrical characteristics

- Battery charging time: Up to 2,5 hour(s)
- Battery capacity: 7,4V 2x 2600 mAh
- Battery run time (boost): Up to 3 hours
- Battery run time (eco): Up to 12 hours

- Battery type: Lithium battery
- Plug type: 110-240 V adapter (EU plug)
- Charging cable type: 5 m cable
- Power Source: Dual mode
- Wattage: 20/12 W
- Voltage: 7.4 V

Ordering information

- Order entry: 02736831
- Ordering code: X61BONNX1

Packaging Data

- EAN1: 8719018027368
- EAN3: 8719018027375

Packed product information

- Pack Quantity / MOQ: 6
- Weight with cable: 1950 g
- Length: 69 cm
- Width: 17 cm (6.7")
- Height: 8.2 cm
- Cable length: 5 m cable with 110-240 V adapter

Outer pack information

- Length: 72 cm cm
- Width: 26 cm cm
- Height: 38 cm cm

X61BONNX1

Highlights

Powerful, bright LED light

The Philips Xperion 6100 Under-bonnet LED lamp offers up to 2400 lumens of light, helping you spot even the smallest of details. Tune the light intensity as you wish with a rotary control to match your environment or preserve battery life.

5-metre robust cable

Ideal for extended periods of use, the Philips Xperion 6100 Under-bonnet LED lamp is equipped with a long, robust 5 metre cable (110-240 V), offering continuous illumination of up to 2400 lumens as you work. Similar to the lamp itself, the cable is designed to withstand tough workshop environments and resist chemicals, including hydrocarbons.

Long-life battery

Need to move around your workshop as you work? No problem. Simply detach the cable from the Philips Xperion 6100 Under-bonnet LED lamp. The 7.4 V 2 x 2600 mAh fast charging, long-life battery provides 3 hours of continuous use at 1400- lumens, up to 12 hours in Eco mode, and fully recharges in 2.5 hours. It features a battery-status indicator that shows how much battery life is left, ensuring that you never run out of power in the middle of a job again.

Telescopic, extendable mount

The Philips Xperion 6100 Under-bonnet LED lamp has two integrated telescopic hooks which are extendable on both sides and rotatable through 360°. The hooks feature wider openings and are covered with soft rubber for easy attachment to the vehicle bonnet without scratching the paintwork. With a mount stretching from 1.10 to 2.10 metres, our Philips Xperion 6100 Under-bonnet LED Light can be used in a wide range of locations. Whether under the bonnet, roof or rear hatch of any car, van or truck, this lamp offers the flexibility you need.

Foldable for easy storage

The Philips Xperion 6100 Under-bonnet LED lamp is foldable in half, reducing its length by half for easy storage.

Enhanced durability

Complying with the IK07 international impact-resistance standard, the robust aluminium housing of the Philips Under-bonnet LED lamp is designed to withstand tough working environments. It is IP54-rated for splash and dust resistance. Built to strict manufacturing standards with multiple sealing processes, our lamp is resistant to splashed water and protected from dust.

Up to 3 year warranty

Benefit from Philips standard 2 year warranty plus 1 additional year.*



Issue date 2024-05-24

Version: 4.4.1

EAN: 87 19018 02736 8

© 2024 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* *to be claimed on the Philips extended-warranty webpage