

PHILIPS

Automotive

Philips LED upgrade car compatibility list



Which LED lamp do you need?



Images for illustration purposes only.

* Applies to Ultinon Pro9000 HL [H4], [H7], [HB3/4], [H11], [HIR2] and FOG [H8/H11/H16].

** Compared to the minimum legal standard for halogen bulbs. Up to +200% for Ultinon Pro9000 HL [H1] and [H3] types.

It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.

New

Original automotive performance in LED

Ultinon Pro9000

Lumileds
TopContact
OEM LED*

2
years

+3
extended
warranty




Beam performance*



Standard **Up to +250%**

Light color



Up to **5800 K**

Standard: 3100 K

Lifetime



Up to **5000 h**

Available in

LED-HL [≈H1], [≈H3], [≈H4], [≈H7], [≈HB3/4], [≈H11], [≈HIR2]

LED-FL [≈H8/H11/H16]

New



The perfect blend of performance and durability

Ultinon Pro5000


Automotive
grade LED

2
years

+1
extended
warranty





Beam performance*



Standard **Up to +160%**


Light color



Up to **5800 K**

Standard: 3100 K

Lifetime



Up to **3000 h**



Available in

LED-HL [≈H1], [≈H3], [≈H4], [≈H7], [≈HB3/4], [≈H11], [≈HIR2]


LED-FL [≈H8/H11/H16]

Transform your car lights

Ultinon Essential





Beam performance*



Standard **Extra performance**


Light color



Up to **6500 K**

Standard: 3100 K

Lifetime



Up to **1500 h**

Available in

LED-HL [≈H1], [≈H3], [≈H4], [≈H7], [≈HB3/4], [≈H11], [≈HIR2]

LED-FL [≈H8/H11/H16]

Technical data



Bulb type	Base	Range	Ordering number	GOC	V	W
HL [≈H4]	P43t-38	Ultinon Pro9000	11342U90CWX2	00718631	12/24V	18W
		Ultinon Pro5000	11342U50CWX2	00782731	12/24V	15W
		Ultinon Essential	11342UE2X2	00318831	12/24V	21W
HL [≈H7]	PX26d	Ultinon Pro9000	11972U90CWX2	00720931	12/24V	18W
		Ultinon Pro5000	11972U50CWX2	00784131	12/24V	15W
		Ultinon Essential	11972UE2X2	00320131	12/24V	20W
FL [≈H8/H11/H16]	PGJ19-1/2/3	Ultinon Pro9000	11366U90CWX2	00712431	12/24V	15W
		Ultinon Pro5000	11366U50CWX2	00776631	12/24V	12W
		Ultinon Essential	11366UE2X2	00322531	12/24V	24W



It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.

LED accessories



LED CANbus

Some car models present particular challenges for LED-based retrofit lamps. When upgrading your car with LED retrofit bulbs, a few challenges may occur such as an error message on the dashboard, a flickering, or a dimming effect. These error messages don't mean the LED bulb itself is faulty.

Therefore, we have developed smart solutions to overcome those challenges. Unique Philips CANbus adapters ensure the vehicle's lighting systems function smoothly, for a reliable electrical performance over time.

Error	Solution	Bulb type	Ordering number	GOC	Compatible Philips range
Inaccurate dashboard warnings The car electronics tells the LED bulb is defective, even though the LED bulb is lighting up and functioning well.	Philips Adapter CANbus	HL [≈H1]	18960C2	39809030	Ultinon Pro9000 Ultinon Pro5000 Ultinon Essential
		HL [≈H7]	18952C2	5064930	Ultinon Pro9000 Ultinon Pro5000 Ultinon Essential
		FL [≈H8/H11/H16]	18954C2	05066330	Ultinon Pro9000 Ultinon Pro5000 Ultinon Essential
Flickering Unsteady light or loss of brightness (dimming).	Philips Light Repair CANbus	HL [≈H1]	18962C2	00283930	Ultinon Pro9000 Ultinon Pro5000 Ultinon Essential
		HL [≈H7]	18961C2	00281530	Ultinon Pro9000* Ultinon Pro5000* Ultinon Essential

* Philips Light Repair CANbus is directly integrated into our new-generation bulbs. No need for additional accessories! In some rare cases, an additional CANbus might be required to eliminate the flickering effect completely.



Connector rings

Almost every car model has a different type of socket in which halogen bulbs are secured. When replacing your halogen bulbs with LED lighting, you may need a connector ring to secure the LED bulbs inside the headlamp. **Every Philips HL [≈H7] upgrade is supplied with a center ring, type A.** If another type of connector ring is needed, you can find the concerning ring type mentioned in the Philips application list.

Please contact your nearest Philips dealer to buy the right connector ring fitting your car model, or contact our Philips Consumer Care.

Philips Ultinon Pro9000

Car model	Production year	Application	Lamp type	Philips LED upgrade range	Connector rings	Philips CANbus	Difficulty level when installing
Alfa Romeo							
Giulietta	2010 ▶ 2013	Low beam	H7	Ultinon Pro9000	Type A*		Hard
MiTo 955	2008 ▶ 2013	Low beam	H7	Ultinon Pro9000	Type I		Hard
MiTo 955	2008 ▶ 2013	High beam	H7	Ultinon Pro9000	Type A*		Hard
Audi							
A1	2010 ▶ 2018	Low beam	H7	Ultinon Pro9000	Type A*		Medium
A3	2004 ▶ 2008	Low beam	H7	Ultinon Pro9000	Type A*		Easy
A3 Sportback	2008 ▶ 2012	High beam	H7	Ultinon Pro9000	Type P		Medium
A3 Sportback	2008 ▶ 2012	Low beam	H7	Ultinon Pro9000	Type P		Hard
A4	2011 ▶ 2015	Low beam	H7	Ultinon Pro9000	Type A*		Medium
A4	2011 ▶ 2015	High beam	H7	Ultinon Pro9000	Type A*		Medium
BMW							
216	2014 ▶ 2018	Low beam	H7	Ultinon Pro9000	Type A*		Easy
216	2014 ▶ 2018	High beam	H7	Ultinon Pro9000	Type A*		Easy
1-Series Phase 2	2015 ▶ 2017	Low beam	H7	Ultinon Pro9000	Type P		Hard
1-Series Phase 2	2015 ▶ 2017	High beam	H7	Ultinon Pro9000	Type P		Hard
3-Series	2005 ▶ 2008	Low beam	H7	Ultinon Pro9000	Type A*		Medium
3-Series	2005 ▶ 2008	High beam	H7	Ultinon Pro9000	Type A*		Medium
Mini One	2006 ▶ 2010	Low beam	H7	Ultinon Pro9000	Type A*		Easy
Mini One	2006 ▶ 2010	High beam	H7	Ultinon Pro9000	Type A*		Easy
X1	2009 ▶ 2012	High beam	H7	Ultinon Pro9000	Type A*		Easy
X1	2012 ▶ 2015	Low beam	H7	Ultinon Pro9000	Type A*	Adaptor CANbus	Easy
X1	2012 ▶ 2015	High beam	H7	Ultinon Pro9000	Type A*	Adaptor CANbus	Easy
Citroën							
Berlingo	2012 ▶ 2015	Low / High beam	H4	Ultinon Pro9000	Type A*		Easy
C4	2004 ▶ 2010	Low beam	H7	Ultinon Pro9000	Type A*		Medium
C4	2010 ▶ 2014	Low beam	H7	Ultinon Pro9000	Type A*		Easy
C4	2015 ▶ 2018	Low beam	H7	Ultinon Pro9000	Type A*		Easy
C4	2015 ▶ 2018	High beam	H7	Ultinon Pro9000	Type A*		Easy
C4 Picasso	2013 ▶ 2016	Low beam	H7	Ultinon Pro9000	Type A*		Medium



It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.

*Each Philips HL [=H7] upgrade is supplied with a center ring type A.

Car model	Production year	Application	Lamp type	Philips LED upgrade range	Connector rings	Philips CANbus	Difficulty level when installing
Dacia							
Dokker	2016 ▶ 2020	Low / High beam	H4	Ultinon Pro9000	Type A*		Medium
Duster	2010 ▶ 2013	Low beam	H7	Ultinon Pro9000	Type A*		Easy
Logan MCV II FL	2016 ▶ 2020	Low beam	H7	Ultinon Pro9000	Type A*		Easy
Sandero	2016 ▶ 2021	Low beam	H7	Ultinon Pro9000	Type A*		Easy
DS							
DS3	2014 ▶ 2016	Low beam	H7	Ultinon Pro9000	Type A*		Easy
DS3	2010 ▶ 2014	Low beam	H7	Ultinon Pro9000	Type A*		Easy
DS4	2011 ▶ 2015	Low beam	H7	Ultinon Pro9000	Type A*		Easy
Fiat							
Doblo	2000 ▶ 2010	Low / High beam	H4	Ultinon Pro9000	Type A*		Easy
Panda	2003 ▶ 2009	Low / High beam	H4	Ultinon Pro9000	Type A*		Easy
Tipo	2015 ▶ 2020	Low beam	H7	Ultinon Pro9000	Type A*		Medium
Ford							
B-MaX	2012 ▶ 2017	Low beam	H7	Ultinon Pro9000	Type A*		Hard
C-MaX	2010 ▶ 2015	Low beam	H7	Ultinon Pro9000	Type A*		Easy
Fiesta	2012 ▶ 2017	Low beam	H7	Ultinon Pro9000	Type A*		Easy
Fiesta MK VII	2008 ▶ 2012	Low beam	H7	Ultinon Pro9000	Type P		Medium
Focus	2004 ▶ 2008	Low beam	H7	Ultinon Pro9000	Type A*		Easy
Ka	2008 ▶ 2016	Low / High beam	H4	Ultinon Pro9000	Type A*		Easy
Mondeo	2014 ▶ 2019	Low beam	H7	Ultinon Pro9000	Type A*		Hard
Hyundai							
Getz 1M	2005 ▶ 2009	Low / High beam	H4	Ultinon Pro9000	Type A*		Easy
I30 GD	2011 ▶ 2017	Low beam	H7	Ultinon Pro9000	Type M		Easy
IX	2013 ▶	High beam	H7	Ultinon Pro9000	Type A*		Medium
IX20	2013 ▶	Low beam	H7	Ultinon Pro9000	Type A*		Medium
Mazda							
Premacy CR1	1999 ▶ 2005	Low / High beam	H4	Ultinon Pro9000	Type A*		Medium
Mercedes							
A-Class W176	2012 ▶ 2018	Low beam	H7	Ultinon Pro9000	Type P		Medium
C-Class W204	2007 ▶ 2014	Low beam	H7	Ultinon Pro9000	Type E		Medium
C-Class W204	2007 ▶ 2014	High beam	H7	Ultinon Pro9000	Type E		Medium
Mitsubishi							
Colt Gen4	1978 ▶ 2012	Low / High beam	H4	Ultinon Pro9000	Type A*		Easy



It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.

*Each Philips HL [=H7] upgrade is supplied with a center ring type A.

Car model	Production year	Application	Lamp type	Philips LED upgrade range	Connector rings	Philips CANbus	Difficulty level when installing
Nissan							
Juke	2010 ▶ 2014	Low / High beam	H4	Ultinon Pro9000	Type A*		Easy
Micra	2005 ▶ 2010	Low / High beam	H4	Ultinon Pro9000	Type A*		Easy
Note	2012 ▶	Low / High beam	H4	Ultinon Pro9000	Type A*		Easy
Qashqai 1 phase2	2010 ▶ 2013	Low beam	H7	Ultinon Pro9000	Type P		Hard
Qashqai 1 phase2	2010 ▶ 2013	High beam	H7	Ultinon Pro9000	Type L		Hard
Qashqai 2	2014 ▶ 2017	High beam	H7	Ultinon Pro9000	Type A*		Easy
Opel							
Astra	2009 ▶ 2015	Low beam	H7	Ultinon Pro9000	Type A*		Easy
Astra Sports Tourer	2009 ▶ 2012	Low beam	H7	Ultinon Pro9000	Type P		Medium
Mokka	2016 ▶ 2019	Low beam	H7	Ultinon Pro9000	Type A*		Easy
Peugeot							
208	2012 ▶ 2015	Low beam	H7	Ultinon Pro9000	Type N		Hard
208	2012 ▶ 2015	High beam	H7	Ultinon Pro9000	Type N		Medium
307	2001 ▶ 2005	Low beam	H7	Ultinon Pro9000	Type A*		Easy
308	2013 ▶ 2017	Low beam	H7	Ultinon Pro9000	Type A*		Hard
3008	2016 ▶ 2020	Low beam	H7	Ultinon Pro9000	Type N		Medium
5008	2009 ▶ 2013	Low beam	H7	Ultinon Pro9000	Type N		Easy
307 CC	2001 ▶ 2005	Low beam	H7	Ultinon Pro9000	Type A*		Easy
Partner	2015 ▶ 2018	Low beam	H7	Ultinon Pro9000	Type A*		Medium
RCZ	2010 ▶ 2013	Low beam	H7	Ultinon Pro9000	Type A*		Easy
Renault							
Clio 4	2012 ▶ 2016	Low beam	H7	Ultinon Pro9000	Type A*		Medium
Mégane 2	2002 ▶ 2006	Low beam	H7	Ultinon Pro9000	Type A*		Medium
Mégane 3	2008 ▶ 2012	Low beam	H7	Ultinon Pro9000	Type A*		Easy
Mégane 3 estate	2008 ▶ 2012	Low beam	H7	Ultinon Pro9000	Type A*		Easy
Mégane 4	2016 ▶ 2020	Low beam	H7	Ultinon Pro9000	Type I		Easy
Mégane 4	2016 ▶ 2020	High beam	H7	Ultinon Pro9000	Type A*		Easy
Scénic 2	2006 ▶ 2009	Low beam	H7	Ultinon Pro9000	Type L		Hard
Twingo 3	2015 ▶ 2020	Low / High beam	H4	Ultinon Pro9000	Type A*		Easy
Zoé phase 1	2012 ▶ 2019	Low / High beam	H7	Ultinon Pro9000	Type L		Hard
Seat							
Alhambra	2010 ▶ 2015	Low beam	H7	Ultinon Pro9000	Type D		Medium
Altea XL	2006 ▶ 2015	Low beam	H7	Ultinon Pro9000	Type A*		Easy
Leon I	1999 ▶ 2006	Low beam	H7	Ultinon Pro9000	Type A*		Easy



It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.

*Each Philips HL [=H7] upgrade is supplied with a center ring type A.

Car model	Production year	Application	Lamp type	Philips LED upgrade range	Connector rings	Philips CANbus	Difficulty level when installing
Seat							
Leon II	2009 ▶ 2012	Low beam	H7	Ultinon Pro9000	Type A*		Hard
Leon III	2012 ▶ 2020	Low beam	H7	Ultinon Pro9000	Type A*		Easy
Skoda							
Octavia II	2004 ▶ 2008	Low beam	H7	Ultinon Pro9000	Type A*		Easy
Smart							
Fortwo	2007 ▶ 2014	Low beam	H7	Ultinon Pro9000	Type A*		Easy
Volkswagen							
A3	2005 ▶ 2008	Low beam	H7	Ultinon Pro9000	Type A*		Easy
Golf 5	2003 ▶ 2008	Low beam	H7	Ultinon Pro9000	Type D		Medium
Golf 5	2003 ▶ 2008	High beam	H7	Ultinon Pro9000	Type D		Medium
Golf 6	2008 ▶ 2014	Low beam	H7	Ultinon Pro9000	Type D	Adaptor CANbus	Medium
Golf 7	2017 ▶ 2020	Low beam	H7	Ultinon Pro9000	Type P		Medium
Passat B6	2005 ▶ 2010	Low beam	H7	Ultinon Pro9000	Type I	Adaptor CANbus	Medium
Passat B8	2015 ▶ 2019	Low beam	H7	Ultinon Pro9000	Type A*		Medium
Polo type 6C	2014 ▶ 2017	Low beam	H7	Ultinon Pro9000	Type P		Hard
Polo type 6C	2014 ▶ 2017	High beam	H7	Ultinon Pro9000	Type P		Hard
Polo type 6R	2009 ▶ 2014	Low beam	H7	Ultinon Pro9000	Type P		Hard
Polo type 6R	2009 ▶ 2014	High beam	H7	Ultinon Pro9000	Type P		Hard
Tiguan	2007 ▶ 2011	Low beam	H7	Ultinon Pro9000	Type P		Hard
Tiguan	2007 ▶ 2011	High beam	H7	Ultinon Pro9000	Type A*		Easy
Touran	2007 ▶ 2010	Low beam	H7	Ultinon Pro9000	Type E		Medium
Touran	2007 ▶ 2010	High beam	H7	Ultinon Pro9000	Type A*		Easy
T-Roc	2017 ▶	Low beam	H7	Ultinon Pro9000	Type D		Medium
Up	2016 ▶	Low / High beam	H4	Ultinon Pro9000	Type A*		Easy
Volvo							
V70 Gen3 1,6l Diesel	2007 ▶ 2016	Low beam	H7	Ultinon Pro9000	Type A*		Easy



It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.

*Each Philips HL [=H7] upgrade is supplied with a center ring type A.

Philips Ultinon Pro5000

Car model	Production year	Application	Lamp type	Philips LED upgrade range	Connector rings	Philips CANbus	Difficulty level when installing
Alfa Romeo							
Giulietta	2010 ▶ 2013	Low beam	H7	Ultinon Pro5000	Type A*		Hard
MiTo 955	2008 ▶ 2013	High beam	H7	Ultinon Pro5000	Type A*		Hard
MiTo 955	2008 ▶ 2013	Low beam	H7	Ultinon Pro5000	Type I		Hard
Audi							
A1	2010 ▶ 2018	Low beam	H7	Ultinon Pro5000	Type A*		Medium
A3	2004 ▶ 2008	Low beam	H7	Ultinon Pro5000	Type A*		Easy
A3 Sportback	2008 ▶ 2012	High beam	H7	Ultinon Pro5000	Type P		Medium
A3 Sportback	2008 ▶ 2012	Low beam	H7	Ultinon Pro5000	Type P		Hard
A4	2011 ▶ 2015	Low beam	H7	Ultinon Pro5000	Type A*		Medium
A4	2011 ▶ 2015	High beam	H7	Ultinon Pro5000	Type A*		Medium
BMW							
216	2014 ▶ 2018	Low beam	H7	Ultinon Pro5000	Type A*		Easy
216	2014 ▶ 2018	High beam	H7	Ultinon Pro5000	Type A*		Easy
1-Series Phase 2	2015 ▶ 2017	Low beam	H7	Ultinon Pro5000	Type P		Hard
1-Series Phase 2	2015 ▶ 2017	High beam	H7	Ultinon Pro5000	Type P		Hard
3-Series	2005 ▶ 2008	Low beam	H7	Ultinon Pro5000	Type A*		Medium
3-Series	2005 ▶ 2008	High beam	H7	Ultinon Pro5000	Type A*		Medium
Mini One	2006 ▶ 2010	Low beam	H7	Ultinon Pro5000	Type A*		Easy
Mini One	2006 ▶ 2010	High beam	H7	Ultinon Pro5000	Type A*		Easy
X1	2009 ▶ 2012	Low beam	H7	Ultinon Pro5000	Type A*		Easy
X1	2009 ▶ 2012	High beam	H7	Ultinon Pro5000	Type A*		Easy
X1	2012 ▶ 2015	Low beam	H7	Ultinon Pro5000	Type A*	Adaptor CANbus	Easy
X1	2012 ▶ 2015	High beam	H7	Ultinon Pro5000	Type A*	Adaptor CANbus	Easy
Citroën							
Berlingo	2012 ▶ 2015	Low / High beam	H4	Ultinon Pro5000	Type A*		Easy
C4	2004 ▶ 2010	Low beam	H7	Ultinon Pro5000	Type A*		Medium
C4	2010 ▶ 2014	Low beam	H7	Ultinon Pro5000	Type A*		Easy
C4	2015 ▶ 2018	Low beam	H7	Ultinon Pro5000	Type A*		Easy
C4	2015 ▶ 2018	High beam	H7	Ultinon Pro5000	Type A*		Easy
C4 Picasso	2013 ▶ 2016	Low beam	H7	Ultinon Pro5000	Type A*		Medium



It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.

*Each Philips HL [=H7] upgrade is supplied with a center ring type A.

Car model	Production year	Application	Lamp type	Philips LED upgrade range	Connector rings	Philips CANbus	Difficulty level when installing
Dacia							
Duster	2018 ▶ 2021	Front fog lights	H11	Ultinon Pro5000	Type A*		Medium
Logan MCV II FL	2016 ▶ 2020	Low beam	H7	Ultinon Pro5000	Type A*		Easy
Sandero	2016 ▶ 2021	Low beam	H7	Ultinon Pro5000	Type A*		Easy
DS							
DS3	2014 ▶ 2016	Low beam	H7	Ultinon Pro5000	Type A*		Easy
DS3	2010 ▶ 2014	Low beam	H7	Ultinon Pro5000	Type A*		Easy
DS4	2011 ▶ 2015	Low beam	H7	Ultinon Pro5000	Type A*		Easy
Fiat							
Doblo	2000 ▶ 2010	Low / High beam	H4	Ultinon Pro5000	Type A*		Easy
Panda	2003 ▶ 2009	Low / High beam	H4	Ultinon Pro5000	Type A*		Easy
Tipo	2015 ▶ 2020	Low beam	H7	Ultinon Pro5000	Type A*		Medium
Ford							
B-MaX	2012 ▶ 2017	Low beam	H7	Ultinon Pro5000	Type A*		Hard
C-MaX	2010 ▶ 2015	Low beam	H7	Ultinon Pro5000	Type A*		Easy
Fiesta	2012 ▶ 2017	Front fog lights	H11	Ultinon Pro5000	Type A*		Medium
Fiesta MK VII	2008 ▶ 2012	Low beam	H7	Ultinon Pro5000	Type P		Medium
Ka	2008 ▶ 2016	Low / High beam	H4	Ultinon Pro5000	Type A*		Easy
Mondeo	2014 ▶ 2019	Low beam	H7	Ultinon Pro5000	Type A*		Hard
Hyundai							
Getz 1M	2005 ▶ 2009	Low / High beam	H4	Ultinon Pro5000	Type A*		Easy
I30 GD	2011 ▶ 2017	Low beam	H7	Ultinon Pro5000	Type M		Easy
IX	2013 ▶	High beam	H7	Ultinon Pro5000	Type A*		Medium
IX20	2013 ▶	Low beam	H7	Ultinon Pro5000	Type A*		Medium
Mazda							
Premacy CR1	1999 ▶ 2005	Low / High beam	H4	Ultinon Pro5000	Type A*		Medium
Mercedes							
A-Class W176	2012 ▶ 2018	Low beam	H7	Ultinon Pro5000	Type P		Medium
C-Class W204	2007 ▶ 2014	Low beam	H7	Ultinon Pro5000	Type E		Medium
C-Class W204	2007 ▶ 2014	High beam	H7	Ultinon Pro5000	Type E		Medium
Mitsubishi							
Colt Gen4	1978 ▶ 2012	Low / High beam	H4	Ultinon Pro5000	Type A*		Easy
Nissan							
Juke	2010 ▶ 2014	Low / High beam	H4	Ultinon Pro5000	Type A*		Easy
Micra	2005 ▶ 2010	Low / High beam	H4	Ultinon Pro5000	Type A*		Easy



It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.

*Each Philips HL [=H7] upgrade is supplied with a center ring type A.

Car model	Production year	Application	Lamp type	Philips LED upgrade range	Connector rings	Philips CANbus	Difficulty level when installing
Nissan							
Note	2012 ▶	Low / High beam	H4	Ultinon Pro5000	Type A*		Easy
Qashqai	2010 ▶ 2013	Front fog lights	H11	Ultinon Pro5000	Type A*		Medium
Qashqai 1 phase2	2010 ▶ 2013	Low beam	H7	Ultinon Pro5000	Type P		Hard
Qashqai 1 phase2	2010 ▶ 2013	High beam	H7	Ultinon Pro5000	Type L		Hard
Qashqai 2	2014 ▶ 2017	High beam	H7	Ultinon Pro5000	Type A*		Easy
Opel							
Astra	2009 ▶ 2015	Low beam	H7	Ultinon Pro5000	Type A*		Easy
Astra Sports Tourer	2009 ▶ 2012	Low beam	H7	Ultinon Pro5000	Type P		Medium
Mokka	2016 ▶ 2019	Low beam	H7	Ultinon Pro5000	Type A*		Easy
Peugeot							
208	2012 ▶ 2015	Low beam	H7	Ultinon Pro5000	Type N		Hard
208	2012 ▶ 2015	High beam	H7	Ultinon Pro5000	Type N		Medium
307	2001 ▶ 2005	Low beam	H7	Ultinon Pro5000	Type A*		Easy
308	2013 ▶ 2017	Low beam	H7	Ultinon Pro5000	Type A*		Hard
3008	2016 ▶ 2020	Low beam	H7	Ultinon Pro5000	Type N		Medium
5008	2009 ▶ 2013	Low beam	H7	Ultinon Pro5000	Type N		Easy
307 CC	2001 ▶ 2005	Low beam	H7	Ultinon Pro5000	Type A*		Easy
Partner	2015 ▶ 2018	Low beam	H7	Ultinon Pro5000	Type A*		Medium
RCZ	2010 ▶ 2013	Low beam	H7	Ultinon Pro5000	Type A*		Easy
Renault							
Captur	2013 ▶ 2017	Front fog lights	H11	Ultinon Pro5000	Type A*		Medium
Clio 4	2012 ▶ 2016	Low beam	H7	Ultinon Pro5000	Type A*		Medium
Clio 4	2016 ▶ 2020	Front fog lights	H11	Ultinon Pro5000	Type A*		Medium
Mégane 2	2002 ▶ 2006	Low beam	H7	Ultinon Pro5000	Type A*		Medium
Mégane 3	2008 ▶ 2012	Low beam	H7	Ultinon Pro5000	Type A*		Easy
Mégane 3 estate	2008 ▶ 2012	Low beam	H7	Ultinon Pro5000	Type A*		Easy
Mégane 4	2016 ▶ 2020	Low beam	H7	Ultinon Pro5000	Type I		Easy
Mégane 4	2016 ▶ 2020	High beam	H7	Ultinon Pro5000	Type A*		Easy
Scénic 2	2006 ▶ 2009	Low beam	H7	Ultinon Pro5000	Type L		Hard
Twingo 3	2015 ▶ 2020	Low / High beam	H4	Ultinon Pro5000	Type A*		Easy
Zoé phase 1	2012 ▶ 2019	Low / High beam	H7	Ultinon Pro5000	Type L		Hard
Seat							
Alhambra	2010 ▶ 2015	Low beam	H7	Ultinon Pro5000	Type D		Medium
Altea XL	2006 ▶ 2015	Low beam	H7	Ultinon Pro5000	Type A*		Easy



It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.

*Each Philips HL [=H7] upgrade is supplied with a center ring type A.

Car model	Production year	Application	Lamp type	Philips LED upgrade range	Connector rings	Philips CANbus	Difficulty level when installing
Seat							
Leon I	1999 ▶ 2006	Low beam	H7	Ultinon Pro5000	Type A*		Easy
Leon II	2009 ▶ 2012	Low beam	H7	Ultinon Pro5000	Type A*		Hard
Leon III	2012 ▶ 2020	Low beam	H7	Ultinon Pro5000	Type A*		Easy
Skoda							
Octavia II	2004 ▶ 2008	Low beam	H7	Ultinon Pro5000	Type A*		Easy
Smart							
ForTwo	2007 ▶ 2014	Low beam	H7	Ultinon Pro5000	Type A*		Easy
Volkswagen							
A3	2005 ▶ 2008	Low beam	H7	Ultinon Pro5000	Type A*		Easy
Golf 5	2003 ▶ 2008	Low beam	H7	Ultinon Pro5000	Type D		Medium
Golf 5	2003 ▶ 2008	High beam	H7	Ultinon Pro5000	Type D		Medium
Golf 6	2008 ▶ 2014	Low beam	H7	Ultinon Pro5000	Type D	Adaptor CANbus	Medium
Golf 7	2017 ▶ 2020	Low beam	H7	Ultinon Pro5000	Type P		Medium
Passat B6	2005 ▶ 2010	Low beam	H7	Ultinon Pro5000	Type I	Adaptor CANbus	Medium
Passat B8	2015 ▶ 2019	Low beam	H7	Ultinon Pro5000	Type A*		Medium
Polo type 6C	2014 ▶ 2017	Low beam	H7	Ultinon Pro5000	Type P		Hard
Polo type 6C	2014 ▶ 2017	High beam	H7	Ultinon Pro5000	Type P		Hard
Polo type 6R	2009 ▶ 2014	Low beam	H7	Ultinon Pro5000	Type P		Hard
Polo type 6R	2009 ▶ 2014	High beam	H7	Ultinon Pro5000	Type P		Hard
Tiguan	2007 ▶ 2011	Low beam	H7	Ultinon Pro5000	Type P		Hard
Tiguan	2007 ▶ 2011	High beam	H7	Ultinon Pro5000	Type A*		Easy
Touran	2007 ▶ 2010	Low beam	H7	Ultinon Pro5000	Type E		Medium
Up	2016 ▶	Low / High beam	H4	Ultinon Pro5000	Type A*		Easy
Volvo							
V70 Gen3 1,6l Diesel	2007 ▶ 2016	Low beam	H7	Ultinon Pro5000	Type A*		Easy



It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.

*Each Philips HL [=H7] upgrade is supplied with a center ring type A.

Philips Ultinon Essential

Car model	Production year	Application	Lamp type	Philips LED upgrade range	Connector rings	Philips CANbus	Difficulty level when installing
Audi							
A1	2010 ▶ 2018	Low beam	H7	Ultinon Essential	Type A*		Medium
BMW							
216	2014 ▶ 2018	Low beam	H7	Ultinon Essential	Type A*		Easy
216	2014 ▶ 2018	High beam	H7	Ultinon Essential	Type A*		Easy
X1	2012 ▶ 2015	Low beam	H7	Ultinon Essential	Type A*		Easy
Citroën							
C4	2004 ▶ 2010	Low beam	H7	Ultinon Essential	Type A*		Medium
C4	2010 ▶ 2014	Low beam	H7	Ultinon Essential	Type A*		Easy
C4	2015 ▶ 2018	Low beam	H7	Ultinon Essential	Type A*		Easy
C4	2015 ▶ 2018	High beam	H7	Ultinon Essential	Type A*		Easy
C4 Picasso	2013 ▶ 2016	Low beam	H7	Ultinon Essential	Type A*		Medium
Dacia							
Duster	2010 ▶ 2013	Low beam	H7	Ultinon Essential	Type A*		Easy
DS							
DS3	2014 ▶ 2016	Low beam	H7	Ultinon Essential	Type A*		Easy
DS3	2010 ▶ 2014	Low beam	H7	Ultinon Essential	Type A*		Easy
DS4	2011 ▶ 2015	Low beam	H7	Ultinon Essential	Type A*		Easy
Mercedes							
C-Class W204	2007 ▶ 2014	Low beam	H7	Ultinon Essential	Type E		Medium
C-Class W204	2007 ▶ 2014	High beam	H7	Ultinon Essential	Type E		Medium
Nissan							
Qashqai 1 phase2	2010 ▶ 2013	Low beam	H7	Ultinon Essential	Type P		Hard
Qashqai 1 phase2	2010 ▶ 2013	High beam	H7	Ultinon Essential	Type L		Hard
Opel							
Mokka	2016 ▶ 2019	Low beam	H7	Ultinon Essential	Type A*		Easy
Peugeot							
308	2013 ▶ 2017	Low beam	H7	Ultinon Essential	Type A*		Hard



It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.

*Each Philips HL [=H7] upgrade is supplied with a center ring type A.

Car model	Production year	Application	Lamp type	Philips LED upgrade range	Connector rings	Philips CANbus	Difficulty level when installing
Renault							
Mégane 3	2008 ▶ 2012	Low beam	H7	Ultinon Essential	Type A*		Easy
Scénic 2	2006 ▶ 2009	Low beam	H7	Ultinon Essential	Type L		Hard
Zoé phase 1	2012 ▶ 2019	Low / High beam	H7	Ultinon Essential	Type L		Hard
Seat							
Altea XL	2006 ▶ 2015	Low beam	H7	Ultinon Essential	Type A*		Easy
Leon III	2012 ▶ 2020	Low beam	H7	Ultinon Essential	Type A*		Easy
Volkswagen							
Golf 5	2003 ▶ 2008	Low beam	H7	Ultinon Essential	Type D (UE)		Medium
Golf 5	2003 ▶ 2008	High beam	H7	Ultinon Essential	Type D (UE)		Medium
Passat B6	2005 ▶ 2010	Low beam	H7	Ultinon Essential	Type I	Adaptor CANbus	Medium
Passat B8	2015 ▶ 2019	Low beam	H7	Ultinon Essential	Type A*		Medium
Tiguan	2007 ▶ 2011	Low beam	H7	Ultinon Essential	Type P		Hard
Tiguan	2007 ▶ 2011	High beam	H7	Ultinon Essential	Type A*		Easy
T-Roc	2017 ▶	Low beam	H7	Ultinon Essential	Type D (UE)		Medium

Check Philips bulbs compatibility with your car: philips.com/led-bulbs



It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.

*Each Philips HL [=H7] upgrade is supplied with a center ring type A.



Philips LED web-series

Watch our various episodes on LED technology and lead the way!

philips.com/LEDVideoGuide



2021 © Lumileds Holding B.V. All rights reserved.

The Philips trademark and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V. Specifications are subject to change without notice.

philips.com/led-bulbs