



PHILIPS

LED work light
Xperion Flood mini

Philips LED work light Xperion 6000 Flood mini

Compact LED projector light

Philips Xperion 6000 Flood mini is a compact LED projector that combines a 500 lumens wide flood illumination and a bright focused beam, easily controlled by a smart zoom knob. Resistant to shocks and water, this lamp is built to last.

Compact LED light with multiple outputs

- Lights up large area with **500 lm dimmable flood light**
- Focus light with **250lm spotlight**

Smart-zoom knob to easily control your light

- Adjust your light from wide flood illumination to focused brightness with the turn of a wheel

Long running time in different light modes

- A single charge provides enough energy : **up to 9 hours** in Eco mode, 3 hours in Boost mode and 5 hours with the spot beam.

Smart, ergonomic, versatile design

- **Compact** and light to follow you everywhere
- **Versatile attachments** to fix to any surface
- Rechargeable with micro-USB-C and dock station
- “Find my device” ready

Handles tough conditions easily

- Resistant to impacts, water and solvents (IP65/IK07)



500 lm
Flood light



250 lm
Spotlight



Dimming



Zoom
light



Light settings
memory



Beam angle
(100°)



Operating
time (3h/5h)



Charging
time (<3,5h)



Charging
USB-C

Product data and delivery information



Pack	Philips designation	Reference	EAN1	EAN3	GOC	MOQ
X1	LED WSL Flood mini X1 X60FLMI	X60FLMIX1	8719018019134	8719018019141	1913431	6

Description	Levels	Qty	Length (cm)	Width (cm)	Height (cm)	Gross Weight (kg)
Philips LED work light Xperion 6000 Flood mini X60FLMINX 1	Level 1 (Single box)	1 unit	11	6	13,5	0,372
	Level 3 (Outer box)	6 units	24	15,5	20,5	2,5
	Level 4 (Pallet)	84 units	100	120	140	50

2021 © Lumileds Holding B.V. All rights reserved.
The Philips trademark and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V. Specifications are subject to change without notice.

