

PHILIPS

Ultinon Pro6000 LED



Compatibility list **Philips Ultinon Pro6000**

Updated on: 04.08.2023



Compatibility list

Philips Ultinon Pro6000

Updated on: 04.08.2023

Consult regularly our list on:
Philips.com/roadlegalLED



Product and ordering information

Product description	Application	Part number	Packaging	Order number – GOC
Ultinon Pro6000 H4-LED	Low beam/High beam	11342U6000X2	X2 (2 Bulbs)	01365131
Ultinon Pro6000 H4-LED Motorcycle	Low beam/High beam	11342U6000X1	X1 (1 Bulb)	02422094
Ultinon Pro6000 H7-LED	Low beam/High beam	11972U6000X2	X2 (2 Bulbs)	01361331
Ultinon Pro6000 H7-LED Motorcycle	Low beam/High beam	11972U6000X1	X1 (1 Bulb)	02424494
Ultinon Pro6000 W5W-LED	Front parking light ¹⁾	11961HU60X2	X2 (2 Bulbs)	01638630
Connection ring Type A	Accessories H7-LED ⁶⁾	11184X2	X2 (2 Rings)	02009331
Connection ring Type D	Accessories H7-LED ⁶⁾	11176X2	X2 (2 Rings)	01681231
Connection ring Type E	Accessories H7-LED ⁶⁾	11178X2	X2 (2 Rings)	01679931
Connection ring Type H	Accessories H7-LED ⁶⁾	11172X2	X2 (2 Rings)	01630031
Connection ring Type I	Accessories H7-LED ⁶⁾	11179X2	X2 (2 Rings)	01683631
Connection ring Type K	Accessories H7-LED ⁶⁾	11180X2	X2 (2 Rings)	01675131
Connection ring Type N	Accessories H7-LED ⁶⁾	11183X2	X2 (2 Rings)	01636231
Connection ring Type P	Accessories H7-LED ⁶⁾	11182X2	X2 (2 Rings)	01677531
Adapter CANbus LED H7	Accessories H7-LED ⁶⁾	18952X2	X2 (2 Adapters)	72837794
Adapter CANbus LED H4	Accessories H4-LED ⁶⁾	18960X2	X2 (2 Adapters)	72831594



Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
ADRIA							
Compact, Coral, Matrix, Twin ⁵⁾	B, C	2011 ▶ 2014	H7-LED (11972U6000X2)	E3 2447 (RH) / E3 2448 (LH)	Low beam	-	-
Compact, Coral, Lido, Matrix, Twin ⁵⁾	B, C N, P	2014 ▶ * 2016 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
ALFA ROMEO							
Giulietta	940	2013 ▶ 2016	H7-LED (11972U6000X2)	E3 2841	Low beam	-	-
AUDI							
A1 / A1 Sportback S1 / S1 Sportsback	8X	2015 ▶ 2018	H7-LED (11972U6000X2)	E9 11198	Low beam	-	-
A3 A3 Sportback	8P 8PA	2003 ▶ 2008	H7-LED (11972U6000X2) W5W-LED (11961HU60X2)	E1 1468	Low beam Front parking light ¹⁾	-	⁴⁾ -
A4, S4	B8	2011 ▶ 2015	H7-LED (11972U6000X2)	E1 3064	Low beam	-	⁴⁾
Q3	8U, 8U1	2011 ▶ 2018	H7-LED (11972U6000X2)	E9 6391	Low beam	-	-

Other models ▼



Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
-------------------	------	---------------------	--------------	--------------------------	-------------------	------------------------------------	--------------------------------------

AUSTIN, MORRIS

Mini Cooper	Mini Cooper	1966 ▶ 2000	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾	-	-
Mini Cooper Minor	Mini Minor	1966 ▶ 2000	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾	-	-
Mini Cooper S	Mini Cooper S	1966 ▶ 2000	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾	-	-
Mini Kombi	Mini Kombi, Mini Kombi MK II	1967 ▶ 2000	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾	-	-
Mini Pick Up	Mini Pick Up	1970 ▶ 2000	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾	-	-
Mini Traveller	Mini Traveller MK II	1968 ▶ 2000	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾	-	-
Mini Van	Mini Van	1970 ▶ 2000	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾	-	-

BENTLEY

Continental Azure Brooklands Turbo	NZ, SZ	1995 ▶ 2002	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾	-	-
------------------------------------	--------	-------------	--------------------------	---------------------------	--	---	---

BMW

1er (F20/F21)	IK2, IK4	2011 ▶ 2016	H7-LED (11972U6000X2)	E1 3132	Low beam	Type P (11182X2)	-
1er (F20/F21 Facelift)	IK2, IK4	2014 ▶ 2020	H7-LED (11972U6000X2)	E1 3999	Low beam/ High beam [20 ³⁾	Type P (11182X2)	-
2er Active Tourer (F45)	F2AT, UKL-L	2014 ▶ 2017	H7-LED (11972U6000X2)	E1 3680	Low beam	-	-
2er Gran Tourer (F46)	F2GT, UKL-L	2015 ▶ 2018	H7-LED (11972U6000X2)	E1 3680	Low beam	-	-
3er (E90/E91)	390L, 390X	2005 ▶ 2008	H7-LED (11972U6000X2)	E12 112016	Low beam/ High beam [30 ³⁾	-	-
3er (F30/F31)	3L, 3K, 3K-N1	2011 ▶ 2015	H7-LED (11972U6000X2)	E4 15473	Low beam	-	-
3er (F30/F31) Facelift	3L, 3K, 3K-N1	2015 ▶ 2019	H7-LED (11972U6000X2)	E1 4041	Low beam/ High beam [20 ³⁾	Type P (11182X2)	-
3er GT (F34)	3-V	2013 ▶ 2016	H7-LED (11972U6000X2)	E4 16619	Low beam	-	-
X3 (F25 Facelift)	X3, X-N1	2014 ▶ 2017	H7-LED (11972U6000X2)	E1 3543	Low beam	-	-

Other models ▼



Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
BMW (Motorcycle)							
F 650 GS F 700 GS F 800 GS F 800 GS Adventure	E8GS 4G80r	2008 ▶ 2018 2016 ▶ 2018	H7-LED (11972U6000X1)	E1 3571	High beam [12,5]	-	-
G 650 Xmoto G 650 Xchallenge	E65X	2006 ▶ 2010	H4-LED (11342U6000X1)	E3 2473	Low beam/ High beam [12,5 ³⁾]	-	-
G 650 G 650 GS	E650G	2010 ▶ 2015	H4-LED (11342U6000X1)	E3 2473	Low beam/ High beam [12,5 ³⁾]	-	-
MEGAMOTO	RHP2	2006 ▶ 2008	H4-LED (11342U6000X1)	E3 2473	Low beam/ High beam [12,5 ³⁾]	-	-
R 1200 GS R 1200 GS Adventure	R12	2004 ▶ 2012	H7-LED (11972U6000X1)	E3 2179	High beam [12,5 ³⁾]	-	-
R 1200 GS R 1200 GS Adventure	R12W	2012 ▶ 2018	H7-LED (11972U6000X1)	E4 16103	Low beam/ High beam [12,5]	-	-
R 1250 GS R 1250 GS Adventure	1G13 1G13ind	2018 ▶ * 2019 ▶ *	H7-LED (11972U6000X1)	E4 16103	Low beam/ High beam [12,5]	-	-
R nine T R nine T Pure R nine T Racer R nine T Scrambler R nine T Urban G/S	1N12	2016 ▶ *	H4-LED (11342U6000X1)	E13 13815	Low beam/ High beam [17,5]	-	-
BRITISH LEYLAND							
Mini	MINI 850 MK II, MINI 850 Mk. II, MINI 1000 MK II, MINI 1275 GT	1968 ▶ 2000	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾]	-	-
Mini Clubman	CLUBMAN	1966 ▶ 2000	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾]	-	-
Mini Moke	Mini Moke	1968 ▶ 2000	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾]	-	-
BÜRSTNER							
Argos, Brevio, Ixeo, Nexxo, Travel, Travel Van ⁵⁾	2010, 2020 2080 4010, 3010, 4020	2006 ▶ 2014 2008 ▶ 2014 2012 ▶ 2014	H7-LED (11972U6000X2)	E3 2447 (RH) / E3 2448 (LH)	Low beam	-	-
Argos, Brevio, Ixeo, Lyseo, Nexxo, Travel ⁵⁾	4010, 4020 5020	2014 ▶ * 2017 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
CAPRON / PÖSSL							
Carado, Solifer, Sunlight ⁵⁾	EG/CF 002	2010 ▶ 2014	H7-LED (11972U6000X2)	E3 2447 (RH) / E3 2448 (LH)	Low beam	-	-
Carado, CVE, Etrusco, Solifer, Sunlight, Roadcar ⁵⁾	CKF1, CKF2 EG/CVF 001, CRF1, CRC3 CVF2 EG/CF 002	2015 ▶ * 2018 ▶ * 2019 ▶ * 2014 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
CARTHAGO							
c-Tourer T, chic c-line T ⁵⁾	EG/CF 002	2006 ▶ 2014	H7-LED (11972U6000X2)	E3 2447 (RH) / E3 2448 (LH)	Low beam	-	-
Malibu, c-Tourer T, chic c-line T ⁵⁾	EG/CF004	2014 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
CHRYSLER, DAIMLERCHRYSLER, FCA							
Jeep Wrangler	TJ, JK	1996 ▶ 2018	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾]	-	-

Other models ▼



Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
CITROËN							
Berlingo (1. Gen.)	I phase 2 / M59 (I)	2018 ▶ *	H4-LED (11342U6000X2)	E4 9849	Low beam/ High beam	-	-
Berlingo (3. Gen.)	E	2018 ▶ *	H7-LED (11972U6000X2)	E9 16814	Low beam	-	-
Berlingo (3. Gen.)	K9	2018 ▶ *	H7-LED (11972U6000X2)	E9 16812	Low beam	-	-
C1 (1. Gen)	P*****, PG	2005 ▶ 2012	H4-LED (11342U6000X2)	E2 04048	Low beam/ High beam [25 ³⁾]	-	-
C3 (3. Gen.)	S	2016 ▶ 2020	H7-LED (11972U6000X2)	E9 16205	Low beam/ High beam [17,5]	-	-
C3 Aircross	2R, 2C	2017 ▶ 2021	H7-LED (11972U6000X2)	E9 16527	Low beam	-	-
C3 Picasso	SH (SH*****) SH	2009 ▶ 2017 2010 ▶ 2017	H7-LED (11972U6000X2)	E1 2598	Low beam	-	-
			W5W-LED (11961HU60X2)		Front parking light ¹⁾	-	-
Jumper / Relay (2. Gen.) ⁵⁾	Y	2006 ▶ 2014	H7-LED (11972U6000X2)	E3 2447 (RH) / E3 2448 (LH)	Low beam	-	-
Jumper / Relay (2. Gen.) Facelift ⁵⁾	Y	2014 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
Jumpy (2. Gen.) ⁵⁾ Dispatch (2. Gen.) ⁵⁾	X*****, X CX G9	2007 ▶ 2016 2007 ▶ 2016 2011 ▶ 2016 2007 ▶ 2013	H4-LED (11342U6000X2)	E2 05074	Low beam/ High beam [25 ³⁾]	-	-
			W5W-LED (11961HU60X2)		Front parking light ¹⁾	-	-

DACIA

Dokker	SD	2011 ▶ *	H4-LED (11342U6000X2)	E9 14005	Low beam/ High beam [20 ³⁾]	-	-
			W5W-LED (11961HU60X2)		Front parking light ¹⁾	-	-
Dokker Pick Up	SD	2018 ▶ *	H4-LED (11342U6000X2)	E9 14005	Low beam/ High beam [20 ³⁾]	-	-
			W5W-LED (11961HU60X2)		Front parking light ¹⁾	-	-
Duster (1. Gen.)	SD	2010 ▶ 2013	H7-LED (11972U6000X2)	E1 2737	Low beam	-	-
			W5W-LED (11961HU60X2)		Front parking light ¹⁾	-	-
Duster (1. Gen.) Facelift	SD, SR (HSR), SR	2013 ▶ 2019	H7-LED (11972U6000X2)	E1 3669	Low beam	-	-
Duster (2. Gen.)	SR	2018 ▶ *	H7-LED (11972U6000X2)	E1 4583	Low beam	-	-
Lodgy	SD	2011 ▶ *	H4-LED (11342U6000X2)	E9 14005	Low beam/ High beam [20 ³⁾]	-	-
			W5W-LED (11961HU60X2)		Front parking light ¹⁾	-	-
Sandero (2. Gen.)	SR/HM	2016 ▶ 2021	H7-LED (11972U6000X2)	E9 14210	Low beam	-	-
Sandero (2. Gen.) Facelift Sandero Stepway (2. Gen.) Facelift	SD, SR(5SR)	2016 ▶ 2021	H7-LED (11972U6000X2)	E9 14211	Low beam	-	-
Sandero (3. Gen.)	DJF	2021 ▶ *	H7-LED (11972U6000X2)	E19 0055	High beam	Type K (11180X2)	-
Spring	DBG	2021 ▶ *	H7-LED (11972U6000X2)	E8 11379	Low beam	-	-
Jogger	DJF	2021 ▶ *	H7-LED (11972U6000X2)	E19 0055	High beam	Type K (11180X2)	-

Other models ▼



Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
DETHLEFFS / PÖSSL							
Advantage, Alpa, Esprit, Globe, Globebus, Magic Edition, Trend ⁵⁾	EG/DF 003 EG/DF 004	2006 ▶ 2014 2007 ▶ 2014	H7-LED (11972U6000X2)	E3 2447 (RH) / E3 2448 (LH)	Low beam	-	-
Alpa, Globebus, Just, Pulse, Trend ⁵⁾	EG/DVF 001, EG/DVC 001 EG/DVP 001	2018 ▶ * 2019 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
FIAT							
Ducato 30, Ducato 33, Ducato 35/Maxi, Ducato 40/Maxi, Ducato 42	250	2014 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam/ High beam	-	-
Doblo ⁵⁾	223, 223L	2005 ▶ 2010	H7-LED (11972U6000X2)	E13 1717 (LH) / E13 1718 (RH)	Low beam	-	-
Ducato (3. Gen.) ⁵⁾	250	2006 ▶ 2014	H7-LED (11972U6000X2)	E3 2447 (RH) / E3 2448 (LH)	Low beam	-	-
Ducato (3. Gen.) Facelift ³⁾	250	2014 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
Punto	199	2011 ▶ *	H4-LED (11342U6000X2)	E9 5876	Low beam/ High beam [20 ³⁾]	-	-
Scudo (2. Gen.) ⁵⁾ Scudo Lecapitaine (2. Gen.) ⁵⁾	270, 270L 270Y	2007 ▶ 2016 2012 ▶ 2016	H4-LED (11342U6000X2) W5W-LED (11961HU60X2)	E2 05074	Low beam/ High beam [25 ³⁾] Front parking light ¹⁾	-	-
Tipo Aegea (Ægea)	356	2016 ▶ 2020	H7-LED (11972U6000X2)	E9 16020	Low beam/ High beam [20 ³⁾]	-	-
500X	334	2015 ▶ 2018	H4-LED (11342U6000X2)	E24 6272	Low beam/ High beam [30 ³⁾]	-	-
FIAT, RAPIDO							
Rapido, Esterel, Itineo ⁵⁾	250***** /A	2006 ▶ 2014	H7-LED (11972U6000X2)	E3 2447 (RH) / E3 2448 (LH)	Low beam	-	-
FORD							
C-Max (2. Gen.)	DXA	2010 ▶ 2015	H7-LED (11972U6000X2)	E9 5897	Low beam	-	CANBus H7-LED (18952X2)
Fiesta (7. Gen.)	JA8 JA8-LPG, JR8	2008 ▶ 2012 2009 ▶ 2012	W5W-LED (11961HU60X2)	E8 4762	Front parking light ¹⁾	-	-
Fiesta (8. Gen.)	JHH JGH	2017 ▶ * 2018 ▶ *	H7-LED (11972U6000X2)	E4 25168	Low beam	Type K (11180X2)	-
Focus (3. Gen.)	DYB	2010 ▶ 2014	W5W-LED (11961HU60X2)	E4 14819	Front parking light ¹⁾	-	-
Focus (4. Gen.)	DEH	2018 ▶ *	H7-LED (11972U6000X2)	E8 9147	Low beam	Type K (11180X2)	-
KA (2. Gen.)	RU8	2008 ▶ 2016	H4-LED (11342U6000X2)	E3 2727	Low beam/ High beam	-	-
KA +	1	2014 ▶ 2019	H4-LED (11342U6000X2)	E4 25890	Low beam/ High beam [20 ³⁾]	-	-
Mustang I	T 67, T 68, T 69, T 70, T 71, T 72, T 73	1964 ▶ 1973	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾]	-	-
Mustang II	T 74, T 75	1973 ▶ 1979	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾]	-	-
C-Max (2. Gen.) Grand C-Max (2. Gen.)	DXA	2010 ▶ 2015	H7-LED (11972U6000X2)	E9 5897	Low beam	-	4)
S-Max (2. Gen.)	WA6	2015 ▶ *	H7-LED (11972U6000X2)	E9 11640	Low beam	-	-

Other models ▼



Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANBus-Adapter ⁶⁾
Escort (1. Gen.) Escort (2. Gen.)	ATH, AFH	1968 ▶ 1981	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾	-	-
Galaxy (3. Gen.)	WA6	2015 ▶ *	H7-LED (11972U6000X2)	E9 11640	Low beam	-	-
Tourneo Connect ⁵⁾	PJ2, PU2	2013 ▶ 2018	H7-LED (11972U6000X2) W5W-LED (11961HU60X2)	E9 14122	Low beam Front parking light ¹⁾	-	-
Transit Connect ⁵⁾	PJ2, PU2	2013 ▶ 2018	H7-LED (11972U6000X2) W5W-LED (11961HU60X2)	E9 14122	Low beam Front parking light ¹⁾	-	-

HONDA (Motorcycle)

CB 1000 R CB 1000 RA	SC60	2008 ▶ *	H4-LED (11342U6000X1)	E3 2711	Low beam/ High beam [12,5 ³⁾]	-	-
CB 1100	SC65	2013 ▶ 2022	H4-LED (11342U6000X1)	E13 9465	Low beam/ High beam [20 ³⁾]	-	-
CBF 1000 CBF 1000A	SC58	2006 ▶ 2011	H7-LED (11972U6000X1)	E3 2251	High beam [25 ³⁾]	-	-
CBR 1000 RA CBR 1000 RR	SC59	2008 ▶ 2016	H7-LED (11972U6000X1)	E4 0125	Low beam/ High beam [12,5 ³⁾]	-	-
CBR 650 F CBR 650 FA	RC74	2013 ▶ 2018	H4-LED (11342U6000X1)	E4 17802	Low beam/ High beam [17,5 ³⁾]	-	-
CB 650 F CB 650 FA	RC75						
VFR1200X VFR1200XD	SC70	2012 ▶ *	H7-LED (11972U6000X1)	E4 16019	Low beam/ High beam [17,5 ³⁾]	-	-

HYMER

Compass, Elddis, EXT, Exsis-t, Grand Canyon, Serengeti, Sydney, Rio, Tramp ⁵⁾	EG/HF001 HRC3, EHG250, EHGDUC1, EHGDOC2	2014 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
Exsis-t, Rio, Serengeti, Tramp ⁵⁾	EG/HF001	2012 ▶ 2014	H7-LED (11972U6000X2)	E3 2447 (RH) / E3 2448 (LH)	Low beam	-	-

HYUNDAI

Getz	TB TBI	2002 ▶ 2009 2006 ▶ 2009	H4-LED (11342U6000X2) W5W-LED (11961HU60X2)	E13 8279	Low beam/ High beam [37,5 ³⁾] Front parking light ¹⁾	-	-
i10 (1. Gen.)	PA PAG	2008 ▶ 2013	H4-LED (11342U6000X2)	E13 2540	Low beam/ High beam [20 ³⁾]	-	-
i10 (2. Gen.)	IA IA-HME	2013 ▶ 2019 2015 ▶ 2019	H4-LED (11342U6000X2) W5W-LED (11961HU60X2)	E13 13903	Low beam/ High beam [25 ³⁾] Front parking light ¹⁾	-	-
i20 (1. Gen., Facelift)	PB, PBT	2012 ▶ 2014	H7-LED (11972U6000X2)	E13 13497 E13 13518	Low beam	-	-
i20, i20 Active (2. Gen.), i20 Fließheck, Coupé (2. Gen.)	GB, GB-HME	2014 ▶ 2018	W5W-LED (11961HU60X2)	E13 14184	Front parking light ¹⁾	-	-
i20, i20 Active (2. Gen.)	GB, GB-HME	2014 ▶ 2018	H4-LED (11342U6000X2)	E13 14184	Low beam/ High beam [30 ³⁾]	-	⁴⁾ CANBus H4-LED (18960X2)
i30 / i30cw (2. Gen.)	GDH, GDH-HME, GDHG5	2011 ▶ 2017	H7-LED (11972U6000X2)	E9 6691	Low beam	Type H (11172X2)	-
i30 / i30cw (3. Gen.)	PDE PDe	2017 ▶ 2019 2019 ▶ 2020	H7-LED (11972U6000X2)	E9 16394	Low beam	Type H (11172X2)	-

Other models ▼



Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
-------------------	------	---------------------	--------------	--------------------------	-------------------	------------------------------------	--------------------------------------

JAGUAR, DAIMLER

Mark II, 240, 340 250 V8	340	1959 ▶ 1969	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾	-	-
Mark X, 420 G, Daimler DS420 420, Daimler Sovereign	420 G 420 Saloon	1961 ▶ 1992	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾	-	-

JEEP

Renegade	BU	2014 ▶ *	H4-LED (11342U6000X2)	E24 6268	Low beam/ High beam [20 ³⁾	-	-
----------	----	----------	--------------------------	----------	--	---	---

KAWASAKI (Motorcycle)

NINJA 125	BX125A	2018 ▶ *	H4-LED (11342U6000X1)	E9 6598	Low beam/ High beam [17,5 ³⁾	-	-
	BX125B	2020 ▶ *					
NINJA 250SL	BX250A	2014 ▶ *	H4-LED (11342U6000X1)	E9 6598	Low beam/ High beam [17,5 ³⁾	-	-
VULCAN S	EN650D, EN650DA2	2016 ▶ *	H4-LED (11342U6000X1)	E11 6321	Low beam/ High beam [12,5 ³⁾	-	-
	EN650J, EN650JA2	2020 ▶ *					
Z125	BR125K	2018 ▶ *	H4-LED (11342U6000X1)	E9 6598	Low beam/ High beam [17,5 ³⁾	-	-
	BR125L	2020 ▶ *					
Z250SL	BR250E	2014 ▶ *	H4-LED (11342U6000X1)	E9 6598	Low beam/ High beam [17,5 ³⁾	-	-
Z650	ER650H, ER650HA2	2016 ▶ *	H4-LED (11342U6000X1)	E4 24914	Low beam/ High beam [12,5 ³⁾	-	-
ZEPHYR 1100	ZRT 10 A	1992 ▶ 1997	H4-LED (11342U6000X1)	E4 20582	Low beam/ High beam [20 ³⁾	-	-

KIA

Cee´d (2. Gen.)	JD	2012 ▶ 2018	H7-LED (11972U6000X2)	E9 6738	Low beam/ High beam [17,5 ³⁾	Type H (11172X2) (Low beam only)	-
Cee´d (3. Gen.)	CD, CDG	2018 ▶ *	H7-LED (11972U6000X2)	E9 22079	Low beam	Type H (11172X2)	-
Picanto (2.Gen.)	TA TA/PL	2011 ▶ 2017 2014 ▶ 2017	H4-LED (11342U6000X2)	E13 13170	Low beam/ High beam [25 ³⁾	-	-
Picanto (3. Gen.)	JA, JA/PL	2017 ▶ *	H4-LED (11342U6000X2)	E13 34505	Low beam/ High beam [25 ³⁾	-	-
			W5W-LED (11961HU60X2)		Front parking light ¹⁾		

KNAUS TABBERT / WEINSBERG / BAVARIACAMP

Box Star, Cosmos, Imperiale, Meteor, Sky Ti, Sky Wave, Sky Traveller, Sport Ti, Sport Traveller, Sun Traveller, Sun Ti, Van Ti ⁵⁾	X250	2006 ▶ 2014	H7-LED (11972U6000X2)	E3 2447 (RH) / E3 2448 (LH)	Low beam	-	-
	X250/2, X250/3, X250/4, X250L	2007 ▶ 2014					
	K250/1, K250/2, K250/3, K250/4, K250L	2011 ▶ 2014					
	KYL	2012 ▶ 2014					
Live Ti, Live Wave, Main Camp, Sky Ti, Sky Traveller, Sky Wave, Sun Ti, Van Ti, Van Tourer, CaraCompact, Edition [Pepper], CaraLoft, CaraSuite, CaraHome ⁵⁾	K250L, K250/1, K250/2, K250/3, K250/4, KYL	2014 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
	KYL/1	2019 ▶ *					

Other models ▼



Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
-------------------	------	---------------------	--------------	--------------------------	-------------------	------------------------------------	--------------------------------------

KTM (Motorcycle)

690 DUKE	KTM 690 Duke	2011 ▶ 2016	H4-LED (11342U6000X1)	E9 6200	Low beam/ High beam [20 ³⁾]	-	-
690 DUKE R	KTM 690 Duke	2016 ▶ *	H4-LED (11342U6000X1)	E9 6200	Low beam/ High beam [20 ³⁾]	-	-
690 ENDURO R	KTM 690 LC4	2019 ▶ *	H4-LED (11342U6000X1)	E13 35075	Low beam/ High beam [12,5 ³⁾]	-	-
690 SMC R	KTM 690 LC4	2019 ▶ *	H4-LED (11342U6000X1)	E13 35075	Low beam/ High beam [12,5 ³⁾]	-	-
1290 SUPERDUKE R 1290 SUPERDUKE SE	KTM Superduke	2013 ▶ 2016	H4-LED (11342U6000X1)	E4 17086	Low beam/ High beam [20 ³⁾]	-	-

LADA, VAZ, OAO, AVTOAZ, PJSC

Niva Taiga 4x4, 4x4 Urban	VAZ 2121, 2121DE, 2121A, 212140, 212140 NIVA, 2121, 2121**, 2121***DA, M2121, N2121, MZ2121, NZ2121, MU2121, MU2131, M2131	1980 ▶ *	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾]	-	-
---------------------------------	--	----------	--------------------------	---------------------------	--	---	---

LAND ROVER

Defender 90 Defender 110 Defender 130	LD	1996 ▶ 2016	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾]	-	-
Range Rover (1. Gen.)	Range Rover	1970 ▶ 1996	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾]	-	-

LAND ROVER, ROVER, BRITISH LEYLAND

Land Rover 88	LR 88/oP, LR 88/dP, LR 88/dP, LR 88/oL, LR 88/ dZ, LR 88/oZ, LR 88 OL 3, LR 88 DL 3, LR 88 OP 3, LR 88 DP 3	1970 ▶ 1984	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾]	-	-
Land Rover 109	LR 109/oP, LR 109/dP, LR 109/oL, LR 109/dL, LR 109/oZ, LR 109/dZ, LR 109 OP 3, LR 109 OL 3, LR 109 DP 3, LR 109 DL 3	1970 ▶ 1984	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾]	-	-

LEYLAND INNOCENTI

Mini	Mini B38, Mini B39	1974 ▶ 2000	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾]	-	-
------	--------------------	-------------	--------------------------	---------------------------	--	---	---

LMC

Breezer, Cruiser, Liberty ⁵⁾	FI-70/156 FK-70/156 FI-2007/46 2007/46-3FK	2012 ▶ 2014	H7-LED (11972U6000X2)	E3 2447 (RH) / E3 2448 (LH)	Low beam	-	-
Carado, Cruiser, CVE, Element, Etrusco, Grand Breezer, Innovan, Solifer, Sunlight, V643 ⁵⁾	FI-2007/46, 2007/46-3FK, C-2007/46, LVF2	2014 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-

MAZDA

MX-5 (1. Gen.)	NA	1989 ▶ 1998	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾]	-	-
RX-7 (1. Gen.)	SA2	1979 ▶ 1985	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾]	-	-
2 (3.Gen.)	DJ1	2014 ▶ *	H4-LED (11342U6000X2)	E13 14125	Low beam/ High beam [25 ³⁾]	-	-

Other models ▼



Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
MERCEDES-BENZ							
A-Klasse (W 176)	176, 176 AMG 245 G, 245 G AMG	2012 ▶ 2014 2012 ▶ 2018	H7-LED (11972U6000X2)	E1 3255	Low beam	Type P (11182X2)	-
A-Klasse (W/V 177)	F2A	2018 ▶ *	H7-LED (11972U6000X2)	E8 9130	Low beam/ High beam [27,5 ³⁾]	Type P (11182X2)	-
B-Klasse	W246	2011 ▶ 2014	H7-LED (11972U6000X2)	E1 2994	Low beam/ High beam	Type E (11178X2)	-
B-Klasse (W 246)	246, 245G	2011 ▶ 2014	H7-LED (11972U6000X2)	E1 2994	Low beam	Type E (11178X2)	-
B-Klasse (W 246) Facelift	245G	2014 ▶ 2018	H7-LED (11972U6000X2)	E1 3748	Low beam	Type E (11178X2)	-
B-Klasse (W 247)	F2B	2018 ▶ *	H7-LED (11972U6000X2)	E8 9647	Low beam	Type P (11182X2)	-
Citan (W415, 1.Gen.)	X	2012 ▶ 2021	H4-LED (11342U6000X2)	E11 5814	Low beam/ High beam [27,5 ³⁾]	-	-
C-Klasse (W/S 205)	204, 204 AMG, 204 K, 204 K AMG	2014 ▶ 2019	H7-LED (11972U6000X2)	E1 3528	Low beam	Type E (11178X2)	-
C-Klasse (W/S/C 204, Facelift)	204, 204K	2011 ▶ 2014	H7-LED (11972U6000X2)	E1 2950	Low beam/ High beam [25 ³⁾]	Type E (11178X2)	⁴⁾ CANBus H7-LED (18952X2)
CLA (C/X 117)	117 245 G	2013 ▶ 2014 2013 ▶ 2019	H7-LED (11972U6000X2)	E1 3326	Low beam	Type E (11178X2)	-
GLC (X/C 253)	204 X	2016 ▶ 2019	H7-LED (11972U6000X2)	E4 18438	Low beam	-	-
V-Klasse (W477) ⁵⁾ Vito (W447) ⁵⁾ Vito Tourer (W447) ⁵⁾ Marco Polo (W447) ⁵⁾	639/2, 639/4, 639/5	2014 ▶ *	H7-LED (11972U6000X2)	E1 3655	Low beam	Type A (11184X2)	-
MERCEDES-BENZ / DAIMLER-BENZ							
R 107 SL Cabriolet C 107 SLC Coupé	107	1971 ▶ 1989	H4-LED (11342U6000X2)	E4 9 (LH) / E4 10 (RH)	Low beam/ High beam [45 ³⁾]	-	-
MERCEDES-BENZ / DAIMLER-BENZ/ DAIMLER/STEYER-DAIMLER-PUCH							
G-Klasse	460.2, 460.3, 461.4, 463 D, 463, 461, 461N, 461NN, 461N2	1979 ▶ 2018	H4-LED (11342U6000X2)	E1 14551 E1 14565	Low beam/ High beam [27,5 ³⁾ / 25 ³⁾]	-	-
MG							
MGB Roadster	MG B - 1800	1962 ▶ 1980	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾]	-	-
MGB GT	MG B-GT-Coupe	1965 ▶ 1980	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾]	-	-
MGC, MGC GT	MGC	1967 ▶ 1970	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾]	-	-
MG AUSTIN							
Midget Healey Sprite	Midget MK III Healey Sprite MK IV	1966 ▶ 1979	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾]	-	-
MINI							
MINI MINI Cabrio	R50, MINI, MINI-N	2001 ▶ 2008	H7-LED (11972U6000X2)	E1 1808	Low beam/ High beam [27,5 ³⁾]	-	-

Other models ▼



Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
mitsubishi							
Space Star/ Mirage (1. Facelift)	A00	2016 ▶ 2019	H4-LED (11342U6000X2)	E4 16195	Low beam/ High beam [30 ³⁾]	-	-
Space Star/ Mirage (2. Facelift)	A00	2019 ▶ *	H4-LED (11342U6000X2)	E4 27297	Low beam/ High beam [27,5 ³⁾]	-	-
Space Star, Mirage, Space Star Cross	A00	2016 ▶ 2019	W5W-LED (11961HU60X2)	E4 16195	Front parking light ¹⁾	-	-
MITSUBISHI, MMC							
Pajero (1. Gen.)	L 040	1982 ▶ 1991	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ /25 ³⁾ /37,5 ³⁾]	-	-
MORGAN							
4/4 Plus 4, Plus 4 Sport, Plus 4 Super Sport	1800, 2000, 4/4, 1600	1998 ▶ *	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ /25 ³⁾ /37,5 ³⁾]	-	-
Plus 8, +8	Plus 8	1968 ▶ *	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ /25 ³⁾ /37,5 ³⁾]	-	-
Roadster, Roadster Sport	3000	2011 ▶ *	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ /25 ³⁾ /37,5 ³⁾]	-	-
NISSAN							
Juke	F15 F15-LPG F15M	2010 ▶ 2014 2012 ▶ 2014 2013 ▶ 2014	H4-LED (11342U6000X2)	E8 5540	Low beam/ High beam [25 ³⁾]	-	-
			W5W-LED (11961HU60X2)	E4 14492	Front parking light ¹⁾	-	-
Micra (4. Gen. Facelift)	K13, K13-LPG, K13M	2014 ▶ 2018	H4-LED (11342U6000X2)	E9 11032	Low beam/ High beam [20 ³⁾]	-	-
OPEL / VAUXHALL							
Astra (J, 4. Gen.)	P-J	2009 ▶ 2015	H7-LED (11972U6000X2)	E1 2820	Low beam	Type P (11182X2)	-
Astra (J, 4. Gen.) Sports Tourer	P-J/SW	2010 ▶ 2015	H7-LED (11972U6000X2)	E1 2820	Low beam	Type P (11182X2)	-
Astra (J, 4. Gen.) Sports Tourer Van	P-J/SW/V	2010 ▶ 2015	H7-LED (11972U6000X2)	E1 2820	Low beam	Type P (11182X2)	-
Astra (J, 4. Gen.) Van	P-J/V	2010 ▶ 2015	H7-LED (11972U6000X2)	E1 2820	Low beam	Type P (11182X2)	-
Astra (K, 5. Gen.)	B-K	2015 ▶ 2019	H7-LED (11972U6000X2)	E9 11834	Low beam	-	CANBus H7-LED (18952X2)
Crossland X	P7 Monocab C	2017 ▶ 2020	H7-LED (11972U6000X2)	E9 16429	Low beam/ High beam [30 ³⁾]	-	-
Karl	D-A	2015 ▶ *	H4-LED (11342U6000X2)	E13 14352	Low beam/ High beam [25 ³⁾]	-	-
Karl Rocks	D-A	2015 ▶ *	H4-LED (11342U6000X2)	E13 14352	Low beam/ High beam [25 ³⁾]	-	-
Mokka	G1 (A)	?? ▶ ??	H7-LED (11972U6000X2)	E13 13562	Low beam	-	-
Mokka (A)	J-A	2012 ▶ 2016	H7-LED (11972U6000X2)	E13 13562	Low beam	-	-
Movano C (3. Gen.)	Y	2021 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
Viva	D-A	2015 ▶ *	H4-LED (11342U6000X2)	E13 14352	Low beam/ High beam [25 ³⁾]	-	-
Zafira Tourer (3. Gen. Facelift)	P-J/SW, P-J/SW/V	2016 ▶ 2019	H7-LED (11972U6000X2)	E1 4238	Low beam	Type E (11178X2)	-

Other models ▼



Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
-------------------	------	---------------------	--------------	--------------------------	-------------------	------------------------------------	--------------------------------------

PEUGEOT

3008 (1. Gen., Facelift)	0U	2013 ▶ 2016	H7-LED (11972U6000X2)	E2 13023	Low beam	Type N (11183X2)	CANBus H7-LED (18952X2)
308 (1. Gen.)	4A/4C	2007 ▶ 2015	H7-LED (11972U6000X2)	E3 2551 / E3 2552	Low beam	-	-
308 (2. Gen.)	4*****, L	2013 ▶ 2016	H7-LED (11972U6000X2)	E24 6252	Low beam	-	-
308 (2. Gen.) Facelift	L	2017 ▶ 2021	H7-LED (11972U6000X2)	E24 6284	Low beam/ High beam [12,5 ³⁾]	-	-
Boxer (2. Gen.) ⁵⁾	Y	2006 ▶ 2014	H7-LED (11972U6000X2)	E3 2447 (RH) / E3 2448 (LH)	Low beam	-	-
Boxer (2. Gen.) Facelift ⁵⁾	Y	2014 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
Expert ⁵⁾	X*****, X G9	2006 ▶ 2016 2007 ▶ 2013	H4-LED (11342U6000X2) W5W-LED (11961HU60X2)	E2 05074	Low beam/ High beam [25 ³⁾] Front parking light ¹⁾	- -	- -
Partner (1. Gen.) ⁵⁾ Ranch (1. Gen.) ⁵⁾	M59, G*KFW*, G*NFU*, G*WJY*, G*RHY*	2002 ▶ 2009	H4-LED (11342U6000X2)	E4 9849	Low beam/ High beam [30 ³⁾]	-	-
Partner (1. Gen.) ⁵⁾ Ranch (1. Gen.) ⁵⁾	M 59 GL, M 59 GN	2003 ▶ 2009	H4-LED (11342U6000X2)	E4 9849	Low beam/ High beam [30 ³⁾]	-	-
Partner (1. Gen.) ⁵⁾ Ranch (1. Gen.) ⁵⁾	G*9HX*, G*9HW*	2005 ▶ 2009	H4-LED (11342U6000X2)	E4 9849	Low beam/ High beam [30 ³⁾]	-	-

PIAGGIO (Motorcycle)

Beverly M69100 Beverly M69200 Beverly M69300 Beverly M69400	M69	2010 ▶ *	H7-LED (11972U6000X1)	E13 12536	Low beam/ High beam [12,5 ³⁾]	-	-
--	-----	----------	--------------------------	-----------	--	---	---

RENAULT

Clio (4. Gen., Facelift)	R	2016 ▶ 2020	H7-LED (11972U6000X2)	E1 3362	Low beam	-	-
Kadjar	RFE	2015 ▶ 2022	H7-LED (11972U6000X2)	E1 4049	Low beam	Type P (11182X2)	-
Kangoo (2. Gen.)	FW	2013 ▶ *	H4-LED (11342U6000X2)	E11 5826	Low beam/ High beam	-	-
Kangoo (2. Gen.) Kangoo BE BOP Kangoo Z.E.	W, KW, FW	2008 ▶ 2012	H4-LED (11342U6000X2)	E13 2442	Low beam/ High beam [30 ³⁾]	-	-
Kangoo (2. Gen. Facelift) Kangoo Z.E. Kangoo Z.E. H2	W, KW, FW	2013 ▶ 2020	H4-LED (11342U6000X2) W5W-LED (11961HU60X2)	E11 5827	Low beam/ High beam [27,5 ³⁾] Front parking light ¹⁾	- -	- -
Megane (3. Gen.)	Z	2008 ▶ 2016	H7-LED (11972U6000X2) W5W-LED (11961HU60X2)	E1 2538	Low beam Front parking light ¹⁾	- -	- -
Megane (4. Gen.)	RFB	2016 ▶ 2020	H7-LED (11972U6000X2)	E9 11935	Low beam/ High beam [17,5 ³⁾]	Type I (11179X2)	-
Trafic (2. Gen.)	EL, FL, JL	2001 ▶ 2015	H4-LED (11342U6000X2)	E9 5635	Low beam/ High beam	-	-
Twingo (2. Gen.)	CN0	2007 ▶ 2011	H4-LED (11342U6000X2)	E1 2340	Low beam/ High beam	-	-
Twingo (2. Gen. Facelift)	N	2012 ▶ 2014	H4-LED (11342U6000X2)	E9 6447	Low beam/ High beam [20 ³⁾]	-	-

ROLLS-ROYCE

Corniche	NZ, SZ	1995 ▶ 2002	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [27,5 ³⁾ / 25 ³⁾]	-	-
----------	--------	-------------	--------------------------	---------------------------	--	---	---

Other models ▼



Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
-------------------	------	---------------------	--------------	--------------------------	-------------------	------------------------------------	--------------------------------------

ROVER

Mini	Mini MK II, XN	1975 ▶ 2000	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾	-	-
------	----------------	-------------	--------------------------	---------------------------	--	---	---

SACHSENRING

Trabant P 601	P 601, Trabant P 601 A, Trabant P 601 L	1966 ▶ 1990	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [27,5 ³⁾ / 25 ³⁾	-	-
---------------	--	-------------	--------------------------	---------------------------	--	---	---

SEAT

Ibiza (4. Gen. Facelift) Ibiza ST	6J, 6JN	2012 ▶ 2016	H4-LED (11342U6000X2) W5W-LED (11961HU60X2)	E9 5788	Low beam/ High beam [30 ³⁾] Front parking light ¹⁾	-	-
Mii Mii Electric	AA, AAE, AAN	2012 ▶ *	H4-LED (11342U6000X2)	E1 3215	Low beam/ High beam [27,5 ³⁾]	-	-

SKODA

Citigo	AA, AAE, AAN	2011 ▶ 2017	H4-LED (11342U6000X2)	E1 3192	Low beam/ High beam [25 ³⁾]	-	-
Octavia (3. Gen.)	5E	2012 ▶ 2016	H7-LED (11972U6000X2)	E1 3340	Low beam	-	-
Octavia (3. Gen., Facelift)	5E	2016 ▶ 2020	H7-LED (11972U6000X2)	E1 4337	Low beam	-	-
Yeti	5L	2009 ▶ 2013	H4-LED (11342U6000X2)	E1 2646	Low beam/ High beam [27,5 ³⁾]	-	-

SMART

Fortwo (3. Gen.) Forfour (2. Gen.)	453	2014 ▶ *	H4-LED (11342U6000X2)	E9 11392	Low beam/ High beam [20 ³⁾]	-	-
Fortwo (3. Gen.) Forfour (2. Gen.)	451	2014 ▶ *	H4-LED (11342U6000X2)	E9 11294	Low beam/ High beam [17,5 ³⁾]	-	-

TRIUMPH, STANDARD, BRITISH LEYLAND

Triumph TR 5	Triumph TR 5	1967 ▶ 1969	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾	-	-
Triumph TR 6	TR 6	1969 ▶ 1976	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾	-	-
Triumph TR 7	TR 7	1976 ▶ 1980	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾	-	-
Triumph Spitfire	Spitfire MK 3, Spitfire MK IV	1967 ▶ 1980	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾	-	-

SUZUKI

Swift (4. Gen.)	FZ/NZ	2013 ▶ 2017	H4-LED (11342U6000X2)	E13 12913	Low beam/ High beam	-	-
Swift (5. Gen. Facelift)	NZ	2013 ▶ 2017	H4-LED (11342U6000X2) W5W-LED (11961HU60X2)	E13 12913	Low beam/ High beam [27,5 ³⁾] Front parking light ¹⁾	-	-
Swift (6. Gen.)	AZ	2017 ▶ *	H4-LED (11342U6000X2)	E13 24687	Low beam/ High beam [30 ³⁾]	-	-

Other models ▼



Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
-------------------	------	---------------------	--------------	--------------------------	-------------------	------------------------------------	--------------------------------------

SUZUKI (Motorcycle)

DL1000 V-Strom	DD WDD0	2014 ▶ 2019 2016 ▶ 2019	H7-LED (11972U6000X1)	E13 13829	Low beam	-	-
DL650 V-Strom	WC70	2016 ▶ *	H7-LED (11972U6000X1)	E13 13829	Low beam	-	-
DL650U V-Strom	WC71	2016 ▶ *	H7-LED (11972U6000X1)	E13 13829	Low beam	-	-
GLADIUS	WVCX	2009 ▶ 2016	H4-LED (11342U6000X1)	E11 5310	Low beam/ High beam [20 ³⁾]	-	-
GSX-S750	WC50	2016 ▶ *	H4-LED (11342U6000X1)	E4 24961	Low beam/ High beam [17,5 ³⁾]	-	-
GSX-S750W	WC51	2018 ▶ *	H4-LED (11342U6000X1)	E4 24961	Low beam/ High beam [17,5 ³⁾]	-	-
GSX-S750U	WC52	2018 ▶ *	H4-LED (11342U6000X1)	E4 24961	Low beam/ High beam [17,5 ³⁾]	-	-
INTRUDER C800	WVBM	2005 ▶ 2016	H4-LED (11342U6000X1)	E13 9465	Low beam/ High beam [20 ³⁾]	-	-
INTRUDER C1500	C1	2012 ▶ 2016	H4-LED (11342U6000X1)	E13 9465	Low beam/ High beam [20 ³⁾]	-	-
SFV650 SFV650U SFV650A SFV650UA	WVCX	2009 ▶ 2016	H4-LED (11342U6000X1)	E11 5310	Low beam/ High beam [20 ³⁾]	-	-
VL800 VL800U VL800B VL800BUE VL800C VL800CUE	WVBM	2005 ▶ 2016	H4-LED (11342U6000X1)	E13 9465	Low beam/ High beam [20 ³⁾]	-	-
VL1500	WVAL	2004 ▶ 2016	H4-LED (11342U6000X1)	E13 9465	Low beam/ High beam [20 ³⁾]	-	-
VL1500	C1	2012 ▶ 2016	H4-LED (11342U6000X1)	E13 9465	Low beam/ High beam [20 ³⁾]	-	-

TOYOTA

Vitz (3. Gen.)	XP13M(a), XP13N(a), XP13M(a)MS1	2010 ▶ 2014	H4-LED (11342U6000X2)	E13 13140	Low beam/ High beam [20 ³⁾]	-	-
Yaris (1. Gen.)	XP13	2010 ▶ 2014	H4-LED (11342U6000X2)	E13 13140	Low beam/ High beam	-	-
Yaris (2. Gen.)	XP13	2014 ▶ 2017	H4-LED (11342U6000X2)	E11 6259	Low beam/ High beam	-	-
Yaris (2. Gen.)	XP9(a), XP9F(a) XP9F(a)MS1	2005 ▶ 2011 2010 ▶ 2011	H4-LED (11342U6000X2) W5W-LED (11961HU60X2)	E2 08700	Low beam/ High beam [25 ³⁾] Front parking light ¹⁾	-	-
Yaris (3. Gen.)	XP13M(a), XP13N(a), XP13M(a)MS1	2010 ▶ 2014	H4-LED (11342U6000X2) W5W-LED (11961HU60X2)	E13 13140	Low beam/ High beam [20 ³⁾] Front parking light ¹⁾	-	-

TRIUMPH (Motorcycle)

STREET SCRAMBLER	DC03, DC03R	2018 ▶ *	H4-LED (11342U6000X1)	E9 11895	Low beam/ High beam [10 ³⁾]	-	-
STREET TWIN	DP03, DP03R	2018 ▶ *	H4-LED (11342U6000X1)	E9 11895	Low beam/ High beam [10 ³⁾]	-	-
SPEED TWIN	DD01	2018 ▶ *	H4-LED (11342U6000X1)	E9 11895	Low beam/ High beam [10 ³⁾]	-	-
Tiger 1050	115NG	2006 ▶ 2020	H7-LED (11972U6000X1)	E9 1270	Low beam	-	-

Other models ▼



Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
VW							
914	47	1969 ▶ 1976	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾	-	-
Beetle Beetle Dune Beetle Cabrio	16 16/5C7 & 5C8	2011 ▶ 2016	H4-LED (11342U6000X2)	E1 3203	Low beam/ High beam [30 ³⁾	-	-
Caddy (1. Gen.) ⁵⁾	14D	1979 ▶ 2007	H4-LED (11342U6000X2)	E1 14551 E1 14565	Low beam/ High beam [27,5 ³⁾ / 25 ³⁾	-	-
Golf (1. Gen.)	17, 17 CK	1974 ▶ 1983	H4-LED (11342U6000X2)	E1 14551 E1 14565	Low beam/ High beam [27,5 ³⁾ / 25 ³⁾	-	-
Golf Cabrio (1. Gen.)	155	1979 ▶ 1993	H4-LED (11342U6000X2)	E1 14551 E1 14565	Low beam/ High beam [27,5 ³⁾ / 25 ³⁾	-	-
Golf (2. Gen.)	19 E, 19 E-299, 19EL	1983 ▶ 1992	H4-LED (11342U6000X2)	E1 14551 E1 14565	Low beam/ High beam [27,5 ³⁾ / 25 ³⁾	-	-
Golf (3. Gen.) Golf Variant (3. Gen.) Golf Cabrio (3. Gen.)	1HX0, 1HX0F, 1HX1, 1HX0E, 1HX1, 1HX1, 1EXO	1991 ▶ 1999	H4-LED (11342U6000X2)	E1 44464 (LH) / E1 44465 (RH)	Low beam/ High beam [50 ³⁾	-	-
Golf (4. Gen.)	1J	1997 ▶ 2006	H7-LED (11972U6000X2)	E1 7611	Low beam	-	-
Golf (6. Gen.) Golf Cabrio (6. Gen.)	1K, 1KM 1K	2008 ▶ 2013 2011 ▶ 2016	H7-LED (11972U6000X2) W5W-LED (11961HU60X2)	E8 4816 E8 4816 E9 5813	Low beam Front parking light ¹⁾	Type A (11184X2) - -	- - -
Golf (7. Gen.) Golf Variant (7. Gen.)	AU, AUV, 1 K, 1 KM	2012 ▶ 2017	H7-LED (11972U6000X2)	E8 7169 E9 6765	Low beam Low beam	Type A (11184X2) Type D (11176X2)	- -
Golf (7. Gen.) (Facelift) Golf Variant (7. Gen.) (Facelift)	AU, AUV, 1 K, 1 KM	2017 ▶ 2020	H7-LED (11972U6000X2)	E8 8526	Low beam	Type P (11182X2)	-
Golf Sportsvan	AUV 1 KM	2014 ▶ 2017 2015 ▶ 2017	H7-LED (11972U6000X2)	E9 11342	Low beam	Type D (11176X2)	-
Käfer	11, 13	1967 ▶ 2004	H4-LED (11342U6000X2)	E1 14551 E1 14565	Low beam/ High beam [27,5 ³⁾ / 25 ³⁾	-	-
Käfer Cabriolet	15	1967 ▶ 1980	H4-LED (11342U6000X2)	E1 14551 E1 14565	Low beam/ High beam [27,5 ³⁾ / 25 ³⁾	-	-
Kurierwagen (Type 181/182)	18, 18 - 63	1969 ▶ 1980	H4-LED (11342U6000X2)	E1 14551 E1 14565	Low beam/ High beam [27,5 ³⁾ / 25 ³⁾	-	-
LT (1. Gen.) ³⁾	283 CF, 283, 281 CH, 281, 281 CG, 283 CG, 291 CH, 291, 293 CH, 293, 291 CG, 293 CG, 281-363 CH, 281- 363 CG, 281-363, 291- 512, 293-512, 293-909	1975 ▶ 1985	H4-LED (11342U6000X2)	E1 14551 E1 14565	Low beam/ High beam [27,5 ³⁾ / 25 ³⁾	-	-
Passat B6	3C	2005 ▶ 2010	H7-LED (11972U6000X2)	E9 5507	Low beam	Type I (11179X2)	CANBus H7-LED (18952X2)
Passat B7 (Facelift)	3C	2010 ▶ 2015	H7-LED (11972U6000X2)	E1 3058	Low beam	-	-
Passat B8	3C	2014 ▶ *	H7-LED (11972U6000X2)	E9 11464	Low beam	-	-

Other models ▼



Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
Polo (5. Gen.)	6R	2009 ▶ 2014	H4-LED (11342U6000X2)	E9 5856	Low beam/ High beam [17,5 ³⁾]	-	-
Polo (5. Gen., Facelift)	6R	2014 ▶ 2017	H7-LED (11972U6000X2)	E8 6879	Low beam/ High beam [27,5 ³⁾]	Type P (11182X2)	-
PoloCross, CrossPolo	6R	2010 ▶ 2015	H7-LED (11972U6000X2)	E1 2714	Low beam/ High beam [17,5 ³⁾]	Type P (11182X2)	-
T2 Bus ⁵⁾ T2 Transporter ⁵⁾	21 F, 26, 28, 23, 22, 21, 22	1967 ▶ 1979	H4-LED (11342U6000X2)	E1 14551 E1 14565	Low beam/ High beam [27,5 ³⁾ / 25 ³⁾]	-	-
T3 Transporter ⁵⁾ T3 Kombi ⁵⁾ T3 Bus ⁵⁾ T3 Caravelle ⁵⁾ T3 California ⁵⁾	245, 251, 253, 255, 253-135, 253-609, 253- 299, 255-299, 251-299, 245-299, 253-6-299, 247, 247-299	1979 ▶ 1992	H4-LED (11342U6000X2)	E1 14551 E1 14565	Low beam/ High beam [27,5 ³⁾ / 25 ³⁾]	-	-
T4 Transporter ⁵⁾ T4 Multivan ⁵⁾ T4 California ⁵⁾ T4 Caravelle ⁵⁾	70X0A, 70X0D, 70X0B, 70X0BL, 70X0BN, 70X1B, 70X1A, 70X1D, 70X1BL, 70X0C, 70X1C, 70X02C, 70X12C, 70X02BN, 70X02D, 70X02A, 70X12A, 70X12D, 7DB	1990 ▶ 2003	H4-LED (11342U6000X2)	E1 44437 (LH) / E1 44438 (RH)	Low beam/ High beam [50 ³⁾]	-	-
T5 Caravelle ⁵⁾ T5 California ⁵⁾ T5 Multivan ⁵⁾ T5 Transporter ⁵⁾	7HM, 7HC, 7HCA, 7HMA, 7HK, 7J0	2003 ▶ 2009	H4-LED (11342U6000X2) W5W-LED (11961HU60X2)	E1 1366	Low beam/ High beam [37,5 ³⁾] Front parking light ¹⁾	- - -	- - -
T5 Caravelle Facelift ⁵⁾ T5 California Facelift ⁵⁾ T5 Multivan Facelift ⁵⁾ T5 Transporter Facelift ⁵⁾	7HC, 7HMA, 7J0	2009 ▶ 2016	H4-LED (11342U6000X2) W5W-LED (11961HU60X2)	E1 2705	Low beam/ High beam [30 ³⁾] Front parking light ¹⁾	- - -	4) -
T5 Facelift (Caravelle, California, Multivan, Transporter)	7Hx	??? ▶ ??	H4-LED (11342U6000X2)	E1 2707	Low beam/ High beam	-	-

Note for VW T5: some models have been factory-fitted with H7 and not H4 halogen lamps, despite identical headlamp approval numbers. Before purchasing the H4-LED lamp, please indicate directly the type of halogen lamp installed. The approval of the Philips Ultinon Pro6000 H4-LED is only valid for the type of H4 lamp installed.

T-Cross	C1	2018 ▶ *	H7-LED (11972U6000X2)	E9 22186	Low beam	-	CANBus H7-LED (18952X2)
Tiguan (1. Gen.)	5N	2007 ▶ 2011	H7-LED (11972U6000X2)	E1 2393	Low beam	Type P (11182X2)	-
Tiguan (1. Gen.) Facelift	5N	2011 ▶ 2016	H7-LED (11972U6000X2)	E1 3175	Low beam	Type A (11184X2)	-
Tiguan (2. Gen.)	5N	2016 ▶ 2020	H7-LED (11972U6000X2)	E1 4116	Low beam/ High beam [25 ³⁾]	Type E (11178X2)	-
Touran (2. Gen.)	1T	2015 ▶ *	H7-LED (11972U6000X2)	E1 3985	Low beam	Type D (11176X2)	-
T-Roc	A1	2017 ▶ *	H7-LED (11972U6000X2)	E9 16552	Low beam	Type D (11176X2)	-
Type 3 (1500 / 1600)	31	1961 ▶ 1973	H4-LED (11342U6000X2)	E1 14551 E1 14565	Low beam/ High beam [27,5 ³⁾ / 25 ³⁾]	-	-
up! e-up! cross up!	AA, AAE, AAN	2011 ▶ 2016	H4-LED (11342U6000X2)	E1 3149	Low beam/ High beam [30 ³⁾]	-	-
up! (Facelift) e-up! cross up! up! GTI	AA, AAN	2016 ▶ *	H4-LED (11342U6000X2)	E8 8227	Low beam/ High beam [27,5 ³⁾]	-	7)

Other models ▼



Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
-------------------	------	---------------------	--------------	--------------------------	-------------------	------------------------------------	--------------------------------------

VW, MAN-VW, ARGE VW-MAN

6.90 F 8.136 F 8.90 F 9.136 F	6.90 F 8.136 F 8.90 F 9.136 F	1979 ▶ 1987	H4-LED (11342U6000X2)	E4 1 E4 12 E11 0035	Low beam/ High beam [20 ³⁾ / 25 ³⁾ /37,5 ³⁾	-	-
--	--	-------------	--------------------------	---------------------------	--	---	---

WESTFALIA, RAPIDO

Jules Verne ⁵⁾	639 639/5	2016 ▶ * 2019 ▶ *	H7-LED (11972U6000X2)	E1 3655	Low beam	Type A (11184X2)	-
---------------------------	--------------	----------------------	--------------------------	---------	----------	---------------------	---

YAMAHA (Motorcycle)

MT-07 MT07A	RM17, RM18	2016 ▶ 2018	H4-LED (11342U6000X1)	E4 17394	Low beam/ High beam [12,5 ³⁾	-	-
MT-07 MT07A MTN690-A	RM17, RM18	2018 ▶ *	H4-LED (11342U6000X1)	E4 17066	Low beam/ High beam [12,5 ³⁾	-	-
MT-09	RN29	2013 ▶ 2016	H4-LED (11342U6000X1)	E4 17066	Low beam/ High beam [12,5 ³⁾	-	-
MTM850 XSR900	RN43	2015 ▶ *	H4-LED (11342U6000X1)	E13 8785	Low beam/ High beam [17,5 ³⁾	-	-
YZF-R1	RN12	2003 ▶ 2008	H7-LED (11972U6000X1)	E13 8996	Low beam	-	-

YAMAHA, MBK (Motorcycle)

XSR700	RM11, RM12	2015 ▶ *	H4-LED (11342U6000X1)	E13 8785	Low beam/ High beam [17,5 ³⁾	-	-
MTM690 MTM690D	RM36, RM37	2021 ▶ *	H4-LED (11342U6000X1)	E13 8785	Low beam/ High beam [17,5 ³⁾	-	-

Legal note: you are responsible for compliance with all applicable legal requirements. The Philips Ultinon Pro6000 range is type-approved for certain vehicle models only. To check if your vehicle is covered and the procedure in force in your country please visit: philips.com/roadlegalLED.

¹⁾ * corresponds to end of production

²⁾ ** LB corresponds to passing beam/ HB corresponds to driving beam

³⁾ The specified high beam index I'_{M} with H4-LED or H7-LED differs from the specification on the headlamp. The permissible sum of the main beam characteristics of all main beam headlamps must not exceed 100. Reference mark I'_{M} with H7-LED or H4-LED for the main beam of each model is as below. For more information, see Q&A.

⁴⁾ In the event of an error message, the optional CANbus must be used.

⁵⁾ Those vehicles (camper-vans and similar classes / body types) are also approved whose headlamps comply with the listed UN(ECE) type approval and have a multi-stage approval on the basis of the named basic vehicle.

⁶⁾ The road approval of the Philips Ultinon Pro6000 LED lamp is only valid if installed where required with Philips original accessories. Please check the compatibility list to see if additional accessories are required for your vehicle.

⁷⁾ For vehicle models with faulty cornering light function, the use of the optional CANbus is required.

