

PHILIPS

Ultinon Pro6000 LED



Compatibility list **Philips Ultinon Pro6000**

Updated on: 30.05.2023



Compatibility list

Philips Ultinon Pro6000

Updated on: 30.05.2023

Consult regularly our list on:
Philips.com/roadlegalLED



Product and ordering information

Product description	Application	Part number	Packaging	Order number – GOC
Ultinon Pro6000 H4-LED	Low beam/High beam	11342U6000X2	X2 (2 Lamps)	01365131
Ultinon Pro6000 H7-LED	Low beam/High beam	11972U6000X2	X2 (2 Lamps)	01361331
Connection ring Type A	Accessories H7-LED ⁶⁾	11184X2	X2 (2 Rings)	02009331
Connection ring Type D	Accessories H7-LED ⁶⁾	11176X2	X2 (2 Rings)	01681231
Connection ring Type E	Accessories H7-LED ⁶⁾	11178X2	X2 (2 Rings)	01679931
Connection ring Type H	Accessories H7-LED ⁶⁾	11172X2	X2 (2 Rings)	01630031
Connection ring Type I	Accessories H7-LED ⁶⁾	11179X2	X2 (2 Rings)	01683631
Connection ring Type K	Accessories H7-LED ⁶⁾	11180X2	X2 (2 Rings)	01675131
Connection ring Type N	Accessories H7-LED ⁶⁾	11183X2	X2 (2 Rings)	01636231
Connection ring Type P	Accessories H7-LED ⁶⁾	11182X2	X2 (2 Rings)	01677531
Adapter CANbus LED H7	Accessories H7-LED ⁶⁾	18952C2	C2 (2 Adapter)	05064994
Adapter CANbus LED H4	Accessories H4-LED ⁶⁾	18960C2	C2 (2 Adapter)	39809094

Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
ADRIA							
Compact, Coral, Lido, Matrix, Twin ³⁾	B, C N, P	2014 ▶ * 2016 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
ALFA ROMEO							
Giulietta	940	2013 ▶ 2016	H7-LED (11972U6000X2)	E3 2841	Low beam	-	-
AUDI							
A1 / A1 Sportback S1 / S1 Sportsback	8X	2015 ▶ 2018	H7-LED (11972U6000X2)	E9 11198	Low beam	-	-
A3 / A3 Sportback S3	8P 8PA	2003 ▶ 2008	H7-LED (11972U6000X2)	E1 1468	Low beam	-	4)
A4 S4	B8	2011 ▶ 2015	H7-LED (11972U6000X2)	E1 3064	Low beam	-	4)
Q3	8U, 8U1	2011 ▶ 2018	H7-LED (11972U6000X2)	E9 6391	Low beam	-	-
BMW							
1er (F20/F21)	IK2, IK4	2011 ▶ 2016	H7-LED (11972U6000X2)	E1 3132	Low beam	Type P (11182X2)	-
1er (F20/F21 Facelift)	IK2, IK4	2014 ▶ 2020	H7-LED (11972U6000X2)	E1 3999	Low beam/ High beam [20 ³⁾]	Type P (11182X2)	-
2er Active Tourer (F45)	F2AT, UKL-L	2014 ▶ 2017	H7-LED (11972U6000X2)	E1 3680	Low beam	-	-
2er Gran Tourer (F46)	F2GT, UKL-L	2015 ▶ 2018	H7-LED (11972U6000X2)	E1 3680	Low beam	-	-
3er GT (F34)	3-V	2013 ▶ 2016	H7-LED (11972U6000X2)	E4 16619	Low beam	-	-

Other models ▼

Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
BÜRSTNER							
Argos, Brevio, Ixeo, Lyseo, Nexxo, Travel ⁵⁾	4010, 4020 5020	2014 ▶ * 2017 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
CAPRON							
Carado, CVE, Etrusco, Solifer, Sunlight, Roadcar ⁵⁾	CKF1, CKF2 EG/CVF 001, CRF1, CRC3 CVF2 EG/CF 002	2015 ▶ * 2018 ▶ * 2019 ▶ * 2014 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
CARTHAGO							
Malibu, c-Tourer T, chic c-line T ⁵⁾	EG/CF004	2014 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
CITROËN							
Jumper / Relay	Y	2014 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
Jumpy Dispatch (2. Gen.) ⁵⁾	X CX G9	2007 ▶ 2016	H4-LED (11342U6000X2)	E2 05074	Low beam/ High beam [25 ³⁾]	-	-
DACIA							
Dokker	SD	2011 ▶ *	H4-LED (11342U6000X2)	E9 14005	Low beam/ High beam [20 ³⁾]	-	-
Dokker Pick Up	SD	2011 ▶ *	H4-LED (11342U6000X2)	E9 14005	Low beam/ High beam [20 ³⁾]	-	-
Duster (1. Gen.)	SD	2010 ▶ 2013	H7-LED (11972U6000X2)	E1 2737	Low beam	-	-
Duster (2. Gen.)	SR	2018 ▶ *	H7-LED (11972U6000X2)	E1 4583	Low beam	-	-
Lodgy	SD	2011 ▶ *	H4-LED (11342U6000X2)	E9 14005	Low beam/ High beam [20 ³⁾]	-	-
DETHLEFFS / PÖSSL							
Alpa, Globibus, Just, Pulse, Trend ⁵⁾	EG/DVF 001, EG/DVC 001 EG/DVP 001	2018 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
FIAT							
Doblo ⁵⁾	223, 223L	2005 ▶ 2010	H7-LED (11972U6000X2)	E13 1717 (LH) / E13 1718 (RH)	Low beam	-	-
Ducato	250	2014 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
Punto	199	2011 ▶ *	H4-LED (11342U6000X2)	E9 5876	Low beam/ High beam [20 ³⁾]	-	-
Scudo Scudo Lecapitaine	270, 270L 270Y	2007 ▶ 2016	H4-LED (11342U6000X2)	E2 05074	Low beam/ High beam [25 ³⁾]	-	-
Tipo Aegea (Ægea)	356	2016 ▶ 2020	H7-LED (11972U6000X2)	E9 16020	Low beam/ High beam [20 ³⁾]	-	-
500X	334	2015 ▶ 2018	H4-LED (11342U6000X2)	E24 6272	Low beam/ High beam [30 ³⁾]	-	-
FORD							
C-Max (2. Gen.)	DXA	2010 ▶ 2015	H7-LED (11972U6000X2)	E9 5897	Low beam	-	⁴⁾
Grand C-Max (2. Gen.)	DXA	2010 ▶ 2015	H7-LED (11972U6000X2)	E9 5897	Low beam	-	⁴⁾
Focus (4. Gen.)	DEH	2018 ▶ *	H7-LED (11972U6000X2)	E8 9147	Low beam	Type K (11180X2)	-
Tourneo Connect ⁵⁾	PJ2, PU2	2013 ▶ 2018	H7-LED (11972U6000X2)	E9 14122	Low beam	-	-
Transit Connect ⁵⁾	PJ2, PU2	2013 ▶ 2018	H7-LED (11972U6000X2)	E9 14122	Low beam	-	-

Other models ▼

Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
HYMER							
Compass, Elddis, EXT, Exsis-t, Grand Canyon, Serengeti, Sydney, Rio, Tramp ⁵⁾	EG/HF001 HRC3, EHG250, EHG2UC1, EHG2UC2	2014 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
HYUNDAI							
Getz	TB TBI	2002 ▶ 2009	H4-LED (11342U6000X2)	E13 8279	Low beam/ High beam [37,5 ³⁾]	-	-
i10 (2. Gen.)	IA IA-HME	2013 ▶ 2019	H4-LED (11342U6000X2)	E13 13903	Low beam/ High beam [25 ³⁾]	-	-
i20	PB, PBT	2012 ▶ 2014	H7-LED (11972U6000X2)	E13 13497	Low beam	-	-
i30 / i30cw (2. Gen.)	GDH, GDH-HME, GDHG5	2011 ▶ 2017	H7-LED (11972U6000X2)	E9 6691	Low beam	Type H (11172X2)	-
KNAUS TABBERT / WEINSBERG / BAVARIACAMP							
Live Ti, Live Wave, Main Camp, Sky Ti!, Sky Traveller, Sky Wave, Sun Ti, Van Ti, Van Tourer, CaraCompact, Edition [Pepper], CaraLoft, CaraSuite, CaraHome ⁵⁾	K250L, K250/1, K250/2, K250/3, K250/4, KYL KYL/1	2014 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
LMC							
Carado, Cruiser, CVE, Element, Etrusco, Grand Breezer, Innovan, Solifer, Sunlight, V643 ⁵⁾	FI-2007/46, 2007/46-3FK, C-2007/46, LVF2	2014 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
MERCEDES-BENZ							
A-Klasse (W 176)	176, 176 AMG 245 G, 245 G AMG	2012 ▶ 2018	H7-LED (11972U6000X2)	E1 3255	Low beam	Type P (11182X2)	-
B-Klasse (W 246)	246, 245G	2011 ▶ 2018	H7-LED (11972U6000X2)	E1 2994	Low beam	Type E (11178X2)	-
C-Klasse (W/S 205)	204, 204 AMG, 204 K, 204 K AMG	2014 ▶ 2019	H7-LED (11972U6000X2)	E1 3528	Low beam	Type E (11178X2)	-
CLA-Klasse (C/X 117)	117 245 G	2013 ▶ 2019	H7-LED (11972U6000X2)	E1 3326	Low beam	Type E (11178X2)	-
MINI							
MINI MINI Cabrio	R50, MINI, MINI-N	2001 ▶ 2008	H7-LED (11972U6000X2)	E1 1808	Low beam/ High beam [27,5 ³⁾]	-	-
NISSAN							
Juke	F15 F15-LPG F15M	2010 ▶ 2014	H4-LED (11342U6000X2)	E8 5540	Low beam/ High beam [25 ³⁾]	-	-
Micra (4. Gen. Facelift)	K13, K13-LPG, K13M	2014 ▶ 2018	H4-LED (11342U6000X2)	E9 11032	Low beam/ High beam [20 ³⁾]	-	-

Other models ▼

Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
OPEL / VAUXHALL							
Astra (J, 4. Gen.)	P-J	2009 ▶ 2015	H7-LED (11972U6000X2)	E1 2820	Low beam	Type P (11182X2)	-
Astra (J, 4. Gen.) Sports Tourer	P-J/SW	2010 ▶ 2015	H7-LED (11972U6000X2)	E1 2820	Low beam	Type P (11182X2)	-
Astra (J, 4. Gen.) Sports Tourer Van	P-J/SW/V	2010 ▶ 2015	H7-LED (11972U6000X2)	E1 2820	Low beam	Type P (11182X2)	-
Astra (J, 4. Gen.) Van	P-J/V	2010 ▶ 2015	H7-LED (11972U6000X2)	E1 2820	Low beam	Type P (11182X2)	-
Karl	D-A	2015 ▶ *	H4-LED (11342U6000X2)	E13 14352	Low beam/ High beam [25 ³⁾]	-	-
Karl Rocks	D-A	2015 ▶ *	H4-LED (11342U6000X2)	E13 14352	Low beam/ High beam [25 ³⁾]	-	-
Viva	D-A	2015 ▶ *	H4-LED (11342U6000X2)	E13 14352	Low beam/ High beam [25 ³⁾]	-	-
Mokka (A)	J-A	2012 ▶ 2016	H7-LED (11972U6000X2)	E13 13562	Low beam	-	-
Zafira Tourer (3. Gen. Facelift)	P-J/SW, P-J/SW/V	2016 ▶ 2019	H7-LED (11972U6000X2)	E1 4238	Low beam	Type E (11178X2)	-
PEUGEOT							
308 (2. Gen.)	4*****, L	2013 ▶ 2016	H7-LED (11972U6000X2)	E24 6252	Low beam	-	-
Boxer	Y	2014 ▶ *	H7-LED (11972U6000X2)	E24 6266	Low beam	-	-
Expert	X G9	2007 ▶ 2016	H4-LED (11342U6000X2)	E2 05074	Low beam/ High beam [25 ³⁾]	-	-
RENAULT							
Kangoo (2. Gen.) Kangoo BE BOP Kangoo Z.E.	W, KW, FW	2008 ▶ 2012	H4-LED (11342U6000X2)	E13 2442	Low beam/ High beam [30 ³⁾]	-	-
Kangoo (2. Gen. Facelift) Kangoo Z.E. Kangoo Z.E. H2	W, KW, FW	2013 ▶ 2020	H4-LED (11342U6000X2)	E11 5827	Low beam/ High beam [27,5 ³⁾]	-	-
Twingo (2. Gen. Facelift)	N	2012 ▶ 2014	H4-LED (11342U6000X2)	E9 6447	Low beam/ High beam [20 ³⁾]	-	-
SEAT							
Ibiza (4. Gen. Facelift) Ibiza ST	6J, 6JN	2012 ▶ 2016	H4-LED (11342U6000X2)	E9 5788	Low beam/ High beam [30 ³⁾]	-	-
Mii	AA, AAE, AAN	2012 ▶ *	H4-LED (11342U6000X2)	E1 3215	Low beam/ High beam [27,5 ³⁾]	-	-
SKODA							
Citigo	AA, AAE, AAN	2011 ▶ 2017	H4-LED (11342U6000X2)	E1 3192	Low beam/ High beam [25 ³⁾]	-	-
Octavia (3. Gen.)	5E	2012 ▶ 2016	H7-LED (11972U6000X2)	E1 3340	Low beam	-	-
Octavia (3. Gen., Facelift)	5E	2016 ▶ 2020	H7-LED (11972U6000X2)	E1 4337	Low beam	-	-
SMART							
ForTwo (3. Gen.)	451	2014 ▶ 2019	H4-LED (11342U6000X2)	E9 11392	Low beam/ High beam [20 ³⁾]	-	-
ForFour (2. Gen.)	451	2014 ▶ 2019	H4-LED (11342U6000X2)	E9 11392	Low beam/ High beam [20 ³⁾]	-	-
SUZUKI							
Swift (5. Gen. Facelift)	NZ	2013 ▶ 2017	H4-LED (11342U6000X2)	E13 12913	Low beam/ High beam [27,5 ³⁾]	-	-

Other models ▼

Model description	Type	Year of manufacture	Type of lamp	Headlamp approval number	Light function **	Philips Adapter-Ring ⁶⁾	Philips CANbus-Adapter ⁶⁾
-------------------	------	---------------------	--------------	--------------------------	-------------------	------------------------------------	--------------------------------------

TOYOTA

Yaris (2. Gen.)	XP9(a), XP9F(a) XP9F(a)MS1	2005 ▶ 2011	H4-LED (11342U6000X2)	E2 08700	Low beam/ High beam [25 ³⁾]	-	-
-----------------	-------------------------------	-------------	--------------------------	----------	--	---	---

VW

Beetle Beetle Dune	16	2011 ▶ 2016	H4-LED (11342U6000X2)	E1 3203	Low beam/ High beam [30 ³⁾]	-	-
Golf (7. Gen.)	AU, AUV	2012 ▶ 2017	H7-LED (11972U6000X2)	E9 6765	Low beam	Type D (11176X2)	-
Passat B6	3C	2005 ▶ 2010	H7-LED (11972U6000X2)	E9 5507	Low beam	Type I (11179X2)	CANbus H7-LED (18952C2)
Passat B7 (Facelift)	3C	2010 ▶ 2015	H7-LED (11972U6000X2)	E1 3058	Low beam	-	-
Passat B8	3C	2014 ▶ *	H7-LED (11972U6000X2)	E9 11464	Low beam	-	-
Polo (5. Gen.)	6R	2009 ▶ 2014	H4-LED (11342U6000X2)	E9 5856	Low beam/ High beam [17,5 ³⁾]	-	-
T5 Caravelle ⁵⁾ T5 California ⁵⁾ T5 Multivan ⁵⁾ T5 Transporter ⁵⁾	7HM, 7HC, 7HCA, 7HMA, 7HK, 7J0	2003 ▶ 2009	H4-LED (11342U6000X2)	E1 1366	Low beam/ High beam [37,5 ³⁾]	-	-
T5 Caravelle Facelift ⁵⁾ T5 California Facelift ⁵⁾ T5 Multivan Facelift ⁵⁾ T5 Transporter Facelift ⁵⁾	7HC, 7HMA, 7J0	2009 ▶ 2016	H4-LED (11342U6000X2)	E1 2705	Low beam/ High beam [30 ³⁾]	-	CANbus H4-LED ⁴⁾ (18960C2) (LB only)

Note for VW T5: some models have been factory-fitted with H7 and not H4 halogen lamps, despite identical headlamp approval numbers. Before purchasing the H4-LED lamp, please indicate directly the type of halogen lamp installed. The approval of the Philips Ultinon Pro6000 H4-LED is only valid for the type of H4 lamp installed.

up! e-up! cross up!	AA, AAE, AAN	2011 ▶ 2016	H4-LED (11342U6000X2)	E1 3149	Low beam/ High beam [30 ³⁾]	-	-
up! (Facelift) e-up! cross up! up! GTI	AA, AAN	2016 ▶ *	H4-LED (11342U6000X2)	E8 8227	Low beam/ High beam [27,5 ³⁾]	-	CANbus H4-LED ⁷⁾ (18960C2) (LB only)

Legal note: you are responsible for compliance with all applicable legal requirements. The Philips Ultinon Pro6000 range is type-approved for certain vehicle models only. To check if your vehicle is covered and the procedure in force in your country please visit: philips.com/roadlegalLED.

¹⁾ * corresponds to end of production

²⁾ ** LB corresponds to passing beam / HB corresponds to driving beam

³⁾ The specified high beam index I'_{M} with H4-LED or H7-LED differs from the specification on the headlamp. The permissible sum of the main beam characteristics of all main beam headlamps must not exceed 100. Reference mark I'_{M} with H7-LED or H4-LED for the main beam of each model is as below. For more information, see Q&A.

⁴⁾ In the event of an error message, the optional CANbus must be used.

⁵⁾ Those vehicles (camper-vans and similar classes / body types) are also approved whose headlamps comply with the listed UN(ECE) type approval and have a multi-stage approval on the basis of the named basic vehicle.

⁶⁾ The road approval of the Philips Ultinon Pro6000 LED lamp is only valid if installed where required with Philips original accessories. Please check the compatibility list to see if additional accessories are required for your vehicle.

⁷⁾ For vehicle models with faulty cornering light function, the use of the optional CANbus is required.

