

PHILIPS

Car headlight bulb

Ultinon Pro6000

Road-legal LED*

W5W-LED

Color-matching your
headlights

CeraLight ultra-durable

11961HU60X2



Taking bright white light to the next level

The perfect blend of performance and durability

Enjoy an unprecedented driving experience with Philips first road-approved* W5W-LED upgrade. Featuring a bright light** and a daylight-like white beam, these LED bulbs illuminate everything clearly giving you a harmonious stylish look.

Safe and road-legal LED light

- Road-legal LED upgrade lamps*

Color-matched stylish white light

- 6000 Kelvin color temperature for crisp white light

Performance made to last

- Enhanced lifetime of up to 10,000 hours

Automotive-grade quality

- The durability that today's drivers demand

Comply with Interior lighting

- Suitable with a wide range of interior applications

Highlights

6000 K for crisp white light

With a high color temperature of up to 6000 Kelvin, the Philips Ultinon Pro6000 W5W-LED produces a bright white light that's close to daylight. The optimal color temperature avoids tiring or straining the eyes, giving you more comfortable and safer night-time driving by headlights, while the position lights are color-matched for a harmonious stylish look.

LED lamps for road traffic use*

With the Philips Ultinon Pro6000 lamps, approved for road use in Germany and for certain vehicle models*, it is now possible to convert halogen lamps for front parking lights to high-performance and durable LED lamps. You too can benefit from reliable lighting and unrivalled LED driving. Philips Ultinon Pro6000 W5W-LED lamps are certifiable in some European countries through an individual process*. Visit philips.com/roadlegalLED for more information on the current protocols and the list of vehicles covered in each country.

Comply with Interior lighting

Want to convert your interior car lights to LED for a brighter and more stylish effect? Philips Ultinon Pro6000 W5W LED lights are compatible with most interior lighting applications such as boot light, door light, entry light, glove box light or reading light. Experience superior light quality inside your car for better visibility and comfort.

3-year warranty

You want bright, stylish lights but you don't want to keep replacing failed lamps. That's a major weakness of conventional headlights; the more powerful the light, the shorter its lifespan. At a higher light-intensity level, LEDs last much longer, and Philips Ultinon Pro6000 signaling lights are built to last. Due to their unique ceramic heat-management system CeraLight, they last for up to 10,000 hours of operation. Visit philips.com/auto-warranty to register for an extended warranty***.

Durability for today's drivers

Philips Ultinon Pro6000 bulbs are also guaranteed EMI-compliant, conforming to automotive-industry standards on electromagnetic interference. Precision-engineered to withstand the rigors of modern motoring life, they offer the durability that today's drivers demand. Their daily performance provides confidence behind the wheel and brighter, consistent light throughout the journey.

Specifications

Product description

Designation: W5W-LED 11961 HU60 X2
Range: Ultinon Pro6000
Base: W2.1X9.5D
Type: W5W-LED
Technology: LED
Application: Position lights, Interior lights
Homologation ECE: No
Approved for road use: Yes, applicable for position lights only for car models listed in the Philips compatibility list*

Ordering information

Order entry: LUM11961HU60X2
Ordering code: 01638630

Electrical characteristics

Voltage: 13.5 V
Wattage: 0.9 W

Light characteristics

Color temperature: 6000 K

Lifetime

Lifetime: 10000 hrs

Marketing specifications

Expected benefits: Brighter, elegant signals
Product highlight: Road-legal LED bulbs
Technical features: CeraLight

Packaging Data

EAN1: 8719018016386
EAN3: 8719018016393
Packaging type: X2

Packed product information

Height: 9.5 cm
Length: 7 cm
Width: 3 cm
Pack Quantity: 2 pcs
MOQ (for professionals): 10 packs
Net weight per piece: 3 g

Outerpack information

Height: 8.3 cm
Length: 19.6 cm
Width: 15.6 cm
Gross weight [kg]: 0.33 kg

