

PHILIPS

Ultinon Pro6000 Boost



Compatibility list **Philips Ultinon Pro6000 Boost**

Updated on: 20.05.2024



Compatibility list

Check our online Philips compatibility list regularly at [Philips.com/roadlegalLED](https://philips.com/roadlegalLED), as we update it continuously.

Glossary

Table legend	
LB, EN Low beam	DE Abblendlicht, FR Feux de croisement, CR Kratko svjetlo, SI Kratki svetlobni pramen, PL Światła mijania, CZ Potkávací světla, ES Luz de Cruce, NL Dimlicht, BG Къси светлини, GR Χαμηλή δέσημη, IT Anabbagliante, SE Halvljus, LA Tuvās gaismas, LI Artimosios šviesos, PT Farol baixo, SK Stretávacie svetlá
HB, EN High beam	DE Fernlicht, FR Feux de route, CR Dugo svjetlo, SL Daljši svetlobni pramen, PL Światła drogowe, CZ Dálkové svetla, ES Luz Larga, NL Grootlicht, BG Дълги светлини, GR Μεγάλη δέσημη φωτός, IT Luce abbagliante, SE Helljus, LA Tālās gaismas, LI Tolimosios šviesos, PT Farol alto, SK Dialkové svetlá
Model description	DE Modell, FR Modèle du véhicule, CZ Značka, ES Modelo, NL Automeerk, BG Марка автомобил, SE Bilmärke, PT Marca do veículo
Type	DE Typ, FR Plateforme, CZ Model, ES Tipo, NL Automodel, BG Модел автомобил, SE Bilmodell, PT Modelo do veículo
Year of manufacture	DE Baujahr, FR Année de production, CZ Rok výroby, ES Año de construcción, NL Productiejaar, BG Година на производство, SE Tillverkningsår, PT Ano de produção
Lamp type	DE Lampentyp, FR Les types de lampe, CZ Typ žárovky, ES Tipo de lámpara, NL Lamptype, BG Тип лампа, SE Lampa typ, PT Lamp type
Headlamp approval number	DE Scheinwerfer-Genehmigungs-nummer, FR Numéro d'homologation du phare, CZ Schvalovací číslo světlometu, ES Faronúmero de aprobación, NL Controleer het goedkeuringsnummer van de koplamp, BG Проверете номера за одобрение за фарове, SE Se strålkastarens godkännandenummer, PT Verifique o número de aprovação da lâmpada para faróis
Light function	DE Lichtfunktion, FR Fonction d'éclairage, CZ Světelná funkce, ES Función de luz, NL Toepassing, BG Приложение, SE Tillämpning, PT Aplicação
Adapter Ring	DE Adapter-Ring, FR Anneau, CZ Středicí kroužek, ES Anillos adaptadores, NL Aansluitringen, BG Свързващи пръстени, SE Kontaktringar, PT Anéis de ligação
CANBus Adapter	DE CANBus-Adapter, FR CANbus, CZ CANBus adaptér, ES Adaptador CANBus, NL Adaptor CANbus, BG Адаптер CANbus, SE CANbus-adapter, PT Adaptador CANbus

Applicable in the following countries: Germany, Spain and Denmark. Extended to: Belgium, Bulgaria, Greece, Sweden, Iceland, Latvia, Lithuania, Luxemburg, Portugal, Slovakia, Slovenia and Norway.

Model description	Type	Year of manufacture ⁹⁾	Lamp type	Headlamp approval number	Light function**	Accessories	
						Adapter Ring ⁶⁾	CANBus Adapter ⁶⁾

ADRIA

Compact, Coral, Lido, Matrix, Twin	B / C / N / P	2014 ▶ *	H7-LED (11972U60BX2)	E24 6266	LB/HB [25]	-	-
Compact, Coral, Matrix, Twin ⁵⁾	B, C	2011 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-

ALFA ROMEO

Giulia	105.14, 105.02, 105.06, 105.03, 105.57, 105.48, 105.44, 105.91, 105.85, 105.39, 105.30, 105.26, 105.24, 105.09, 105.03, 105.07	1962 ▶ 1977	H4-LED (11342U60BX2)	E4 1 www./opt. E4 12 www./opt. E11 0035	HB/LB [20], HB/LB [25], HB/LB [37,5]	-	-
Giulietta	940	2013 ▶ 2016	H7-LED (11972U60BX2)	E3 2841	LB	-	-

AUDI

50	86	1974 ▶ 1978	H4-LED (11342U60BX2)	E1 14592	HB/LB [25]	-	-
A1 / A1 Sportback (2. Gen.) A1 / A1 CityCarver / AllStreet	GB	2018 ▶	H7-LED (11972U60BX2)	E9 22034	LB	-	-
A1, A1 Sportback S1, S1 Sportback	8X	2015 ▶ 2018	H7-LED (11972U60BX2)	E9 11198	LB	-	-
A2	8Z	1999 ▶ 2005	H7-LED (11972U60BX2)	E9 5267	LB	-	-
A3, A3 Sportback	8P, 8PA	2003 ▶ 2008	H7-LED (11972U60BX2)	E1 1468	LB	-	4)

A4 (2. Gen.)	8E	2000 ▶ 2004	H7-LED (11972U60BX2)	E9 5316	LB/HB [30]	-	-
A4, S4	B8	2011 ▶ 2015	H7-LED (11972U60BX2)	E1 3064	LB	-	4)
Q2	GA	2016 ▶ 2020	H7-LED (11972U60BX2)	E9 16103	LB/HB [20]	-	-
Q3	8U, 8U1	2011 ▶ 2018	H7-LED (11972U60BX2)	E9 6391	LB	-	-

AUSTIN, MORRIS

Mini Cooper	Mini Cooper	1966 ▶ 2000	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
Mini Cooper Minor	Mini Minor	1966 ▶ 2000	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
Mini Cooper S	Mini Cooper S	1966 ▶ 2000	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
Mini Kombi	Mini Kombi, Mini Kombi MK II	1967 ▶ * ▶ 2000	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
Mini Pick Up	Mini Pick Up	1970 ▶ 2000	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
Mini Traveller	Mini Traveller MK II	1968 ▶ 2000	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
Mini Van	Mini Van	1970 ▶ 2000	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-

BENTLEY

Continental, Azure Brooklands, Turbo	NZ, SZ	1995 ▶ 2002	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
--------------------------------------	--------	-------------	--------------------------------	---------------------------	--	---	---

BMW

1er (E81/E87, 1. Gen. Facelift)	187, 1K2, 1K4	2007 ▶ 2020	H7-LED (11972U60BX2)	E9 5475	HB/LB [20]	-	CANBus H7-LED
1er (F20/F21)	IK2, IK4	2011 ▶ 2016	H7-LED (11972U60BX2)	E1 3132	LB	Type P (11182X2)	-
1er (F20/F21)	IK2, IK4	2014 - 2020	H7-LED (11972U60BX2)	E1 3999	LB / HB	Type P (11182X2)	-
1er (F40, 3. Gen.)	F1H	2019 ▶ *	H7-LED (11972U60BX2)	E9 22265	LB/HB [25]	-	-
1er Cabrio (E88, 1. Gen. Facelift)	182, 1C	2007 ▶ 2013	H7-LED (11972U60BX2)	E9 5475	HB/LB [20]	-	CANBus H7-LED
1er Coupe (E82, 1. Gen. Facelift)	182, 1C	2007 ▶ 2013	H7-LED (11972U60BX2)	E9 5475	HB/LB [20]	-	CANBus H7-LED
1er (F20/F21 Facelift)	IK2, IK4	2014 ▶ 2020	H7-LED (11972U60BX2)	E1 3999	HB / LB [20 ³⁾	Type P (11182X2)	-
2er Active Tourer (F45)	F2AT, UKL-L	2014 ▶ 2017	H7-LED (11972U60BX2)	E1 3680	LB	-	-
2er Gran Tourer (F46)	F2GT, UKL-L	2015 ▶ 2018	H7-LED (11972U60BX2)	E1 3680	LB	-	-
3er (E21, 1. Gen.)	BMW 3	1975 ▶ 1985	H1-LED (11258U60BX2)	E1 14466 (HC) / E1 14464 (HR)	HB/LB [17,5 ³⁾	-	-
3er (E30, 2. Gen.)	BMW 3/1, BMW 3/A	1983 ▶ 1994	H1-LED (11258U60BX2)	E1 14466 (HC) / E1 14464 (HR)	HB/LB [17,5 ³⁾	-	-
3er (E90/E91)	390L, 390X	2005 ▶ 2008	H7-LED (11972U60BX2)	E12 112016	HB / LB [30 ³⁾	-	-
3er (E90/E91, 5. Gen. Facelift)	390L, 390X, 3L, 3K, 3K-N1	2008 ▶ 2013	H7-LED (11972U60BX2)	E4 12663	HB/LB [17.5]	-	CANBus H7-LED

NEW

	3er (E90/E91, 5. Gen. Facelift)	390L, 390X, 3L, 3K, 3K-N1	2008 ▶ 2013	H7-LED (11972U60BX2)	E9 5518	LB	-	CANBus H7-LED
	3er (F30/F31)	3L, 3K, 3K-N1	2011 ▶ 2015	H7-LED (11972U60BX2)	E4 15473	LB	-	-
	3er (F30/F31) Facelift	3L, 3K, 3K-N1	2015 ▶ 2019	H7-LED (11972U60BX2)	E1 4041	HB / LB [20 ³⁾]	Type P (11182X2)	-
NEW	3er Cabrio (E30, 2. Gen.)	BMW 3/R	1986 ▶ 1994	H1-LED (11258U60BX2)	E1 14466 (HC) / E1 14464 (HR)	HB/LB [17,5 ³⁾]	-	-
	3er GT (F34)	3-V	2013 ▶ 2016	H7-LED (11972U60BX2)	E4 16619	LB	-	-
NEW	3er M3 (E30, 2. Gen.)	BMW M3	1986 ▶ 1994	H1-LED (11258U60BX2)	E1 14466 (HC) / E1 14464 (HR)	HB/LB [17,5 ³⁾]	-	-
	F 650 GS, F 700 GS, F 800 GS, F800 GS Adventure	E8GS, 4G80r	2008 ▶ 2018 2016 ▶ 2018	H7-LED (11972U60BX2)	E1 3571	HB [12.5]	-	-
	G 650 Xmoto, G 650 Xchallenge	E65X	2006 ▶ 2010	H4-LED (11342U60BX2)	E3 2473	HB / LB [12.5 ³⁾]	-	-
	G 650, G 650 GS	E650G	2010 ▶ 2015	H4-LED (11342U60BX2)	E3 2473	HB / LB [12.5 ³⁾]	-	-
	Megamoto	RHP2	2006 ▶ 2008	H4-LED (11342U60BX2)	E3 2473	HB / LB [12.5 ³⁾]	-	-
	R 1200 GS, R 1200 GS Adventure	R12	2004 ▶ 2012	H7-LED (11972U60BX2)	E3 2179	HB [12.5 ³⁾]	-	-
	R 1200 GS, R 1200 GS Adventure	R12W	2012 ▶ 2018	H7-LED (11972U60BX2)	E4 16103	HB / LB [12.5]	-	-
	R 1250 GS, R 1250 GS Adventure	1G13, 1G13ind	2018 ▶ * 2019 ▶ *	H7-LED (11972U60BX2)	E4 16103	HB / LB [12.5]	-	-
	R nine T, R nine T Pure, R nine T Racer, R nine T Scrambler, R nine T Urban G/S	1N12	2016 ▶ *	H4-LED (11342U60BX2)	E13 13815	HB / LB [17.5]	-	-
	X1 (E84, 1. Gen)	X1, X1-N1	2009 ▶ 2012	H7-LED (11972U60BX2)	E9 5880	LB/HB [20]	-	CANBus H7-LED
	X3 (F25 Facelift)	X3, X-N1	2014 ▶ 2017	H7-LED (11972U60BX2)	E1 3543	LB	-	-
	X3 (F25, 2. Gen.)	X3, X-N1	2010 ▶ 2014	H7-LED (11972U60BX2)	E1 2960	HB/LB [20]	-	CANBus H7-LED

BRITISH LEYLAND

	Mini	MINI 850 MK II, MINI 850 Mk. II, MINI 1000 MK II, MINI 1275 GT	1968 ▶ * ▶ 2000	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB / LB [20 / 25 ³⁾ / 37.5 ³⁾	-	-
	Mini Clubman	CLUBMAN	1971 ▶ 2000	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB / LB [20 / 25 ³⁾ / 37.5 ³⁾	-	-
	Mini Moke	Mini Moke	1968 ▶ 2000	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB / LB [20 / 25 ³⁾ / 37.5 ³⁾	-	-

BÜRSTNER

	Argos, Brevio, Ixeo, Nexxo, Travel, Travel Van ⁵⁾	2010, 2020	2006 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-
	Argos, Brevio, Ixeo, Nexxo, Travel, Travel Van ⁵⁾	2080	2008 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-
	Argos, Brevio, Ixeo, Nexxo, Travel, Travel Van ⁵⁾	4010, 3010, 4020	2012 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-
	Argos, Brevio, Ixeo, Lyseo, Nexxo, Travel	4010 / 4020 / 5020	2014 ▶ *	H7-LED (11972U60BX2)	E24 6266	LB/HB [25]	-	-

CAPRON / PÖSSL

	Carado, CVE, Etrusco, Solifer, Sunlight, Roadcar	CKF1 / CKF2 / EG/CVF 001 / CRF1 / CRC3 / CVF2 / EG/CF 002	2015 ▶ *	H7-LED (11972U60BX2)	E24 6266	LB/HB [25]	-	-
	Carado, Solifer, Sunlight ⁵⁾	EG/CF 002	2010 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-

CARTHAGO

c-Tourer T, chic c-line T ⁵⁾	EG/CF002	2006 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-
Malibu, c-Tourer T, chic c-line T	EG/CF004	2014 ▶ *	H7-LED (11972U60BX2)	E24 6266	LB/HB [25]	-	-

CHRYSLER, DAIMLERCHRYSLER, FCA

Jeep Wrangler	TJ, JK	1996 ▶ * ▶ 2018	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
---------------	--------	-----------------	--------------------------------	---------------------------	--	---	---

CITROËN

Berlingo (3. Gen.)	E	2018 ▶ *	H7-LED (11972U60BX2)	E9 16814	LB	-	-
Berlingo (3. Gen.)	E	2018 ▶ *	H7-LED (11972U60BX2)	E9 16814	LB	-	-
NEW Berlingo (3. Gen.) ⁵⁾ ë-Berlingo	E	2018 ▶ *	H1-LED (11258U60BX2)	E9 16812	HB [12,5]	-	-
C1 (1. Gen.)	P*****, PG	2005 ▶ 2014	H4-LED (11342U60BX2)	E2 04048	HB / LB [25]	-	-
C1 (2. Gen.)	P*****/P	2014 ▶	H7-LED (11972U60BX2)	E9 11276	LB/HB [17.5]	-	-
C3 (3. Gen.)	S	2016 ▶ 2020	H7-LED (11972U60BX2)	E9 16205	HB / LB [17.5]	Type N (11183X2)	-
C3 Aircross	2R, 2C	2017 ▶ 2021	H7-LED (11972U60BX2)	E9 16527	LB	-	-
C3 Picasso	SH (SH*****) SH	2009 ▶ 2017 2010 ▶ 2017	H7-LED (11972U60BX2)	E1 2598	LB	-	-
NEW C4 Cactus (2. Gen.)	0	2018 ▶ *	H1-LED (11258U60BX2)	E9 16785	HB [12,5]	-	-
Jumper / Relay (2.Gen.) ⁵⁾	Y	2006 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-
Jumper/Relay (2. Gen, Facelift)	Y	2014 ▶ *	H7-LED (11972U60BX2)	E24 6266	LB/HB [25]	-	-
Jumpy (2.Gen) ⁵⁾ Dispatch (2.Gen) ⁵⁾	X***** X CX G9	2007 ▶ 2016 2007 ▶ 2016 2011 ▶ 2016 2007 ▶ 2013	H4-LED (11342U60BX2)	E2 05074	HB / LB [25 ³⁾	-	-

DACIA / RENAULT

Clio (4. Gen., Facelift)	R	2016 ▶ 2020	H7-LED (11972U60BX2)	E1 3362	LB	-	-
Dokker	SD	2011 ▶ *	H4-LED (11342U60BX2)	E9 14005	HB / LB [20 ³⁾	-	-
Dokker Pick Up	SD	2018 ▶ *	H4-LED (11342U60BX2)	E9 14005	HB / LB [20 ³⁾	-	-
Duster (1. Gen.)	SD	2010 ▶ 2013	H7-LED (11972U60BX2)	E1 2737	LB	-	-
NEW Duster (1. Gen.)	SD	2010 ▶ 2013	H1-LED (11258U60BX2)	E1 2737	HB [12,5 ³⁾	-	-
Duster (1. Gen.) Facelift	SD, SR (HSR), SR	2013 ▶ 2019	H7-LED (11972U60BX2)	E1 3669	LB	-	-
NEW Duster (1. Gen.) Facelift	SD, SR (HSR), SR	2013 ▶ 2019	H1-LED (11258U60BX2)	E1 3669	HB [12,5 ³⁾	-	-
Duster (2. Gen.)	SR	2018 ▶ *	H7-LED (11972U60BX2)	E1 4583	LB	-	-
NEW Duster (2. Gen.)	SR	2018 ▶ *	H1-LED (11258U60BX2)	E1 4583	HB [12,5 ³⁾	-	-
Jogger (1. Gen.)	DJF	2021 ▶ *	H7-LED (11972U60BX2)	E19 0055	HB	Type K (11180X2)	-
Kadjar	RFE	2015 ▶ 2022	H7-LED (11972U60BX2)	E1 4049	LB / HB	Type P (11182X2)	-

NEW	Kangoo (2. Gen.)	FW	2013 ▶ *	H4-LED (11342U60BX2)	E11 5826	LB / HB	-	-
	Kangoo (2. Gen. Facelift) Kangoo Z.E.	W, KW, FW	2013 ▶ 2020	H4-LED (11342U60BX2)	E11 5827	HB / LB [27,5 ³⁾	-	-
	Kangoo (2. Gen.) Kangoo BE BOP	W, KW, FW	2008 ▶ 2012	H4-LED (11342U60BX2)	E13 2442	HB / LB [30 ³⁾	-	-
	Laguna (1. Gen.)	B56, K56	1993 ▶ 2001	H1-LED (11258U60BX2)	E2 92705	LB	-	-
	Lodgy	SD	2011 ▶ *	H4-LED (11342U60BX2)	E9 14005	HB / LB [20 ³⁾	-	-
	Megane (3. Gen. 2. Facelift)	Z	2014 ▶ 2016	H7-LED (11972U60BX2)	E1 3674	HB/LB [20]	-	-
	Megane (3.Gen.)	Z	2008 ▶ 2012 2012 ▶ 2014	H7-LED (11972U60BX2)	E1 2538	LB	-	-
	Megane (4.Gen.)	RFB	2016 ▶ 2020	H7-LED (11972U60BX2)	E9 11935	HB / LB [17,5 ³⁾	Type I (for LB only)	-
	Sandero (2.Gen.) Facelift Sandero Stepway (2.Gen.) Facelift	SD, SR (5SR)	2016 ▶ 2021	H7-LED (11972U60BX2)	E9 14211	LB	-	-
	Sandero (3. Gen.)	DJF	2021 ▶ *	H7-LED (11972U60BX2)	E19 0055	HB	Type K (11180X2)	-
	Scenic (3. Gen., Facelift), Grand Scenic (3. Gen., Facelift)	JZ, JZ-A	2012 ▶ 2016	H7-LED (11972U60BX2)	E9 6621	LB	-	-
	Spring	DBG	2020 ▶	H7-LED (11972U60BX2)	E8 11379	LB	-	-
	Trafic (2. Gen.)	EL-FL-JL	2001 ▶ 2015	H4-LED (11342U60BX2)	E9 5635	LB / HB	-	-
	Twingo (2. Gen.)	CN0	2007 ▶ 2011	H4-LED (11342U60BX2)	E1 2340	LB / HB	-	-
	Twingo (2.Gen. Facelift)	N	2012 ▶ 2014	H4-LED (11342U60BX2)	E9 6447	HB / LB [20 ³⁾	-	-

DETHLEFFS / PÖSSL

Alpa, Globebus, Just, Pulse, Trend	EG/DVF 001 / EG/DVC 001 / EG/DVP 001	2018 ▶ *	H7-LED (11972U60BX2)	E24 6266	LB/HB [25]	-	-
Advantage, Alpa, Esprit, Globe, Globebus, Magic Edition, Trend ⁵⁾	EG/DF 003	2006 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-
Advantage, Alpa, Esprit, Globe, Globebus, Magic Edition, Trend ⁵⁾	EG/DF 004	2007 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-
Alpa, Globebus, Just, Pulse, Trend ⁵⁾	EG/DF 003, EG/DF 004	2014 ▶ *	H7-LED (11972U60BX2)	E24 6266	LB/HB [25]	-	-

FIAT

500L	199	2012 ▶ 2017	H7-LED (11972U60BX2)	E13 13541	HB [25 ³⁾	-	-
500L	199	2012 ▶ 2017	H7-LED (11972U60BX2)	E13 13542	LB	-	-
Ducato (3. Gen, Facelift)	250	2014 ▶ *	H7-LED (11972U60BX2)	E24 6266	LB/HB [25]	-	-
500X	334	2015 ▶ 2018	H4-LED (11342U60BX2)	E24 6272	HB / LB [30 ³⁾	-	-
Doblo ⁵⁾	223, 223L	2005 ▶ 2010	H7-LED (11972U60BX2)	E13 1717 (LH) / E13 1718 (RH)	LB	-	-
Ducato (3. Gen.) ⁵⁾	250	2006 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-
Punto	199	2011 ▶ *	H4-LED (11342U60BX2)	E9 5876	HB / LB [20 ³⁾	-	-
Scudo (2.Gen) ⁵⁾ Scudo Lecapitaine (2.Gen) ⁵⁾	270, 270L 270Y	2007 ▶ 2016 2012 ▶ 2016	H4-LED (11342U60BX2)	E2 05074	HB / LB [25 ³⁾	-	-
Tipo, Aegea	356	2016 ▶ 2020	H7-LED (11972U60BX2)	E9 16020	HB / LB [20 ³⁾	-	-

FIAT / ABARTH

	500 (Facelift) / 500C (Facelift) / 595 (Facelift) / 595C (Facelift) / 695 (Facelift)	312	2015 ▶	H7-LED (11972U60BX2)	E24 5105	LB	-	-
NEW	500 / 500C / 595 / 595C / 695	312	2007 ▶ 2016	H1-LED (11258U60BX2)	E3 2594	HB [12,5]	-	-
	500 / 500C / 595 / 595C / 695	312	2007 ▶ 2016	H7-LED (11972U60BX2)	E3 2596 (LH) / E3 2595 (RH)	LB	Type K (11180X2)	-
NEW	595 / 595C / 695	312	2010 ▶ 2016	H1-LED (11258U60BX2)	E3 2594	HB [12,5]	-	-

FIAT, RAPIDO

	Rapido, Esterel, Itineo ⁵⁾	250 ***** /A	2006 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-
--	---------------------------------------	--------------	-------------	--------------------------------	-----------------------------	----	---	---

FORD

NEW	Capri RS (1. Gen.)	ECK	1972 ▶ 1974	H1-LED (11258U60BX2)	E1 14466 (HC) / E1 14464 (HR)	HB/LB [17,5 ³⁾]	-	-
	Capri (2. Gen.), Capri (2. Gen., Facelift)	GECP	1974 ▶ 1986	H1-LED (11258U60BX2)	E1 14466 (HC) / E1 14464 (HR)	HB/LB [17,5 ³⁾]	-	-
	C-Max (2. Gen., Facelift) / Grand C-Max (2. Gen., Facelift)	DXA	2015 ▶ 2019	H7-LED (11972U60BX2)	E9 11678	LB	-	-
	Fiesta (8. Gen.)	JHH JGH	2017 ▶ * 2018 ▶ *	H7-LED (11972U60BX2)	E4 25168	LB	Type K (11180X2)	-
	Ka (2. Gen.)	RU8	2008 ▶ 2016	H4-LED (11342U60BX2)	E3 2727	HB/LB [20]	-	-
	Ka+	1	2014 ▶ 2019	H4-LED (11342U60BX2)	E4 25890	LB/HB	-	-
	Mustang I	T 67, T 68, T 69, T 70, T 71, T 72, T 73, T 74, T 75	1964 ▶ 1973	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾]	-	-
	Mustang II	T 74, T 75	1973 ▶ 1979	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾]	-	-
	Transit (7. Gen.)	FAD, FBD, FCD, FDD, FED, FFD	2014 ▶ *	H7-LED (11972U60BX2)	E9 6892	LB	-	-
	Transit Custom (7. Gen., Facelift), Tourneo Custom (7. Gen., Facelift)	FCC / FAC	2017 ▶	H7-LED (11972U60BX2)	E9 16678	LB	-	-
	C-Max (2. Gen.)	DXA	2010 ▶ 2015	H7-LED (11972U60BX2)	E9 5897	LB	-	-
	Escort (1. Gen.) Escort (2. Gen.)	ATH, AFH	1968 ▶ * ▶ 1981	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾]	-	-
	Fiesta (7. Gen., Facelift)	JA8 / JR8, JA_LPG, JA8-N	2013 ▶ 2017	H7-LED (11972U60BX2)	E8 6390	LB	-	-
	Focus (4. Gen.)	DEH	2018 ▶ *	H7-LED (11972U60BX2)	E8 9147	LB	Type K (11180X2)	-
	Galaxy (3. Gen.)	WA6	2015 ▶ *	H7-LED (11972U60BX2)	E9 11640	LB	-	-
	Grand C-Max (2. Gen.)	DXA	2010 ▶ 2015	H7-LED (11972U60BX2)	E9 5897	LB	-	4)
	Kuga (2. Gen.)	DM2	2013 ▶ 2017	H7-LED (11972U60BX2)	E9 14084	LB	-	-
	S-Max (2. Gen.)	WA6	2015 ▶ *	H7-LED (11972U60BX2)	E9 11640	LB	-	-
	Tourneo Connect ⁵⁾	PJ2, PU2	2013 ▶ 2018	H7-LED (11972U60BX2)	E9 14122	LB	-	-
	Transit Connect ⁵⁾	PJ2, PU2	2013 ▶ 2018	H7-LED (11972U60BX2)	E9 14122	LB	-	-

HONDA

CB 1000 R, CB 1000 RA	SC60	2008 ▶ *	H4-LED (11342U60BX2)	E3 2711	HB/LB [12,5]	-	-
CB 1100	SC65	2013 ▶ 2022	H4-LED (11342U60BX2)	E13 9465	HB/LB [20]	-	-
CBF 1000, CBF 1000A	SC58	2006 ▶ 2011	H7-LED (11972U60BX2)	E3 2251	HB [25 ³⁾	-	-
CBR 1000RA, CBR 1000RR	SC59	2008 ▶ 2016	H7-LED (11972U60BX2)	E4 0125	HB/LB [12,5 ³⁾	-	-
CBR 650 F, CBR 650 FA, CB 650 F, CB 650 FA	RC74, RC75	2013 ▶ 2018	H4-LED (11342U60BX2)	E4 17802	HB/LB [17,5]	-	-
VFR1200X, VFR1200XD	SC70	2012 ▶ *	H7-LED (11972U60BX2)	E4 16019	HB/LB [17,5 ³⁾	-	-

HYMER

Compass, Elddis, EXT, Exsis-t, Grand Canyon, Serengeti, Sydney, Rio, Trend	EG/HF001 / HRC3 / EHG250 / EHGDU1 / EHGDU2	2014 ▶ *	H7-LED (11972U60BX2)	E24 6266	LB/HB [25]	-	-
Exsis-t, Rio, Serengeti, Tramp ⁵⁾	EG/HF001	2012 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-

HYUNDAI

Getz	TB	2002 ▶ 2009	H4-LED (11342U60BX2)	E13 8279	HB / LB [37,5 ³⁾	-	-
Getz	TBI	2006 ▶ 2009	H4-LED (11342U60BX2)	E13 8279	HB / LB [37,5 ³⁾	-	-
i10 (1. Gen.)	PA, PAG	2008 ▶ 2013	H4-LED (11342U60BX2)	E13 2540	HB / LB [20 ³⁾	-	-
i10 (2.Gen)	IA IA-HME	2013 ▶ 2019 2015 ▶ 2019	H4-LED (11342U60BX2)	E13 13903	HB / LB [25 ³⁾	-	-
i20 (1. Gen. , Facelift)	PB, PBT	2012 ▶ 2014	H7-LED (11972U60BX2)	E13 13497	LB	-	-
i20 (1. Gen. , Facelift)	PB, PBT	2012 ▶ 2014	H7-LED (11972U60BX2)	E13 13518	LB	-	-
i20, i20 Active (2. Gen.)	GB, GB-HME	2014 ▶ 2020	H4-LED (11342U60BX2)	E13 14184	HB/LB [30 ³⁾	-	⁴⁾ CANBus H4-LED
i30, i30cw (2. Gen.)	GDH, GDH-HME, GDHG5	2011 ▶ 2017	H7-LED (11972U60BX2)	E9 6691	LB	Type H (11172X2)	-
i30, i30cw (3. Gen.)	PDe	2017 ▶ 2019 2019 ▶ 2020	H7-LED (11972U60BX2)	E9 16394	LB	Type H (11172X2)	-
Tucson (3. Gen.) / ix35	TL, TLE, TLE-HME	2015 ▶ 2018	H7-LED (11972U60BX2)	E9 11827	LB/HB [25]	Type H (for LB only)	CANBus H7-LED
Tucson (3. Gen., Facelift) / ix35	TL / TLE	2018 ▶	H7-LED (11972U60BX2)	E9 22241	LB	Type H (11172X2)	CANBus H7-LED

JAGUAR, DAIMLER

Mark II, 240, 340 250 V8	340	1959 ▶ 1969	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
Mark X, 420 G, Daimler DS420 420, Daimler Sovereign	420 G 420 Saloon	1961 ▶ 1992	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-

JEEP

Renegade	BU	2014 ▶ *	H4-LED (11342U60BX2)	E24 6268	HB / LB [20 ³⁾	-	-
----------	----	----------	--------------------------------	----------	---------------------------	---	---

KAWASAKI

Ninja 125	BX125A	2018 ▶ *	H4-LED (11342U60BX2)	E9 6598	HB/LB [17,5]	-	-
Ninja 125	BX125B	2020 ▶ *	H4-LED (11342U60BX2)	E9 6598	HB/LB [17,5]	-	-

Ninja 250SL	BX250A	2014 ▶ *	H4-LED (11342U60BX2)	E9 6598	HB/LB [17,5]	-	-
Vulcan S	EN650D, EN650DA2	2016 ▶ *	H4-LED (11342U60BX2)	E11 6321	HB/LB [12,5]	-	-
Vulcan S	EN650J, EN650JA2	2020 ▶ *	H4-LED (11342U60BX2)	E11 6321	HB/LB [12,5]	-	-
Z125	BR125K	2018 ▶ *	H4-LED (11342U60BX2)	E9 6598	HB/LB [17,5]	-	-
Z125	BR125L	2020 ▶ *	H4-LED (11342U60BX2)	E9 6598	HB/LB [17,5]	-	-
Z250SL	BR250E	2014 ▶ *	H4-LED (11342U60BX2)	E9 6598	HB/LB [17,5]	-	-
Z650	ER650H, ER650HA2	2016 ▶ *	H4-LED (11342U60BX2)	E4 24914	HB/LB [12,5]	-	-
Zephyr 1100	ZRT 10 A	1992 ▶ 1997	H4-LED (11342U60BX2)	E4 20582	HB/LB [20]	-	-

KIA

Cee'd (2. Gen.)	JD	2012 ▶ 2018	H7-LED (11972U60BX2)	E9 6738	HB / LB [17.5 ³⁾]	Type H (for LB only)	-
Cee'd (3. Gen.)	CD, CDG	2018 ▶ * 2018 ▶ *	H7-LED (11972U60BX2)	E9 22079	LB	Type H (11172X2)	-
Picanto (2. Gen.)	TA, TA/PL	2011 ▶ 2017 2014 ▶ 2017	H4-LED (11342U60BX2)	E13 13170	HB / LB [25 ³⁾]	-	-
Picanto (3. Gen.)	JA, JA, JA/PL	2017 ▶ *	H4-LED (11342U60BX2)	E13 34505	HB / LB [25]	-	-

KNAUS TABBERT / WEINSBERG / BAVARIACAMP

Box Star, Cosmos, Imperiale, Meteor, Sky Ti, Sky Wave, Sky Traveller, Sport Ti, Sport Traveller, Sun Traveller, Sun Ti, Van Ti ⁵⁾	X250	2006 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-
Box Star, Cosmos, Imperiale, Meteor, Sky Ti, Sky Wave, Sky Traveller, Sport Ti, Sport Traveller, Sun Traveller, Sun Ti, Van Ti ⁵⁾	X250/2, X250/3, X250/4, X250L	2007 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-
Box Star, Cosmos, Imperiale, Meteor, Sky Ti, Sky Wave, Sky Traveller, Sport Ti, Sport Traveller, Sun Traveller, Sun Ti, Van Ti ⁵⁾	K250/1, K250/2, K250/3, K250/4, K250L	2011 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-
Box Star, Cosmos, Imperiale, Meteor, Sky Ti, Sky Wave, Sky Traveller, Sport Ti, Sport Traveller, Sun Traveller, Sun Ti, Van Ti ⁵⁾	KYL	2012 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-
Llve Ti, Llve Wave, Main Camp, Sky Ti, Sky Traveller, Sky Wave, Sun Ti, Van Ti, Van Tourer, CaraCompact, Edition [Pepper], CaraLoft, CaraSuite, CaraHome	K250L / K250/1 / K250/3 / K250/4 / KYL / KYL/1	2014 ▶ *	H7-LED (11972U60BX2)	E24 6266	LB/HB [25]	-	-

KTM

690 Duke	KTM 690 Duke	2011 ▶ 2016	H4-LED (11342U60BX2)	E9 6200	HB/LB [20]	-	-
690 Duke R	KTM 690 Duke	2016 ▶ *	H4-LED (11342U60BX2)	E9 6200	HB/LB [20]	-	-
690 Enduro R	KTM 690 LC4	2019 ▶ *	H4-LED (11342U60BX2)	E13 35075	HB/LB [12,5]	-	-
690 SMC R	KTM 690 LC4	2019 ▶ *	H4-LED (11342U60BX2)	E13 35075	HB/LB [12,5]	-	-
1290 Superduke R, 1290 Superduke SE	KTM Superduke	2013 ▶ 2016	H4-LED (11342U60BX2)	E4 17086	HB/LB [20]	-	-

LADA, VAZ, OAO, AVTOAZ, PJSC

Niva Taiga 4x4, 4x4 Urban	VAZ 2121, 2121DE, 2121A, 212140, 212140 NIVA, 2121, 2121**, 2121****DA, M2121, N2121, MZ2121, NZ2121, MU2121, MU2131, M2131	1980 ▶ *	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³ , 37,5 ³]	-	-
---------------------------------	--	----------	--------------------------------	---------------------------	--	---	---

LAND ROVER

Defender 90 Defender 110	LD	1995 ▶ * ▶ 2016	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³ , 37,5 ³]	-	-
Defender 90 Defender 110 Defender 130	LD	1996 ▶ * ▶ 2016	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³ , 37,5 ³]	-	-
Range Rover (1. Gen.)	Range Rover	1970 ▶ 1996	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³ , 37,5 ³]	-	-

LAND ROVER, ROVER, BRITISH LEYLAND

Land Rover 109	LR 109/oP, LR 109/dP, LR 109/oL, LR 109/dL, LR 109/oZ, LR 109/dZ, LR 109 OP 3, LR 109 OL 3, LR 109 DP 3, LR 109 DL 3	1970 ▶ * ▶ 1984	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³ , 37,5 ³]	-	-
Land Rover 88	LR 88/oP, LR 88/dP, LR 88/dP, LR 88/oL, LR 88/dZ, LR 88/oZ, LR 88 OL 3, LR 88 DL 3, LR 88 OP 3, LR 88 DP 3	1970 ▶ * ▶ 1984	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³ , 37,5 ³]	-	-

LEYLAND INNOCENTI

Mini	Mini B 38, Mini B 39	1974 ▶ 2000	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³ , 37,5 ³]	-	-
------	----------------------	-------------	--------------------------------	---------------------------	--	---	---

LMC

Breezer, Cruiser, Liberty ⁵⁾	FI-70/156	2006 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-
Breezer, Cruiser, Liberty ⁵⁾	FK-70/156	2007 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-
Breezer, Cruiser, Liberty ⁵⁾	FI-2007/46	2011 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-
Breezer, Cruiser, Liberty ⁵⁾	2007/46-3FK	2012 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-
Carado, Cruiser, CVE, Element, Etrusco, Grand Breezer, Innovan, Solifer, Sunlight, V643	FI-2007/46 / 2007/46-3FK / C-2007/46 / LVF2	2014 ▶ *	H7-LED (11972U60BX2)	E24 6266	LB/HB [25]	-	-

MASERATI

Mistral	AM 109	1963 ▶ 1970	H4-LED (11342U60BX2)	E4 1 ww./opt. E4 12 ww./opt. E11 0035	HB/LB [20], HB/LB [25], HB/LB [37,5]	-	-
---------	--------	-------------	--------------------------------	--	---	---	---

MAZDA

2 (3. Gen.)	DJ1	2014 ▶ *	H4-LED (11342U60BX2)	E13 14125	HB / LB [25 ³]	-	-
NEW 6 (1. Gen.)	GG/GY, GG1	2002 ▶ 2007	H1-LED (11258U60BX2)	E1 1344	LB	-	-
MX-5 (1. Gen.)	NA	1989 ▶ * ▶ 1998	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³ , 37,5 ³]	-	-

RX-7 (1. Gen.)	SA2	1979 ▶ 1985	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
----------------	-----	-------------	--------------------------------	---------------------------	--	---	---

MERCEDES-BENZ

190 (W201)	201, 201E	1982 ▶ 1993	H4-LED (11342U60BX2)	E1 34575 (LH) / E1 34576 (RH)	HB/LB [37,5]	-	-
A-Klasse (W 176)	176, 176 AMG	2012 ▶ 2014	H7-LED (11972U60BX2)	E1 3255	LB	Type P (11182X2)	-
A-Klasse (W 176)	245 G, 245 G AMG	2012 ▶ 2018	H7-LED (11972U60BX2)	E1 3255	LB	Type P (11182X2)	-
A-Klasse (W 177)	F2A	2018 ▶ *	H7-LED (11972U60BX2)	E8 9130	HB / LB [27,5 ³⁾	Type P (11182X2)	-
B-Klasse (W 246)	246, 245G	2011 ▶ 2014	H7-LED (11972U60BX2)	E1 2994	LB	Type E (11178X2)	-
B-Klasse (W 246) Facelift	245G	2014 ▶ 2018	H7-LED (11972U60BX2)	E1 3748	LB	Type E (11178X2)	-
B-Klasse (W 247)	F2B	2018 ▶ *	H7-LED (11972U60BX2)	E8 9647	LB	Type P (11182X2)	-
Citan (W 415, 1. Gen.)	X	2012 ▶ 2021 2013 ▶ 2021	H4-LED (11342U60BX2)	E11 5814	HB / LB [27,5 ³⁾	-	-
C-Klasse (W/S 205)	204, 204 AMG, 204 K, 204 K AMG	2014 ▶ 2019	H7-LED (11972U60BX2)	E1 3528	LB	Type E (11178X2)	-
C-Klasse (W/S/C 204, Facelift)	204, 204 K	2011 ▶ 2014	H7-LED (11972U60BX2)	E1 2950	HB / LB [25]	Type E (11178X2)	CANBus H7-LED (for HB only)
CLA (C/X 117)	117, 245 G	2013 ▶ 2014 2013 ▶ 2019	H7-LED (11972U60BX2)	E1 3326	LB	Type E (11178X2)	-
GLC (X/C 253)	204 X	2016 ▶ 2019	H7-LED (11972U60BX2)	E4 18438	LB	-	-
Sprinter (W 901-905, 1. Gen. Facelift) ⁵⁾	902.6 KA, 903.6 KA, 904.6 KA, 902.6, 903.6, 904.6, 904.6/4x4, 904.6 KA/4x4, 903.6/4x4, 903.6 KA/4x4, 903.6 P, 905.6 P, C, D, E	2000 ▶ 2007	H7-LED (11972U60BX2)	E1 1524 (LH) / E1 1525 (RH)	LB	-	-
Sprinter (W 906, 2. Gen.) ⁵⁾	906 QK 30, 906 QK 35, 906 QK 50, 906 KA 30, 906 KA 35, 906 KA 50, 906 QK 35/4x4, 906 KA 35/4x4, 906 QK 50/4x4, 906 KA 50/4x4, 906 PD 35, 906 AC 30, 906 AC 35, 906 AC 35/4x4, 906 AX 35 G, 906BA30, 906BB30, 906BA35, 906BA35/4x4, 906BA35G, 906BB35, 906BB35/4x4, 906BA35G, 906BB35, 906BB35/4x4, 906BB35G, 906BA50, 906BA50/4x4, 906BB50, 906BB50/4x4	2006 ▶ 2013	H7-LED (11972U60BX2)	E4 10881	HB/LB [20]	Type P (11182X2)	CANBus H7-LED
Sprinter James Cook (W 906, 2. Gen.) ⁵⁾	906 JC 35	2006 ▶ 2013	H7-LED (11972U60BX2)	E4 10881	HB/LB [20]	Type P (11182X2)	CANBus H7-LED
V-Klasse (W477) ⁵⁾ Vito (W447) ⁵⁾ Vito Tourer (W447) ⁵⁾ Marco Polo (W447) ⁵⁾	639/2, 639/4, 639/5	2014 ▶ *	H7-LED (11972U60BX2)	E1 3655	LB	Type A (11184X2)	-

MERCEDES-BENZ / DAIMLER-BENZ

R 107 SL Cabriolet C 107 SLC Coupé	107	1971 ▶ 1989	H4-LED (11342U60BX2)	E4 9 (LH) / E4 10 (RH)	HB/LB [45 ³⁾	-	-
---------------------------------------	-----	-------------	--------------------------------	---------------------------	-------------------------	---	---

MERCEDES-BENZ / DAIMLER-BENZ/ DAIMLER/STEYER-DAIMLER-PUCH

G-Klasse	460.2, 460.3, 461.4, 463 D, 463, 461, 461N, 461NN, 461N2	1979 ▶ * ▶ 2018	H4-LED (11342U60BX2)	E1 14551 E1 14565	HB/LB [27,5 ³⁾ , 25 ³⁾	-	-
----------	--	-----------------	--------------------------------	----------------------	--	---	---

MG

MGB GT	MG B-GT-Coupe	1965 ▶ 1980	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
MGB Roadster	MG B - 1800	1962 ▶ 1980	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
MGC, MGC GT	MGC	1967 ▶ 1970	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-

MG, AUSTIN

Midget Healey Sprite	Midget MK III Healey Sprite MK IV	1966 ▶ 1979	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
-------------------------	--------------------------------------	-------------	--------------------------------	---------------------------	--	---	---

MINI

MINI MINI Cabrio	R50, MINI, MINI-N	2001 ▶ 2008	H7-LED (11972U60BX2)	E1 1808	HB / LB [27,5 ³⁾	-	-
---------------------	-------------------	-------------	--------------------------------	---------	-----------------------------	---	---

MITSUBISHI

Space Star / Mirage (1. Facelift)	A00	2016 ▶ 2019	H4-LED (11342U60BX2)	E4 16195	HB / LB [30 ³⁾	-	-
Space Star / Mirage (2. Facelift)	A00	2019 ▶ *	H4-LED (11342U60BX2)	E4 27297	HB / LB [27,5 ³⁾	-	-

MITSUBISHI, MMC

Pajero (1. Gen.)	L 040	1982 ▶ 1991	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
------------------	-------	-------------	--------------------------------	---------------------------	--	---	---

MORGAN

4/4 Plus 4, Plus 4 Sport, Plus 4 Super Sport	1800, 2000, 4/4, 1600	1998 ▶ *	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
Plus 8, +8	Plus 8	1968 ▶ *	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
Roadster, Roadster Sport	3000	2011 ▶ *	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-

NISSAN

Juke	F15 F15-LPG F15M	2010 ▶ 2014 2012 ▶ 2014 2013 ▶ 2014	H4-LED (11342U60BX2)	E8 5540	HB / LB [25 ³⁾	-	-
Micra (4.Gen Facelift)	K13, K13-LPG, K13M	2014 ▶ 2018	H4-LED (11342U60BX2)	E9 11032	HB / LB [20 ³⁾	-	-

OPEL / VAUXHALL

Astra (J, 4. Gen.)	P-J	2009 ▶ 2015	H7-LED (11972U60BX2)	E1 2820	LB	Type P (11182X2)	-
Astra (J, 4. Gen.) Sports Tourer	P-J/SW	2010 ▶ 2015	H7-LED (11972U60BX2)	E1 2820	LB	Type P (11182X2)	-
Astra (J, 4. Gen.) Sports Tourer Van	P-J/SW/V	2010 ▶ 2015	H7-LED (11972U60BX2)	E1 2820	LB	Type P (11182X2)	-
Astra (J, 4. Gen.) Van	P-J/V	2010 ▶ 2015	H7-LED (11972U60BX2)	E1 2820	LB	Type P (11182X2)	-

NEW	Astra (K, 5. Gen.)	B-K	2015 ▶ 2019	H7-LED (11972U60BX2)	E9 11834	LB	-	CANBus H7-LED
	Astra (K, 5. Gen.)	B-K	2015 ▶ 2019	H1-LED (11258U60BX2)	E9 11834	HB [20]	-	-
	Corsa (D, 4. Gen., Facelift)	S-D, S-D/Van, S-D/V	2010 ▶ 2014	H1-LED (11258U60BX2)	E9 5969	HB [17,5 ³⁾	-	-
	Corsa (D, 4. Gen., Facelift)	S-D, S-D/Van, S-D/V	2010 ▶ 2014	H7-LED (11972U60BX2)	E9 5969	LB	-	-
	Corsa (E, 5. Gen.)	S-D, S-D/Van, S-D/V	2014 ▶ 2019	H7-LED (11972U60BX2)	E26 9047	LB/HB [20]	Type K (11180X2)	-
	Crossland X	P7 Monocab C	2017 ▶ 2022	H7-LED (11972U60BX2)	E9 16429	HB / LB [30 ³⁾	-	-
	Karl	D-A	2015 ▶ *	H4-LED (11342U60BX2)	E13 14352	HB / LB [25 ³⁾	-	-
	Karl Rocks	D-A	2015 ▶ *	H4-LED (11342U60BX2)	E13 14352	HB / LB [25 ³⁾	-	-
	Mokka (A)	J-A	2012 ▶ 2016	H7-LED (11972U60BX2)	E13 13562	LB	-	-
	Movano C (3. Gen.) ⁵⁾	Y	2021 ▶ * 2022 ▶ *	H7-LED (11972U60BX2)	E24 6266	LB/HB [25]	-	-
	Viva	D-A	2015 ▶ *	H4-LED (11342U60BX2)	E13 14352	HB / LB [25 ³⁾	-	-
	Zafira Tourer (3. Gen. Facelift)	P-J/SW, P-J/SW/V	2016 ▶ 2019	H7-LED (11972U60BX2)	E1 4238	LB	Type E (11178X2)	-

PEUGEOT

NEW	2008	C	2013 ▶ 2019	H7-LED (11972U60BX2)	E2 6898	LB/HB [25]	-	-
	208 (Facelift)	C	2015 ▶ 2019	H7-LED (11972U60BX2)	E9 11726	LB/HB [17.5]	Type N (for HB only)	-
	3008 (1. Gen., Facelift)	0U	2013 ▶ 2016	H7-LED (11972U60BX2)	E2 13023	LB	Type N (11183X2)	CANBus H7-LED
	308 (1. Gen.)	4A/4C	2007 ▶ 2015	H7-LED (11972U60BX2)	E3 2551	LB	-	-
	308 (1. Gen., 2. Facelift)	4, 4*****	2010 ▶ 2016	H1-LED (11258U60BX2)	E3 2552 (LH) / E3 2551 (RH)	HB [10 ³⁾	-	-
	308 (2. Gen.)	4*****, L	2013 ▶ 2016	H7-LED (11972U60BX2)	E24 6252	LB	-	-
	308 (2. Gen.) Facelift	L	2017 ▶ 2021	H7-LED (11972U60BX2)	E24 6284	HB / LB [12.5 ³⁾	-	-
	Boxer (2. Gen., Facelift)	Y	2014 ▶ *	H7-LED (11972U60BX2)	E24 6266	LB/HB [25]	-	-
	Boxer (2.Gen.) ⁵⁾	Y	2006 ▶ 2014	H7-LED (11972U60BX2)	E3 2447 (RH) / E3 2448 (LH)	LB	-	-
	Expert ⁵⁾	X*****, X G9	2006 ▶ 2016 2007 ▶ 2013	H4-LED (11342U60BX2)	E2 05074	HB / LB [25 ³⁾	-	-
	Partner (1. Gen.) ⁵⁾ Ranch (1. Gen.) ⁵⁾	M59, G*KFW*, G*NFU*, G*WJY*, G*RHY*	2002 ▶ 2009	H4-LED (11342U60BX2)	E4 9849	HB/LB [30 ³⁾	-	-
	Partner (1. Gen.) ⁵⁾ Ranch (1. Gen.) ⁵⁾	M 59 GL, M 59 GN	2003 ▶ 2009	H4-LED (11342U60BX2)	E4 9849	HB/LB [30 ³⁾	-	-
	Partner (1. Gen.) ⁵⁾ Ranch (1. Gen.) ⁵⁾	G*9HX*, G*9HW*	2005 ▶ 2009	H4-LED (11342U60BX2)	E4 9849	HB/LB [30 ³⁾	-	-
	208	C	2012 ▶ 2015	H7-LED (11972U60BX2)	E9 6551	LB/HB [17.5]	Type N (for HB only)	-
	207 (Facelift)	W*****/W	2009 ▶ 2015	H7-LED (11972U60BX2)	E2 05702	LB	-	-

PIAGGIO

Beverly M69100, M69200, M69300, M69400	M69	2010 ▶ *	H7-LED (11972U60BX2)	E13 12536	HB/LB [12,5 ³⁾	-	-
--	-----	----------	--------------------------------	-----------	---------------------------	---	---

RENAULT

Clio (4. Gen., Facelift)	R	2016 ▶ 2020	H7-LED (11972U60BX2)	E1 3362	LB	-	-
--------------------------	---	-------------	--------------------------------	---------	----	---	---

Kangoo (2.Gen. Facelift) Kangoo Z.E. Kangoo Z.E. H2 Kangoo (2.Gen.)	W, KW, FW	2013 ▶ 2020	H4-LED (11342U60BX2)	E11 5827	HB / LB [27,5 3]]	-	-
Kangoo BE BOP Kangoo Z.E.	W, KW, FW	2008 ▶ 2012	H4-LED (11342U60BX2)	E13 2442	HB / LB [30 3]]	-	-
Megane (3. Gen. 2. Facelift)	Z	2014 ▶ 2016	H7-LED (11972U60BX2)	E1 3674	HB/LB [20]	-	-
Megane (3.Gen.)	Z	2008 ▶ 2012 2012 ▶ 2014	H7-LED (11972U60BX2)	E1 2538	LB	-	-
Megane (4.Gen.)	RFB	2016 ▶ 2020	H7-LED (11972U60BX2)	E9 11935	HB / LB [17.5 3]]	Type I (for LB only)	-
Scenic (3. Gen., Facelift), Grand Scenic (3. Gen., Facelift)	JZ, JZ-A	2012 ▶ 2016	H7-LED (11972U60BX2)	E9 6621	LB	-	-
Twingo (2.Gen. Facelift)	N	2012 ▶ 2014	H4-LED (11342U60BX2)	E9 6447	HB / LB [20 3]]	-	-

ROLLS-ROYCE

Corniche	NZ, SZ	1995 ▶ 2002	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 3], 37,5 3]]	-	-
----------	--------	-------------	--------------------------------	---------------------------	----------------------------	---	---

ROVER

Mini	Mini MK II, XN	1975 ▶ * ▶ 2000	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 3], 37,5 3]]	-	-
------	----------------	-----------------	--------------------------------	---------------------------	----------------------------	---	---

SACHSENRING

Trabant P 601	P 601, Trabant P 601 A, Trabant P 601 L	1966 ▶ * ▶ 1990	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 3], 37,5 3]]	-	-
---------------	--	-----------------	--------------------------------	---------------------------	----------------------------	---	---

SEAT

Arona (1. Gen.)	KJ	2017 ▶ 2021	H7-LED (11972U60BX2)	E9 16479	LB/HB [20]	-	-
Arona (1. Gen.)	KJ	2017 ▶ 2021	H7-LED (11972U60BX2)	E9 16481	LB/HB [25]	-	-
Ateca	5FP	2016 ▶ 2021	H7-LED (11972U60BX2)	E9 14198	LB/HB [20]	-	-
Ibiza (4. Gen., Facelift), Ibiza SC, Ibiza ST	6J, 6JN	2012 ▶ 2015	H7-LED (11972U60BX2)	E9 5790	LB/HB [17.5]	-	-
Ibiza (4.Gen Facelift) Ibiza ST	6J, 6JN	2012 ▶ 2016	H4-LED (11342U60BX2)	E9 5788	HB / LB [30 3]]	-	-
Ibiza (5. Gen.)	KJ	2017 ▶ 2021	H7-LED (11972U60BX2)	E9 16479	LB/HB [20]	-	-
Ibiza (5. Gen.)	KJ	2017 ▶ 2021	H7-LED (11972U60BX2)	E9 16481	LB/HB [25]	-	-
Leon (3. Gen.)	5F	2012 ▶ 2017	H7-LED (11972U60BX2)	E9 14064	HB/LB [17.5]	-	-
Leon (3. Gen., Facelift)	5F	2016 ▶ 2020	H7-LED (11972U60BX2)	E9 14220	HB/LB [17.5]	-	-
MII MII Electric	AA, AAE, AAN	2012 ▶ *	H4-LED (11342U60BX2)	E1 3215	HB / LB [27,5 3]]	-	-

SKODA

Citigo	AA, AAE, AAN	2011 ▶ 2017	H4-LED (11342U60BX2)	E1 3192	HB / LB [25 3]]	-	-
Octavia (3. Gen.)	5E	2012 ▶ 2016	H7-LED (11972U60BX2)	E1 3340	LB	-	-
Octavia (3. Gen., Facelift)	5E	2016 ▶ 2020	H7-LED (11972U60BX2)	E1 4337	LB	-	-
Yeti	5L	2009 ▶ 2013	H4-LED (11342U60BX2)	E1 2646	HB / LB [27,5 3]]	-	-
Yeti (Facelift)	5L	2013 ▶ 2017	H7-LED (11972U60BX2)	E1 3493	LB	-	-

SMART

Fortwo (3. Gen.) Forfour (2. Gen.)	451 (453)	2014 ▶ *	H4-LED (11342U60BX2)	E9 11394	HB / LB [17,5 ³⁾	-	-
Fortwo (3. Gen.) Forfour (2. Gen.)	451 (453)	2014 ▶ 2019	H4-LED (11342U60BX2)	E9 11392	HB / LB [20 ³⁾	-	-
Fortwo, Fortwo electric drive	451, 451 E	2007 ▶ 2015	H7-LED (11972U60BX2)	E1 2234	LB/HB [17,5]	-	-

STANDARD TRIUMPH, BRITISH LEYLAND

Triumph Spitfire	Spitfire MK 3, Spitfire MK IV	1967 ▶ 1980	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
Triumph TR 5	Triumph TR 5	1967 ▶ 1969	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
Triumph TR 6	TR 6	1969 ▶ 1976	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-
Triumph TR 7	TR 7	1976 ▶ 1980	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾	-	-

SUZUKI

DL1000 V-Strom	DD, WDD0	2014 ▶ 2019 2016 ▶ 2019	H7-LED (11972U60BX2)	E13 13829	LB	-	-
DL650 V-Strom, DL650U V-Strom	WC70, WC71	2016 ▶ *	H7-LED (11972U60BX2)	E13 13829	LB	-	-
Gladius	WVCX	2009 ▶ 2016	H4-LED (11342U60BX2)	E11 5310	HB/LB [20]	-	-
GSX-S750	WC50	2016 ▶ *	H4-LED (11342U60BX2)	E4 24961	HB/LB [17,5]	-	-
GSX-S750W, GSX-S750U	WC51, WC52	2018 ▶ *	H4-LED (11342U60BX2)	E4 24961	HB/LB [17,5]	-	-
Intruder C800	WVBM	2005 ▶ 2016	H4-LED (11342U60BX2)	E13 9465	HB/LB [20]	-	-
LJ80	LJ80		H4-LED (11342U60BX2)	E4 1 ww./opt. E4 12 ww./opt. E11 0035	HB/LB [20], HB/LB [25], HB/LB [37,5]	-	-
SFV650, SFV650U, SFV650A, SFV650UA	WVCX	2009 ▶ 2016	H4-LED (11342U60BX2)	E11 5310	HB/LB [20]	-	-
Swift (5. Gen Facelift)	NZ	2013 ▶ 2017	H4-LED (11342U60BX2)	E13 12913	HB / LB [27,5 ³⁾	-	-
Swift (6. Gen.)	AZ	2017 ▶ *	H4-LED (11342U60BX2)	E13 24687	HB / LB [30]	-	-
VL1500	WVAL	2004 ▶ 2016	H4-LED (11342U60BX2)	E13 9465	HB/LB [20]	-	-
VL1500, Intruder C1500	C1	2012 ▶ 2016	H4-LED (11342U60BX2)	E13 9465	HB/LB [20]	-	-
VL800, VL800U, VL800B, VL800BUE, VL800C, VL800CUE	WVBM	2005 ▶ 2016	H4-LED (11342U60BX2)	E13 9465	HB/LB [20]	-	-

SUZUKI, SANTANA SAMURAI

Samurai, SJ, SJ 410, SJ 413, SJ 410 K	SJ40, SJ, SJ 40V, SUZUKI SJ	1981 ▶ 2004	H4-LED (11342U60BX2)	E4 1 ww./opt. E4 12 ww./opt. E11 0035	HB/LB [20], HB/LB [25], HB/LB [37,5]	-	-
---------------------------------------	-----------------------------	-------------	--------------------------------	--	---	---	---

TOYOTA

Corolla	KE 30	1974 ▶ 1979	H4-LED (11342U60BX2)	E4 1 ww./opt. E4 12 ww./opt. E11 0035	HB/LB [20], HB/LB [25], HB/LB [37,5]	-	-
Cressida	RX 3, RX 3K	1973 ▶ 1992	H4-LED (11342U60BX2)	E4 1 ww./opt. E4 12 ww./opt. E11 0035	HB/LB [20], HB/LB [25], HB/LB [37,5]	-	-

HiAce	H2, H5, H6	1977 ▶ 1989	H4-LED (11342U60BX2)	E4 1 ww./opt. E4 12 ww./opt. E11 0035	HB/LB [20], HB/LB [25], HB/LB [37,5]	-	-
Land Cruiser	J6, J7	1981 ▶	H4-LED (11342U60BX2)	E4 1 ww./opt. E4 12 ww./opt. E11 0035	HB/LB [20], HB/LB [25], HB/LB [37,5]	-	-
LiteAce	M2G, M2	1979 ▶ 1986	H4-LED (11342U60BX2)	E4 1 ww./opt. E4 12 ww./opt. E11 0035	HB/LB [20], HB/LB [25], HB/LB [37,5]	-	-
Starlet, Starlet Kombi	KP6, KP6 K	1978 ▶ 1984	H4-LED (11342U60BX2)	E4 1 ww./opt. E4 12 ww./opt. E11 0035	HB/LB [20], HB/LB [25], HB/LB [37,5]	-	-
Yaris (2.Gen.)	XP9(a), XP9F(a) XP9F(a)MS1	2005 ▶ 2011 2010 ▶ 2011	H4-LED (11342U60BX2)	E2 08700	HB / LB [25 ³⁾]	-	-
Yaris (3. Gen, Facelift)	XP13M(a), XP13N(a), XP13M(a)MS1	2017 ▶ 2020	H4-LED (11342U60BX2)	E13 24831	HB/LB [25]	-	-
Yaris (3. Gen.) Vitz (3. Gen.)	XP13M(a), XP13N(a), XP13M(a)MS1	2010 ▶ 14	H4-LED (11342U60BX2)	E13 13140	HB / LB [20]	-	-

TRIUMPH

Speed Twin	DD01	2018 ▶ *	H4-LED (11342U60BX2)	E9 11895	HB/LB [10]	-	-
Street Scrambler	DC03, DC03R	2018 ▶ *	H4-LED (11342U60BX2)	E9 11895	HB/LB [10]	-	-
Street Twin	DP03, DP03R	2018 ▶ *	H4-LED (11342U60BX2)	E9 11895	HB/LB [10]	-	-
Tiger 1050	115NG	2006 ▶ 2020	H7-LED (11972U60BX2)	E9 1270	LB	-	-

VW

914	47	1969 ▶ 1976	H4-LED (11342U60BX2)	E4 1 E4 12 E11 0035	HB/LB [20, 25 ³⁾ , 37,5 ³⁾]	-	-
Beetle Beetle Dune	16	2011 ▶ 2016	H4-LED (11342U60BX2)	E1 3203	HB / LB [30 ³⁾]	-	-
Caddy (1. Gen.) ⁵⁾	14 D	1979 ▶ 2007	H4-LED (11342U60BX2)	E1 14551 E1 14565	HB/LB [27,5 ³⁾ , 25 ³⁾]	-	-
Derby	86	1977 ▶ 1985	H4-LED (11342U60BX2)	E1 14592	HB/LB [25]	-	-
Golf (1. Gen.)	17, 17 CK	1974 ▶ * ▶ 1983	H4-LED (11342U60BX2)	E1 14551 E1 14565	HB/LB [27,5 ³⁾ , 25 ³⁾]	-	-
Golf (2. Gen.)	19 E, 19 E-299, 19EL	1983 ▶ * ▶ 1992	H4-LED (11342U60BX2)	E1 14551 E1 14565	HB/LB [27,5 ³⁾ , 25 ³⁾]	-	-
Golf (3. Gen.) Golf Variant (3. Gen.)	1HX0, 1HX0F, 1HX1, 1HX0E, 1HX1, 1HX1	1991 ▶ 1999	H4-LED (11342U60BX2)	E1 44464 (LH) / E1 44465 (RH)	HB/LB [50 ³⁾]	-	-
Golf (4. Gen.)	1J	1997 ▶ 2006	H1-LED (11258U60BX2)	E1 761	HB [12,5 ³⁾]	-	-
Golf (4. Gen.)	1J	1997 ▶ 2006	H1-LED (11258U60BX2)	E9 5163	HB [12,5 ³⁾]	-	-
Golf (6. Gen.), Golf Cabrio (6. Gen.)	1K / 1KM	2008 ▶ 2013	H7-LED (11972U60BX2)	E9 5813	LB	Type D (11176X2)	-
Golf (7. Gen.), Golf 7, Golf 7 Variant	AU, AUV, 1 K, 1 KM	2012 ▶ 2017	H7-LED (11972U60BX2)	E8 7169	LB	Type A (11184X2)	-
Golf (7. Gen.), Golf 7, Golf 7 Variant	AU, AUV, 1 K, 1 KM	2012 ▶ 2017	H7-LED (11972U60BX2)	E9 6765	LB	Type D (11176X2)	-
Golf (7. Gen.), Golf 7, Golf 7 Variant	AU, AUV, 1 K, 1 KM	2014 ▶ 2017	H7-LED (11972U60BX2)	E8 7169	LB	Type A (11184X2)	-
Golf (7. Gen.), Golf 7, Golf 7 Variant	AU, AUV, 1 K, 1 KM	2014 ▶ 2017	H7-LED (11972U60BX2)	E9 6765	LB	Type D (11176X2)	-
Golf (7. Gen., Facelift), Golf 7 (Facelift) Golf 7 Variant (Facelift)	AU, AUV, 1 K, 1 KM	2017 ▶ 2020	H7-LED (11972U60BX2)	E8 8526	LB	Type P (11182X2)	-
Golf 4	1J	1997 ▶ 2006	H7-LED (11972U60BX2)	E1 761	LB	-	-
Golf 6 Golf Cabrio 6	1K, 1KM 1K	2008 ▶ 2013 2011 ▶ 2016	H7-LED (11972U60BX2)	E8 4816	LB	Type A (11184X2)	-

NEW

Golf Cabrio (1. Gen.)	155	1979 ▶ 1993	H4-LED (11342U60BX2)	E1 14551 E1 14565	HB/LB [27,5 ³⁾ , 25 ³⁾	-	-
Golf Cabrio (3. Gen.)	1EXO	1993 ▶ 1999	H4-LED (11342U60BX2)	E1 44464 (LH) / E1 44465 (RH)	HB/LB [50 ³⁾	-	-
Golf Sportsvan	AUV	2014 ▶ 2017	H7-LED (11972U60BX2)	E9 11342	LB	Type D (11176X2)	-
Golf Sportsvan	1 KM	2015 ▶ 2017	H7-LED (11972U60BX2)	E9 11342	LB	Type D (11176X2)	-
Käfer	11, 13	1967 ▶ * ▶ 2004	H4-LED (11342U60BX2)	E1 14551 E1 14565	HB/LB [27,5 ³⁾ , 25 ³⁾	-	-
Käfer Cabriolet	15	1967 ▶ 1980	H4-LED (11342U60BX2)	E1 14551 E1 14565	HB/LB [27,5 ³⁾ , 25 ³⁾	-	-
Kurierwagen (Typ 181 / 182)	18, 18 - 63	1969 ▶ 1980	H4-LED (11342U60BX2)	E1 14551 E1 14565	HB/LB [27,5 ³⁾ , 25 ³⁾	-	-
LT (1. Gen.) ⁵⁾	283 CF, 283, 281 CH, 281, 281 CG, 283 CG, 291 CH, 291, 293 CH, 293, 291 CG, 293 CG, 281-363 CH, 281- 363 CG, 281-363, 291-512, 293-512, 293-909	1975 ▶ * ▶ 1985	H4-LED (11342U60BX2)	E1 14551 E1 14565	HB/LB [27,5 ³⁾ , 25 ³⁾	-	-
New Beetle	9C	1998 ▶ 2005	H1-LED (11258U60BX2)	E1 610 (LH) / E1 611 (RH)	LB	-	-
New Beetle Cabrio	1Y	2002 ▶ 2005	H1-LED (11258U60BX2)	E1 610 (LH) / E1 611 (RH)	LB	-	-
Passat (B4, 4. Gen.)	35I	1993 ▶ 1997	H1-LED (11258U60BX2)	E1 44515 (LH) / E1 44516 (RH)	HB/LB [12,5 ³⁾	-	-
Passat B6	3C	2005 ▶ 2010	H7-LED (11972U60BX2)	E9 5507	LB	Type I (11179X2)	CANBus H7-LED
Passat B7 (Facelift)	3C	2010 ▶ 2015	H7-LED (11972U60BX2)	E1 3058	LB	-	-
Passat B8	3C	2014 ▶ *	H7-LED (11972U60BX2)	E9 11464	LB	-	-
Polo (1. Gen)	86	1975 ▶ 1981	H4-LED (11342U60BX2)	E1 14592	HB/LB [25]	-	-
Polo (2. Gen)	86C	1981 ▶ 1989	H4-LED (11342U60BX2)	E1 14592	HB/LB [25]	-	-
Polo (2. Gen, Facelift)	86C, 86CF	1989 ▶ 1994	H4-LED (11342U60BX2)	E1 44449 (LH) / E1 44450 (RH)	HB/LB [37,5]	-	-
Polo (5.Gen)	6R	2009 ▶ 2014	H4-LED (11342U60BX2)	E9 5856	HB / LB [17,5 ³⁾	-	-
Polo (5.Gen., Facelift)	6R	2014 ▶ 2017	H7-LED (11972U60BX2)	E8 6879	HB / LB [27,5 ³⁾	Type P (11182X2)	-
Polo (6. Gen.)	AW	2017 ▶ 2021	H7-LED (11972U60BX2)	E9 16592	LB	-	-
PoloCross, CrossPolo	6R	2010 ▶ 2015	H7-LED (11972U60BX2)	E1 2714	HB / LB [17,5 ³⁾	Type P (11182X2)	-
Sharan (2.Gen)	7N	2010 ▶ *	H7-LED (11972U60BX2)	E1 2581	LB/HB [27,5 ³⁾	Type D (for LB only)	-
T2 Bus ⁵⁾ T2 Transporter ⁵⁾	21 F, 26, 28, 23, 22, 21, 22	1967 ▶ * ▶ 1979	H4-LED (11342U60BX2)	E1 14551 E1 14565	HB/LB [27,5 ³⁾ , 25 ³⁾	-	-
T3 Transporter ⁵⁾ T3 Kombi ⁵⁾ T3 Bus ⁵⁾ T3 Caravelle ⁵⁾ T3 California ⁵⁾	245, 251, 253, 255, 253- 135, 253-609, 253-299, 255- 299, 251-299, 245-299, 253- 6-299, 247, 247-299	1979 ▶ * ▶ 1992	H4-LED (11342U60BX2)	E1 14551 E1 14565	HB/LB [27,5 ³⁾ , 25 ³⁾	-	-
T3 Transporter, T3 Kombi, T3 Bus; T3 Caravelle, T3 California ⁵⁾	245, 251, 253, 255, 253- 135, 253-609, 253-299, 255- 299, 251-299, 245-299, 253- 6-299, 247, 247-299	1979 ▶ 1992	H4-LED (11342U60BX2)	E1 34482 (LH) / E1 34483 (RH)	HB/LB [17,5]	-	-

NEW

T4 Transporter (FL), T4 Multivan (FL), T4 California (FL), T4 Caravelle (FL)	70X0A, 70X0D, 70X0B, 70X0BL, 70X0BN, 70X1B, 70X1A, 70X1D, 70X1BL, 70X1BN, 70X0C, 70X1C, 70X02C, 70X12C, 70X02BN, 70X02D, 70X02A, 70X12A, 70X12D, 7DB, 7DZ, 7DW, 7DWA, 7DZA	1995 ▶ 2003	H4-LED (11342U60BX2)	E9 5082	HB/LB [50]	-	-
T4 Transporter ⁵⁾ T4 Multivan ⁵⁾ T4 California ⁵⁾ T4 Caravelle ⁵⁾	70X0A, 70X0D, 70X0B, 70X0BL, 70X0BN, 70X1B, 70X1A, 70X1D, 70X1BL, 70X0C, 70X1C, 70X02C, 70X12C, 70X02BN, 70X02D, 70X02A, 70X12A, 70X12D, 7DB	1990 ▶ * ▶ 2003	H4-LED (11342U60BX2)	E1 44437 (LH) / E1 44438 (RH)	HB/LB [50 ³⁾]	-	-
T5 California, T5 Multivan, T5 Transporter, T5 Caravelle	7HM, 7HC, 7HCA, 7HMA, 7HK, 7J0	2003 ▶ 2009	H7-LED (11972U60BX2)	E1 1370	LB	-	-
T5 Caravelle ⁵⁾ T5 California ⁵⁾ T5 Multivan ⁵⁾ T5 Transporter ⁵⁾	7HM, 7HC, 7HCA, 7HMA, 7HK, 7J0	2003 ▶ 2009	H4-LED (11342U60BX2)	E1 1366	HB / LB [37,5 ³⁾]	-	-
T5 Caravelle Facelift ⁵⁾ T5 California Facelift ⁵⁾ T5 Multivan Facelift ⁵⁾ T5 Transporter Facelift ⁵⁾	7HC, 7HMA, 7J0	2009 ▶ 2016	H4-LED (11342U60BX2)	E1 2707	HB / LB [30 ³⁾]	-	⁴⁾ CANBus H4-LED
T5 Caravelle (Facelift), T5 California (Facelift), T5 Multivan (Facelift), T5 Transporter (Facelift)	7HC, 7HMA, 7J0	2009 ▶ 2016	H7-LED (11972U60BX2)	E1 2707	LB	Type D (11176X2)	CANBus H7-LED
T6 Caravelle (Facelift, T6.1), T6 California (Facelift, T6.1), T6 Multivan (Facelift, T6.1), T6 Transporter (Facelift, T6.1)	7HC, 7HMA, 7J0	2019 ▶ *	H7-LED (11972U60BX2)	E9 22767	LB	-	-
T6 Caravelle, T6 California, T6 Multivan, T6 Transporter	7HC, 7HMA, 7J0	2015 ▶ 2019	H7-LED (11972U60BX2)	E9 11760	LB	-	CANBus H7-LED
T-Cross	C1	2018 ▶ *	H7-LED (11972U60BX2)	E9 22186	LB	-	CANBus H7-LED
Tiguan (1.Gen.)	5N	2007 ▶ 2011	H7-LED (11972U60BX2)	E1 2393	LB	Type P (11182X2)	-
Tiguan (1.Gen.) Facelift	5N	2011 ▶ 2016	H7-LED (11972U60BX2)	E1 3175	LB	Type A (11184X2)	-
Tiguan (2.Gen.)	5N	2016 ▶ 2020	H7-LED (11972U60BX2)	E1 4116	HB / LB [25 ³⁾]	Type E (for LB only)	-
Touran (1. Gen, 2. Facelift)	1T, 1t	2010 ▶ 2015	H7-LED (11972U60BX2)	E1 2855	LB	Type D (11176X2)	-
Touran (2. Gen.)	1T	2015 ▶ *	H7-LED (11972U60BX2)	E1 3985	LB	Type D (11176X2)	-
T-Roc	A1	2017 ▶ *	H7-LED (11972U60BX2)	E9 16552	LB	Type D (11176X2)	-
Typ 3 (1500 / 1600)	31	1961 ▶ 1973	H4-LED (11342U60BX2)	E1 14551 E1 14565	HB/LB [27,5 ³⁾ , 25 ³⁾]	-	-
up! (Facelift) e-up! cross up! up! GTI up! e-up! cross up!	AA, AAN	2016 ▶ *	H4-LED (11342U60BX2)	E8 8227	HB / LB [27,5 ³⁾]	-	⁸⁾ CANBus H4-LED
	AA, AAE, AAN	2011 ▶ 2016	H4-LED (11342U60BX2)	E1 3149	HB / LB [30 ³⁾]	-	-

VW, MAN-VW, ARGE VW-MAN

6.90 F, 8.136 F, 8.90 F	6.90 F, 8.136 F, 8.90 F	1980 ▶ 1987	H4-LED (11342U60BX2)	E1 14551 E1 14565	HB/LB [27,5 ³⁾ , 25 ³⁾]	-	-
9.136 F	9.136 F	1979 ▶ 1987	H4-LED (11342U60BX2)	E1 14551 E1 14565	HB/LB [27,5 ³⁾ , 25 ³⁾]	-	-

WESTFALIA, RAPIDO

Jules Verne ⁵⁾	639	2016 ▶ *	H7-LED (11972U60BX2)	E1 3655	LB	Type A (11184X2)	-
Jules Verne ⁵⁾	639/5	2019 ▶ *	H7-LED (11972U60BX2)	E1 3655	LB	Type A (11184X2)	-

YAMAHA

MT-07, MT07A	RM17, RM18	2016 ▶ 2018	H4-LED (11342U60BX2)	E4 17394	HB/LB [12,5]	-	-
MT-07, MT07A, MTN690-A	RM17, RM18	2018 ▶ *	H4-LED (11342U60BX2)	E4 17066	HB/LB [12,5]	-	-
MT-09	RN29	2013 ▶ 2016	H4-LED (11342U60BX2)	E4 17066	HB/LB [12,5]	-	-
MTM850, XSR900	RN43	2015 ▶ *	H4-LED (11342U60BX2)	E13 8785	HB/LB [17,5]	-	-
YZF-R1	RN12	2003 ▶ 2008	H7-LED (11972U60BX2)	E13 8996	LB	-	-

YAMAHA, MBK

MTM690, MTM690D	RM36, RM37	2021 ▶ *	H4-LED (11342U60BX2)	E13 8785	HB/LB [17,5]	-	-
XSR700	RM11, RM12	2015 ▶ *	H4-LED (11342U60BX2)	E13 8785	HB/LB [17,5]	-	-

1) *corresponds to end of production.

2) ** LB corresponds to low/passing beam, HB corresponds to high/driving beam

3) The specified high beam index I'M with H7-LED, H4-LED or H1-LED differs from the specification on the headlamp. The permissible sum of the main beam characteristics of all main beam headlamps must not exceed 100. Reference mark I'M with H7-LED, H4-LED or H1-LED for the main beam of each model is as below.

4) In the event of an error message, the optional CANbus must be used.

5) Vehicles (SO.KFZ Wohnmobil and other classes / body types) are also approved whose headlights correspond to the listed UN(ECE) type approval and have received a multi-stage approval on the basis of the named basic vehicle.

6) The road approval of the Philips Ultinon Pro6000 LED lamp is only valid if installed where required with Philips original accessories. Please check the compatibility list to see if additional accessories are required for your vehicle.

7) The road approval for the Volkswagen T5, only applies when the H4 lamp type is installed. Please check whether your vehicle is equipped with H4 halogen lamps before

8) For vehicle models with faulty cornering light function, the use of the optional CANbus is required.

9) The year of production is not relevant for the approval. It serves as means for orientation.



2024 © Lumileds Holding B.V. All rights reserved.

The Philips trademark and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V. Specifications are subject to change without notice.

[Philips.com/roadlegalLED](https://philips.com/roadlegalLED)

EN • 09-2023