

PHILIPS

Automotive lighting

Catalog
2023-24



Table of content



Introduction 4

Safety you can see

LED Road-legal 6

Cars and two-wheelers

Ultinon Pro6000 HL	10
Ultinon Pro6000 Standard HL	11
LED CANbus Adapters	12
LED Adapter Rings	12

LED Off-road 16

Cars and trucks

Ultinon Pro9100 HL	20
Ultinon Pro5100 HL	22
Ultinon Pro3022 HL	23
Ultinon Access HL	24
Ultinon Pro6000 SI	26
Ultinon Pro3100 SI	28
LED CANbus Adapters	30
LED Adapter Rings	30
Which LED lighting for which function?	32

Halogen 46

Cars

RacingVision GT200	50
X-tremeVision Pro150	51
VisionPlus	52
WhiteVision ultra	53
LongLife EcoVision	54
Vision	55
Which lamp for which function?	56

Halogen 74

Two-wheelers

RacingVision GT200 moto	77
CityVision moto	77
WhiteVision ultra moto	78
Vision moto	78
Which lamp for which function?	79

Halogen 82

24V Bus and trucks

MasterDuty	85
MasterLife	86
MasterDuty BlueVision	86
Which lamp for which function?	87

Halogen 94

Kits

12V spare kits	96
24V spare kits	98
Headlight restoration kit	99

Xenon 100

Cars and trucks

Xenon X-tremeVision gen2	103
Xenon WhiteVision gen2	104
Xenon LongerLife	105
Xenon Vision	106

Annexes 112

Glossary	112
Specimen packaging	114
Understanding Philips ordering codes	115
Technical illustrations bases	116
Product index	117

Safety you can see!

Our advanced light engine technology has been on the forefront of automotive lighting for more than 100 years.

As a **leading supplier** of lamps and lighting products to the automotive industry and aftermarket, we combine technical innovations with a genuine concern for **safety** and driving comfort.

Our automotive lighting is today the choice of many consumers and major automobile manufacturers.

Our mission is to introduce **innovative products** that constantly improve road safety and increase workshop productivity.

Our products are designed to perform efficiently and durably for continuous **customer satisfaction**.

Many garages and workshops already appreciate our new range of professional LED work lights for their outstanding light output and robustness.

High-quality lighting really does make a difference.

That's safety you can see!



Original equipment quality

We are committed to producing **best-in-class products** and services in the Original Equipment Manufacturer (OEM) market and automotive aftermarket. Our products are manufactured from **high-quality materials** and tested

to the highest specifications to maximize **safety** and driving **comfort** of our customers.

- We are the **choice** of major car manufacturers

- Our lighting equips **one in two cars** in Europe and one in three in the world

- Manufacturing processes that **exceed** current industry **specifications**

Philips anti-UV-quartz glass for optimal lighting performance

All Philips quartz-glass lamps also offer a UV shield to protect your modern plastic optics from harmful UV rays.

- **More powerful light**

Quartz glass high resistance allows for increased pressure inside the lamp and thus generates more powerful light.

- **Better resistance**

Philips quartz glass lamps (filament at 2 800°C and glass up to 800°C) are capable of withstanding severe thermal shocks.

- **Optimal protection against ultraviolet rays**

All Philips quartz-glass lamps also offer a UV shield to protect your modern plastic optics from harmful UV rays.

LED Road-legal



Car and two-wheeler

lighting



Which road-legal LED lamp do you need?



Up to 230% more brightness*

Ultinon Pro6000

Lumileds LUXEON Altilon LEDs

2 years +1 extended warranty

Beam performance*

Standard Up to **+230%**

Light color

Up to **5800 K**

Standard: 3100 K

Lifetime

Up to **3000 h**

Standard halogen: 500 h

Available in **HL H4-LED, H7-LED**

Up to 220% more brightness*

Ultinon Pro6000 Standard

Automotive grade LED

2 years +1 extended warranty

Beam performance*

Standard Up to **+220%**

Light color

Up to **5800 K**

Standard: 3100 K

Lifetime

Up to **2000 h**

Standard halogen: 500 h

Available in **HL H7-LED**

Images for illustration purposes only.
* Compared to the minimum legal standard for halogen bulbs.

The Philips Ultinon Pro6000 LED and Ultinon Pro6000 LED Standard ranges are approved for road traffic in the respective countries where approval exists and for the listed range of vehicle models and lighting functions only.
For more information about the legal requirements that apply in your country and to check our latest compatibility list, visit: Philips.com/RoadLegalLED. Drivers are responsible for complying with legal requirements applicable in their country.



Car and two-wheeler lighting

LED Road-legal



Ultinon Pro6000 HL

Taking bright white light to the next level

Experience unprecedented driving experience with **Philips's first road-approved* LED headlight bulbs.**

- **100% road-legal***
- Lumileds' exclusive high-performance automotive LEDs
- Up to **230% brighter homogeneous light**** for optimal light distribution
- **5800 Kelvin** color temperature for crisp white light
- Special light spectrum for improved contrast and visibility
- Reliable, long-lasting performance thanks to our innovating Airboost cooling technology
- **SafeBeam** technology for glare-free driving
- Over 350 compatible vehicle models***
- Longer lifetime of up to **3,000 hours**

*Check the legal requirement applying in our country at Philips.com/RoadLegalLED
 **Compared to the minimum legal standard for halogen bulbs
 ***The Philips Ultinon Pro6000 bulbs are approved for road traffic in the respective countries where approval exists and for listed range of vehicle models and lighting functions only. Check at Philips.com/RoadLegalLED



Standard Halogen



Ultinon Pro6000

Available in X1 and X2 packaging



Available in



H4-LED

H7-LED

W5W-LED



Ultinon Pro6000 Standard HL

Quick, easy installation

Introducing the groundbreaking Philips Ultinon Pro6000 Standard LED replacement lamp at a pocket-friendly price.

- 100% road-legal*
- +220% remarkable brightness**
- Covers both low- and high-beam functions
- 5800 Kelvin color temperature for crisp white light
- Special light spectrum for improved contrast and visibility
- SafeBeam technology for glare-free driving
- Compatible with vehicle models***
- Lifetime of up to 2,000 hours

*Check the legal requirement applying in our country at Philips.com/RoadLegalLED
 **Compared to the minimum legal standard for halogen bulbs
 ***The Philips Ultinon Pro6000 Standard bulb is approved for road traffic in the respective countries where approval exists and for listed range of vehicle models and lighting functions only. Check at Philips.com/RoadLegalLED



Standard Halogen



Ultinon Pro6000 Standard

Available in X2 packaging



Available in



H7-LED

Car and two-wheeler lighting

LED Road-legal

CANbus Adapters

- Designed to **prevent inaccurate dashboard error messages** for vehicles equipped with bulb failure detection
- **Avoid flickering and light-dimming issues**
- Ensure smooth installation of Philips HL-LED bulbs
- EMI compliance on electromagnetic interference
- IP65 ingress protection from dust and water
- Available for the main headlight types: H4 and H7



Available in



H7-LED

H4-LED

Available in X2 packaging



Adapter Rings

Almost every car model has a different type of socket in which halogen bulbs are secured. When replacing your halogen bulbs with LED lighting, you may need a connector ring to secure the LED bulbs inside the headlamp.

Every Philips H7-LED upgrade is supplied with a standard center ring. If another type of adapter ring is needed, you can find the concerning ring type mentioned in the Philips application list.

Philips.com/LEDcompatibility-check



Available in



Type A

Type D

Type E

Type H

Type I

Type K

Type N

Type P

Available in X2 packaging





Car and two-wheeler lighting

LED Road-legal

12V LED Headlighting and Signaling lighting

H4-LED Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11342U6000X2	12	18	P43t-38	01361331		-	8719018013644	Yes	6
11342U6000X1	12	18	P43t-38	02422094		-	8719018024237	Yes	4

H7-LED Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11972U6000X2	12	15	PX26d	01365131		-	8719018013668	Yes	6
11972U6000X1	12	15	PX26d	02424494		-	8719018024251	Yes	4

H7-LED Ultinon Pro6000 Standard



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11972U60SX2	12	17	W2.1x9.5d	02556231		-	8719018025579	Yes	10

W5W-LED Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11961HU60X2	12	0,9	W2.1x9.5d	01638630		-	8719018016393	Yes	10

CANbus Adapters

CANbus adapter for H4-LED



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
18960X2	12	12	-	72831594	6 974260 728315	-	6974260728322	-	4

CANbus adapter for H7-LED



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
18952X2	12	12	-	72837794	6 974260 728377	-	6974260728384	-	4

Adapter Rings

Type A



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11184X2	-	-	-	02009331	8 719018 020093	-	8719018020109	Yes	6

Type H



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11172X2	-	-	-	01630031	8 719018 016300	-	8719018016317	Yes	6

Type D



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11176X2	-	-	-	01681231	8 719018 016812	-	8719018016829	Yes	6

Type E



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11178X2	-	-	-	01679931	8 719018 016799	-	8719018016805	Yes	6

Type I



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11179X2	-	-	-	01683631	8 719018 016836	-	8719018016843	Yes	6

Type K



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11180X2	-	-	-	01675131	8 719018 016751	-	8719018016768	Yes	6

Type N



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11183X2	-	-	-	01636231	8 719018 016362	-	8719018016379	Yes	6

Type P



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11182X2	-	-	-	01677531	8 719018 016775	-	8719018016782	Yes	6

LED Off-road

Car and truck

lighting



Which LED lamp do you need?



Professional performance

Original automotive LED performance

Ultinon Pro9100


Lumileds LUXEON TopContact LED™
2 years +3 extended warranty




Beam performance*



Light color



Lifetime



Available in

HL [≈H1], [≈H3], [≈H4], [≈H7], [≈HB3/HB4], [≈H11], [≈HIR2]

FL [≈H8/H11/H16]

White light for brighter roads

Ultinon Pro5100


Automotive grade LED
2 years +1 extended warranty



Beam performance*



Light color



Lifetime



Available in

HL [≈H1], [≈H3], [≈H4], [≈H7], [≈HB3/HB4], [≈H11], [≈HIR2]

FL [≈H8/H11/H16]


Stylish LED light

Ultinon Pro3022


2 years +1 extended warranty



Beam performance*



Light color



Lifetime



Available in

HL [≈H1], [≈H3], [≈H4], [≈H7], [≈HB3/HB4], [≈H11], [≈HIR2]

FL [≈H8/H11/H16]

Quick and easy installation

Upgrade. Drive. Enjoy.

Ultinon Access


2 years +1 extended warranty




Beam performance*



Light color



Lifetime



Available in

HL [≈H1], [≈H3], [≈H4/H19], [≈H7/H18], [≈HB3/HB4], [≈H11], [≈HIR2]

FL [≈H8/H9/H16]

Images for illustration purposes only.

* Compared to the minimum legal standard for halogen bulbs.

** Except for Ultinon Pro9100 HL [≈H1] and [≈H3] types.



It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.

Philips.com/led-bulbs



Car and truck lighting

LED Off-road



Ultinon Pro9100

Original automotive LED performance


- **Exclusive** automotive LED technology thanks to Lumileds LUXEON TopContact LEDs*
- Up to **350% brighter homogeneous light****
- Up to **5800 K** color temperature for **cool white light**
- **Optimal spectrum** for best road sign visibility
- **IP-certified** against dust ingress and with splash-water protection
- Unique Philips heat-management technologies
- **SafeBeam** technology for glare-free driving
- Lifetime up to **5,000 hours**
- **High compatibility** with major vehicle models
- **Extended warranty** up to **5 years**.
- Compatible with 12V and 24V electrical systems

*Except HL [=H1] and HL [=H3] bulb types.

**Compared to the minimum legal standard for halogen bulbs



Standard halogen



Ultinon Pro9100

Available in X2 packaging



Available in



HL [=H1]



HL [=H3]



HL [=H4]



HL [=H7]



FL
[=H8/H11/H16]



HL [=H11]



HL
[=H3/HB4]



HL [=HIR2]





Car and truck lighting

LED Off-road



Ultinon Pro5100

White light, for brighter roads

- Get up to **+160% brighter light*** for superior visibility
- Up to **5800 K** color temperature for **bright white light and modern look**
- **SafeBeam** technology for glare-free driving
- Lifetime up to **3,000 hours**
- **High compatibility** with major vehicle models
- **Extended warranty** up to **3 years**.
- Compatible with 12V and 24V electrical systems

*Compared to the minimum legal standard for halogen bulbs



Standard halogen



Ultinon Pro5100

Available in X2 packaging



Available in





Ultinon Pro3022


Stylish LED lighting that's easy to fit

- Up to **+100 brighter light***
- Up to **6000 K color temperature** for a cool-white-light look
- Compact **all-in-one design** for plug and play use
- Compatible with major vehicle models
- **Long-lasting performance**
- Extended **warranty** up to **3 years**
- Compatible with 12V and 24V electrical systems

*Compared to the legal minimum standard for halogen bulbs



Standard halogen



Ultinon Pro5100



Available in X2 packaging



Available in



HL [≈H1]



HL [≈H3]



HL [≈H4]



HL [≈H7]



FL [≈H8/H11/H16]



HL [≈H11]



HL [≈HB3/HB4]



HL [≈HIR2]



It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.




Ultinon Access


Upgrade. Drive. Enjoy.

- **Plug-and-play installation:** as simple and fast to install as halogen bulbs!
- **Direct-fit design:** very compact body and integrated IEC 60061 compatible base
- **Better light performance:** up to +80% brighter light*
- Lifetime up to **1,500 hours**
- Up to **6000 K** color temperature for a cool white look
- **Extended warranty** up to **3 years**.

*Compared to the minimum legal standard for halogen bulbs.



Standard halogen



Ultinon Access

Available in



HL [=H1]

HL [=H3]

HL [=H4/H19]

HL [=H7/H18]



FL
[=H8/H9/H16]

HL [=H11]

HL
[=HB3/HB4]

HL [=HIR2]

Available in CX packaging



This special CX pack includes 2x individual C1 pack





Car and truck lighting

LED Off-road



Ultinon Pro6000 SI

Brighter, elegant signals

The Philips Ultinon Pro6000 signaling bulbs offer superior visibility and style for your car.

Superior visibility

- Powerful light with high lumen output
- Variety of powerful white light
- Instant-on technology for more safety
- Uniform light distribution

High-end, elegant signaling


- Stylish LED signaling light available in white, vibrant red and vibrant amber

Performance made to last

- High-end LED technology
- Long lifetime up to 5,000 hours
- *HeatShield* technology to endure any thermal challenge for T10 bulbs

Simple plug-and-play replacement

- Electrically compatible with most cars
- No flickering thanks to dark-current immunity for festoons
- Standard caps and polarity-free for quick and easy replacement
- Large portfolio for all car applications
































Ultinon Pro6000 SI

Available in

12V

 SI-T10 [≈W5W] Warm White	 SI-T10 [≈W5W] Cool White	 SI-T10 [≈W5W] Extra white	 SI-AMB [≈W5W] Amber	 SI-T16 [≈W16W]
 SI-WHITE [≈P21W]	 SI-RED [≈P21W]	 SI-AMB [≈P21W]	 SI-FEST 30mm Warm White	 SI-FEST 30mm Cool White
 SI-WHITE [≈P21/5W]	 SI-RED [≈P21/5W]	 SI-AMB [≈P21/5W]	 SI-FEST 38mm Warm White	 SI-FEST 38mm Cool White
 SI-WHITE [≈W21W]	 SI-RED [≈W21W]	 SI-AMB [≈W21W]	 SI-FEST 43mm Warm White	 SI-FEST 43mm Cool White
 SI-WHITE [≈W21/5W]	 SI-RED [≈W21/5W]	 SI-AMB [≈W21/5W]		

24V

 LED-T10 [≈W5W] Warm White	 LED-T10 [≈W5W] Cool White	 LED-FEST 30mm Cool White	 LED-WHITE [≈R5W/R10W]
---	---	--	---



Ultinon Pro3100 SI

Stand out from the crowd

The Philips Ultinon Pro3100 signaling range provides the best value for your money. Whether you're looking for a bright, new interior or a stunning style.



Powerful brightness and performance

- Stylish white light, up to cool blue 8000 K for some types
- New amber signaling bulb types
- Matching the performance standard*

Simple plug-and-play

- Easily upgrade from conventional bulbs to LED with a simple installation

Philips Reliability

- Lifetime of up to 3,000 hours

Compatible with major vehicle models

- Compatible with 12V electrical systems
- Optional CANbus available for troubleshooting

*Comply with ECE R37 lumen output requirement (for indication use only)





Ultinon Pro3100 SI

Available in

12V



SI-FEST 30mm
Cool white



SI-FEST 38mm
Cool white



SI-FEST 43mm
Cool white



SI-WHITE
[≈W5W]



SI-WHITE
[≈W21W]



SI-WHITE
[≈P21W]



SI-WHITE
[≈W21/5W]



SI-WHITE
[≈W16W]



SI-WHITE
[≈R5W/R10W]



SI-RED
[≈P21/5W]



SI-RED
[≈W21W]



SI-RED
[≈P21W]



SI-RED
[≈W21/5W]




SI-AMBER
[≈WY21W]



SI-AMBER
[≈PY21W]

CANbus Adapters

- Designed to **prevent inaccurate dashboard error messages** for vehicles equipped with bulb failure detection
- **Avoid flickering and light-dimming issues**
- Ensure smooth installation of Philips HL-LED bulbs
- EMI compliance on electromagnetic interference
- IP65 ingress protection from dust and water
- Available for the main headlight types: H7, H4, H11, FOG, HB3, HB4 and HIR2



Available in



HL [≈H7]

HL [≈H4]

FL [≈H8/
H11/H16]

HL [≈HB3/
HB4/HIR2]

Available in X2 packaging



Adapter Rings

Almost every car model has a different type of socket in which halogen bulbs are secured. When replacing your halogen bulbs with LED lighting, you may need a connector ring to secure the LED bulbs inside the headlamp. Every Philips HL [≈H7] upgrade is supplied with a standard center ring. If another type of adapter ring is needed, you can find the concerning ring type mentioned in the Philips application list.

[Philips.com/LEDcompatibility-check](https://www.philips.com/LEDcompatibility-check)

Ultinon Pro9100		Ultinon Pro5100		Ultinon Pro3022	
Type A		Type RCD		Type RAD	
Type D		Type RCE		Type RAE	
Type E		Type H		Type RAH	
Type H		Type I		Type I	
Type I		Type K		Type K	
Type K		Type N		Type N	
Type N		Type RCP		Type RAP	
Type P					

Available in X2 packaging








Car and truck lighting

LED Off-road

Which LED for which function?



Headlights	Front fog lights	Front position/parking lights	Front indicators	Dashboard lights	Interior lights	Side indicators
Ultinon Pro9100 HL  <ul style="list-style-type: none"> HL [≈H1] 5800K HL [≈H3] 5800K HL [≈H4] 5800K HL [≈H7] 5800K FL [≈H8/H11/H16] 5800K HL [≈HB3/HB4] 5800K HL [≈H11] 5800K HL [≈HIR2] 5800K 		Ultinon Pro6000 SI <ul style="list-style-type: none"> SI-T10 [≈W5W] 4000K, 6000K, 8000K SI-AMB [≈P21W] AMBER SI-AMB [≈P21/5W] AMBER SI-T10 [≈W5W] 4000K, 6000K SI-T10 [≈W5W] 4000K, 6000K SI-AMB [≈W5W] AMBER SI-WHITE [≈R5W/R10W] WHITE SI-AMB [≈W21W] AMBER SI-AMB [≈W21/5W] AMBER SI-FEST 30/38/43 mm 4000K, 6000K SI-FEST 30/38/43 mm 4000K, 6000K SI-T10 [≈W5W] 6000K, 8000K SI-WHITE [≈P21/5W] WHITE SI-WHITE [≈R5W/R10W] WHITE SI-WHITE [≈R5W/R10W] WHITE SI-WHITE [≈W21/5W] WHITE 				
Ultinon Pro5100 HL  <ul style="list-style-type: none"> HL [≈H1] 5800K HL [≈H3] 5800K HL [≈H4] 5800K HL [≈H7] 5800K FL [≈H8/H11/H16] 5800K HL [≈HB3/HB4] 5800K HL [≈H11] 5800K HL [≈HIR2] 5800K 		Ultinon Pro3100 SI <ul style="list-style-type: none"> SI-WHITE [≈W5W] 6000K SI-AMB [≈P21W] 6000K SI-AMB [≈W21W] AMBER SI-WHITE [≈W5W] 6000K SI-WHITE [≈W5W] 6000K SI-WHITE [≈R5W/R10W] WHITE SI-WHITE [≈R5W/R10W] WHITE SI-WHITE [≈P21/5W] WHITE SI-FEST 30/38/43 mm 6000K SI-WHITE [≈R5W/R10W] WHITE SI-WHITE [≈P21/5W] WHITE SI-WHITE [≈R5W/R10W] WHITE 				
Ultinon Pro3022 HL  <ul style="list-style-type: none"> HL [≈H1] 6000K HL [≈H3] 6000K HL [≈H4] 6000K HL [≈H7] 6000K FL [≈H8/H11/H16] 6000K HL [≈HB3/HB4] 6000K HL [≈H11] 6000K HL [≈HIR2] 6000K 		Ultinon Access HL <ul style="list-style-type: none"> HL [≈H1] 6000K HL [≈H3] 6000K HL [≈H4/H19] 6000K HL [≈H7/H18] 6000K FL [≈H8/H9/H16] 6000K HL [≈HB3/HB4] 6000K HL [≈H11] 6000K HL [≈HIR2] 6000K 				

Philips.com/LED-bulbs



It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.



Glove compartment lights	Rear position/parking lights	Rear indicators	Rear fog lights	Trunk lights	License plate lights	Stop lights	Reversing light	3 rd stop light

 SI-T10 [≈W5W]	 SI-RED [≈P21/5W]	 SI-RED [≈W21/5W]	 SI-AMB [≈P21W]	 SI-RED [≈P21W]	 SI-RED [≈W21W]	 SI-T10 [≈W5W]	 SI-T10 [≈W5W]	 SI-RED [≈P21W]	 SI-RED [≈W21W]	 SI-WHITE [≈P21W]	 SI-RED [≈P21W]	 SI-RED [≈W21W]
 SI-FEST 30/38/43 mm	 SI-WHITE [≈P21/5W]	 SI-WHITE [≈W21/5W]	 SI-AMB [≈W21W]	 SI-WHITE [≈P21W]	 SI-WHITE [≈W21W]	 SI-FEST 30/38/43 mm	 SI-FEST 30/38/43 mm	 SI-RED [≈P21/5W]	 SI-RED [≈W21/5W]	 SI-WHITE [≈W21W]	 SI-WHITE [≈P21W]	 SI-WHITE [≈W21W]
 SI-WHITE [≈R5W/R10W]	 SI-WHITE [≈R5W/R10W]	 SI-WHITE [≈P21W]	 SI-T16 [≈W16W]	 SI-WHITE [≈R5W/R10W]	 SI-WHITE [≈R5W/R10W]	 SI-WHITE [≈R5W/R10W]	 SI-WHITE [≈R5W/R10W]	 SI-WHITE [≈P21W]	 SI-WHITE [≈W21W]	 SI-T16 [≈W16W]	 SI-WHITE [≈R5W/R10W]	 SI-WHITE [≈R5W/R10W]
		 SI-WHITE [≈W21W]						 SI-WHITE [≈P21/5W]	 SI-WHITE [≈W21/5W]			

 SI-WHITE [≈W5W]	 SI-RED [≈P21/5W]	 SI-AMB [≈P21W]	 SI-RED [≈P21W]	 SI-WHITE [≈W5W]	 SI-WHITE [≈W5W]	 SI-RED [≈P21W]	 SI-RED [≈P21/5W]	 SI-WHITE [≈P21W]	 SI-WHITE [≈W21W]	 SI-RED [≈P21W]	 SI-RED [≈W21W]
 SI-FEST 30/38/43 mm	 SI-RED [≈W21/5W]	 SI-AMB [≈W21W]	 SI-RED [≈W21W]	 SI-FEST 30/38/43 mm	 SI-FEST 30/38/43 mm	 SI-RED [≈W21W]	 SI-RED [≈W21/5W]	 SI-T16 [≈W16W]	 SI-WHITE [≈P21W]	 SI-WHITE [≈R5W/R10W]	 SI-WHITE [≈W21W]
 SI-WHITE [≈R5W/R10W]				 SI-WHITE [≈R5W/R10W]	 SI-WHITE [≈R5W/R10W]						

12V/24V LED Headlighting

HL [≈H1] Ultinon Pro9100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11258U91X2	12/24	20	P14,5s	01862594	8 719018 018625	-	8719018018632	-	4

HL [≈H1] Ultinon Pro5100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11258U51X2	12/24	12,5	P14,5s	01878694	8 719018 018786	-	8719018018793	-	4

HL [≈H1] Ultinon Pro3022



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11258U3022X2	12/24	18	P14,5s	01812094	8 719018 018120	-	8719018018137	-	4

HL [≈H1] Ultinon Access



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11258U2500CX	12	13	P14,5s	02583850	-	8 719018 025845	8719018025821	-	4x2

HL [≈H3] Ultinon Pro9100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11336U91X2	12/24	20	PK22s	01874894	8 719018 018748	-	8719018018755	-	4

HL [≈H3] Ultinon Pro5100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11336U51X2	12/24	12	PK22s	01890894	8 719018 018908	-	8719018018915	-	4

HL [≈H3] Ultinon Pro3022



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11336U3022X2	12/24	18	PK22s	01814494	8 719018 018144	-	8719018018151	-	4

HL [≈H3] Ultinon Access



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11336U2500CX	12	13	PK22s	02586950	-	8 719018 025876	8719018025883	-	4x2

HL [≈H4] Ultinon Pro9100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11342U91X2	12/24	18	P43t-38	01866394	8 719018 018663	-	8719018018670	-	4

HL [≈H4] Ultinon Pro5100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11342U51X2	12/24	12	P43t-38	01882394	8 719018 018823	-	8719018018830	-	4

HL [≈H4] Ultinon Pro3022



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11342U3022X2	12/24	20	P43t-38	01800794	8 719018 018007	-	8719018018014	-	4

HL [≈H4/H19] Ultinon Access



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11342U2500CX	12	20/22	P43t-38/PJ43t-3		-	8 719018 025661	8719018025678	-	4x2

HL [≈H7] Ultinon Pro9100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11972U91X2	12/24	18	PX26d	01868794	8 719018 018687	-	8719018018694	-	4

HL [≈H7] Ultinon Pro5100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11972U51X2	12/24	12	PX26d	01884794	8 719018 018847	-	8719018018854	-	4

HL [≈H7] Ultinon Pro3022



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11972U3022X2	12/24	20	PX26d	01802194	8 719018 018021	-	8719018018038	-	4

HL [≈H7/H18] Ultinon Access



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11972U2500CX	12	16	PX26d/PY26d-1	02568550	-	8 719018 025708	8719018025692	-	4x2

HL [≈H11] Ultinon Pro9100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11362U91X2	12/24	16	PGJ19-2	01864994	8 719018 018649	-	8719018018656	-	4

HL [≈H11] Ultinon Pro5100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11362U51X2	12/24	12	PGJ19-2	01880994	8 719018 018809	-	8719018018816	-	4

HL [≈H11] Ultinon Pro3022



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11362U3022X2	12/24	20	PGJ19-2	01810694	8 719018 018106	-	8719018018113	-	4

HL [≈H11] Ultinon Access



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11362U2500CX	12	20	PGJ19-2	02571550	-	8 719018 025722	8719018025739	-	4x2



12V/24V LED Headlighting

FL [≈H8/H11/H16] Ultinon Pro9100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11366U91X2	12/24	11	PGJ19-1/2/3	01860194	8 719018 018601	-	8719018018618	-	4

FL [≈H8/H11/H16] Ultinon Pro5100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11366U51X2	12/24	9	PGJ19-1/2/3	01876294	8 719018 018762	-	8719018018779	-	4

FL [≈H8/H11/H16] Ultinon Pro3022



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11366U3022X2	12/24	20	PGJ19-1/2/3	01804594	8 719018 018045	-	8719018018052	-	4

FL [≈H8/H9/H16] Ultinon Access



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11366U2500CX	12	20	PGJ19-1/3/5	02580750	-	8 719018 025814	8719018025821	-	4x2

HL [≈HIR2] Ultinon Pro9100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11012U91X2	12/24	20	PX22d	01872494	8 719018 018724	-	8719018018731	-	4

HL [≈HIR2] Ultinon Pro5100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11012U51X2	12/24	12	PX22d	01888594	8 719018 018885	-	8719018018892	-	4

HL [≈HIR2] Ultinon Pro3022



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11012U3022X2	12/24	20	PX22d	01808394	8 719018 018083	-	8719018018090	-	4

HL [≈HIR2] Ultinon Access



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11012U2500CX	12	20	PX22d	02577750	-	8 719018 025784	8719018025791	-	4x2

HL [≈HB3/HB4] Ultinon Pro9100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11005U91X2	12/24	20	P20d/P22d	01870094	8 719018 018700	-	8719018018717	-	4

HL [≈HB3/HB4] Ultinon Pro5100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11005U51X2	12/24	12	P20d/P22d	01886194	8 719018 018861	-	8719018018878	-	4

HL [≈HB3/HB4] Ultinon Pro3022



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11005U3022X2	12/24	20	P20d/P22d	01806994	8 719018 018069	-	8719018018076	-	4

HL [≈HB3/HB4] Ultinon Access



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11005U2500CX	12	20	P20d/P22d	02574650	-	8 719018 025753	8719018025760	-	4x2



Car and truck lighting

LED Off-road

12V LED Signaling and interior lighting

SI-FEST 30 mm 6000K Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11860CU60X1	12	1.0	SV8.5	01530330	8 719018 015303	-	8719018015310	-	10

SI-FEST 30 mm 6000K Ultinon Pro3100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11860CU31B1	12	0.8	SV8.5	02184730	8 719018 021847	-	8719018021854	-	1x10

SI-FEST 30 mm 4000K Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11860WU60X1	12	1.0	SV8,5	01524230	8 719018 015242	-	8719018015259	-	10

SI-FEST 38 mm 6000K Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11854CU60X1	12	1.0	SV8,5	01532730	8 719018 015327	-	8719018015334	-	10

SI-FEST 38 mm 6000K Ultinon Pro3100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11854CU31B1	12	0.6	SV8.5	02210330	8 719018 022103	-	8719018022110	-	1x10

SI-FEST 38 mm 4000K Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11854WU60X1	12	1.0	SV8,5	01526630	8 719018 015266	-	8719018015273	-	10

SI-FEST 43 mm 6000K Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11866CU60X1	12	1.0	SV8,5	01534130	8 719018 015341	-	8719018015358	-	10

SI-FEST 43 mm 6 000 K Ultinon Pro3100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11866CU31B1	12	0.6	SV8.5	02212730	8 719018 022127	-	8719018022134	-	1x10

SI-FEST 43 mm 4000K Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11866WU60X1	12	1.0	SV8,5	01528030	8 719018 015280	-	8719018015297	-	10

SI-AMBER [≈P21/5W] Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11499AU60X2	12	2.5/0.5	BAY15D	01546430	8 719018 015464	-	8719018015471	-	10

SI-RED [≈P21/5W] Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11499RU60X2	12	2.5/0.5	BAY15D	01538930	8 719018 015389	-	8719018015396	-	10

SI-RED [≈P21/5W] Ultinon Pro3100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11499RU31B2	12	1.75/0.65	BAY15D	02190830	8 719018 021908	-	8719018021915	-	2x10

SI-WHITE [≈P21/5W] Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11499CU60X2	12	2.5/0.5	BAY15D	01544030	8 719018 015440	-	8719018015457	-	10

SI-WHITE [≈P21/5W] 6000 K Ultinon Pro3100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11499CU31B2	12	2.4/0.48	BAY15D	02200430	8 719018 022004	-	8719018022011	-	2x10

SI-AMBER [≈P21W] Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498AU60X2	12	2.3	BAU15s	01548830	8 719018 015488	-	8719018015495	-	10

SI-AMBER [≈PY21W] Ultinon Pro3100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11496AU31B2	12	2.15	BAY15D	02202830	8 719018 022028	-	8719018022035	-	2x10

SI-RED [≈P21W] Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498RU60X2	12	2.3	BA15S	01542630	8 719018 015426	-	8719018015433	-	10

SI-RED [≈P21W] Ultinon Pro3100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498RU31B2	12	1.73	BA15S	02188530	8 719018 021885	-	8719018021892	-	2x10

SI-WHITE [≈P21W] Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498CU60X2	12	2.3	BA15S	01540230	8 719018 015402	-	8719018015419	-	10

SI-WHITE [≈P21W] 6000 k Ultinon Pro3100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498CU31B2	12	2.2	BA15S	02186130	8 719018 021861	-	8719018021878	-	2x10

SI-WHITE [≈W16W] Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11067CU60X1	12	2.4	W2.1x9.5d	01566230	8 719018 015662	-	8719018015679	-	10

12V LED Signaling and interior lighting

SI-WHITE [≈W16W] 6000 K Ultinon Pro3100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11067CU31B1	12	1,8	W2.1x9.5d	02204230	8 719018 022042	-	8719018022059	-	2x10

SI-AMBER [≈W21/5W] Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11066AU60X2	12	2.5/0.5	W3x16q	01556330	8 719018 015563	-	8719018015570	-	10

SI-RED [≈W21/5W] Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11066RU60X2	12	2.5/0.5	W3x16q	01552530	8 719018 015525	-	8719018015532	-	10

SI-RED [≈W21/5W] Ultinon Pro3100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11066RU31B2	12	1.75/0.65	W3x16q	02196030	8 719018 021960	-	8719018021977	-	2x10

SI-WHITE [≈W21/5W] Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11066CU60X2	12	2.5/0.5	W3x16q	01550130	8 719018 015501	-	8719018015518	-	10

SI-WHITE [≈W21/5W] 6000 K Ultinon Pro3100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11066CU31B2	12	2.4/0.48	W3x16q	02208030	8 719018 022080	-	8719018022097	-	2x10

SI-AMBER [≈W21W] Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065AU60X2	12	2,3	WX3x16d	01558730	8 719018 015587	-	8719018015594	-	10

SI-AMBER [≈WY21W] Ultinon Pro3100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11071AU31B2	12	2,15	WX3x16d	02198430	8 719018 021984	-	8719018021991	-	2x10

SI-RED [≈W21W] Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065RU60X2	12	2,3	W3x16d	01564830	8 719018 015648	-	8719018015655	-	10

SI-RED [≈W21W] Ultinon Pro3100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065RU31B2	12	1,73	W3x16d	02194630	8 719018 021946	-	8719018021953	-	2x10

SI-WHITE [≈W21W] Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065CU60X2	12	2,3	W3x16d	01554930	8 719018 015549	-	8719018015556	-	10

SI-WHITE [≈W21W] 6000 K Ultinon Pro3100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065CU31B2	12	2,2	W3x16d	02192230	8 719018 021922	-	8719018021939	-	2x10

SI-AMBER [≈W5W] Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11961AU60X2	12	0,5	W2.1x9.5d	01560030	8 719018 015600	-	8719018015617	-	10

SI-T10 [≈W5W] 8000 K Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11961XU60X2	12	0,7	W2.1x9.5d	01522830	8 719018 015228	-	8719018015235	-	10

SI-T10 [≈W5W] 6000 K Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11961CU60X2	12	0,9	W2.1x9.5d	01516730	8 719018 015167	-	8719018015174	-	10

SI-WHITE [≈W5W] 6000 K Ultinon Pro3100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11961CU31B2	12	0,74	W2.1x9.5d	02182330	8 719018 021823	-	8719018021830	-	2x10

SI-T10 [≈W5W] 4000 K Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11961WU60X2	12	0,9	W2.1x9.5d	01514330	8 719018 015143	-	8719018015150	-	10

SI-WHITE [≈R5/R10W] 6000 K Ultinon Pro3100



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11090CU31B2	12	1,8	BA15s	02206630	8 719018 022066	-	8719018022073	-	2x10

CANbus Adapters

CANbus adapter for LED 5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12956X2	12	5	-	39722294	8 727900 397222	-	8719018005007	-	4

CANbus adapter for LED 21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
18957X2	12	21	-	39587794	8 727900 395877	-	8719018004956	-	4

CANbus adapter for HL [≈H4]



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
18960X2	12	12	-	72831594	6 974260 728315	-	6974260728322	-	4

CANbus adapter for HL [≈H7]



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
18952X2	12	12	-	72837794	6 974260 728377	-	6974260728384	-	4

CANbus adapter for FL [≈H8/H11/H16]



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
18954X2	12	12	-	72833994	6 974260 728339	-	6974260728346	-	4

CANbus adapter for HL [≈HB3/HB4/HIR2]



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
18956X2	12	12	-	72835394	6 974260 728353	-	6974260728360	-	4

Adapter Rings

Type A for U9100



Ordering number	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11184X2	-	02009331	8 719018 020093	-	8719018020109	-	6

Type D for U9100



Ordering number	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11176X2	-	01681231	8 719018 016812	-	8719018016829	-	6

Type E for U9100



Ordering number	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11178X2	-	01679931	8 719018 016799	-	8719018016805	-	6

Type H for U9100, U5100



Ordering number	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11172X2	-	01630031	8 719018 016300	-	8719018016317	-	6

Type I for U9100, U5100, U3022



Ordering number	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11179X2	-	01683631	8 719018 016836	-	8719018016843	-	6

Type K for U9100, U5100, U3022



Ordering number	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11180X2	-	01675131	8 719018 016751	-	8719018016768	-	6

Type N for U9100, U5100, U3022



Ordering number	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11183X2	-	01636231	8 719018 016362	-	8719018016379	-	6

Type P for U9100



Ordering number	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11182X2	-	01677531	8 719018 016775	-	8719018016782	-	6

Type RCD for U5100



Ordering number	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11009RCDX2	-	02058131	8 719018 020581	-	8719018020598	-	6

Type RCE for U5100



Ordering number	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11010RCEX2	-	02060431	8 719018 020604	-	8719018020611	-	6

Type RCP for U5100



Ordering number	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11011RCPX2	-	02062831	8 719018 020628	-	8719018020635	-	6

Type RAH for U3022



Ordering number	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11013RAHX2	-	02046831	8 719018 020468	-	8719018020475	-	6

Type RAP for U3022



Ordering number	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11016RAPX2	-	02052931	8 719018 020529	-	8719018020536	-	6

Type RAE for U3022



Ordering number	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11015RAEX2	-	02050531	8 719018 020505	-	8719018020512	-	6

Type RAD for U3022



Ordering number	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11014RADX2	-	02048231	8 719018 020482	-	8719018020499	-	6



24V LED Signaling and interior lighting

SI-FEST 30mm Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24844CU60X1	24	1,5	SV8.5	01536530	8 719018 015365	-	8719018015372	-	10

SI-WHITE [≈R5W/R10W] Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24805CU60X2	24	1	BA15s	01562430	8 719018 015624	-	8719018015631	-	10

SI-T10 [≈ W5W] 6000K Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24961CU60X2	24	1	W2.1x9.5d	01520430	8 719018 015204	-	8719018015211	-	10

SI-T10 [≈ W5W] 4000K Ultinon Pro6000



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24961WU60X2	24	1	W2.1x9.5d	01518130	8 719018 015181	-	8719018015198	-	10

Halogen



Car lighting



Which car lamp do you need?

Enhanced
brightness






Up to **200%**
more brightness*

**RacingVision
GT200**

Beam
up to
+80 m***



Beam performance*



Available in
H4, H7


Up to **150%**
more brightness*

**X-tremeVision
Pro150**

Beam
up to
+70 m***



Beam performance*





Available in
**H1, H4, H7, H11,
HB3, HB4, HIR2**

Up to **60%**
more vision*

VisionPlus



Beam performance*





Available in
H1, H4, H7

Up to **30%**
more vision*

Vision



Beam performance*



Available in
**H1, H3, H4, H7, H11,
HB3, HB4**

Images for illustration purposes only.

* Compared to the minimum legal standard. ** Lifetime and color temperature differ per type, indication for H7 only.

Philips.com/Halogen



Unique style




Sharp white look

WhiteVision ultra


H4, H7
up to
4200 K



Beam performance*



Light color**



Lifetime**



Available in


H1, H3, H4, H7, H8, H11, HB3, HB4, HIR2, PSX24W

Extended lifetime




Lifetime up to
1500 hours**


LongLife EcoVision




Beam performance



Light color**



Lifetime**



Available in

H1, H3, H4, H7, H11, H18, H19, HIR2

*** Compared to derived minimum after ECE regulation, based on 1 Lux. Farthest distance from the car, applies to H4 and H7.

Philips RacingVision GT200 and X-tremeVision Pro150 ranges are not available in all countries. For more information, please contact your Philips representative.



RacingVision GT200

Incredible performance in a road-legal bulb

- Up to 200% brighter light* to transform your drive
- Extends your beam by 80 meters**
- Fully road-legal for an enjoyable drive

If you're passionate about driving, let Philips RacingVision GT200 car bulbs elevate your automotive experience. Up to 200% brighter light that shines over 80 meters longer means better vision and faster reactions for a more exciting drive.

*Compared to minimum legal standard.

**Compared to derived minimum after ECE regulation, based on 1 Lux. Farthest distance from the car.



Standard



RacingVision GT200

Available in S2 and B1 packaging



Available in



H4



H7



X-tremeVision Pro150

The best blend of high performance and lifetime

- See the road better with up to 150% brighter light*
- Longer lasting for a lifetime of safety**
- High-performance beam throws light 70 meters further***
- More contrast and visibility with cool light

Combining striking brightness with the kind of lifespan previously unavailable in such a high-performance bulb, Philips X-tremeVision Pro150 provides the visibility to keep you and your loved ones even safer on the road.

*Compared to minimum legal standard. Applies to headlight bulbs.
 **Lifetime differs per type. Indication for H7: up to 450 hours.
 ***Compared to derived minimum after ECE regulation, based on 1 Lux.
 Farthest distance from the car. Applies to H4, H7.



Standard



X-tremeVision Pro150

Available in S2 and B1 packaging



Available in





VisionPlus

Fast reactions save lives

- Up to 60% more vision*
- Greater driving comfort with enhanced visibility
- High-quality and ultra-resistant car lamp

Philips VisionPlus headlamps allow drivers to see farther for greater **safety** and **comfort**.

*Compared to the minimum legal standard



Standard



VisionPlus

Available in S2 and B1 packaging



Available in



H1



H4



H7



WhiteVision ultra

Sharp white look

- Superior white stylish look with up to 4 200 Kelvin*
- Driving comfort with up to 60% more vision**
- 100% road-legal performance

Philips WhiteVision ultra, featuring the latest gradient ultra-white coating formula, delivers a stunning white light of up to 4 200 Kelvin. These are the whitest road-legal halogen lights in our portfolio and the perfect choice if you're looking for a cool, stylish look and a safer drive.

*Applies to H4, H7. Light temperature differs per technical type.
 **Compared to the minimum legal standard. Applies to headlight bulbs.



Standard

WhiteVision ultra



Available in S2, B1 and B2 packaging



Available in





LongLife EcoVision

Longer Lifetime, less replacement

- Lasts significantly longer*
- High-quality and ultra-resistant car lamp

Tired of **changing** your headlamps all the time? With **longer lifetime**, Philips LongLife EcoVision is the choice for drivers seeking to **minimize maintenance** on their vehicles.


*Lifetime differs per type. Indication for H7: up to 1500 hours.



Available in S2, C1 and B1 packaging



Available in





Vision

Feel safe, drive safe

- **Up to 30% more vision***
- **Competitive price-performance ratio**
- **High-quality and ultra-resistant car lamp**

Philips Vision headlamps ensure excellent light-beam performance at a very **competitive price**.

*Compared to the minimum legal standard



Standard



Vision



Available in C1 and B1 packaging



Available in



Which lamp for which function?



Low beam – high beam



Front indicators




Interior lights



Front parking lights



Side indicators



Front fog lights



Daytime Running Lights



Dashboard lights





Philips.com/mylamps



Trunk lights

Rear indicators




STOP 3rd stop light



R Reversing light



Glove compartment lights




Rear parking lights



License plate lights



Rear fog lights



STOP Stop lights

*Combines stop and rear parking light function

Headlighting

H1 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258PRB1	12	55	P14,5s	47516930	8 711500 475169	-	8711500475176	ECE	10
12258PRC1	12	55	P14,5s	47518360	8 711500 475183	8727900363791	8711500475190	ECE	100

H1 VisionPlus



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258VPS2	12	55	P14,5s	36322728	8 727900 363227	-	8727900363210	ECE	5
12258VPB1	12	55	P14,5s	36320330	8 727900 363203	-	8727900363197	ECE	10

H1 X-tremeVision Pro150



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258XVPS2	12	55	P14,5s	00565628	8 719018 005656	-	8719018005663	ECE	5
12258XVPB1	12	55	P14,5s	00549630	8 719018 005496	-	8719018005502	ECE	10

H1 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258LLECOS2	12	55	P14,5s	36255828	8 727900 362558	-	8727900362565	ECE	5
12258LLECOB1	12	55	P14,5s	36196430	8 727900 361964	-	8727900361971	ECE	10
12258LLECO1	12	55	P14,5s	36187230	8 727900 361872	-	8727900370683	ECE	10

H1 WhiteVision ultra



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258WUJSM	12	55	P14,5s	00525028	8 719018 005250	-	8719018005267	ECE	5
12258WUB1	12	55	P14,5s	00523630	8 719018 005236	-	8719018005243	ECE	10

H1 Spot



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258SPC1	12	55	P14,5s	40460230	8 711500 404602	-	8727900370690	ECE	10

H2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12311C1	12	55	X511	47752130	8 711500 477521	-	8727900370782	ECE	10

H3 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12336PRB1	12	55	PK22s	69561130	8 711500 695611	-	8711500695628	ECE	10
12336PRC1	12	55	PK22s	69534560	8 711500 695345	8711500775696	8711500695352	ECE	100

Packing quantity: number of packs per outer box

H3 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12336LLECO1	12	55	PK22s	77704130	8 711500 777041	-	8711500779366	ECE	10

H3 WhiteVision ultra



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12336WVUB1	12	55	PK22s	00531128	8 719018 005311	-	8719018005328	ECE	5

H4 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342PRB1	12	60/55	P43t-38	47480330	8 711500 474803	-	8711500474810	ECE	10
12342PRC1	12	60/55	P43t-38	49099560	8 711500 490995	8711500827807	8711500490988	ECE	100
12342PRC2	12	60/55	P43t-38	78028760	8 711500 780287	8711500780294	8711500780300	ECE	50

H4 VisionPlus



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342VPS2	12	60/55	P43t-38	39925728	8 727900 399257	-	8727900350937	ECE	5
12342VPB1	12	60/55	P43t-38	39934930	8 727900 399349	-	8727900399332	ECE	10
12342VPC2	12	60/55	P43t-38	37435360	8 727900 374353	8727900374360	8727900374377	ECE	50

H4 X-tremeVision Pro150



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342XVPS2	12	60/55	P43t-38	00567028	8 719018 005670	-	8719018005687	ECE	5
12342XVPB1	12	60/55	P43t-38	00553330	8 719018 005533	-	8719018005540	ECE	10

H4 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342LLECOS2	12	60/55	P43t-38	36257228	8 727900 362572	-	8727900362589	ECE	5
12342LLECOB1	12	60/55	P43t-38	36198830	8 727900 361988	-	8727900361995	ECE	10
12342LLECO1	12	60/55	P43t-38	36189630	8 727900 361896	-	8727900370836	ECE	10

H4 WhiteVision ultra



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342WVUSM	12	60/55	P43t-38	35490428	8 727900 354904	-	8727900354911	ECE	5
12342WVUB1	12	60/55	P43t-38	35489830	8 727900 354898	-	8727900354881	ECE	10

H4 RacingVision GT200



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342RGTS2	12	60/55	P43t-38	00575528	8 719018 005755	-	8719018005762	ECE	5
12342RGTB1	12	60/55	P43t-38	00571730	8 719018 005717	-	8719018005724	ECE	10

H7 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972PRB1	12	55	PX26d	40607130	8 711500 406071	-	8711500406088	ECE	10
12972PRC1	12	55	PX26d	40593760	8 711500 405937	8711500827838	8711500405944	ECE	100
12972PRC2	12	55	PX26d	37432260	8 727900 374322	8727900374339	8727900374346	ECE	50

H7 VisionPlus



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972VPS2	12	55	PX26d	39938728	8 727900 399387	-	8727900399370	ECE	5
12972VPB1	12	55	PX26d	39936330	8 727900 399363	-	8727900399356	ECE	10
12972VPC2	12	55	PX26d	37426160	8 727900 374261	8727900374278	8727900374285	ECE	50

H7 X-tremeVision Pro150



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972XVPS2	12	55	PX26d	00569428	8 719018 005694	-	8719018005700	ECE	5
12972XVPB1	12	55	PX26d	00555730	8 719018 005557	-	8719018005564	ECE	10

H7 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972LLECOS2	12	55	PX26d	36259628	8 727900 362596	-	8727900362602	ECE	5
12972LLECOB1	12	55	PX26d	36200830	8 727900 362008	-	8727900362015	ECE	10
12972LLECO1	12	55	PX26d	36192630	8 727900 361926	-	8727900371024	ECE	10

H7 WhiteVision ultra



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972WVUSM	12	55	PX26d	35495928	8 727900 354959	-	8727900354942	ECE	5
12972WVUB1	12	55	PX26d	35493530	8 727900 354935	-	8727900354928	ECE	10

H7 RacingVision GT200



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972RGTS2	12	55	PX26d	00577928	8 719018 005779	-	8719018005786	ECE	5
12972RGTB1	12	55	PX26d	00573130	8 719018 005731	-	8719018005748	ECE	10

H8 WhiteVision ultra



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12360WVUB1	12	35	PGJ19-1	00533528	8 719018 005335	-	8719018005342	ECE	5

H8



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12360B1	12	35	PGJ19-1	82416530	8 711500 824165	-	8727900362909	ECE	10
12360C1	12	35	PGJ19-1	47582430	8 711500 475824	-	8727900371017	ECE	10

H9



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12361B1	12	65	PGJ19-5	36308130	8 727900 363081	-	8727900363098	ECE	10
12361C1	12	65	PGJ19-5	47584830	8 711500 475848	-	8727900371000	ECE	10

H10



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9145C1	12	45	PY20d	52974530	8 711559 529745	-	8727900370737	ECE	10

H11 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12362PRB1	12	55	PGJ19-2	36428630	8 727900 364286	-	8727900364293	ECE	10
12362PRC1	12	55	PGJ19-2	36430930	8 727900 364309	-	8727900370751	ECE	10

H11 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12362LLECOB1	12	55	PGJ19-2	36310430	8 727900 363104	-	8727900363111	ECE	10
12362LLECO1	12	55	PGJ19-2	36194030	8 727900 361940	-	8727900370744	ECE	10

H11 WhiteVision ultra



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12362WWUB1	12	55	PGJ19-2	00535928	8 719018 005359	-	8719018005366	ECE	5

H11 X-tremeVision Pro150



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12362XVPB1	12	55	PGJ19-2	00551928	8 719018 005519	-	8719018005526	ECE	5

H13



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9008C1	12	60/55	P26,4t	87798730	8 711500 877987	-	8727900370768	ECE	10

H15



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12580B1	12	55/15	PGJ23t-1	02001730	8 719018 020017	-	8719018020031	ECE	10
12580C1	12	55/15	PGJ23t-1	02000030	8 719018 020000	-	8719018020024	ECE	10

H16



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12366C1	12	19	PGJ19-3	36856730	8 727900 368567	-	8727900370775	ECE	10

H18 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12643LLC1	12	65	PY26d-1	35603830	8 727900 356038	-	8727900356045	ECE	10

H19 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12644LLC1	12	60/65	PU43t-3	35605230	8 727900 356052	-	8727900356069	ECE	10

HB1 9004



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9004C1	12	65/45	P29t	47074430	8 711500 470744	-	8727900370997	-	10

HB3 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9005PRB1	12	60	P20d	24724730	8 711500 247247	-	8711500247254	ECE	10
9005PRC1	12	60	P20d	24689930	8 711500 246899	-	8727900370980	ECE	10

HB3 WhiteVision ultra



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9005WWUB1	12	60	P20d	00537328	8 719018 005373	-	8719018005380	ECE	5

HB3 X-tremeVision Pro150



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9005XVPB1	12	60	P20d	00557128	8 719018 005571	-	8719018005588	ECE	5

HB4 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9006PRB1	12	51	P22d	24726130	8 711500 247261	-	8711500247278	ECE	10
9006PRC1	12	51	P22d	24687530	8 711500 246875	-	8727900370973	ECE	10

HB4 WhiteVision ultra



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9006WWUB1	12	55	P22d	00539728	8 719018 005397	-	8719018005403	ECE	5

HB4 X-tremeVision Pro150



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9006XVPB1	12	51	P22d	00559528	8 719018 005595	-	8719018005601	ECE	5

HB5 9007



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9007C1	12	65/55	PX29t	24550230	8 711500 245502	-	8727900370966	-	10

HIR2 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9012LLC1	12	55	PX22d	35125530	8 727900 351255	-	8727900370935	ECE	10

HIR2 WhiteVision ultra



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9012WWUB1	12	55	PX22d	00541028	8 719018 005410	-	8719018005427	ECE	5

HIR2 X-tremeVision Pro150



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9012XVPB1	12	55	PX22d	00561828	8 719018 005618	-	8719018005625	ECE	5

H27W/1



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12059C1	12	27	PG13	52854030	8 711559 528540	-	8727900370799	ECE	10

H27W/2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12060C1	12	27	PGJ13	52857130	8 711559 528571	-	8727900370805	ECE	10

R2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12620B1	12	45/40	P45t-41	5543930	8 711500 055439	-	8711559525327	ECE	10
12620C1	12	45/40	P45t-41	40085730	8 711500 400857	-	8711500779359	ECE	10

R2 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12475B1	12	45/40	P45t-41	24716230	8 711500 247162	-	8711500247179	ECE	10
12475C1	12	45/40	P45t-41	40466430	8 711500 404664	-	8727900371130	ECE	10

Signaling and interior lighting

P21W VisionPlus



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12498VPB2	12	21	BA15s	36318030	8 727900 363180	-	8727900363173	ECE	10

P21W LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12498LLECOB2	12	21	BA15s	38210530	8 727900 382105	-	8727900382112	ECE	10
12498LLECOCP	12	21	BA15s	38198628	8 727900 381986	8727900381993	8727900391695	ECE	5x10

P21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12498B2	12	21	BA15s	05549130	8 711500 055491	-	8711559520131	ECE	10
12498CP	12	21	BA15s	49078073	8 711500 490780	8711500490797	8711500490803	ECE	20x10

P21/4W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12594B2	12	21/4	BAZ15d	40485530	8 711500 404855	-	8711500471017	ECE	10
12594CP	12	21/4	BAZ15d	48433828	8 711500 484338	8711500484345	8727900391565	ECE	5x10

P21/5W VisionPlus



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12499VPB2	12	21/5	BAY15d	36316630	8 727900 363166	-	8727900363159	ECE	10

P21/5W LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12499LLECOB2	12	21/5	BAY15d	38212930	8 727900 382129	-	8727900382136	ECE	10
12499LLECOCP	12	21/5	BAY15d	38201328	8 727900 382013	8727900382020	8727900391053	ECE	5x10

P21/5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12499B2	12	21/5	BAY15d	05545330	8 711500 055453	-	8711559520148	ECE	10
12499CP	12	21/5	BAY15d	48159773	8 711500 481597	8711500481603	8711500481610	ECE	20x10

PR21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12088CP	12	21	BAW15s	48531128	8 711500 485311	8711500485328	8727900391589	ECE	5x10

PR21/5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12495CP	12	21/5	BAW15d	48873228	8 711500 488732	8711500488749	8727900391572	ECE	5x10

PY21W SilverVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12496SVB2	12	21	BAU15s	31117730	8 711500 311177	-	8711500311191	ECE	10

PY21W LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12496LLECOCP	12	21	BAU15s	38218128	8 727900 382181	8727900382198	8727900391084	ECE	5x10

PY21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12496NAB2	12	21	BAU15s	52372930	8 711559 523729	-	8711559523743	ECE	10
12496NACP	12	21	BAU15s	52534173	8 711559 525341	8711559525358	8711559525365	ECE	20x10

Stop P22



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12401CP	12	15	BA15s	87821228	8 711500 878212	8711500878229	8711500790538	-	5x10

Stop P25



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12445CP	12	18	BA15s	48440628	8 711500 484406	8711500484413	8727900391602	-	5x10

R5W LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12821LLECOB2	12	5	BA15s	38208230	8 727900 382082	-	8727900382099	ECE	10
12821LLECOCP	12	5	BA15s	38195528	8 727900 381955	8727900381962	8727900390940	ECE	5x10

R5W BA15s



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12821B2	12	5	BA15s	5546030	8 711500 055460	-	8711500417701	ECE	10
12821CP	12	5	BA15s	48269373	8 711500 482693	8711500482709	8711500482716	ECE	20x10

R5W BA15d



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12822CP	12	5	BA15d	45407228	8 711500 454072	8711500454959	8711500790521	ECE	5x10

R10W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12814B2	12	10	BA15s	5547730	8 711500 055477	-	8711500417718	ECE	10
12814CP	12	10	BA15s	48341673	8 711500 483416	8711500483423	8711500483430	ECE	20x10

RY10W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12093NACP	12	10	BAU15s	48362128	8 711500 483621	8711500483638	8727900391619	ECE	5x10

BA7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12829CP	12	2	BA7s	52123728	8 711559 521237	8711500401236	8727900390933	-	5x10

T2W - T3W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12913CP	12	2	BA9s	21997828	8 711500 219978	8711500219985	8711500220820	-	5x10
12910CP	12	3	BA9s	21949728	8 711500 219497	8711500219503	8711500220837	-	5x10

T4W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12929B2	12	4	BA9s	5550730	8 711500 055507	-	8711559520094	ECE	10
12929CP	12	4	BA9s	21979473	8 711500 219794	8711500219800	8711500219817	ECE	20x10

Miniature halogen signaling USA

H5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12023CP	12	5	BA9s	51270928	8 711559 512709	8711559512464	8727900371222	-	5x10

H6W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12036B2	12	6	BAX9s	24720930	8 711500 247209	-	8711500247216	ECE	10
12036CP	12	6	BAX9s	87603428	8 711500 876034	8711500876041	8727900370676	ECE	5x10

H6W WhiteVision ultra



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12036WVUB2	12	6	BAX9s	00543430	8 719018 005434	-	8719018005441	ECE	10

H10W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12024CP	12	10	BA9s	52941728	8 711559 529417	8711559529424	8727900371192	-	5x10

H20W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12025CP	12	20	BA9s	87600328	8 711500 876003	8711500876010	8727900371154	-	5x10

H21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12356CP	12	21	BAY9s	87989928	8 711500 879899	8711500879905	8727900371116	ECE	5x10

HY21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12146CP	12	21	BAW9s	35244328	8 727900 352443	8727900352450	8727900370867	ECE	5x10

Wedge base

W1,2W - W2,3W - W2W - WBT5



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12521CP	12	1	W2x4,6d	48321828	8 711500 483218	8711500483225	8727900391671	-	5x10
12516B2	12	1.2	W2x4,6d	5554530	8 711500 055545	-	8711500417763	-	10
12516CP	12	1.2	W2x4,6d	48153573	8 711500 481535	8711500481542	8711500481559	-	20x10
12505CP	12	2	W2x4,6d	48327028	8 711500 483270	8711500483287	8727900391657	-	5x10
12061CP	12	2.3	W2x4,6d	48330028	8 711500 483300	8711500483317	8727900391640	ECE	5x10

W2,2W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12960CP	12	2.2	W2,1x9,5d	48150428	8 711500 481504	8711500481511	8727900391633	-	5x10

W3W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12256B2	12	3	W2,1x9,5d	52410830	8 711559 524108	-	8711559524122	ECE	10
12256CP	12	3	W2,1x9,5d	48144328	8 711500 481443	8711500481450	8727900391664	ECE	5x10

W5W LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12961LLECOB2	12	5	W2,1x9,5d	38204430	8 727900 382044	-	8727900382051	ECE	10
12961LLECOCP	12	5	W2,1x9,5d	38189428	8 727900 381894	8727900381900	8727900390872	ECE	5x10

W5W X-tremeVision Pro150



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12961XVPB2	12	5	W2,1x9,5d	00563230	8 719018 005632	-	8719018005649	ECE	10

W5W WhiteVision ultra



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12961WUJB2	12	5	W2,1x9,5d	35484330	8 727900 354843	-	8727900354874	ECE	10

W5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12961B2	12	5	W2,1x9,5d	40421330	8 711500 404213	-	8711559520070	ECE	10
12961CP	12	5	W2,1x9,5d	49090273	8 711500 490902	8711500490919	8711500490926	ECE	20x10

WY5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12396NAB2	12	5	W2,1x9,5d	40058130	8 711500 400581	-	8711500400598	ECE	10
12396NACP	12	5	W2,1x9,5d	53002428	8 711559 530024	8711559530031	8727900390889	ECE	5x10

WBT10 VisionPlus



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12040VPB2	12	6	W2,1x9,5d	52416030	8 711559 524160	-	8711559524184	-	10

W16W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12067B2	12	16	W2,1x9,5d	40587630	8 711500 405876	-	8711559521053	ECE	10
12067CP	12	16	W2,1x9,5d	48272328	8 711500 482723	8711500482730	8727900391626	ECE	5x10

W21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12065B2	12	21	W3x16d	70146330	8 727900 701463	-	8727900701470	ECE	10
12065CP	12	21	W3x16d	47135228	8 711500 471352	8711500471369	8727900391107	ECE	5x10

W21/5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12066B2	12	21/5	W3x16q	69739130	8 727900 697391	-	8727900697407	ECE	10
12066CP	12	21/5	W3x16q	47138328	8 711500 471383	8711500471390	8727900391091	ECE	5x10

WY21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12071B2	12	21	WX3x16d	69741430	8 727900 697414	-	8727900697421	ECE	10
12071CP	12	21	WX3x16d	52539628	8 711559 525396	8711559525402	8727900391688	ECE	5x10

Festoon

Festoon T6,2x27



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12818CP	12	3	SV6	48461128	8 711500 484611	8711500484628	8727900695632	-	5x10

Festoon T6,2x35



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12848CP	12	3	SV6	48467328	8 711500 484673	8711500484680	8727900391558	-	5x10

Festoon C5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12844B2	12	5	SV8,5	5551430	8 711500 055514	-	8711500417749	ECE	10
12844CP	12	5	SV8,5	48156673	8 711500 481566	8711500481573	8711500481580	ECE	20x10

Festoon T10,5x30 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12860LLECOCP	12	10	SV8,5	38192428	8 727900 381924	8727900381931	8727900391114	-	5x10

Festoon T10,5x38



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12854CP	12	10	SV8,5	48248828	8 711500 482488	8711500482495	8727900391510	-	5x10

Festoon T10,5x43



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12864CP	12	5	SV8,5	48205128	8 711500 482051	8711500482075	8727900391527	-	5x10
12866B2	12	10	SV8,5	5552130	8 711500 055521	-	8711500417756	-	10
12866CP	12	10	SV8,5	48242628	8 711500 482426	8711500482433	8727900391534	-	5x10

Festoon T15x43



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12850CP	12	15	SV8,5	48285328	8 711500 482853	8711500482860	8727900391541	-	5x10

Bax

Bax 8,3s/1,35 black



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12597B2	12	1.2	B8,3s/1,35	53018530	8 711559 530185	-	8711559530192	-	10
12597CP	12	1.2	B8,3s/1,35	48365228	8 711500 483652	8711500483669	8727900390957	-	5x10

Bax 8,3s/1,5 blue



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12602CP	12	2	B8,3s/1,5	48396628	8 711500 483966	8711500483973	8727900390995	-	5x10

Bax 8,5d/2 black



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12598B2	12	1.2	B8,5d/2	40588330	8 711500 405883	-	8711500405890	-	10
12598CP	12	1.2	B8,5d/2	48387428	8 711500 483874	8711500483881	8727900390964	-	5x10

Bax 8,5d/1,5 blue



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12603CP	12	1.2	B8,5d/1,5	48399728	8 711500 483997	8711500484000	8727900391015	-	5x10

Bax 8,5d/2 green



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12600CP	12	2	B8,5d/2	48393528	8 711500 483935	8711500483942	8727900390971	-	5x10

Bax 8,5d green



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12604CP	12	2	B8,5d	40508128	8 711500 405081	8711500404589	8727900391022	-	5x10

Bax 8,5d beige



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12637CP	12	1.5	B8,5d	51487128	8 711559 514871	8711500400178	8727900371048	-	5x10

Bax 10d black halogen



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12615CP	12	5	B10d	52807628	8 711559 528076	8711500243768	8727900370911	-	5x10

Bax 10d brown halogen



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12614CP	12	3	B10d	52805228	8 711559 528052	8711559512723	8727900370928	-	5x10

Bax 8,4d light blue



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12623CP	12	1.2	BX8,4d	51384328	8 711559 513843	8711500244154	8727900370904	-	5x10

Bax 8,4d beige



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12627CP	12	1.5	BX8,4d	51414728	8 711559 514147	8711500247414	8727900370959	-	5x10
12629CP	12	1.8	BX8,4d	51488828	8 711559 514888	8711559512488	8727900371031	-	5x10

Bax 8,4d black



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12625CP	12	1.2	BX8,4d	51409328	8 711559 514093	8711500244420	8727900371208	-	5x10

Bax 8,4d light green



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12626CP	12	2	BX8,4d	51412328	8 711559 514123	8711500246066	8727900370942	-	5x10

Bax 8,4d olive green



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12611CP	12	1.3	BX8,4d	77432328	8 711500 774323	8711500774330	8711500779397	-	5x10

Bax 8,4d orange



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12624CP	12	1.1	BX8,4d	51411628	8 711559 514116	8711500245137	8727900370898	-	5x10

Bax 8,5d white



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12638CP	12	1.12	BX8,5d	48846628	8 711500 488466	8711500488473	8727900391503	-	5x10

HiPerVision

P13W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12277C1	12	13	PG18,5d-1	69672130	8 727900 696721	-	8727900391008	ECE	10



PCY16W HiPerClick



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12271AC1	12	16	PU20d/2	38965430	8 727900 389654	-	8727900391152	ECE	10



PW16W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12177C1	12	16	WP3,3x14,5/8	39623230	8 727900 396232	-	8727900396249	ECE	10



PS19W LongLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12085LLC1	12	19	PG20/1	70046630	8 727900 700466	-	8727900390926	ECE	10



PS19W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12085C1	12	19	PG20/1	69653030	8 727900 696530	-	8727900390988	ECE	10



PSY19W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12275NAC1	12	19	PG20/2	52735230	8 711559 527352	-	8727900390858	ECE	10



HiPerVision LCP



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12197HTRC1	13.5	24	HPSL 2A	39621830	8 727900 396218	-	8727900396225	-	10



PS24W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12086FFC1	12	24	PG20/3	70044230	8 727900 700442	-	8727900390919	ECE	10



PSX24W WhiteVision ultra



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12276WWUB1	12	24	PG20/7	00545828	8 719018 005458	-	8719018005465	ECE	5



PSX24W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12276C1	12	24	PG20/7	69676930	8 727900 696769	-	8727900390902	ECE	10



PSY24W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12188NAC1	12	24	PG20/4	69668430	8 727900 696684	-	8727900390834	ECE	10

PSY24W SilverVision+



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12180SV+C1	12	24	PG20/4	70379530	8 727900 703795	-	8727900390841	ECE	10

PW24W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12182HTRC1	12	24	WP3,3x14,5/3	39196130	8 727900 391961	-	8727900397369	ECE	10

PWY24W SilverVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12174SVHTRC1	12	24	WP3,3x14,5/4	39200530	8 727900 392005	-	8727900397352	ECE	10

PWY24W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12174NAHTRC1	12	24	WP3,3x14,5/4	39202930	8 727900 392029	-	8727900397345	ECE	10

PY24W SilverVision+



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12274SV+C1	12	24	PGU20/4	69678330	8 727900 696783	-	8727900390780	ECE	10

PY24W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12190NAC1	12	24	PGU20/4	69690530	8 727900 696905	-	8727900390803	ECE	10

PSX26W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12278C1	12	26	PG18,5d/3	38874930	8 727900 388749	-	8727900390896	ECE	10

Halogen



Two-wheeler lighting





Which two-wheeler lamp do you need?

Enhanced brightness




Up to **200%** more brightness*


RacingVision GT200 moto



Beam performance*



Light color**




Lifetime**



Available in H4, H7

See and **be seen**


CityVision moto



Beam performance*



Light color**



Lifetime**



Available in H4, H7, HS1

Up to **30%** more vision*

Vision moto



Beam performance*



Light color**



Lifetime**



Available in H4, H7, HS1

Unique style



Sharp **white** look

WhiteVision ultra moto



Beam performance*



Light color**



Lifetime**



Available in H4, H7, HS1



Philips two-wheeler lighting is designed to resist extreme vibration – up to 10 G.

Images for illustration purposes only.

* Compared to the minimum legal requirement.

** Lifetime and color temperature differ per type, indication for H7 only.

*** 10 G applies to H4 and H7.

Philips.com/Motorcycle-lights

RacingVision GT200 moto

Incredible road-legal performance

- Up to 200% brighter light*
- Fully road-legal for an enjoyable drive
- The best-performing beam in our portfolio

If you're passionate about driving, let Philips RacingVision GT200 moto bulbs elevate your automotive experience. Up to 200% brighter light* means better vision and faster reactions for a more exciting drive.

*Compared to the minimum legal standard



Standard



RacingVision GT200 moto

Available in



H4



H7


CityVision moto

See and be seen

- Distinctive orange effect
- Maximum safety
- Specifically designed for city use
- Up to 40% more vision*

For maximum safety and visibility, Philips CityVision moto produces a distinctive, attention-grabbing **orange effect**. Motorcycle riders everywhere are looking for more safety, especially riders in heavy city traffic.

*Compared to the minimum legal standard



Standard



CityVision moto

Available in



H4



H7



HS1

WhiteVision ultra moto

The latest stylish white lights


- **White stylish look with up to 4200 Kelvin**
- **Up to 60% more vision***
- **Road-legal performance**

Philips WhiteVision ultra moto bulbs, featuring the latest coating formula, deliver up to 4200 Kelvin. These are the whitest road-legal halogen lights in our portfolio and the perfect choice if you're looking for a cool, stylish look.

*Compared to the minimum legal standard



Available in



Standard

WhiteVision ultra moto



H4

H7

HS1

Vision moto

Up to 30% more vision*

- **Better performance***
- **High-quality and ultra-resistant motorcycle lamp**

Producing **up to 30% more vision*** than a standard lamp, Philips Vision moto allows riders to see farther with improved light-beam performance at a very **competitive price**.

*Compared to the minimum legal standard



Available in



Standard

Vision moto



H4

H7

HS1

Which lamp for which function?



12258 H1 12336 H3 12342 H4 12972 H7 12361 H9 12362 H11 12636 HS1 9005 HB3 9006 HB4 12620 R2 12728 S2 12008 S3



Low beam – high beam



12961 W5W 12067 W16W 12065 W21W 12071 WY21W 12396 WY5W 12356 H21W



12821 R5W 12814 R10W 12093 RY10W 12498 P21W 12496 PY21W 12499 P21/5W



Front indicators



12256 W3W 12961 W5W 12066 W21/5W 12929 T4W 12821 R5W 12814 R10W 12498 P21W 12499 P21/5W



Rear position light



12256 W3W 12961 W5W 12929 T4W 12821 R5W 12814 R10W 12036 H6W 12844 C5W



Licence plate light



RacingVision GT200 moto

CityVision moto



WhiteVision ultra moto

Vision moto

Philips.com/Motorcycle-lights



12929 T4W 12821 R5W 12814 R10W 12036 H6W



12256 W3W 12961 W5W 12067 W16W 12913 T2W 12910 T3W



Front position light



12067 W16W 12066 W21/5W 12498 P21W 12088 PR21W 12499 P21/5W 12495 PR21/5W



Stop light



12356 W5W 12961 W16W 12067 W21W 12065 WY21W 12071 H21W



12821 R5W 12814 R10W 12093 RY10W 12498 P21W 12496 PY21W



Rear indicators

Two-wheeler lighting

Halogen

H4 Vision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342PRBW	12	60/55	P43t-38	49024730	8 711500 490247	-	8711500490254	ECE	10

H4 CityVision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342CTVBW	12	60/55	P43t-38	39896030	8 727900 398960	-	8727900398977	ECE	10

H4 RacingVision GT200 moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342RGTBW	12	60/55	P43t-38	02381030	8 719018 023810	-	8719018023827	ECE	10

H4 WhiteVision ultra moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342WUUBW	12	60/55	P43t-38	02385830	8 719018 023858	-	8719018023865	ECE	10

H7 Vision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972PRBW	12	55	PX26d	49026130	8 711500 490261	-	8711500490278	ECE	10

H7 CityVision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972CTVBW	12	55	PX26d	39898430	8 727900 398984	-	8727900398991	ECE	10

H7 RacingVision GT200 moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972RGTBW	12	55	PX26d	02383430	8 719018 023834	-	8719018023841	ECE	10

H7 WhiteVision ultra moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972WUUBW	12	55	PX26d	02387230	8 719018 023872	-	8719018023889	ECE	10

HS1 Vision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12636BW	12	35/35	PX43t	53035330	8 727900 530353	-	8727900530360	ECE	10
12636C1	12	35/35	PX43t	51250130	8 711559 512501	-	8727900370881	ECE	10

HS1 CityVision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12636CTVBW	12	35/35	PX43t	39894630	8 727900 398946	-	8727900398953	ECE	10

HS1 WhiteVision ultra moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12636WUJBW	12	35/35	PX43t	02401530	8 719018 024015	-	8719018024022	ECE	10

S2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12728BW	12	35/35	BA20d	77385230	8 711500 773852	-	8711500773869	ECE	10
12728C1	12	35/35	BA20d	77359330	8 711500 773593	-	8711500779342	ECE	10

S3



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12008BW	12	15	P26s	77381430	8 711500 773814	-	8711500773845	ECE	10
12008C1	12	15	P26s	77394430	8 711500 773944	-	8711500779335	ECE	10

Signaling lamps

W3W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12256B2	12	3	W2,1x9,5d	52410830	8 711559 524108	-	8711559524122	ECE	10
12256CP	12	3	W2,1x9,5d	48144328	8 711500 481443	8711500481450	8727900391664	ECE	5x10

P21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12498B2	12	21	BA15s	05549130	8 711500 055491	-	8711559520131	ECE	10
12498CP	12	21	BA15s	49078073	8 711500 490780	8711500490797	8711500490803	ECE	20x10

P21/5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12499B2	12	21/5	BAY15d	05545330	8 711500 055453	-	8711559520148	ECE	10

Halogen



24V Bus and truck lighting



Which **24 V lamp** do you need?



Safety and **durability**



Built to **last**

MasterDuty




Best-in-class lifetime

MasterLife



Beam performance*




Lifetime**

Up to **550 h**




Available in
H1, H3, H4, H7, H11

Beam performance*



Lifetime**

Up to **1200 h**



Available in
H1, H3, H4, H7, H11

Safety and **style**




Maximum xenon effect

MasterDuty BlueVision



Heavy duty vibration resistant

Light color



Lifetime**

Up to **500 h**



Available in
H3, H4, H7

Images for illustration purposes only


* Compared to the minimum legal standard, applies to H1, H4, H7 and H11

** Lifetime differs per type, indication for H7 only

Safety and durability

Philips 24V headlighting advantage

Combining **vibration resistance** with **high quality**, Philips truck headlamps last longer than standard lamps.



MasterDuty

Built to last

- Lasts up to 550 hours*
- Maximum vibration resistance
- Up to 130% more vision**
- Reinforced mount and base guards against shocks
- Extra robust double-coil filament

The Philips MasterDuty headlamps are designed for **maximum vibration resistance** and excellent **lifetime**. MasterDuty is the **right choice** for drivers seeking **toughness** that **lasts**.

*Lifetime differs per type, indication for H7 only

**Compared to the minimum legal standard, applies to H1, H4, H7 and H11.



Available in B1 and C1 packaging



Available in



MasterLife

Best-in-class lifetime

- Lasts up to 1200 hours*
- Up to 100% more vision**
- Maximum vibration resistance*
- Extra-robust double-coil filament

Philips MasterLife lasts up to **1200 hours*** while withstanding extreme **stress** and **vibration**. With a **minimum failure rate** our lamps keep your fleet productive and on the move by minimizing time-consuming interruptions.

MasterLife is the smartest choice for large fleet owners!

*Lifetime differs per type, indication for H7 only.

**Compared to the minimum legal standard, applies to H1, H4, H7 and H11.



Available in C1 packaging



Available in



H1



H3



H4



H7



H11

MasterDuty BlueVision

Maximum xenon effect

- Maximum vibration resistance*
- High-performance quartz glass with xenon-effect coating
- Distinctive blue cap, looks sharp even when turned off

For drivers seeking **ultimate style** and **performance**, Philips MasterDuty BlueVision produces a **blue xenon effect**. It combines the **durability** and **vibration resistance** of Philips MasterDuty with an additional blue xenon effect for maximum style.

*Compared to average H4 or H7 24V lamps on the market



Standard



MasterDuty BlueVision



Available in S2 and B1 packaging



Available in



H3



H4



H7

Which lamp for which function?



philips.com/trucklight

Low beam – high beam
 13258 H1 13336 H3 13342 H4 13972 H7 24362 H11 13620 R2 D1S/R D2S D2R

Front fog lights
 13258 H1 13311 H2 13336 H3 13972 H7 24362 H11

Interior lights
 13844 C5W 13821 R5W 13929 T4W 13961 W5W

Dashboard lights
 13256 W3W 13961 W5W 13516 WBT5 13974 Bax

Front indicators
 24356 H21W 13498 P21W 13496 PY21W

Front position lights
 13821 R5W 13929 T4W 13256 W3W 13961 W5W

Side indicators
 24356 H21W 13821 R5W 13814 R10W 13961 W5W

Rear position lights
 13499 P21/5W 13821 R5W 13814 R10W

Running lights
 13844 C5W 13821 R5W 13814 R10W 13961 W5W
 24356 H21W 13498 P21W 13499 P21/5W 13401 P22 13445 P25
 24356 H21W 13498 P21W

License plate lights
 13844 C5W 13821 R5W 13814 R10W 13961 W5W

Stop lights
 24356 H21W 13498 P21W 13499 P21/5W 13401 P22 13445 P25

Reversing light
 24356 H21W 13498 P21W

Rear fog lights
 24356 H21W 13498 P21W

24V headlighting

H1 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13258MDB1	24	70	P14,5s	82585830	8 711500 825858	-	8711500825865	ECE	10
13258MDC1	24	70	P14,5s	82577360	8 711500 825773	8711500828507	8711500825780	ECE	100

H1 MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13258MLC1	24	70	P14,5s	82569830	8 711500 825698	-	8727900370812	ECE	10

H2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13311C1	24	70	X511	47751430	8 711500 477514	-	8727900371079	ECE	10

H3 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13336MDB1	24	70	PK22s	77459030	8 711500 774590	-	8711500774613	ECE	10
13336MDC1	24	70	PK22s	77460660	8 711500 774606	8711500775313	8711500774637	ECE	100

H3 MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13336MLC1	24	70	PK22s	77462030	8 711500 774620	-	8711500779403	ECE	10

H3 MasterDuty BlueVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13336MDBVS2	24	70	PK22s	77486628	8 711500 774866	-	8711500774897	ECE	5
13336MDBVB1	24	70	PK22s	77488030	8 711500 774880	-	8711500774910	ECE	10

H4 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13342MDB1	24	75/70	P43t-38	82587230	8 711500 825872	-	8711500825889	ECE	10
13342MDC1	24	75/70	P43t-38	82579760	8 711500 825797	8711500828002	8711500825803	ECE	100

H4 MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13342MLC1	24	75/70	P43t-38	82571130	8 711500 825711	-	8727900371086	ECE	10

H4 MasterDuty BlueVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13342MDBVS2	24	75/70	P43t-38	53275328	8 727900 532753	-	8727900532760	ECE	5
13342MDBVB1	24	75/70	P43t-38	53281430	8 727900 532814	-	8727900532821	ECE	10

H7 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13972MDB1	24	70	PX26d	82589630	8 711500 825896	-	8711500825902	ECE	10
13972MDC1	24	70	PX26d	82581060	8 711500 825810	8711500828514	8711500825827	ECE	100

H7 MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13972MLC1	24	70	PX26d	82573530	8 711500 825735	-	8727900371147	ECE	10

H7 MasterDuty BlueVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13972MDBVS2	24	70	PX26d	53277728	8 727900 532777	-	8727900532784	ECE	5
13972MDBVB1	24	70	PX26d	53279130	8 727900 532791	-	8727900532807	ECE	10

H11 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24362MDC1	24	70	PGJ19-2	82583430	8 711500 825834	-	8727900371055	ECE	10

H11 MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24362MLC1	24	70	PGJ19-2	82575930	8 711500 825759	-	8727900371062	ECE	10

R2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13620C1	24	55/50	P45t-41	40087130	8 711500 400871	-	8711500779458	ECE	10

24V signaling and interior lighting

P21W MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13498MDCP	24	21	BA15s	69949473	8 727900 699494	8727900699500	8727900699517	ECE	20x10

P21W MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13498MLCP	24	21	BA15s	69961628	8 727900 699616	8727900699623	8727900391145	ECE	5x10

P21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13498B2	24	21	BA15s	40455830	8 711500 404558	-	8711500405449	ECE	10
13498CP	24	21	BA15s	48415473	8 711500 484154	8711500484161	8711500484178	ECE	20x10

P21/5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13499B2	24	21/5	BAY15d	40456530	8 711500 404565	-	8711500405371	ECE	10
13499CP	24	21/5	BAY15d	48424673	8 711500 484246	8711500484253	8711500484260	ECE	20x10

PY21W MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13496MLCP	24	21	BAU15s	69964728	8 727900 699647	8727900699654	8727900391138	ECE	5x10

Stop P22



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13401CP	24	15	BA15s	87826728	8 711500 878267	8711500878274	8711500790507	-	5x10
13402CP	24	15	BA15d	87836628	8 711500 878366	8711500878373	8711500790514	-	5x10

Stop P25



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13445CP	24	18	BA15s	48443728	8 711500 484437	8711500484444	8727900390810	-	5x10

R5W MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13821MDCP	24	5	BA15s	69955528	8 727900 699555	8727900699562	8727900390766	ECE	5x10

R5W MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13821MLCP	24	5	BA15s	69970828	8 727900 699708	8727900699715	8727900390773	ECE	5x10

R5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13821B2	24	5	BA15s	40453430	8 711500 404534	-	8711500405425	ECE	10
13821CP	24	5	BA15s	48338673	8 711500 483386	8711500483393	8711500483409	ECE	20x10
13822CP	24	5	BA15d	40904128	8 711500 409041	8711500878021	8711500790491	ECE	5x10

R10W MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13814MDCP	24	10	BA15s	69952428	8 727900 699524	8727900699531	8727900391121	ECE	5x10

R10W MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13814MLCP	24	10	BA15s	69967828	8 727900 699678	8727900699685	8727900390742	ECE	5x10

R10W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13814B2	24	10	BA15s	40452730	8 711500 404527	-	8711559526409	ECE	10
13814CP	24	10	BA15s	48344773	8 711500 483447	8711500483454	8711500483461	ECE	20x10

BA7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13829CP	24	3	BA7s	52133628	8 711559 521336	8711500401274	8727900390759	-	5x10

T4W MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13929MDCP	24	4	BA9s	69958628	8 727900 699586	8727900699593	8727900391039	ECE	5x10

T4W MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13929MLCP	24	4	BA9s	69976028	8 727900 699760	8727900699777	8727900391046	ECE	5x10

T2W - T3W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13913CP	24	2	BA9s	22003528	8 711500 220035	8711500220042	8711500220844	-	5x10
13910CP	24	3	BA9s	21955828	8 711500 219558	8711500219565	8711500220851	-	5x10

T4W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13929B2	24	4	BA9s	40454130	8 711500 404541	-	8711500405432	ECE	10
13929CP	24	4	BA9s	21985573	8 711500 219855	8711500219862	8711500219879	ECE	20x10

Miniature halogen signaling USA

H21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24356CP	24	21	BAY9s	87615728	8 711500 876157	8711500876164	8727900371161	ECE	5x10

Wedge base

W2,5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13960CP	24	2.5	W2,1x9,5d	48147428	8 711500 481474	8711500481481	8727900391275	-	5x10

W3W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13256CP	24	3	W2,1x9,5d	48141228	8 711500 481412	8711500481429	8727900391169	ECE	5x10

W5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13961B2	24	5	W2,1x9,5d	52420730	8 711559 524207	-	8711559524214	ECE	10
13961CP	24	5	W2,1x9,5d	48138273	8 711500 481382	8711500481399	8711559530376	ECE	20x10

WBT5



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13521CP	24	1	W2x4,6d	48324928	8 711500 483249	8711500483256	8727900391176	-	5x10
13516CP	24	1.2	W2x4,6d	48306573	8 711500 483065	8711500483072	8711500483089	-	20x10
13974CP	24	2	W2x4,6d	48318828	8 711500 483188	8711500483195	8727900391183	-	5x10

Festoon

Festoon T6,2x27



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13818CP	24	3	SV6	48464228	8 711500 484642	8711500484659	8727900391251	-	5x10

Festoon T6,2x35



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13848CP	24	3	SV6	48470328	8 711500 484703	8711500484710	8727900391268	-	5x10

Festoon T10,5x38 10W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13854CP	24	10	SV8,5	48251828	8 711500 482518	8711500482525	8727900391206	-	5x10

Festoon C5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13844B2	24	5	SV8,5	40463330	8 711500 404633	-	8711500405388	ECE	10
13844CP	24	5	SV8,5	48197973	8 711500 481979	8711500481986	8711500481993	ECE	20x10

Festoon T10,5x43 5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13864CP	24	5	SV8,5	48233428	8 711500 482334	8711500482341	8727900391213	-	5x10

Festoon T10,5x43 10W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13866CP	24	10	SV8,5	48245728	8 711500 482457	8711500482464	8727900391220	-	5x10

Festoon T15x43 15W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13850CP	24	15	SV8,5	48288428	8 711500 482884	8711500482891	8727900391244	-	5x10

Festoon T15x43 18W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13807CP	24	18	SV8,5	48294528	8 711500 482945	8711500482952	8727900391237	-	5x10

Bax

Bax 8,3s/1,35 grey



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13597CP	24	1.2	B8,3s/1,35	48384328	8 711500 483843	8711500483850	8727900390797	-	5x10

Bax 8,5d/2 grey



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13598CP	24	1.2	B8,5d/2	48390428	8 711500 483904	8711500483911	8727900390827	-	5x10

Bax 8,5d brown



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24032CP	24	1.2	B8,5d	48852728	8 711500 488527	8711500488534	8727900391077	-	5x10

Bax 8,5d/2 yellow



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24029CP	24	1.2	B8,5d/2	48402428	8 711500 484024	8711500484031	8727900391190	-	5x10

Kits





Spare and headlight restoration **kits** for cars and trucks

For increased **safety**, it is **recommended** by most European countries that all vehicles be equipped with a **homologated spare kit**. It will not only keep drivers in **compliance** with the law, but will also keep them **safer** as they will always be prepared to **replace** a burned-out lamp.

Our **Headlight restoration kit** renovates car, truck and two-wheeler lenses to like-new condition. It's our **cost-effective alternative** to complete headlight replacement.



12V spare kits

Easy Kit H1



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55472EKKM	12	-	-	69551928	8 727900 695519	-	8727900695533	ECE	5

Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A
Quantity	1	-	-	-	1	1	1	1	1

Easy Kit H4



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55473EKKM	12	-	-	69555728	8 727900 695557	-	8727900695571	ECE	5

Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A
Quantity	-	1	-	-	1	1	1	1	1

Easy Kit H7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55474EKKM	12	-	-	69558828	8 727900 695588	-	8727900695601	ECE	5

Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A
Quantity	-	-	1	-	1	1	1	1	1

Easy Kit H1/H7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55475EKKM	12	-	-	69562528	8 727900 695625	-	8727900695656	ECE	5

Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A
Quantity	1	-	1	-	1	1	1	1	1



12V spare kits

Essential Box H1



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55717EBKM	12	-	-	70032928	8 727900 700329	-	8727900700336	ECE	5

Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A	Fuse 15A	Fuse 20A
Quantity	1	-	-	-	1	1	1	1	1	1	1

Essential Box H4



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55718EBKM	12	-	-	70034328	8 727900 700343	-	8727900700350	ECE	5

Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A	Fuse 15A	Fuse 20A
Quantity	-	1	-	-	1	1	1	1	1	1	1

Essential Box H7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55719EBKM	12	-	-	70036728	8 727900 700367	-	8727900700374	ECE	5

Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A	Fuse 15A	Fuse 20A
Quantity	-	-	1	-	1	1	1	1	1	1	1

Essential Box H1/H7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55720EBKM	12	-	-	70038128	8 727900 700381	-	8727900700398	ECE	5

Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A	Fuse 15A	Fuse 20A
Quantity	1	-	1	-	1	1	1	1	1	1	1

24V spare kits

MiniKit H4 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55554SKMDKM	24	-	-	69586130	8 727900 695861	-	8727900695885	ECE	10

Content

Lamp type	H4	H7	P21W	R5W	R10W	C5W	T4W	Fuse15A	Fuse 20A	Fuse 30A
Quantity	1	-	1	1	1	1	1	1	1	1

MiniKit H7 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55555SKMDKM	24	-	-	69590830	8 727900 695908	-	8727900695939	ECE	10

Content

Lamp type	H4	H7	P21W	R5W	R10W	C5W	T4W	Fuse15A	Fuse 20A	Fuse 30A
Quantity	-	1	1	1	1	1	1	1	1	1

MaxiKit H4 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55559LKMDKM	24	-	-	69684494	8 727900 696844	-	8727900696851	ECE	4

Content

Lamp type	H4	P21W	P21/5W	PY21W	R5W	R10W	C5W	W5W	T4W	Fuse 10A	Fuse 15A	Fuse 20A	Fuse 30A
Quantity	2	2	2	1	3	2	2	1	1	2	2	2	2

MaxiKit H7 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55560LKMDKM	24	-	-	69686894	8 727900 696868	-	8727900696875	ECE	4

Content

Lamp type	H7	P21W	P21/5W	PY21W	R5W	R10W	C5W	W5W	T4W	Fuse 10A	Fuse 15A	Fuse 20A	Fuse 30A
Quantity	2	2	2	1	3	2	2	1	1	2	2	2	2

MaxiKit H1/H7 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55561LKMDKM	24	-	-	69688294	8 727900 696882	-	8727900696899	ECE	4

Content

Lamp type	H1	H7	P21W	P21/5W	PY21W	R5W	R10W	C5W	W5W	T4W	Fuse 10A	Fuse 15A	Fuse 20A	Fuse 30A
Quantity	1	1	2	2	1	3	2	2	1	1	2	2	2	2



Headlight restoration kit

Restores headlight lenses to like-new condition!

- **Less glare and up to 100% brighter lenses**
- **Provides safer night-time driving**
- **Removes haze and yellowing from harmful UV-rays and dirt**
- **Professional results without power tools in 30 minutes**
- **High-quality and economical**
- **2-year UV-protection guaranteed**

Removes the fading and yellowing of headlight lenses and restores them to their original state of **transparency** for **greater safety**. Headlight lenses fade and oxidize from constant exposure to the elements and become scratched due to impacts.



Before

After



Ordering number	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
HRK00XM	39976931	8 727900 399769	-	8727900399776	-	6

Xenon



Car and truck

lighting



Which **xenon lamp** do you need?




Enhanced **brightness**




Up to **150%** more vision*

Xenon X-tremeVision gen2



Beam performance*





Available in
D1S, D2S, D2R, D3S, D4S, D5S

Ideal for **replacement**

Xenon Vision



Beam performance



Available in
D1S, D1R, D2S, D2R, D3S, D3R, D4S, D4R, D5S, D8S

Unique **style**




Homogeneous white
LED effect

Xenon WhiteVision gen2



Beam performance*




Available in
D1S, D2S, D2R, D3S

Extended **lifetime**




Peace of mind
4 + 3 years warranty

Xenon LongerLife**



4 years warranty
+3

Beam performance



Available in
D1S, D2S, D2R

Images for illustration purposes only.

* Compared to the minimum legal standard (except for D2R that provides up to 20% more vision)

** Not available in all countries, please contact your sales representative

philips.com/automotive



Xenon X-tremeVision gen2

Our brightest xenon lamp

- Optimal light performance
- Up to 150% more vision*
- Maximum safety and visibility
- Designed for demanding drivers

Philips Xenon X-tremeVision gen2 is the latest development in **Xenon technology**. It offers the **most powerful** beam with light emission pushed to the limit. This means outstanding light performance with a unique light setting for **optimal driving comfort**.

www.philips.com/xenongen2

*Compared to the minimum legal standard (except for D2R that provides up to 20% more vision, and D5S which supports up to +120% more vision).



Standard



Xenon X-tremeVision gen2

Available in C1 and S1 packaging



Available in



D1S

D2S

D2R

D3S

D4S

D5S

Images for illustration purposes only **103**



Enjoy your
passion

Xenon WhiteVision gen2

Ultimate white LED effect

- Intense homogeneous bright white light
- Perfect match with LED lighting on your car
- Up to 5000 K white light on the road
- Up to 120% more vision*
- 100% road legal

Philips Xenon WhiteVision gen2 lamps create an **intense white look** of your car and produce brighter, homogeneous white light on the road.

www.philips.com/xenongen2

*Compared to the minimum legal standard (except for D2R that provides up to 20% more vision).



Standard

Xenon WhiteVision gen2

Available in C1 and S1 packaging



Available in



D1S

D2S

D2R

D3S



4 years warranty
+3

Xenon LongerLife

Peace of mind with the longest guarantee

Equip your car with Philips Xenon LongerLife lamps and you can drive up to 7 years without the worry of lamp failures. Philips Xenon LongerLife lamps automatically come with a **4-year warranty**. Register your purchase online and you can extend this warranty by an **extra 3 years**.



Available in C1 and S1 packaging



Available in



D1S

D2S

D2R

3 years extra warranty for free in 3 simple steps

Register online at Philips.com/auto-warranty, within 30 days of purchase



Xenon Vision

Ideal for replacement

- **Single-lamp replacement technology:** new lamp matches color temperature of the unchanged one
- Ideal economical solution for a **single-lamp replacement**
- **Homologated 4300K**

Philips Xenon Vision allows drivers to replace a single burned-out lamp while **matching** the **color** of the unchanged one.



Standard



Xenon Vision

Available in C1 and S1 packaging



Available in



D1S



D1R



D2S



D2R



D3S



D3R



D4S



D4R



D5S



D8S



Car and truck lighting

Xenon

D1S Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85415VIS1	85	35	PK32d-2	36489733	8 727900 364897	-	8727900364903	ECE	2
85415VIC1	85	35	PK32d-2	36473633	8 727900 364736	-	8727900364743	ECE	2

D1S X-tremeVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85415XV2S1	85	35	PK32d-2	37697533	8 727900 376975	-	8727900376982	ECE	2
85415XV2C1	85	35	PK32d-2	37701933	8 727900 377019	-	8727900377026	ECE	2

D1S LongerLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85415SYS1	85	35	PK32d-2	37246533	8 727900 372465	-	8727900372472	ECE	2
Ordering codes for Germany, Austria, Switzerland, Netherlands, Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom									
85415SYC1	85	35	PK32d-2	37516933	8 727900 375169	-	8727900375176	ECE	2
Ordering codes for Germany, Austria, Switzerland, Netherlands									
85415SYC1	85	35	PK32d-2	37250233	8 727900 372502	-	8727900372519	ECE	2
Ordering codes for Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom									
85415SYC1	85	35	PK32d-2	37522033	8 727900 375220	-	8727900375237	ECE	2
Ordering codes for Central Europe (Poland, Romania, Czech Republic) and other East European countries									

D1S WhiteVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85415WHV2S1	85	35	PK32d-2	36072133	8 727900 360721	-	8727900377248	ECE	2
85415WHV2C1	85	35	PK32d-2	37725533	8 727900 377255	-	8727900377262	ECE	2

D1R Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85409VIC1	85	35	PK32d-3	36475033	8 727900 364750	-	8727900364767	ECE	2

D2S Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85122VIS1	85	35	P32d-2	36491033	8 727900 364910	-	8727900364927	ECE	2
85122VIC1	85	35	P32d-2	36477433	8 727900 364774	-	8727900364781	ECE	2

D2S X-tremeVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85122XV2S1	85	35	P32d-2	37703333	8 727900 377033	-	8727900377040	ECE	2
85122XV2C1	85	35	P32d-2	37707133	8 727900 377071	-	8727900377088	ECE	2

Philips Xenon LongerLife lighting is not available in all countries. For more information, please contact your Philips representative.

D2S LongerLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85122SYS1	85	35	P32d-2	37254033	8 727900 372540	-	8727900372557	ECE	2
Ordering codes for Germany, Austria, Switzerland, Netherlands, Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom									
85122SYC1	85	35	P32d-2	37518333	8 727900 375183	-	8727900375190	ECE	2
Ordering codes for Germany, Austria, Switzerland, Netherlands									
85122SYC1	85	35	P32d-2	37244133	8 727900 372441	-	8727900372458	ECE	2
Ordering codes for Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom									
85122SYC1	85	35	P32d-2	37524433	8 727900 375244	-	8727900375251	ECE	2
Ordering codes for Central Europe (Poland, Romania, Czech Republic) and other East European countries									

D2S WhiteVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85122WHV2S1	85	35	P32d-2	37727933	8 727900 377279	-	8727900377286	ECE	2
85122WHV2C1	85	35	P32d-2	37729333	8 727900 377293	-	8727900377309	ECE	2

D2R Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85126VIS1	85	35	P32d-3	36493433	8 727900 364934	-	8727900364941	ECE	2
85126VIC1	85	35	P32d-3	36479833	8 727900 364798	-	8727900364804	ECE	2

D2R X-tremeVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85126XV2S1	85	35	P32d-3	37709533	8 727900 377095	-	8727900377101	ECE	2
85126XV2C1	85	35	P32d-3	37711833	8 727900 377118	-	8727900377125	ECE	2

D2R LongerLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85126SYS1	85	35	P32d-3	37248933	8 727900 372489	-	8727900372496	ECE	2
Ordering codes for Germany, Austria, Switzerland, Netherlands, Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom									
85126SYC1	85	35	P32d-3	37520633	8 727900 375206	-	8727900375213	ECE	2
Ordering codes for Germany, Austria, Switzerland, Netherlands									
85126SYC1	85	35	P32d-3	37252633	8 727900 372526	-	8727900372533	ECE	2
Ordering codes for Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom									
85126SYC1	85	35	P32d-3	37526833	8 727900 375268	-	8727900375275	ECE	2
Ordering codes for Central Europe (Poland, Romania, Czech Republic) and other East European countries									

D2R WhiteVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85126WHV2S1	85	35	P32d-3	37731633	8 727900 377316	-	8727900377323	ECE	2
85126WHV2C1	85	35	P32d-3	37733033	8 727900 377330	-	8727900377347	ECE	2

Philips Xenon LongerLife lighting is not available in all countries. For more information, please contact your Philips representative.

D3S Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42403VIS1	42	35	PK32d-5	36495833	8 727900 364958	-	8727900364965	ECE	2
42403VIC1	42	35	PK32d-5	36481133	8 727900 364811	-	8727900364828	ECE	2

D3S X-tremeVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42403XV2S1	42	35	PK32d-5	37713233	8 727900 377132	-	8727900377149	ECE	2
42403XV2C1	42	35	PK32d-5	37717033	8 727900 377170	-	8727900377187	ECE	2

D3S WhiteVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42403WHV2S1	42	35	PK32d-5	37735433	8 727900 377354	-	8727900377361	ECE	2
42403WHV2C1	42	35	PK32d-5	37737833	8 727900 377378	-	8727900377385	ECE	2

D3R Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42306VIC1	42	35	PK32d-6	36483533	8 727900 364835	-	8727900364842	ECE	2

D4S Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42402VIC1	42	35	P32d-5	36485933	8 727900 364859	-	8727900364866	ECE	2

D4S X-tremeVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42402XV2S1	42	35	P32d-5	37719433	8 727900 377194	-	8727900377200	ECE	2
42402XV2C1	42	35	P32d-5	37721733	8 727900 377217	-	8727900377224	ECE	2

D4R Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42406VIC1	42	35	P32d-6	36487333	8 727900 364873	-	8727900364880	ECE	2

D5S Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12410C1	12	25	PK32d-7	36981633	8 727900 369816	-	8727900369823	ECE	2

D5S X-tremeVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12410XV+C1	12/24	25	PK32d-7	35392133	8 727900 353921	-	8719018005090	ECE	2

D8S Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12411C1	42	25	PK32d-1	00467333	8 719018 004673	-	8719018004680	ECE	2



Glossary

■ AirCool technology

Smart cooling system that diverts heat away from the light's critical components (active cooling with a fan).

■ AirFlux technology

Optimal thermal management resulting in longer lifetime (passive cooling using heat sink).

■ Asymmetrical beam pattern

An offset beam pattern for low-beam applications. Provides a longer beam in the lane of traffic, which avoids blinding oncoming traffic.

■ Automotive Grade Quality

The Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards.

■ Ballast

The electronic driver that controls a xenon HID bulb.

■ Base

Bottom part of the bulb which ensures a proper mechanical and electrical connection with the lamp unit of the car. Its precision is important for a correct beam pattern.

■ Board voltage

Electrical voltage in the board net of the vehicle. In cars, the operational voltage at the bulb connector typically varies between 13 and 14 volts (V). The official test voltage for halogen headlight bulbs is 13.2V according to ECE R37. For trucks with a 24V board net the test voltage is 28V. The board voltage has a significant impact on filament bulb lifetime. In general, a 5% voltage increase reduces the lifetime by 50%.

■ Burner

Burner is the glass part of a halogen or xenon HID bulb in which the light emission is generated. It consists of hard or quartz glass and contains the filament and the two electrodes.

■ Candela (cd)

Unit of luminous intensity that measures the amount of luminous power emitted by a light source in a particular direction.

■ CeraLight

Cooling system using ceramic material for enhanced heat and vibration resistance.

■ Color temperature

Thermal measure for light color. Derived from the color emitted by a "black body" which is heated up to a certain temperature (see also Kelvin).

■ Cut-off zone

The line between the bright and dark zones of low beam light. Above the cut-off zone the amount of light is limited in order to avoid blinding oncoming traffic.

■ D(...)

Nomenclature for xenon HID bulbs where **D** stands for "discharge." Available technical types: **D1S**, **D1R**, **D2S**, **D2R**, **D3S**, **D3R**, **D4S**, **D4R** and **D5S**.

D1 and **D2** First bulbs introduced in 1991

D3 and **D4** Mercury-free bulbs that replace D1 and D2

For D1 and D3, the electronic high-voltage starter is already integrated in the bulb base. The **S** type is used with projector (lens) systems. Version **R** is used in open reflectors and features an additional coating on the outer tube (pinstripe) which blocks out some areas to avoid glare.

The **D5S** is a 25-watt bulb with integrated starter and integrated ballast.

■ Discharge bulb

The correct, technical term of the so-called xenon bulb is **high-intensity discharge** bulb. The light is emitted by an electric arc which is produced between two electrodes. **See also** HID and xenon light.

■ DOT

The United States Department of Transportation which oversees federal highway, air, railroad, maritime and other transportation administration functions. It fulfills a role similar to the Economic Commission for Europe (ECE).

■ DRL

Daytime Running Lights.

■ ECE

Economic Commission for Europe. One of five regional commissions of the United Nations (UN) based in Geneva that contributes to enhancing the effectiveness of the UN through the regional implementation of outcomes of global UN Conferences and Summits. The ECE is responsible for harmonizing technical specifications for vehicles whose regulations are also mandatory in many countries outside Europe.

■ ECE R

This stands for the ECE Regulation.

Examples for vehicle lighting:

R37 Filament lamps

R99 Gas-discharge light sources

R48 Installation of lighting and light-signaling devices

■ Electric arc

The connecting luminous discharge between the two electrodes of a xenon HID bulb. This is similar in principle to a bolt of lightning. The electric arc is created by the high-voltage starter and stabilized and controlled by the ballast.

■ Electrodes

Electrical conductors which are positioned opposite each other in the vessel of a xenon gas-discharge bulb. The electric arc, which emits light, is produced between the electrodes.

■ EMI conform

Automotive standards of electromagnetic interference.

■ E-mark

The ECE mark of approval. The digit following the "E" indicates in which country the approval has been granted. For example: E1 indicates Germany and E2 indicates France. An approval granted by one ECE member is valid for all member states and is typically adopted by national regulations. Single minor deviations are possible.

■ Festoon

A tube-shaped bulb with contacts at each end such as C5W, which is commonly used for interior and license plate lighting.

■ Filament

A coiled tungsten wire that emits light.

■ H(...)

Nomenclature for halogen bulbs. H = halogen.

The bulbs are numbered consecutively.

The most common types are:

H1 First halogen bulb (single filament).

H4 Double filament for both low beam and high beam application in one headlamp unit.

H7 Most common halogen bulb in Europe for low beam, high beam, and fog lighting.

■ Halogen

A gas that is used to create the halogen cycle process in a light bulb. During operation the tungsten molecules evaporate from the tungsten. In the cycle process they combine with the halogen molecules and fall back to the wire. This extends the lifetime of a bulb and allows operation at a higher intensity. Halogen bulbs contain a high-pressure halogen filling. Non-halogen incandescent bulbs often use a vacuum.

■ HB(...)

ECE name of original North American bulb types which were approved for use in Europe as well. For example: HB3 refers to 9005 and HB4 refers to 9006.

■ Hg

Symbol for mercury (Latin: hydrargyrum). Xenon bulb types D1 and D2 still contain approximately one third of the amount of mercury as a normal domestic energy-saving bulb. D3, D4 und D5 are completely mercury free.

■ HID

High Intensity Discharge. Correct technical name for a so-called xenon bulb.

See also gas-discharge bulb, xenon light, xenon system.

■ High-voltage starter

Creates high-voltage pulses of approximately 20 000 volts to ignite the electric arc in a xenon HID bulb.

■ HiPerVision

Very compact signaling-bulb range with high-precision filaments and a long lifetime. For use in signaling lights, fog lamps, rear and daytime running lights.

■ Illuminance (lux)

Contrary to luminous flux (lumen), which is a measure of the total amount of light emitted by a light source, illuminance describes the amount of luminous flux per unit area, such as on the road. This is measured with a lux meter.

■ IP certification

Dust ingress and splash water protection improving durability.

■ Kelvin (K)

A unit of measure of temperature based upon an absolute scale whereby zero (minus 273° C) represents the point where all thermal motion ceases. In lighting, however, this is a measure of color temperature. The higher the color temperature, the whiter and cooler the light appears.

■ LED

Light Emitting Diode.

■ Lifetime

Statistical data that indicate the failure rate of a percentage of bulbs operated at a specific voltage over a certain period of time. Common lifetime data indication:

B3 Time when statistically 3% of the test samples have failed

TC Time when 63% of the test samples have failed.

■ Luminance

The intensity of light emitted from a surface per unit area in a given direction from, for example, the filament or the electric arc of a xenon HID bulb. An important indicator of the amount of light a headlamp unit provides on the road. The unit is candela/m² (cd/m²).

■ Lumen (lm)

Unit of luminous flux.

■ Luminous flux (lumen)

The total amount of light that is emitted by a light source in all directions.

■ Lux (lx)

Unit of illuminance. 1 Lux = 1 lm/m².

See also Illuminance.

■ Lux meter

Illuminance measuring device.

■ LUXEON®

Lumileds LED chips technology.

■ Pb

Symbol for lead (Latin: plumbum).

All Philips automotive bulbs are **lead-free**.

■ Quartz glass

Temperature and pressure resistant glass for halogen and xenon HID bulbs. The glass also has a special coating to block out harmful ultraviolet (UV) light.

■ SafeBeam technology

Technology that projects the light exactly where you need it on the road.

■ Tungsten

Filament and electrode material.

■ UV-block

Ultraviolet (UV) rays blocking glass absorbs the UV light created by the filament or the electric arc. UV block is mandatory for all ECE complying car bulbs because UV light can damage the plastic cover of the headlamp.

See also Quartz glass.

■ Wedge base

Bulb with a glass base, such as W5W. Mainly used for position lights, side indicators and interior lighting.

■ Xenon (Xe)

One of the noble gases. Commonly used to refer to HID bulbs.

■ Xenon light

Headlights with HID bulbs.

See also D(...), Discharge bulb, HID.

■ Xenon system

A complete xenon system consists of the HID bulb, the high-voltage starter and the electronic ballast which controls the electric arc.

Specimen packaging

Discover the perfect anti-theft solution for your store.



VP VisionPlus



LLECO LongLife EcoVision



WVU WhiteVision ultra



XVP X-tremeVision Pro150



RGT RacingVision GT200



VI Xenon Vision



SY Xenon LongerLife



XV2 Xenon X-tremeVision gen2



WHV2 Xenon WhiteVision gen2

Ordering information

Description	Ordering number	GOC	EAN1	EAN3
12V halogen				
H4 RGT BF	56865BF	00596030	8719018005960	8719018005977
H7 RGT BF	56866BF	00598430	8719018005984	8719018005991
H4 RGT SF	56873SF	00606628	8719018006066	8719018006073
H7 RGT SF	56874SF	00608028	8719018006080	8719018006097
H1 XVP BF	56859BF	00584730	8719018005847	8719018005854
H4 XVP BF	56860BF	00586130	8719018005861	8719018005878
H7 XVP BF	56861BF	00588530	8719018005885	8719018005892
H1 XVP SF	56862SF	00590828	8719018005908	8719018005915
H4 XVP SF	56863SF	00592228	8719018005922	8719018005939
H7 XVP SF	56864SF	00594630	8719018005946	8719018005953
H1 WVU BF	56869BF	00600430	8719018006004	8719018006011
H4 WVU BF	56870BF	00602830	8719018006028	8719018006035
H7 WVU BF	56871BF	00604230	8719018006042	8719018006059
H1 WVU SF	56875SF	00610328	8719018006103	8719018006110
H4 WVU SF	56876SF	00612728	8719018006127	8719018006134
H7 WVU SF	56877SF	00614128	8719018006141	8719018006158
H1 LLECO BF	56273BF	26939830	8718696269398	8718696269404
H4 LLECO BF	56270BF	26933630	8718696269336	8718696269343
H7 LLECO BF	56268BF	26927530	8718696269275	8718696269282
H4 LLECO SF	56292SF	39002528	8727900390025	8727900390032
H1 LLECO SF	56261SF	26909128	8718696269091	8718696269107
H7 LLECO SF	56294SF	39004928	8727900390049	8727900390056
H1 VP BF	56279BF	26949730	8718696269497	8718696269503
H4 VP BF	56278BF	26947330	8718696269473	8718696269480
H7 VP BF	56277BF	26945930	8718696269459	8718696269466
H1 VP SF	56252SF	39991228	8727900399912	8727900399929
H4 VP SF	56293SF	39010028	8727900390100	8727900390117
H7 VP SF	56295SF	39012428	8727900390124	8727900390131


Description	Ordering number	GOC	EAN1	EAN3
Xenon				
D1S XV2 SF	56643SF	39655333	8727900396553	8727900396560
D2S XV2 SF	56644SF	39657733	8727900396577	8727900396584
D2R XV2 SF	56645SF	39659133	8727900396591	8727900396607
D3S XV2 SF	56646SF	39661433	8727900396614	8727900396621
D4S XV2 SF	56647SF	39663833	8727900396638	8727900396645
D1S WHV2 SF	56640SF	39649233	8727900396492	8727900396508
D2S WHV2 SF	56641SF	39651533	8727900396515	8727900396522
D3S WHV2 SF	56642SF	39653933	8727900396539	8727900396546
D1S SY SF	56477SF	39467233	8727900394672	8727900394689
D2S SY SF	56478SF	39469633	8727900394696	8727900394689
D2R SY SF	56479SF	39470233	8727900394702	8727900394719
D1S VI SF	85415VISF	36504733	8727900365047	8727900365054
D2R VI SF	85126VISF	36511533	8727900365115	8727900365122
D2S VI SF	85122VISF	36507833	8727900365078	8727900365085
D3S VI SF	42403VISF	36515333	8727900365153	8727900365160

Understanding Philips ordering codes

All our automotive lighting products can be ordered using **Philips Order Entry**.

With Philips Order Entry you can identify the **lamp type**, the **product range** and the **packaging type**.

Example: **12972WVUB1**, H7 WhiteVision ultra, single blister



1/ Lamp type

Every **lamp type** is designated by Philips with a unique number called lamp type.

- All 12V lamps start with 12 (for example: 12972 for H7 12V)
- All 24V lamps starting with 13 (for example: 13972 for H7 24V)

2/ Range type

Most lamp types are available in different product **ranges**.

These are indicated by a **color code**, to indicate the availability of a lamp in a specific product range.

Color code

	RacingVision GT200 Up to 200% brighter light	Range type RGT
	X-tremeVision Pro150 Up to 150% brighter light	Range type XVP
	VisionPlus Up to 60% more vision	Range type VP
	LongLife EcoVision Lifetime up to 1,500 hours	Range type LLECO
	WhiteVision ultra Sharp white look	Range type WVU
	Vision Up to 30% more vision	Range type PR
	Standard	Range type STD

3/ Packaging type



Commercial pack
Material carton
Content **C1** 1 lamp
Content **CP** 10 lamps
Packaging type **C1/CP**



Single blister
Material carton/plastic
Content 1 lamp
Packaging type **B1**



Double blister
Material carton/plastic
Content 2 lamps
Packaging type **B2**



Halogen special pack
Material plastic
Content **S2** 2 lamps
Content **SM** 4 lamps
(2 headlamps,
2 position lamps)
Packaging type **S2/SM**



Xenon single blister
Material carton/plastic
Content 1 lamp
Packaging type **S1**



LED blister
Material carton/plastic
Content **X1** 1 lamp
Content **X2** 2 lamps
Packaging types **X1/X2**


































































LED special pack
Material carton
Content **X2** 2 lamps
Packaging type **X2**



LED Adapter Rings
Material carton
Content **X2** 2 rings
Packaging type **X2**

	Ultinon Pro6000 Taking bright white light to the next level	Range type U60
	Ultinon Pro6000 Standard A bright new journey ahead	Range type U60S
	Ultinon Pro9100 Original automotive LED performance	Range type U9100
	Ultinon Pro5100 White light, for brighter roads	Range type U5100
	Ultinon Pro3022 Stylish LED lighting that's easy to fit!	Range type U3022
	Ultinon Access Quick, easy installation	Range type U2500
	Ultinon Pro6000 SI Brighter, elegant signals	Range type U6000
	Ultinon Pro3100 SI Stand out from the crowd	Range type U3100

Technical illustrations Bases

						
SV6 IEC 7004-5	SV8,5-8 IEC 7004-81	W2x4,6d IEC 7004-94	W2,1x9,5d IEC 7004-91	W3x16d IEC 7004-105	W3x16q IEC 7004-106	WX3x16d IEC 7004-105
						
BAX 9s IEC 7004-8	BAY 9s IEC 7004-9	BA 7s	BA 9s IEC 7004-14	BA 15s IEC 7004-11A	BA 15d IEC 7004-11A	BAU 15s IEC 7004-11A
						
BAY 15d IEC 7004-11B	BAW 9s IEC 7004-149-1	BAW 15d IEC 7004-11E-1	BAW 15s IEC 7004-11E11	BAZ 15d IEC 7004-11C	BA20d IEC 7004-12	P43t-38 IEC 7004-39
						
P45t-41 IEC 7004-95	P20d-PY20d IEC 7004-31	P22d IEC 7004-32	PX22d	PG13 IEC 7004-107	PGJ13 IEC 7004-107	PGJ23t-1
						
HPSL HTR	PG18,5d IEC 7004-147	PG20 IEC 7004-127	PGU20	PU20d	PGJ19-1/2 IEC 7004-110	PGJ19-3 IEC 7004-110
						
PGJ19-5 IEC 7004-110	PGJ23t-1	P14,5s IEC 7004-46	X511 IEC 7004-99	P26s	PX26d,4t IEC 7004-128-2	PX26d IEC 7004-5
						
P29t-PX29t IEC 7004-66	P32d IEC 7004-111	P32d-2 IEC 7004-111	P32d-3 IEC 7004-111	P32d-5 IEC 7004-111	P32d-6 IEC 7004-111	PK32d-2 IEC 7004-111
						
PK32d-3/5/6 IEC 7004-111	PK32d-7 IEC 7004-111	PK22s IEC 7004-47	PU43t-3 IEC 7004-171-2	PY26d-1 IEC 7004-5-7	W3x16d IEC 7004-105-1	W3x16q IEC 7004-106-1
						
W2,1x9,5d	WP3,3x14,5/3	Bax 8,3s	Bax 8,4d	Bax 8,5d/1	Bax 8,5d/2	Bax 10d

Product index

LED 12 V car and two-wheeler lighting - 24 V truck lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
11005U2500CX	HL [=HB3/HB4]	U2500	12	20	P20d/P22d	02574650	-	8719018025753	8719018025760	37
11005U3022X2	HL [=HB3/HB4]	U3022SI	12/24	20	P20d/P22d	01806994	8719018018069	-	8719018018076	37
11005U51X2	HL [=HB3/HB4]	U5100	12/24	12	P20d/P22d	01886194	8719018018861	-	8719018018878	36
11005U91X2	HL [=HB3/HB4]	U9100	12/24	20	P20d/P22d	01870094	8719018018700	-	8719018018717	36
11012U2500CX	HL [=HIR2]	U2500	12	20	PX22d	02577750	-	8719018025784	8719018025791	36
11012U3022X2	HL [=HIR2]	U3022SI	12/24	20	PX22D	01808394	8719018018083	-	8719018018090	36
11012U51X2	HL [=HIR2]	U5100	12/24	12	PX22d	01888594	8719018018885	-	8719018018892	36
11012U91X2	HL [=HIR2]	U9100	12/24	20	PX22d	01872494	8719018018724	-	8719018018731	36
11065AU60X2	SI-AMBER [=W21W]	U6000SI	12	2.3	WX3x16d	01558730	8719018015587	-	8719018015594	40
11065CU31B2	SI-WHITE [=W21W]	U3100SI	12	2.2	W3x16d	02192230	8719018021922	-	8719018021939	41
11065CU60X2	SI-WHITE [=W21W]	U6000SI	12	2.3	W3x16d	01554930	8719018015549	-	8719018015556	41
11065RU31B2	SI-RED [=W21W]	U3100SI	12	1.73	W3x16d	02194630	8719018021946	-	8719018021953	41
11065RU60X2	SI-RED [=W21W]	U6000SI	12	2.3	W3x16d	01564830	8719018015648	-	8719018015655	40
11066AU60X2	SI-AMBER [=W21/5W]	U6000SI	12	2.5/0.5	W3x16q	01556330	8719018015563	-	8719018015570	40
11066CU31B2	SI-WHITE [=W21/5W]	U3100SI	12	2.4/0.48	W3x16q	02208030	8719018022080	-	8719018022097	40
11066CU60X2	SI-WHITE [=W21/5W]	U6000SI	12	2.5/0.5	W3x16q	01550130	8719018015501	-	8719018015518	40
11066RU31B2	SI-RED [=W21/5W]	U3100SI	12	1.75/0.65	W3x16q	02196030	8719018021960	-	8719018021977	40
11066RU60X2	SI-RED [=W21/5W]	U6000SI	12	2.5/0.5	W3x16q	01552530	8719018015525	-	8719018015532	40
11067CU31B1	SI-WHITE [=W16W]	U3100SI	12	1.8	W2.1x9.5d	02204230	8719018022042	-	8719018022059	40
11067CU60X1	SI-T16 [=W16W]	U6000SI	12	2.4	W2.1x9.5d	01566230	8719018015662	-	8719018015679	39
11071AU31B2	SI-AMBER [=WY21W]	U3100SI	12	2.15	WX3x16d	02198430	8719018021984	-	8719018021991	40
11090CU31B2	SI-WHITE [=R5/R10W]	U3100SI	12	1.8	BA15s	02206630	8719018022066	-	8719018022073	41
11258U2500CX	HL [=H1]	U2500	12	13	P14.5s	02583850	-	8719018025845	8719018025852	34
11258U3022X2	HL [=H1]	U3022SI	12/24	18	P14.5s	01812094	8719018018120	-	8719018018137	34
11258U51X2	HL [=H1]	U5100	12/24	12.5	P14.5s	01878694	8719018018786	-	8719018018793	34
11258U91X2	HL [=H1]	U9100	12/24	20	P14.5s	01862594	8719018018625	-	8719018018632	34
11336U2500CX	HL [=H3]	U2500	12	13	PK22s	02586950	-	8719018025876	8719018025883	34
11336U3022X2	HL [=H3]	U3022SI	12/24	18	PK22s	01814494	8719018018144	-	8719018018151	34
11336U51X2	HL [=H3]	U5100	12/24	12	PK22s	01890894	8719018018908	-	8719018018915	34
11336U91X2	HL [=H3]	U9100	12/24	20	PK22s	01874894	8719018018748	-	8719018018755	34
11342U2500CX	HL [=H4/H19]	U2500	12	20/22	P43t-38/ PU43t-3	02565450	-	8719018025661	8719018025678	35
11342U3022X2	HL [=H4]	U3022SI	12/24	20	P43t-38	01800794	8719018018007	-	8719018018014	35
11342U51X2	HL [=H4]	U5100	12/24	12	P43t-38	01882394	8719018018823	-	8719018018830	34
11342U6000X1	HL [=H4]	U60	12	18	P43t-38	02424494	8719018024244	-	8719018024251	14
11342U6000X2	HL [=H4]	U60	12	18	P43t-38	01365131	8719018013651	-	8719018013668	14
11342U91X2	HL [=H4]	U9100	12/24	18	P43t-38	01866394	8719018018663	-	8719018018670	34
11362U2500CX	HL [=H11]	U2500	12	20	PGJ19-2	02571550	-	8719018025722	8719018025739	35
11362U3022X2	HL [=H11]	U3022SI	12/24	20	PGJ19-2	01810694	8719018018106	-	8719018018113	35
11362U51X2	HL [=H11]	U5100	12/24	12	PGJ19-2	01880994	8719018018809	-	8719018018816	35
11362U91X2	HL [=H11]	U9100	12/24	16	PGJ19-2	01864994	8719018018649	-	8719018018656	35
11366U2500CX	FL [=H8/H9/H16]	U2500	12	20	PGJ19-1/3/5	02580750	-	8719018025814	8719018025821	36
11366U3022X2	FL [=H8/H11/H16]	U3022SI	12/24	20	PGJ19-1/2/3	01804594	8719018018045	-	8719018018052	36
11366U51X2	FL [=H8/H11/H16]	U5100	12/24	9	PGJ19-1/2/3	01876294	8719018018762	-	8719018018779	36
11366U91X2	FL [=H8/H11/H16]	U9100	12/24	11	PGJ19-1/2/3	01860194	8719018018601	-	8719018018618	36
11496AU31B2	SI-AMBER [=PY21W]	U3100SI	12	2.15	BAY15D	02202830	8719018022028	-	8719018022035	39
11498AU60X2	SI-AMBER [=P21W]	U6000SI	12	2.3	BAU15S	01548830	8719018015488	-	8719018015495	39
11498CU31B2	SI-WHITE [=P21W]	U3100SI	12	2.2	BA15S	02186130	8719018021861	-	8719018021878	39
11498CU60X2	SI-WHITE [=P21W]	U6000SI	12	2.3	BA15S	01540230	8719018015402	-	8719018015419	39
11498RU31B2	SI-RED [=P21W]	U3100SI	12	1.73	BA15S	02188530	8719018021885	-	8719018021892	39
11498RU60X2	SI-RED [=P21W]	U6000SI	12	2.3	BA15S	01542630	8719018015426	-	8719018015433	39
11499AU60X2	SI-AMBER [=P21/5W]	U6000SI	12	2.5/0.5	BAY15d	01546430	8719018015464	-	8719018015471	38
11499CU31B2	SI-WHITE [=P21/5W]	U3100SI	12	2.4/0.48	BAY15D	02200430	8719018022004	-	8719018022011	39
11499CU60X2	SI-WHITE [=P21/5W]	U6000SI	12	2.5/0.5	BAY15d	01544030	8719018015440	-	8719018015457	39
11499RU31B2	SI-RED [=P21/5W]	U3100SI	12	1.75/0.65	BAY15D	02190830	8719018021908	-	8719018021915	39
11499RU60X2	SI-RED [=P21/5W]	U6000SI	12	2.5/0.5	BAY15d	01538930	8719018015389	-	8719018015396	38
11854CU31B1	SI-WHITE [=Fest 38 mm]	U3100SI	12	0.6	SV8.5	02210330	8719018022103	-	8719018022110	38
11854CU60X1	SI-FEST 38mm 6000K	U6000SI	12	1	SV8.5	01532730	8719018015327	-	8719018015334	38
11854WU60X1	SI-FEST 38mm 4000K	U6000SI	12	1	SV8.5	01526630	8719018015266	-	8719018015273	38
11860CU31B1	SI-WHITE [=Fest 30 mm]	U3100SI	12	0.8	SV8.5	02184730	8719018021847	-	8719018021854	38
11860CU60X1	SI-FEST 30mm 6000K	U6000SI	12	1	SV8.5	01530330	8719018015303	-	8719018015310	38
11860WU60X1	SI-FEST 30mm 4000K	U6000SI	12	1	SV8.5	01524230	8719018015242	-	8719018015259	38
11866CU31B1	SI-WHITE [=Fest 43 mm]	U3100SI	12	0.6	SV8.5	02212730	8719018022127	-	8719018022134	38

LED 12 V car and two-wheeler lighting - 24 V truck lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
11866CU60X1	SI-FEST 43mm 6000K	U6000SI	12	1	SV8.5	01534130	8719018015341	-	8719018015358	38
11866WU60X1	SI-FEST 43mm 4000K	U6000SI	12	1	SV8.5	01528030	8719018015280	-	8719018015297	38
11961AU60X2	SI-AMBER [=W5W]	U6000SI	12	0.5	W2.1x9.5d	01560030	8719018015600	-	8719018015617	41
11961CU31B2	SI-WHITE [=W5W]	U3100SI	12	0.74	W2.1x9.5d	02182330	8719018021823	-	8719018021830	41
11961CU60X2	SI-T10 [=W5W] 6000K	U6000SI	12	0.9	W2.1x9.5d	01516730	8719018015167	-	8719018015174	41
11961HU60X2	SI-WHITE [=W5W]	U60	12	0.9	W2.1x9.5d	01638630	8719018016386	-	8719018016393	14
11961WU60X2	SI-T10 [=W5W] 4000K	U6000SI	12	0.9	W2.1x9.5d	01514330	8719018015143	-	8719018015150	41
11961XU60X2	SI-T10 [=W5W] 8000K	U6000SI	12	0.7	W2.1x9.5d	01522830	8719018015228	-	8719018015235	41
11972U2500CX	HL [=H7/H18]	U2500	12	16	PX26d/ PY26d-1	02568550	-	8719018025708	8719018025692	35
11972U3022X2	HL [=H7]	U3022SI	12/24	20	PX26d	01802194	8719018018021	-	8719018018038	35
11972U51X2	HL [=H7]	U5100	12/24	12	PX26d	01884794	8719018018847	-	8719018018854	35
11972U6000X1	HL [=H7]	U60	12	15	PX26d	02422094	8719018024220	-	8719018024237	14
11972U6000X2	HL [=H7]	U60	12	15	PX26d	01361331	8719018013613	-	8719018013644	14
11972U60SX2	HL [=H7]	U60S	12	17	PX26d	02556231	8719018025562	-	8719018025579	14
11972U91X2	HL [=H7]	U9100	12/24	18	PX26d	01868794	8719018018687	-	8719018018694	35
24805CU60X2	SI-WHITE [=R5W/R10W]	U6000SI	24	1	BA15s	01562430	8719018015624	-	8719018015631	45
24844CU60X1	SI-FEST 30mm 6000K	U6000SI	24	1.5	SV8.5	01536530	8719018015365	-	8719018015372	45
24961CU60X2	SI-T10 [=W5W] 6000K	U6000SI	24	1	W2.1x9.5d	01520430	8719018015204	-	8719018015211	45
24961WU60X2	SI-T10 [=W5W] 4000K	U6000SI	24	1	W2.1x9.5d	01518130	8719018015181	-	8719018015198	45

LED CANbus Adapters

Ordering number	Type	V	W	GOC	EAN1	EAN2	EAN3	Page
18952X2	HL [=H7]	12	12	72837794	6974260728377	-	6974260728384	15, 42
18954X2	FL [=H8/H11/H16]	12	12	72833994	6974260728339	-	6974260728346	42
18956X2	HL [=HB3/HB4/HIR2]	12	12	72835394	6974260728353	-	6974260728360	42
18960X2	HL [=H4]	12	12	72831594	6974260728315	-	6974260728322	15, 42

LED Adapter Rings

Ordering number	Type	Range	GOC	EAN1	EAN2	EAN3	Page
11184X2	Type A	U9100	02009331	8719018020093	-	8719018020109	15, 42
11176X2	Type D	U9100	01681231	8719018016812	-	8719018016829	15, 42
11178X2	Type E	U9100	01679931	8719018016799	-	8719018016805	15, 42
11172X2	Type H	U9100	01630031	8719018016300	-	8719018016317	15, 42
11179X2	Type I	U9100	01683631	8719018016836	-	8719018016843	15, 43
11180X2	Type K	U9100	01675131	8719018016751	-	8719018016768	15, 43
11183X2	Type N	U9100	01636231	8719018016362	-	8719018016379	15, 43
11182X2	Type P	U9100	01677531	8719018016775	-	8719018016782	15, 43
11009RCDX2	Type RCD	U5100	02058131	8719018020581	-	8719018020598	43
11010RCEX2	Type RCE	U5100	02060431	8719018020604	-	8719018020611	43
11011RCPX2	Type RCP	U5100	02062831	8719018020628	-	8719018020635	43
11013RAHX2	Type RAH	U3022	02046831	8719018020468	-	8719018020475	43
11016RAPX2	Type RAP	U3022	02052931	8719018020529	-	8719018020536	43
11015RAEX2	Type RAE	U3022	02050531	8719018020505	-	8719018020512	43
11014RADX2	Type RAD	U3022	02048231	8719018020482	-	8719018020499	43

Halogen 12 V car lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12023CP	H5W	Standard	12	5	BA9s	51270928	8711559512709	8711559512464	8727900371222	66
12024CP	H10W	Standard	12	10	BA9s	52941728	8711559529417	8711559529424	8727900371192	66
12025CP	H20W	Standard	12	20	BA9s	87600328	8711500876003	8711500876010	8727900371154	66
12036B2	H6W	Standard	12	6	BAX9s	24720930	8711500247209	-	8711500247216	66
12036CP	H6W	Standard	12	6	BAX9s	87603428	8711500876034	8711500876041	8727900370676	66
12036WVUB2	H6W	WhiteVision ultra	12	6	BAX9s	00543430	8719018005434	-	8719018005441	66
12040VPB2	WBT10	VisionPlus	12	6	W2.1x9.5d	52416030	8711559524160	-	8711559524184	68
12059C1	H27W/1	Standard	12	27	PG13	52854030	8711559528540	-	8727900370799	63
12060C1	H27W/2	Standard	12	27	PGJ13	52857130	8711559528571	-	8727900370805	63
12061CP	W2,3W	Standard	12	2.3	W2x4,6d	48330028	8711500483300	8711500483317	8727900391640	67
12065B2	W21W	Standard	12	21	W3x16d	70146330	8727900701463	-	8727900701470	68
12065CP	W21W	Standard	12	21	W3x16d	47135228	8711500471352	8711500471369	8727900391107	68
12066B2	W21/5W	Standard	12	21/5	W3x16q	69739130	8727900697391	-	8727900697407	68
12066CP	W21/5W	Standard	12	21/5	W3x16q	47138328	8711500471383	8711500471390	8727900391091	68
12067B2	W16W	Standard	12	16	W2.1x9.5d	40587630	8711500405876	-	8711559521053	68
12067CP	W16W	Standard	12	16	W2.1x9.5d	48272328	8711500482723	8711500482730	8727900391626	68

Halogen 12 V car lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12071B2	WY21W	Standard	12	21	WX3x16d	69741430	8727900697414	-	8727900697421	68
12071CP	WY21W	Standard	12	21	WX3x16d	52539628	8711559525396	8711559525402	8727900391688	68
12085C1	PS19W	Standard	12	19	PG20/1	69653030	8727900696530	-	8727900390988	72
12085LLC1	PS19W	LongLife	12	19	PG20/1	70046630	8727900700466	-	8727900390926	72
12086FFC1	PS24W	Standard	12	24	PG20/3	70044230	8727900700442	-	8727900390919	72
12088CP	PR21W	Standard	12	21	BAW15s	48531128	8711500485311	8711500485328	8727900391589	64
12093NACP	RY10W	Standard	12	10	BAU15s	48362128	8711500483621	8711500483638	8727900391619	65
12146CP	HY21W	Standard	12	21	BAW9s	35244328	8727900352443	8727900352450	8727900370867	66
12174NAHTRC1	PWY24W	Standard	12	24	WP3,3x14,5/4	39202930	8727900392029	-	8727900397345	73
12174SVHTRC1	PWY24W	SilverVision+	12	24	WP3,3x14,5/4	39200530	8727900392005	-	8727900397352	73
12177C1	PW16W	Standard	12	16	WP3,3x14,5/8	39623230	8727900396232	-	8727900396249	72
12180SV+C1	PSY24W	SilverVision+	12	24	PG20/4	70379530	8727900703795	-	8727900390841	73
12182HTRC1	PW24W	Standard	12	24	WP3,3x14,5/3	39196130	8727900391961	-	8727900397369	73
12188NAC1	PSY24W	Standard	12	24	PG20/4	69668430	8727900696684	-	8727900390834	73
12190NAC1	PY24W	Standard	12	24	PGU20/4	69690530	8727900696905	-	8727900390803	73
12197HTRC1	HiPerVision LCP	Standard	13.5	24	HPSL 2A	39621830	8727900396218	-	8727900396225	72
12256B2	W3W	Standard	12	3	W2,1x9,5d	52410830	8711559524108	-	8711559524122	81
12256CP	W3W	Standard	12	3	W2,1x9,5d	48144328	8711500481443	8711500481450	8727900391664	81
12258LLECOB1	H1	LongLife EcoVision	12	55	P14,5s	36196430	8727900361964	-	8727900361971	58
12258LLECO1	H1	LongLife EcoVision	12	55	P14,5s	36187230	8727900361872	-	8727900370683	58
12258LLECOS2	H1	LongLife EcoVision	12	55	P14,5s	36255828	8727900362558	-	8727900362565	58
12258PRB1	H1	Vision	12	55	P14,5s	47516930	8711500475169	-	8711500475176	58
12258PRC1	H1	Vision	12	55	P14,5s	47518360	8711500475183	8727900363791	8711500475190	58
12258SPC1	H1	Spot	12	55	P14,5s	40460230	8711500404602	-	8727900370690	58
12258VPB1	H1	VisionPlus	12	55	P14,5s	36320330	8727900363203	-	8727900363197	58
12258VPS2	H1	VisionPlus	12	55	P14,5s	36322728	8727900363227	-	8727900363210	58
12258WVUB1	H1	WhiteVision ultra	12	55	P14,5s	00523630	8719018005236	-	8719018005243	58
12258WVUSM	H1	WhiteVision ultra	12	55	P14,5s	00525028	8719018005250	-	8719018005267	58
12258XVPB1	H1	X-tremeVision Pro150	12	55	P14,5s	00549630	8719018005496	-	8719018005502	58
12258XVPS2	H1	X-tremeVision Pro150	12	55	P14,5s	00565628	8719018005656	-	8719018005663	58
12271AC1	PCY16W	HiPerClick	12	16	PU20d/2	38965430	8727900389654	-	8727900391152	72
12274SV+C1	PY24	SilverVision+	12	24	PGU20/4	69678330	8727900696783	-	8727900390780	73
12275NAC1	PSY19W	Standard	12	19	PG20/2	52735230	8711559527352	-	8727900390858	72
12276C1	PSX24W	Standard	12	24	PG20/7	69676930	8727900696769	-	8727900390902	72
12276WVUB1	PSX24W	WhiteVision ultra	12	24	PG20/7	00545828	8719018005458	-	8719018005465	72
12277C1	P13W	Standard	12	13	PG18,5d-1	69672130	8727900696721	-	8727900391008	72
12278C1	PSX26W	Standard	12	26	PG18,5d/3	38874930	8727900388749	-	8727900390896	73
12311C1	H2	Standard	12	55	X511	47752130	8711500477521	-	8727900370782	58
12336LLECO1	H3	LongLife EcoVision	12	55	PK22s	77704130	8711500777041	-	8711500779366	59
12336PRB1	H3	Vision	12	55	PK22s	69561130	8711500695611	-	8711500695628	58
12336PRC1	H3	Vision	12	55	PK22s	69534560	8711500695345	8711500775696	8711500695352	58
12336WVUB1	H3	WhiteVision ultra	12	55	PK22s	00531128	8719018005311	-	8719018005328	59
12342LLECOB1	H4	LongLife EcoVision	12	60/55	P43t-38	36198830	8727900361988	-	8727900361995	59
12342LLECO1	H4	LongLife EcoVision	12	60/55	P43t-38	36189630	8727900361896	-	8727900370836	59
12342LLECOS2	H4	LongLife EcoVision	12	60/55	P43t-38	36257228	8727900362572	-	8727900362589	59
12342PRB1	H4	Vision	12	60/55	P43t-38	47480330	8711500474803	-	8711500474810	59
12342PRC1	H4	Vision	12	60/55	P43t-38	49099560	8711500490995	8711500827807	8711500490988	59
12342PRC2	H4	Vision	12	60/55	P43t-38	78028760	8711500780287	8711500780294	8711500780300	59
12342RGTB1	H4	RacingVision GT200	12	60/55	P43t-38	00571730	8719018005717	-	8719018005724	59
12342RGTS2	H4	RacingVision GT200	12	60/55	P43t-38	00575528	8719018005755	-	8719018005762	59
12342VPB1	H4	VisionPlus	12	60/55	P43t-38	39934930	8727900399349	-	8727900399332	59
12342VPC2	H4	VisionPlus	12	60/55	P43t-38	37435360	8727900374353	8727900374360	8727900374377	59
12342VPS2	H4	VisionPlus	12	60/55	P43t-38	39925728	8727900399257	-	8727900350937	59
12342WVUB1	H4	WhiteVision ultra	12	60/55	P43t-38	35489830	8727900354898	-	8727900354881	59
12342WVUSM	H4	WhiteVision ultra	12	60/55	P43t-38	35490428	8727900354904	-	8727900354911	59
12342XVPB1	H4	X-tremeVision Pro150	12	60/55	P43t-38	00553330	8719018005533	-	8719018005540	59
12342XVPS2	H4	X-tremeVision Pro150	12	60/55	P43t-38	00567028	8719018005670	-	8719018005687	59
12356CP	H21W	Standard	12	21	BAY9s	87989928	8711500879899	8711500879905	8727900371116	66
12360B1	H8	Standard	12	35	PGJ19-1	82416530	8711500824165	-	8727900362909	60
12360C1	H8	Standard	12	35	PGJ19-1	47582430	8711500475824	-	8727900371017	60
12360WVUB1	H8	WhiteVision ultra	12	35	PGJ19-1	00533528	8719018005335	-	8719018005342	60
12361B1	H9	Standard	12	65	PGJ19-5	36308130	8727900363081	-	8727900363098	61
12361C1	H9	Standard	12	65	PGJ19-5	47584830	8711500475848	-	8727900371000	61
12362XVPB1	H11	X-tremeVision Pro150	12	55	PGJ19-2	00551928	8719018005519	-	8719018005526	61
12362LLECOB1	H11	LongLife EcoVision	12	55	PGJ19-2	36310430	8727900363104	-	8727900363111	61

Halogen 12 V car lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12362LLECO1	H11	LongLife EcoVision	12	55	PGJ19-2	36194030	8727900361940	-	8727900370744	61
12362PRB1	H11	Vision	12	55	PGJ19-2	36428630	8727900364286	-	8727900364293	61
12362PRC1	H11	Vision	12	55	PGJ19-2	36430930	8727900364309	-	8727900370751	61
12362WVUB1	H11	WhiteVision ultra	12	55	PGJ19-2	00535928	8719018005359	-	8719018005366	61
12366C1	H16	Standard	12	19	PGJ19-3	36856730	8727900368567	-	8727900370775	61
12396NAB2	WY5W	Standard	12	5	W2,1x9,5d	40058130	8711500400581	-	8711500400598	67
12396NACP	WY5W	Standard	12	5	W2,1x9,5d	53002428	8711559530024	8711559530031	8727900390889	67
12401CP	Stop P22	Standard	12	15	BA15s	87821228	8711500878212	8711500878229	8711500790538	64
12445CP	Stop P25	Standard	12	18	BA15s	48440628	8711500484406	8711500484413	8727900391602	65
12475B1	R2	R2 Vision	12	45/40	P45t-41	24716230	8711500247162	-	8711500247179	63
12475C1	R2	R2 Vision	12	45/40	P45t-41	40466430	8711500404664	-	8727900371130	63
12495CP	PR21/5W	Standard	12	21/5	BAW15d	48873228	8711500488732	8711500488749	8727900391572	64
12496LLECOCP	PY21W	LongLife EcoVision	12	21	BAU15s	38218128	8727900382181	8727900382198	8727900391084	64
12496NAB2	PY21W	Standard	12	21	BAU15s	52372930	8711559523729	-	8711559523743	64
12496NACP	PY21W	Standard	12	21	BAU15s	52534173	8711559525341	8711559525358	8711559525365	64
12496SVB2	PY21W	SilverVision	12	21	BAU15s	31117730	8711500311177	-	8711500311191	64
12498B2	P21W	Standard	12	21	BA15s	5549130	8711500055491	-	8711559520131	81
12498CP	P21W	Standard	12	21	BA15s	49078073	8711500490780	8711500490797	8711500490803	81
12498LLECOB2	P21W	LongLife EcoVision	12	21	BA15s	38210530	8727900382105	-	8727900382112	63
12498LLECOCP	P21W	LongLife EcoVision	12	21	BA15s	38198628	8727900381986	8727900381993	8727900391695	63
12498VPB2	P21W	VisionPlus	12	21	BA15s	36318030	8727900363180	-	8727900363173	63
12499B2	P21/5W	Standard	12	21/5	BAY15d	5545330	8711500055453	-	8711559520148	64
12499CP	P21/5W	Standard	12	21/5	BAY15d	48159773	8711500481597	8711500481603	8711500481610	64
12499LLECOB2	P21/5W	LongLife Ecovision	12	21/5	BAY15d	38212930	8727900382129	-	8727900382136	64
12499LLECOCP	P21/5W	LongLife Ecovision	12	21/5	BAY15d	38201328	8727900382013	8727900382020	8727900391053	64
12499VPB2	P21/5W	VisionPlus	12	21/5	BAY15d	36316630	8727900363166	-	8727900363159	64
12505CP	W2W	Standard	12	2	W2x4,6d	48327028	8711500483270	8711500483287	8727900391657	67
12516B2	W1,2W	Standard	12	1.2	W2x4,6d	5554530	8711500055545	-	8711500417763	67
12516CP	W1,2W	Standard	12	1.2	W2x4,6d	48153573	8711500481535	8711500481542	8711500481559	67
12521CP	WBT5	Standard	12	1	W2x4,6d	48321828	8711500483218	8711500483225	8727900391671	67
12580C1	H15	Standard	12	55/15	PGJ23t-1	02000030	8719018020000	-	8719018020024	61
12580B1	H15	Standard	12	55/15	PGJ23t-1	02001730	8719018020017	-	8719018020031	61
12594B2	P21/4W	Standard	12	21/4	BAZ15d	40485530	8711500404855	-	8711500471017	64
12594CP	P21/4W	Standard	12	21/4	BAZ15d	48433828	8711500484338	8711500484345	8727900391565	64
12597B2	Bax 8,3s/1,35 black	Standard	12	1.2	B8,3s/1,35	53018530	8711559530185	-	8711559530192	70
12597CP	Bax 8,3s/1,35 black	Standard	12	1.2	B8,3s/1,35	48365228	8711500483652	8711500483669	8727900390957	70
12598B2	Bax 8,5d/2 black	Standard	12	1.2	B8,5d/2	40588330	8711500405883	-	8711500405890	70
12598CP	Bax 8,5d/2 black	Standard	12	1.2	B8,5d/2	48387428	8711500483874	8711500483881	8727900390964	70
12600CP	Bax 8,5d/2 green	Standard	12	2	B8,5d/2	48393528	8711500483935	8711500483942	8727900390971	70
12602CP	Bax 8,3s/1,5 blue	Standard	12	2	B8,3s/1,5	48396628	8711500483966	8711500483973	8727900390995	70
12603CP	Bax 8,5d/1,5 blue	Standard	12	1.2	B8,5d/1,5	48399728	8711500483997	8711500484000	8727900391015	70
12604CP	B8,5d green	Standard	12	2	B8,5d	40508128	8711500405081	8711500404589	8727900391022	70
12611CP	BX8,4d olive green	Standard	12	1.3	BX8,4d	77432328	8711500774323	8711500774330	8711500779397	71
12614CP	B10d brown halogen	Standard	12	3	B10d	52805228	8711559528052	8711559512723	8727900370928	70
12615CP	B10d black halogen	Standard	12	5	B10d	52807628	8711559528076	8711500243768	8727900370911	70
12620B1	R2	Standard	12	45/40	P45t-41	5543930	8711500055439	-	8711559525327	63
12620C1	R2	Standard	12	45/40	P45t-41	40085730	8711500400857	-	8711500779359	63
12623CP	BX8,4d light blue	Standard	12	1.2	BX8,4d	51384328	8711559513843	8711500244154	8727900370904	70
12624CP	BX8,4d orange	Standard	12	1.1	BX8,4d	51411628	8711559514116	8711500245137	8727900370898	71
12625CP	BX8,4d black	Standard	12	1.2	BX8,4d	51409328	8711559514093	8711500244420	8727900371208	71
12626CP	BX8,4d light green	Standard	12	2	BX8,4d	51412328	8711559514123	8711500246066	8727900370942	71
12627CP	BX8,4d beige	Standard	12	1.5	BX8,4d	51414728	8711559514147	8711500247414	8727900370959	71
12629CP	BX8,4d beige	Standard	12	1.8	BX8,4d	51488828	8711559514888	8711559512488	8727900371031	71
12637CP	B8,5d beige	Standard	12	1.5	B8,5d	51487128	8711559514871	8711500400178	8727900371048	70
12638CP	BX8,5d white	Standard	12	1.12	BX8,5d	48846628	8711500488466	8711500488473	8727900391503	71
12643LLC1	H18	LongLife EcoVision	12	65	PY26d-1	35603830	8727900356038	-	8727900356045	61
12644LLC1	H19	LongLife EcoVision	12	60/55	PU43t-3	35605230	8727900356052	-	8727900356069	62
12814B2	R10W	Standard	12	10	BA15s	5547730	8711500055477	-	8711500417718	65
12814CP	R10W	Standard	12	10	BA15s	48341673	8711500483416	8711500483423	8711500483430	65
12818CP	Festoon T6,2x27	Standard	12	3	SV6	48461128	8711500484611	8711500484628	8727900695632	69
12821B2	R5W BA15s	Standard	12	5	BA15s	5546030	8711500055460	-	8711500417701	65
12821CP	R5W BA15s	Standard	12	5	BA15s	48269373	8711500482693	8711500482709	8711500482716	65
12821LLECOB2	R5W	LongLife EcoVision	12	5	BA15s	38208230	8727900382082	-	8727900382099	65
12821LLECOCP	R5W	LongLife EcoVision	12	5	BA15s	38195528	8727900381955	8727900381962	8727900390940	65
12822CP	R5W BA15d	Standard	12	5	BA15d	45407228	8711500454072	8711500454959	8711500790521	65

Halogen 12 V car lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12829CP	BA7	Standard	12	2	BA7s	52123728	8711559521237	8711500401236	8727900390933	65
12844B2	Festoon C5W	Standard	12	5	SV8,5	5551430	8711500055514	-	8711500417749	69
12844CP	Festoon C5W	Standard	12	5	SV8,5	48156673	8711500481566	8711500481573	8711500481580	69
12848CP	Festoon T6,2x35	Standard	12	3	SV6	48467328	8711500484673	8711500484680	8727900391558	69
12850CP	Festoon T15x43	Standard	12	15	SV8,5	48285328	8711500482853	8711500482860	8727900391541	69
12854CP	Festoon T10,5x38	Standard	12	10	SV8,5	48248828	8711500482488	8711500482495	8727900391510	69
12860LLECOCP	Festoon T10,5x30	LongLife EcoVision	12	10	SV8,5	38192428	8727900381924	8727900381931	8727900391114	69
12864CP	Festoon T10,5x43	Standard	12	5	SV8,5	48205128	8711500482051	8711500482075	8727900391527	69
12866B2	Festoon T10,5x43	Standard	12	10	SV8,5	5552130	8711500055521	-	8711500417756	69
12866CP	Festoon T10,5x43	Standard	12	10	SV8,5	48242628	8711500482426	8711500482433	8727900391534	69
12910CP	T3W	Standard	12	3	BA9s	21949728	8711500219497	8711500219503	8711500220837	65
12913CP	T2W	Standard	12	2	BA9s	21997828	8711500219978	8711500219985	8711500220820	65
12929B2	T4W	Standard	12	4	BA9s	5550730	8711500055507	-	8711500220094	65
12929CP	T4W	Standard	12	4	BA9s	21979473	8711500219794	8711500219800	8711500219817	65
12960CP	W2,2W	Standard	12	2.2	W2,1x9,5d	48150428	8711500481504	8711500481511	8727900391633	67
12961B2	W5W	Standard	12	5	W2,1x9,5d	40421330	8711500404213	-	8711559520070	67
12961CP	W5W	Standard	12	5	W2,1x9,5d	49090273	8711500490902	8711500490919	8711500490926	67
12961LLECOB2	W5W	LongLife EcoVision	12	5	W2,1x9,5d	38204430	8727900382044	-	8727900382051	67
12961LLECOCP	W5W	LongLife EcoVision	12	5	W2,1x9,5d	38189428	8727900381894	8727900381900	8727900390872	67
12961WVUB2	W5W	WhiteVision ultra	12	5	W2,1x9,5d	35484330	8727900354843	-	8727900354874	67
12961XVPB2	W5W	X-tremeVision Pro150	12	5	W2,1x9,5d	00563230	8719018005632	-	8719018005649	67
12972LLECOB1	H7	LongLife EcoVision	12	55	PX26d	36200830	8727900362008	-	8727900362015	60
12972LLECOCP	H7	LongLife EcoVision	12	55	PX26d	36192630	8727900361926	-	8727900371024	60
12972LLECOS2	H7	LongLife EcoVision	12	55	PX26d	36259628	8727900362596	-	8727900362602	60
12972PRB1	H7	Vision	12	55	PX26d	40607130	8711500406071	-	8711500406088	60
12972PRC1	H7	Vision	12	55	PX26d	40593760	8711500405937	8711500827838	8711500405944	60
12972PRC2	H7	Vision	12	55	PX26d	37432260	8727900374322	8727900374339	8727900374346	60
12972RGTB1	H7	RacingVision GT200	12	55	PX26d	00573130	8719018005731	-	8719018005748	60
12972RGTS2	H7	RacingVision GT200	12	55	PX26d	00577928	8719018005779	-	8719018005786	60
12972VPB1	H7	VisionPlus	12	55	PX26d	39936330	8727900399363	-	8727900399356	60
12972VPC2	H7	VisionPlus	12	55	PX26d	37426160	8727900374261	8727900374278	8727900374285	60
12972VPS2	H7	VisionPlus	12	55	PX26d	39938728	8727900399387	-	8727900399370	60
12972WVUB1	H7	WhiteVision ultra	12	55	PX26d	35493530	8727900354935	-	8727900354928	60
12972WVUSM	H7	WhiteVision ultra	12	55	PX26d	35495928	8727900354959	-	8727900354942	60
12972XVPB1	H7	X-tremeVision Pro150	12	55	PX26d	00555730	8719018005557	-	8719018005564	60
12972XVPS2	H7	X-tremeVision Pro150	12	55	PX26d	00569428	8719018005694	-	8719018005700	60
9004C1	HB1	Standard	12	65/45	P29t	47074430	8711500470744	-	8727900370997	62
9005PRB1	HB3	Vision	12	60	P20d	24724730	8711500247247	-	8711500247254	62
9005PRC1	HB3	Vision	12	60	P20d	24689930	8711500246899	-	8727900370980	62
9005XVPB1	HB3	X-tremeVision Pro150	12	60	P20d	00557128	8719018005571	-	8719018005588	62
9005WVUB1	HB3	WhiteVision ultra	12	60	P20d	00537328	8719018005373	-	8719018005380	62
9006PRB1	HB4	Vision	12	51	P22d	24726130	8711500247261	-	8711500247278	62
9006PRC1	HB4	Vision	12	51	P22d	24687530	8711500246875	-	8727900370973	62
9006XVPB1	HB4	X-tremeVision Pro150	12	51	P22d	00559528	8719018005595	-	8719018005601	62
9006WVUB1	HB4	WhiteVision ultra	12	51	P22d	00539728	8719018005397	-	8719018005403	62
9007C1	HB5	Standard	12	65/55	PX29t	24550230	8711500245502	-	8727900370966	62
9008C1	H13	Standard	12	60/55	P26,4t	87798730	8711500877987	-	8727900370768	61
9012LLC1	HIR2	LongLife EcoVision	12	55	PX22d	35125530	8727900351255	-	8727900370935	62
9012WVUB1	HIR2	WhiteVision ultra	12	55	PX22d	00541028	8719018005410	-	8719018005427	63
9012XVPB1	HIR2	X-tremeVision Pro150	12	55	PX22d	00561828	8719018005618	-	8719018005625	63
9145C1	H10	Standard	12	45	PY20d	52974530	8711559529745	-	8727900370737	61

Halogen two-wheeler lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12008BW	S3	Standard	12	15	P26s	77381430	8711500773814	-	8711500773845	81
12008C1	S3	Standard	12	15	P26s	77394430	8711500773944	-	8711500779335	81
12256B2	W3W	Standard	12	3	W2,1x9,5d	52410830	8711559524108	-	8711559524122	81
12256CP	W3W	Standard	12	3	W2,1x9,5d	48144328	8711500481443	8711500481450	8727900391664	81
12342CTVBW	H4	CityVision moto	12	60/55	P43t-38	39896030	8727900398960	-	8727900398977	80
12342PRBW	H4	Vision moto	12	60/55	P43t-38	49024730	8711500490247	-	8711500490254	80
12342RGTBW	H4	RacingVision moto	12	60/55	P43t-38	02381030	8719018023810	-	8719018023827	80
12342WVUBW	H4	WhiteVision ultra moto	12	60/55	P43t-38	02385830	8719018023858	-	8719018023865	80
12498B2	P21W	Standard	12	21	BA15s	05549130	8711500055491	-	8711559520131	81
12498CP	P21W	Standard	12	21	BA15s	49078073	8711500490780	8711500490797	8711500490803	81
12499B2	P21/5W	Standard	12	21/5	BAY15d	05545330	8711500055453	-	8711559520148	81

Halogen two-wheeler lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12636BW	HS1	Vision moto	12	35/35	PX43t	53035330	8727900530353	-	8727900530360	80
12636C1	HS1	Vision moto	12	35/35	PX43t	51250130	8711559512501	-	8727900370881	80
12636CTVBW	HS1	CityVision moto	12	35/35	PX43t	39894630	8727900398946	-	8727900398953	81
12636WVUBW	HS1	WhiteVision ultra moto	12	35/35	PX43t	02401530	8719018024015	-	8719018024022	81
12728BW	S2	Standard	12	35/35	BA20d	77385230	8711500773852	-	8711500773869	81
12728C1	S2	Standard	12	35/35	BA20d	77359330	8711500773593	-	8711500779342	81
12972CTVBW	H7	CityVision moto	12	55	PX26d	39898430	8727900398984	-	8727900398991	80
12972PRBW	H7	Vision moto	12	55	PX26d	49026130	8711500490261	-	8711500490278	80
12972RGTBW	H7	RacingVision moto	12	55	PX26d	02383430	8719018023834	-	8719018023841	80
12972WVUBW	H7	WhiteVision ultra moto	12	55	PX26d	02387230	8719018023872	-	8719018023889	80

Halogen 24 V lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
13256CP	W3W	Standard	24	3	W2,1x9,5d	48141228	8711500481412	8711500481429	8727900391169	92
13258MDB1	H1	MasterDuty	24	70	P14,5s	82585830	8711500825858	-	8711500825865	88
13258MDC1	H1	MasterDuty	24	70	P14,5s	82577360	8711500825773	8711500828507	8711500825780	88
13258MLC1	H1	MasterLife	24	70	P14,5s	82569830	8711500825698	-	8727900370812	88
13311C1	H2	Standard	24	70	X511	47751430	8711500477514	-	8727900371079	88
13336MDB1	H3	MasterDuty	24	70	PK22s	77459030	8711500774590	-	8711500774613	88
13336MDBVB1	H3	MasterDuty BlueVision	24	70	PK22s	77488030	8711500774880	-	8711500774910	88
13336MDBVS2	H3	MasterDuty BlueVision	24	70	PK22s	77486628	8711500774866	-	8711500774897	88
13336MDC1	H3	MasterDuty	24	70	PK22s	77460660	8711500774606	8711500775313	8711500774637	88
13336MLC1	H3	MasterLife	24	70	PK22s	77462030	8711500774620	-	8711500779403	88
13342MDB1	H4	MasterDuty	24	75/70	P43t-38	82587230	8711500825872	-	8711500825889	88
13342MDBVB1	H4	MasterDuty BlueVision	24	75/70	P43t-38	53281430	8727900532814	-	8727900532821	88
13342MDBVS2	H4	MasterDuty BlueVision	24	75/70	P43t-38	53275328	8727900532753	-	8727900532760	88
13342MDC1	H4	MasterDuty	24	75/70	P43t-38	82579760	8711500825797	8711500828002	8711500825803	88
13342MLC1	H4	MasterLife	24	75/70	P43t-38	82571130	8711500825711	-	8727900371086	88
13401CP	Stop P22	Standard	24	15	BA15s	87826728	8711500878267	8711500878274	8711500790507	90
13402CP	Stop P22	Standard	24	15	BA15d	87836628	8711500878366	8711500878373	8711500790514	90
13445CP	Stop P25	Standard	24	18	BA15s	48443728	8711500484437	8711500484444	8727900390810	90
13496MLCP	PY21W	MasterLife	24	21	BAU15s	69964728	8727900699647	8727900699654	8727900391138	90
13498B2	P21W	Standard	24	21	BA15s	40455830	8711500404558	-	8711500405449	90
13498CP	P21W	Standard	24	21	BA15s	48415473	8711500484154	8711500484161	8711500484178	90
13498MDCP	P21W	MasterDuty	24	21	BA15s	69949473	8727900699494	8727900699500	8727900699517	89
13498MLCP	P21W	MasterLife	24	21	BA15s	69961628	8727900699616	8727900699623	8727900391145	89
13499B2	P21/5W	Standard	24	21/5	BA15d	40456530	8711500404565	-	8711500405371	90
13499CP	P21/5W	Standard	24	21/5	BA15d	48424673	8711500484246	8711500484253	8711500484260	90
13516CP	WBT5	Standard	24	1.2	W2x4,6d	48306573	8711500483065	8711500483072	8711500483089	92
13521CP	WBT5	Standard	24	1	W2x4,6d	48324928	8711500483249	8711500483256	8727900391176	92
13597CP	Bax 8,3s/1,35 grey	Standard	24	1.2	B8,3s/1,35	48384328	8711500483843	8711500483850	8727900390797	93
13598CP	Bax 8,5d/2 grey	Standard	24	1.2	B8,5d/2	48390428	8711500483904	8711500483911	8727900390827	93
13620C1	R2	Standard	24	55/50	P45t-41	40087130	8711500400871	-	8711500779458	89
13807CP	Festoon T15x43	Standard	24	18	SV8,5	48294528	8711500482945	8711500482952	8727900391237	93
13814B2	R10W	Standard	24	10	BA15s	40452730	8711500404527	-	8711559526409	91
13814CP	R10W	Standard	24	10	BA15s	48344773	8711500483447	8711500483454	8711500483461	91
13814MDCP	R10W	MasterDuty	24	10	BA15s	69952428	8727900699524	8727900699531	8727900391121	90
13814MLCP	R10W	MasterLife	24	10	BA15s	69967828	8727900699678	8727900699685	8727900390742	91
13818CP	Festoon T6,2x27	Standard	24	3	SV6	48464228	8711500484642	8711500484659	8727900391251	92
13821B2	R5W	Standard	24	5	BA15s	40453430	8711500404534	-	8711500405425	90
13821CP	R5W	Standard	24	5	BA15s	48338673	8711500483386	8711500483393	8711500483409	90
13821MDCP	R5W	MasterDuty	24	5	BA15s	69955528	8727900699555	8727900699562	8727900390766	90
13821MLCP	R5W	MasterLife	24	5	BA15s	69970828	8727900699708	8727900699715	8727900390773	90
13822CP	R5W	Standard	24	5	BA15d	40904128	8711500409041	8711500878021	8711500790491	90
13829CP	BA7	Standard	24	3	BA7s	52133628	8711559521336	8711500401274	8727900390759	91
13844B2	C5W	Standard	24	5	SV8,5	40463330	8711500404633	-	8711500405388	92
13844CP	C5W	Standard	24	5	SV8,5	48197973	8711500481979	8711500481986	8711500481993	92
13848CP	Festoon T6,2x35	Standard	24	3	SV6	48470328	8711500484703	8711500484710	8727900391268	92
13850CP	Festoon T15x43	Standard	24	15	SV8,5	48288428	8711500482884	8711500482891	8727900391244	93
13854CP	Festoon T10,5x38 10W	Standard	24	10	SV8,5	48251828	8711500482518	8711500482525	8727900391206	92
13864CP	Festoon T10,5x43 5W	Standard	24	5	SV8,5	48233428	8711500482334	8711500482341	8727900391213	93
13866CP	Festoon T10,5x43 10W	Standard	24	10	SV8,5	48245728	8711500482457	8711500482464	8727900391220	93
13910CP	T3W	Standard	24	3	BA9s	21955828	8711500219558	8711500219565	8711500220851	91
13913CP	T2W	Standard	24	2	BA9s	22003528	8711500220035	8711500220042	8711500220844	91
13929B2	T4W	Standard	24	4	BA9s	40454130	8711500404541	-	8711500405432	91

Halogen 24 V lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
13929CP	T4W	Standard	24	4	BA9s	21985573	8711500219855	8711500219862	8711500219879	91
13929MDCP	T4W	MasterDuty	24	4	BA9s	69958628	8727900699586	8727900699593	8727900391039	91
13929MLCP	T4W	MasterLife	24	4	BA9s	69976028	8727900699760	8727900699777	8727900391046	91
13960CP	W2,5W	Standard	24	2.5	W2,1x9,5d	48147428	8711500481474	8711500481481	8727900391275	92
13961B2	W5W	Standard	24	5	W2,1x9,5d	52420730	8711559524207	-	8711559524214	92
13961CP	W5W	Standard	24	5	W2,1x9,5d	48138273	8711500481382	8711500481399	8711559530376	92
13972MDB1	H7	MasterDuty	24	70	PX26d	82589630	8711500825896	-	8711500825902	89
13972MDBVB1	H7	MasterDuty BlueVision	24	70	PX26d	53279130	8727900532791	-	8727900532807	89
13972MDBVS2	H7	MasterDuty BlueVision	24	70	PX26d	53277728	8727900532777	-	8727900532784	89
13972MDC1	H7	MasterDuty	24	70	PX26d	82581060	8711500825810	8711500828514	8711500825827	89
13972MLC1	H7	MasterLife	24	70	PX26d	82573530	8711500825735	-	8727900371147	89
13974CP	WBT5	Standard	24	2	W2x4,6d	48318828	8711500483188	8711500483195	8727900391183	92
24029CP	Bax 8,5d/2 yellow	Standard	24	1.2	B8,5d/2	48402428	8711500484024	8711500484031	8727900391190	93
24032CP	Bax 8,5d brown	Standard	24	1.2	B8,5d	48852728	8711500488527	8711500488534	8727900391077	93
24356CP	H21W	Standard	24	21	BAY9s	87615728	8711500876157	8711500876164	8727900371161	91
24362MDC1	H11	MasterDuty	24	70	PGJ19-2	82583430	8711500825834	-	8727900371055	89
24362MLC1	H11	MasterLife	24	70	PGJ19-2	82575930	8711500825759	-	8727900371062	89

Halogen Kits

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12V Spare kits										
55472EKKM	H1	Easy Kit	12	-	-	69551928	8727900695519	-	8727900695533	96
55473EKKM	H4	Easy Kit	12	-	-	69555728	8727900695557	-	8727900695571	96
55474EKKM	H7	Easy Kit	12	-	-	69558828	8727900695588	-	8727900695601	96
55475EKKM	H1/H7	Easy Kit	12	-	-	69562528	8727900695625	-	8727900695656	96
55717EBKM	H1	Essential Box	12	-	-	70032928	8727900700329	-	8727900700336	97
55718EBKM	H4	Essential Box	12	-	-	70034328	8727900700343	-	8727900700350	97
55719EBKM	H7	Essential Box	12	-	-	70036728	8727900700367	-	8727900700374	97
55720EBKM	H1/H7	Essential Box	12	-	-	70038128	8727900700381	-	8727900700398	97
24V Spare kits										
55554SKMDKM	MiniKit H4	MasterDuty	24	-	-	69586130	8727900695861	-	8727900695885	98
55555SKMDKM	MiniKit H7	MasterDuty	24	-	-	69590830	8727900695908	-	8727900695939	98
55559LKMDKM	MaxiKit H4	MasterDuty	24	-	-	69684494	8727900696844	-	8727900696851	98
55560LKMDKM	MaxiKit H7	MasterDuty	24	-	-	69686894	8727900696868	-	8727900696875	98
55561LKMDKM	MaxiKit H1/H7	MasterDuty	24	-	-	69688294	8727900696882	-	8727900696899	98
Headlight restoration kit										
HRK00XM	-	-	-	-	-	39976931	8727900399769	-	8727900399776	99

Xenon lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12410C1	D5S	Vision	12	25	PK32d-7	36981633	8727900369816	-	8727900369823	110
12410XV+C1	D5S	X-tremeVision gen2	12/24	25	PK32d-7	35392133	8727900353921	-	8719018005090	110
12411C1	D8S	Vision	42	25	PK32d-1	00467333	8719018004673	-	8719018004680	110
42306VIC1	D3R	Vision	42	35	PK32d-6	36483533	8727900364835	-	8727900364842	110
42402VIC1	D4S	Vision	42	35	P32d-5	36485933	8727900364859	-	8727900364866	110
42402XV2C1	D4S	X-tremeVision gen2	42	35	P32d-5	37721733	8727900377217	-	8727900377224	110
42402XV2S1	D4S	X-tremeVision gen2	42	35	P32d-5	37719433	8727900377194	-	8727900377200	110
42403VIC1	D3S	Vision	42	35	PK32d-5	36481133	8727900364811	-	8727900364828	110
42403VIS1	D3S	Vision	42	35	PK32d-5	36495833	8727900364958	-	8727900364965	110
42403WHV2C1	D3S	WhiteVision gen2	42	35	PK32d-5	37737833	8727900377378	-	8727900377385	110
42403WHV2S1	D3S	WhiteVision gen2	42	35	PK32d-5	37735433	8727900377354	-	8727900377361	110
42403XV2C1	D3S	X-tremeVision gen2	42	35	PK32d-5	37717033	8727900377170	-	8727900377187	110
42403XV2S1	D3S	X-tremeVision gen2	42	35	PK32d-5	37713233	8727900377132	-	8727900377149	110
42406VIC1	D4R	Vision	42	35	P32d-6	36487333	8727900364873	-	8727900364880	110
85122SYC1	D2S	LongerLife	85	35	P32d-2	37518333	8727900375183	-	8727900375190	109
Ordering codes for Germany, Austria, Switzerland, Netherlands										
85122SYC1	D2S	LongerLife	85	35	P32d-2	37244133	8727900372441	-	8727900372458	109
Ordering codes for Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom										
85122SYC1	D2S	LongerLife	85	35	P32d-2	37524433	8727900375244	-	8727900375251	109
Ordering codes for Central Europe (Poland, Romania, Czech Republic) and other East European countries										
85122SYS1	D2S	LongerLife	85	35	P32d-2	37254033	8727900372540	-	8727900372557	109
Ordering codes for Germany, Austria, Switzerland, Netherlands, Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom										
85122VIC1	D2S	Vision	85	35	P32d-2	36477433	8727900364774	-	8727900364781	108
85122VIS1	D2S	Vision	85	35	P32d-2	36491033	8727900364910	-	8727900364927	108
85122WHV2C1	D2S	WhiteVision gen2	85	35	P32d-2	37729333	8727900377293	-	8727900377309	109
85122WHV2S1	D2S	WhiteVision gen2	85	35	P32d-2	37727933	8727900377279	-	8727900377286	109

Xenon lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
85122XV2C1	D2S	X-tremeVision gen2	85	35	P32d-2	37707133	8727900377071	-	8727900377088	108
85122XV2S1	D2S	X-tremeVision gen2	85	35	P32d-2	37703333	8727900377033	-	8727900377040	108
85126SYC1	D2R	LongerLife	85	35	P32d-3	37520633	8727900375206	-	8727900375213	109
Ordering codes for Germany, Austria, Switzerland, Netherlands										
85126SYC1	D2R	LongerLife	85	35	P32d-3	37252633	8727900372526	-	8727900372533	109
Ordering codes for Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom										
85126SYC1	D2R	LongerLife	85	35	P32d-3	37526833	8727900375268	-	8727900375275	109
Ordering codes for Central Europe (Poland, Romania, Czech Republic) and other East European countries										
85126SYS1	D2R	LongerLife	85	35	P32d-3	37248933	8727900372489	-	8727900372496	109
Ordering codes for Germany, Austria, Switzerland, Netherlands										
85126VIC1	D2R	Vision	85	35	P32d-3	36479833	8727900364798	-	8727900364804	109
85126VIS1	D2R	Vision	85	35	P32d-3	36493433	8727900364934	-	8727900364941	109
85126WHV2C1	D2R	WhiteVision gen2	85	35	P32d-3	37733033	8727900377330	-	8727900377347	109
85126WHV2S1	D2R	WhiteVision gen2	85	35	P32d-3	37731633	8727900377316	-	8727900377323	109
85126XV2C1	D2R	X-tremeVision gen2	85	35	P32d-3	37711833	8727900377118	-	8727900377125	109
85126XV2S1	D2R	X-tremeVision gen2	85	35	P32d-3	37709533	8727900377095	-	8727900377101	109
85409VIC1	D1R	Vision	85	35	PK32d-3	36475033	8727900364750	-	8727900364767	108
85415SYC1	D1S	LongerLife	85	35	PK32d-2	37516933	8727900375169	-	8727900375176	108
Ordering codes for Germany, Austria, Switzerland, Netherlands										
85415SYC1	D1S	LongerLife	85	35	PK32d-2	37250233	8727900372502	-	8727900372519	108
Ordering codes for Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom										
85415SYC1	D1S	LongerLife	85	35	PK32d-2	37522033	8727900375220	-	8727900375237	108
Ordering codes for Central Europe (Poland, Romania, Czech Republic) and other East European countries										
85415SYS1	D1S	LongerLife	85	35	PK32d-2	37246533	8727900372465	-	8727900372472	108
Ordering codes for Germany, Austria, Switzerland, Netherlands, Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom										
85415VIC1	D1S	Vision	85	35	PK32d-2	36473633	8727900364736	-	8727900364743	108
85415VIS1	D1S	Vision	85	35	PK32d-2	36489733	8727900364897	-	8727900364903	108
85415WHV2C1	D1S	WhiteVision gen2	85	35	PK32d-2	37725533	8727900377255	-	8727900377262	108
85415WHV2S1	D1S	WhiteVision gen2	85	35	PK32d-2	36072133	8727900360721	-	8727900377248	108
85415XV2C1	D1S	X-tremeVision gen2	85	35	PK32d-2	37701933	8727900377019	-	8727900377026	108
85415XV2S1	D1S	X-tremeVision gen2	85	35	PK32d-2	37697533	8727900376975	-	8727900376982	108



2023 © Lumileds Holding B.V. All rights reserved.

The Philips trademark and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V. Specifications are subject to change without notice.

[Philips.com/Automotive](https://www.philips.com/automotive)