

A detailed photograph of a male mechanic in a dark grey uniform and white gloves working on the underside of a red car. He is using a long-handled tool to adjust a component near the rear wheel. A bright green Philips Xperion LED work light is attached to the tool, illuminating the work area. The car is elevated on a lift, and its blue diamond-plate underbody is visible. In the background, another car is partially visible.

**PHILIPS**

Xperion

Professional work lights




2023-2024

Designed  
with **you**  
in mind




# LED work light features

## Light module




Boost light

Maximum light output (in lumen)




Eco/dimmed light

Light output during power save mode (in lumen)




Spotlight

Additional small light to reach confined spaces (in lumen)




Operating time

Operating time during one charging cycle




Beam angle

Angle of the main light beam




Pivoting light module

Flexibility of the work light thanks to pivoting light module




CRI

High Color Rendering Index (CRI) reveals the true colors of an object, as if seen with natural light



UV light


UV light helps identify leakages



Zoom light


Change the focus of the light beam by simply turning a knob

## Smart, ergonomic design




Grip

Robust ABS\* and soft rubber body to hold the work light securely




Telescopic mount

Integrated telescopic hooks extendable on both sides




Motion detector

Switch the light on and off by moving your hand in front of the sensor




Find My Device

The remote control accessory helps retrieve lost devices up to 10 meters



Sliding light

Slide the light module along the mount to the area you want to illuminate



Presence sensor

Presence sensor that senses human activity within a 2.5-meter radius

## Robustness and durability



Ingress protection

Degree of protection against intrusion from solid objects, dust, accidental contact and water



Shock protection


Degree of protection against external impacts



Grease resistance


Highly resistant to grease and workshop solvents

## Power options and recharging




Charging time

Time needed to fully recharge the integrated battery



Micro USB

Battery rechargeable via a USB Type-C or Micro USB



Charging station

Compatibility with the Multi Dock Station\*\* accessory for cordless charging

\*Acrylonitrile-butadiene-styrene copolymer  
\*\*Accessories to buy separately






# Xperion 6000





Discover our  
**Xperion 6000**  
LED work lights

\* Acrylonitrile-butadiene-styrene copolymer  
\*\* Accessories to buy separately, except for the Philips Xperion 6000 UV Pillar which already includes the Find My Device function


















UV Pillar	Pillar
 reddot winner 2022 iF DESIGN AWARD 2022	 reddot winner 2022 iF DESIGN AWARD 2022
	
Boost light 500 lm Up to 4.5 h	Boost light 500 lm Up to 4.5 h
Eco light 250 lm Up to 10 h	Eco light 250 lm Up to 10 h
Spotlight 180 lm Up to 12 h	Spotlight 180 lm Up to 12 h
Light angle/ flexibility 100° 90° rotatable	Light angle/ flexibility 100° 90° rotatable
Special light features UV light Excellent color rendition	Special light features
Fixture 360° rotatable hook 1 magnet	Fixture 360° rotatable hook 1 magnet
Grip/grease resistance ABS*, Rubber Garage proof	Grip/grease resistance ABS* Garage proof
Robustness IP65 IK07	Robustness IP65 IK07
Lithium battery power supply <4.5 h USB Type-C	Lithium battery power supply <4.5 h USB Type-C
Additional accessories Find My Device Multi Dock Station**	Additional accessories Find My Device** Multi Dock Station**
Philips Order Entry X60UVPX1	Philips Order Entry X60PILLX1

Flood Audio	Flood	Flood Mini	Pocket	Slim	Line
   	  	  	  	  	  
<div>Boost light</div> <div>1000 lm</div> <div>Up to 3 h</div>	<div>Boost light</div> <div>1000 lm</div> <div>Up to 3 h</div>	<div>Boost light</div> <div>500 lm</div> <div>Up to 3 h</div>	<div>Boost light</div> <div>300 lm</div> <div>Up to 3.5 h</div>	<div>Boost light</div> <div>500 lm</div> <div>Up to 4.5 h</div>	<div>Boost light</div> <div>300 lm</div> <div>Up to 4.5 h</div>
<div>Eco light</div> <div>100 lm</div> <div>Up to 22 h</div>	<div>Eco light</div> <div>100 lm</div> <div>Up to 22 h</div>	<div>Eco light</div> <div>100 lm</div> <div>Up to 9 h</div>	<div>Eco light</div> <div>150 lm</div> <div>Up to 7 h</div>	<div>Eco light</div> <div>250 lm</div> <div>Up to 7 h</div>	<div>Eco light</div> <div>150 lm</div> <div>Up to 8 h</div>
<div>Spotlight</div> <div>250 lm</div> <div>Up to 9 h</div>	<div>Spotlight</div> <div>250 lm</div> <div>Up to 9 h</div>	<div>Spotlight</div> <div>250 lm</div> <div>Up to 5 h</div>	<div>Spotlight</div> <div>100 lm</div> <div>Up to 10 h</div>	<div>Spotlight</div> <div>150 lm</div> <div>Up to 9 h</div>	<div>Spotlight</div> <div>120 lm</div> <div>Up to 9 h</div>
<div>Light angle/light function</div> <div>100°</div> <div>Light setting memory</div>	<div>Light angle/light function</div> <div>100°</div> <div>Light setting memory</div>	<div>Light angle/light function</div> <div>100°</div> <div>Light setting memory</div>	<div>Light angle</div> <div>110°</div>	<div>Light angle/flexibility</div> <div>100°</div> <div>270° rotatable</div>	<div>Light angle</div> <div>110°</div>
<div>Special features</div> <div>Zoom light</div> <div>Motion detection</div>	<div>Special features</div> <div>Zoom light</div> <div>Motion detection</div>	<div>Special light features</div> <div>Zoom light</div> <div>Compact design</div>	<div>Special light features</div> <div>25 cm flexible hose, rotatable in all directions</div>	<div>Special light features</div> <div>180° foldable</div>	
<div>Fixture</div> <div>180° rotatable handle</div> <div>Magnetic handle</div>	<div>Fixture</div> <div>180° rotatable handle</div> <div>Magnetic handle</div>	<div>Fixture</div> <div>180° rotatable handle</div> <div>Magnetic handle</div>	<div>Fixture</div> <div>360° rotatable hook</div> <div>1 magnet</div>	<div>Fixture</div> <div>360° rotatable hook</div> <div>1 magnet</div>	<div>Fixture</div> <div>360° rotatable hook</div> <div>1 magnet</div>
<div>Grip/grease resistance</div> <div>ABS*</div> <div>Garage proof</div>	<div>Grip/grease resistance</div> <div>ABS*</div> <div>Garage proof</div>	<div>Grip/grease resistance</div> <div>ABS*</div> <div>Garage proof</div>	<div>Grip/grease resistance</div> <div>ABS*, Rubber</div> <div>Garage proof</div>	<div>Grip/grease resistance</div> <div>ABS*, Rubber</div> <div>Garage proof</div>	<div>Grip/grease resistance</div> <div>ABS*</div> <div>Garage proof</div>
<div>Robustness</div> <div>IP55</div> <div>IK07</div>	<div>Robustness</div> <div>IP65</div> <div>IK07</div>	<div>Robustness</div> <div>IP65</div> <div>IK07</div>	<div>Robustness</div> <div>IP65</div> <div>IK07</div>	<div>Robustness</div> <div>IP54</div> <div>IK07</div>	<div>Robustness</div> <div>IP65</div> <div>IK07</div>
<div>Lithium battery power supply</div> <div>&lt;5 h</div> <div>USB Type-C</div>	<div>Lithium battery power supply</div> <div>&lt;5 h</div> <div>USB Type-C</div>	<div>Lithium battery power supply</div> <div>&lt;3.5 h</div> <div>USB Type-C</div>	<div>Lithium battery power supply</div> <div>&lt;3.5 h</div> <div>USB Type-C</div>	<div>Lithium battery power supply</div> <div>&lt;4 h</div> <div>USB Type-C</div>	<div>Lithium battery power supply</div> <div>&lt;3.5 h</div> <div>USB Type-C</div>
<div>Charging features</div> <div>Multi Dock Station**</div> <div>USB power bank</div>	<div>Charging features</div> <div>Multi Dock Station**</div> <div>USB power bank</div>	<div>Additional accessories</div> <div>Find My Device**</div> <div>Multi Dock Station**</div>	<div>Additional accessories</div> <div>Multi Dock Station**</div>	<div>Additional accessories</div> <div>Find My Device**</div> <div>Multi Dock Station**</div>	
<div>Philips Order Entry</div> <div>X60FLAUX1</div>	<div>Philips Order Entry</div> <div>X60FLX1</div>	<div>Philips Order Entry</div> <div>X60FLMIX1</div>	<div>Philips Order Entry</div> <div>X60POCKX1</div>	<div>Philips Order Entry</div> <div>X60SLIMX1</div>	<div>Philips Order Entry</div> <div>X60LINEX1</div>


















\* Acrylonitrile-butadiene-styrene copolymer \*\* Accessories to buy separately

\* Acrylonitrile-butadiene-styrene copolymer \*\* Accessories to buy separately



















Penlight		
		
		
Boost light	 <b>200 lm</b>	 Up to <b>3 h</b>
Eco light	 <b>100 lm</b>	 Up to <b>5.5 h</b>
Spotlight	 <b>120 lm</b>	 Up to <b>3.5 h</b>
Light angle	 <b>80°</b>	
Special features	 Rotating magnetic clip	
Fixture	 <b>2 magnets</b>	
Grip/grease resistance	 ABS*	 Garage proof
Robustness	 <b>IP65</b>	 <b>IK07</b>
Lithium battery power supply	 <b>&lt;1.6 h</b>	 USB Type-C

Philips Order Entry
X60PENX1

Headlight		
		
		
Boost light	 <b>300 lm</b>	 Up to <b>2.5 h</b>
Eco light	 <b>150 lm</b>	 Up to <b>4 h</b>
Spotlight	 <b>120 lm</b>	 Up to <b>4.5 h</b>
Light angle/ flexibility	 <b>220° panoramic</b>	 <b>60° rotatable</b>
Special features	 Motion detection	
Fixture	 Adjustable headband	
Grip/grease resistance	 Garage proof	
Robustness	 <b>IP65</b>	 <b>IK07</b>
Lithium battery power supply	 <b>&lt;2.5 h</b>	 USB Type-C

Philips Order Entry
X60HEADX1

Under-Bonnet Light		
		
		
Boost light	 <b>1200 lm</b>	 Up to <b>3 h</b>
Eco light	 <b>120 lm</b>	 Up to <b>20 h</b>
Light angle/ feature	 <b>110°</b>	<b>5800 K</b>
Special features	 Presence sensor	 Sliding light
Fixture	 Telescopic hooks	
Grip/grease resistance	 Rubber	 Garage proof
Robustness	 <b>IP54</b>	 <b>IK07</b>
Lithium battery power supply	 <b>&lt;3.5 h</b>	 USB Type-C

Philips Order Entry
X60BONNX1

# Xperion 6000 Penlight

Compact LED worker’s companion


Designed with a broad beam of 200 lumens, the compact, ergonomic Philips Xperion 6000 Penlight is ideal for all inspection work. Our Penlight is equipped with a 120-lm pointer to direct the light where needed.



3 year warranty\*



Smart rotatable clip, strong magnets and ergonomic body



Resistant to impacts, water and solvents



\*To be claimed on Philips.com/LEDworklights-warranty

## Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Penlight X60PEN	8719018021694	8719018021700	02169431	X60PENX1	6

# Xperion 6000 Headlight

Dual-mode, motion-sensing LED light

The Philips Xperion 6000 Headlight projects a 300-lumen panoramic light beam in front of you. Its rotating 120-lumen spotlight allows you to see every detail. An additional motion-detection function makes it a versatile, hands-free tool.



3 year warranty\*

Premium LED light with multiple outputs

300 lm  
1500 lm  
120 lm

220° panoramic LED light beam

220°

Motion-detection mode for hands-free use

Anti-slip elastic headband. Comfortable and easy to adjust

Fully charged within 2.5 hours, via USB-C and battery life indicator

<2.5 h

Resistant to impacts, water and solvents

IP65  
IK07

\*To be claimed on Philips.com/LEDworklights-warranty

## Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Headlight X60HEAD	8719018021731	8719018021748	02173131	X60HEADX1	6

# Xperion 6000 Under-Bonnet Light

Extendable, powerful LED light

The Philips Xperion 6000 Under-Bonnet LED Light offers a seamlessly dimmable beam of up to 1200 lumens, 360° rotatability, and a telescopic mount extending up to 2.08 meters. It is for working on cars, vans, and trucks.



3 year warranty\*

Seamless, premium light dimming with multiple outputs

1200 lm  
120 lm

Telescopic, extendable mount up to 2.08 meters

Sliding light module along the mount

Presence sensor of human activity within a 2.5-meter radius

360° rotatable hooks covered with soft rubber

Fully charged within 3.5 hours, via USB-C and battery life indicator

<3,5 h

Resistant to impacts, water and solvents

IP54  
IK07

\*To be claimed on Philips.com/LEDworklights-warranty

## Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Under-Bonnet Light X60BONN	8719018021717	8719018021724	02171731	X60BONNX1	6



# Xperion 6000 UV Pillar

Advanced lighting performance that lasts

Our premium work light, the Philips Xperion 6000 UV Pillar, is a multi-purpose work light with several powerful light sources, UV light, high CRI and long-lasting battery. Locate your work light in seconds with the Find My Device function.



Premium LED light with multiple outputs

500 lm  
2500 lm  
180 lm

Precision light with ergonomic design and wide beam angle

90°  
100°

High CRI 95 and unique UV light

95 CRI  
UV



3 year warranty\*\*

Strong magnet and 360° rotatable hook

Compatible with the Find My Device accessory (included) and the Multi Dock Station\*

Resistant to impacts, water and solvents

IP65  
IK07

\*Accessories to buy separately  
\*\*To be claimed on Philips.com/LEDworklights-warranty

## Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 UV Pillar X60UVPI	8719018014719	8719018014726	01471931	X60UVPIX1	6

# Xperion 6000 Pillar

Work all day on a single charge

The Philips Xperion 6000 Pillar LED work light lasts all day on a single charge. Its bright 250 and 500 lm main light and inbuilt 180 lm spotlight will meet multiple needs. Foldable for easy carrying and adjustable lighting angles.



Premium LED light with multiple outputs

500 lm  
2500 lm  
180 lm

Precision light with ergonomic design and wide beam angle

90°  
100°

Long operating time in different light modes

<12 h



3 year warranty\*\*

Strong magnet and 360° rotatable hook

Compatible with the Find My Device accessory and the Multi Dock Station\*

Resistant to impacts, water and solvents

IP65  
IK07

\*Accessories to buy separately  
\*\*To be claimed on Philips.com/LEDworklights-warranty

## Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Pillar X60PILL	8719018014696	8719018014702	01469631	X60PILLX1	6



# Xperion 6000 Flood Audio

Audio LED projector light

With its 1000-lm flood light, 250-lm spot and variable beam, the Philips Xperion 6000 Flood audio-enabled projector gets the job done. The smart-zoom knob and motion sensor simplify control, while Bluetooth speakers are music to the ears.



3 year warranty\*

Versatile attachments with integrated magnets

Premium LED light with multiple outputs and light setting memory

Bluetooth audio speakers and power bank function

Fully charged within 5 hours via USB-C and battery life LCD display

Motion detection function

Glove proof smart-zoom knob for easy light control

Resistant to impacts, water and solvents

\*To be claimed on Philips.com/LEDworklights-warranty

## Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Flood Audio X60FLAU	8719018019110	8719018019127	01911031	X60FLAUX1	6

# Xperion 6000 Flood

Multipurpose LED projector light

With its 1000-lm flood light and variable beam, the Philips Xperion 6000 Flood multipurpose projector gets the job done. The smart-zoom knob and motion sensor simplify control, while resistance to impacts and water guarantees durability.



3 year warranty\*

Premium LED light with multiple outputs and light setting memory

Versatile attachments with integrated magnets

Fully charged within 5 hours via USB-C and battery life LCD display

Motion detection function

Glove proof smart-zoom knob for easy light control

Resistant to impacts, water and solvents

\*To be claimed on Philips.com/LEDworklights-warranty

## Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Flood X60FL	8719018019097	8719018019103	01909731	X60FLX1	6



# Xperion 6000 Flood Mini

Compact LED projector light

With its 500-lm flood light and variable beam, the Philips Xperion 6000 Flood compact projector gets the job done. The smart-zoom knob simplifies control, while resistance to impacts and water guarantees durability.



3 year warranty\*

Premium LED light with multiple outputs

100 lm 500 lm 250 lm

Versatile attachments with integrated magnets

Fully charged within 3.5 hours via USB-C and battery life indicator

<3.5 h

Compact and light to follow you everywhere

Glove proof smart-zoom knob for easy light control

Resistant to impacts, water and solvents

IP65 IK07

\*To be claimed on Philips.com/LEDworklights-warranty

## Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Flood X60FLMI	8719018019134	8719018019141	01913431	X60FLMIX1	6

# Xperion 6000 Pocket

The compact but powerful light

The compact, powerful Philips Xperion 6000 Pocket is perfect for confined spaces with an ultra-flexible 100 lm, 25 cm hose spotlight. Its wide-beam light up to 300 lm in Boost mode gives you the bright light you need.



Premium LED light with multiple outputs

300 lm 150 lm 100 lm

Precision light with flexible hose spot and wide beam angle

110°

Long operating time in different light modes

3 year warranty\*\*

## Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Pocket X60POCK	8719018014658	8719018014665	01465831	X60POCKX1	6

Strong magnet and 360° rotatable hook



Compatible with the Multi Dock Station\*



Resistant to impacts, water and solvents



\*\*To be claimed on Philips.com/LEDworklights-warranty

# Xperion 6000 Slim

Perfect for narrow spaces

The versatile Philips Xperion 6000 Slim is ideal for narrow spaces. Featuring 250 lm in Eco and 500 lm in Boost mode, its unique 270° rotating light module helps you direct the powerful beam where you need it.



Premium LED light with multiple outputs

500 lm  
250 lm  
150 lm

Unique 270° rotating light module and wide beam angle

270°  
100°

Long operating time in different light modes

<9 h

3 year warranty\*\*

Strong magnet and 360° rotatable hook

360°

Compatible with the Find My Device accessory and the Multi Dock Station\*

Find My Device  
Multi Dock Station

Resistant to impacts, water and solvents

IP54  
IK07

\*Accessories to buy separately  
\*\*To be claimed on Philips.com/LEDworklights-warranty

## Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Slim X60SLIM	8719018014672	8719018014689	01467231	X60SLIMX1	6

# Xperion 6000 Line

Work on larger areas

Designed with a 110° broad beam of 150 lm in Eco and 300 lm in Boost mode, the Philips Xperion 6000 Line is ideal for lighting up larger areas. It is equipped with a 120 lm spotlight beam to direct the light where it is needed.



Premium LED light with multiple outputs

300 lm  
150 lm  
120 lm

Precision light with ergonomic design and wide beam angle

110°

Long operating time in different light modes

<9 h

3 year warranty\*

Strong magnet and 360° rotatable hook

360°

Fully charged within 3,5 hours via USB-C

<3,5 h  
USB-C

Resistant to impacts, water and solvents

IP65  
IK07

\*To be claimed on Philips.com/LEDworklights-warranty

## Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Line X60LINE	8719018014733	8719018014740	01473331	X60LINEX1	6



# Multi Dock Station

Docking station for charging multiple devices

The Philips Multi Dock Station is a cordless accessory for the Xperion LED work lights. Placed on a table, it can cordlessly charge two devices at a time or simply act as a storage point.

- LED indicator to show charging status
- Dedicated space for the Find My Device remote control
- Compatible with Philips Xperion 6000 UV Pillar, Pillar, Pocket, Slim, Flood Audio, Flood and Flood Mini.



### Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Multi Dock Station ACCMUDO	8719018014757	8719018014764	01475731	ACCMUDOX1	6

# Find My Device

A handy way to find misplaced devices

With the Philips Find My Device accessory, you can use the remote control to trigger an audible buzzer and a flashing light, to find lost Philips Xperion 6000 devices. It works up to 10 meters.

- Insert the plug-and-play chip into the work light's body
- Use remote control to locate your misplaced Philips Xperion 6000 UV Pillar (included), Pillar, Slim or Flood Mini (to buy separately)
- Carry the remote control on your keychain or place it on the Philips Multi Dock Station



### Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Find My Device ACCFIMD	8719018014771	8719018014788	01477131	ACCFIMDX1	6







Xperion 3000



Discover our  
**Xperion 3000**  
LED work lights

Pillar	Slim
	
	
<div>Boost light</div> <div>500 lm</div> <div>Up to 2.5 h</div>	<div>Boost light</div> <div>500 lm</div> <div>Up to 3 h</div>
<div>Eco light</div> <div>200 lm</div> <div>Up to 8 h</div>	<div>Eco light</div> <div>200 lm</div> <div>Up to 8 h</div>
<div>Spotlight</div> <div>120 lm</div> <div>Up to 8.5 h</div>	<div>Spotlight</div> <div>150 lm</div> <div>Up to 8 h</div>
<div>Light angle</div> <div>Main light 90°</div> <div>Spot 30°</div>	<div>Light angle</div> <div>Main light 90°</div> <div>Spot 30°</div>
<div>Flexibility</div> <div>180° foldable stand</div> <div>90° tiltable light module</div>	<div>Flexibility</div> <div>270° tiltable light module</div>
<div>Special features</div> <div>x2</div> <div>Dual hooks</div>	
<div>Fixture</div> <div>360° rotatable hooks</div> <div>3 magnets</div>	<div>Fixture</div> <div>180° rotatable hook</div> <div>1 magnet</div>
<div>Grip/grease resistance</div> <div>Nylon, PC</div> <div>Garage proof</div>	<div>Grip/grease resistance</div> <div>PC, Rubber</div> <div>Garage proof</div>
<div>Robustness</div> <div>IP20</div> <div>IK08</div>	<div>Robustness</div> <div>IP20</div> <div>IK07</div>
<div>Lithium battery power supply</div> <div>&lt;3.5 h</div> <div>USB type-C</div>	<div>Lithium battery power supply</div> <div>&lt;3.5 h</div> <div>USB type-C</div>
<div>Order Entry</div> <div>X30PILLX1</div>	<div>Order Entry</div> <div>X30SLIMX1</div>

\* Acrylonitrile-butadiene-styrene copolymer



Zoom		
Boost light		
	1000 lm	Up to 1.5 h
Eco light		
	600/200 lm	Up to 3/9 h
Spotlight		
	1000 lm	Up to 1.5 h
Light angle		
Main light 120°		
Flexibility		
	180° rotatable light module	
Special features		
	Zoom 20° – 130°	
Fixture		
	1 magnet	
Grip/grease resistance		
	Nylon, Rubber	Garage proof
Robustness		
	IP54	IK07
Lithium battery power supply		
	<3.5 h	USB type-C
Order Entry		
X30ZOOMX1		

Line		
Boost light		
	300 lm	Up to 4 h
Eco light		
	150 lm	Up to 7.5 h
Light angle		
Main light 120°		
Flexibility		
Fixture		
	360° rotatable hook	1 magnet
Grip/grease resistance		
	Robust ABS*	Garage proof
Robustness		
	IP54	IK07
Lithium battery power supply		
	<3 h	USB type-C
Order Entry		
X30LINEX1		

Pocket		
Boost light		
	300 lm	Up to 3 h
Eco light		
	100 lm	Up to 10 h
Light angle		
Main light 90°		
Flexibility		
	180° foldable stand	
Fixture		
	360° rotatable hook	1 magnet
Grip/grease resistance		
	Nylon, PC	Garage proof
Robustness		
	IP20	IK08
Lithium battery power supply		
	<3.5 h	USB type-C
Order Entry		
X30POCKX1		

Headlamp		
Boost light		
	300 lm	Up to 2 h
Eco light		
	100 lm	Up to 6 h
Spotlight		
	200 lm	Up to 3 h
Light angle		
Main light 120°		
Flexibility		
	60° tiltable light module	
Special features		
	Dual lights: spot + flood	
Fixture		
	Soft anti-slip band	
Grip/grease resistance		
	PC, Rubber	Garage proof
Robustness		
	IP65	IK07
Lithium battery power supply		
	<2.5 h	USB type-C
Order Entry		
X30HEADX1		



Flood		
Boost light		
	1000 lm	Up to 3 h
Eco light		
	500 lm	Up to 6 h
Spotlight		
	300 lm	Up to 8 h
Light angle		
Main light 110° Spot 30°		
Flexibility		
	180° foldable stand	
Special features		
	Dual lights: spot + flood	Power bank function
Fixture		
	180° rotatable hook	Magnetic handle
Grip/grease resistance		
	Nylon, Rubber	Garage proof
Robustness		
	IP65	IK08
Lithium battery power supply		
	<5.5 h	USB type-C
Order Entry		
X30FLX1		














Flood mini		
Boost light		
	500 lm	Up to 3 h
Eco light		
	200 lm	Up to 8 h
Spotlight		
	300 lm	Up to 5 h
Light angle		
Main light 110° Spot 30°		
Flexibility		
	180° foldable stand	
Special features		
	Dual lights: spot + flood	
Fixture		
	180° foldable stand	Magnetic handle
Grip/grease resistance		
	Nylon, Rubber	Garage proof
Robustness		
	IP65	IK08
Lithium battery power supply		
	<3.5 h	USB type-C
Order Entry		
X30FLMIX1		

\* Acrylonitrile-butadiene-styrene copolymer



Penlight
















Boost light	 100 lm	 Up to 4 h
Spotlight	 50 lm	 Up to 6 h
Light angle	 Main light 80°	 Spot 30°
Fixture	 Clip	 1 magnet
Grip	 Robust ABS*	
Robustness	 IP20	 IK06
Lithium battery power supply	 <2.2 h	 USB type-C

Order Entry

X30PENX1


Pen eco



Boost light	 90 lm	 Up to 6.5 h
Spotlight	 10 lm	 Up to 10 h
Light angle	 Main light 40°	 Spot 30°
Fixture	 Clip	
Grip	 Robust ABS*	
Robustness	 IP20	 IK07
Power supply	 3x AAA incl.	

Order Entry

X30PECOB1, X30PECOX1






# Xperion 3000 Pillar

Bright LED hand lamp

With its powerful bright light, non-slip grip, lightweight design and versatility, the Philips Xperion 3000 Pillar is an excellent cordless LED work lamp for everyday use. There's even a handy spotlight to help you see in confined spaces.




Bright, comfortable work light



500 lm


200 lm

Handy spotlight



120 lm

Long operating time in different light modes



8.5 h



Three magnets and two 360° rotatable hooks for hands-free use



x2

x3

Flexible adjustment of the lighting module



90°

180°

Robust, shock-resistant housing



IP20

IK08

## Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Pillar X30PILL	8719018024961	8719018024978	02496131	X30PILLX1	6


# Xperion 3000 Slim

Slim, foldable LED hand light

The versatile, ultra-thin Philips Xperion 3000 Slim is ideal for lighting narrow spaces. Tackle any workshop task, from brief inspections to maintenance and repair work, for a full day without interruption.




Bright, comfortable work light



500 lm


200 lm

Handy spotlight



150 lm


Long operating time in different light modes



<8 h



Strong magnet and 360° rotatable hook



x1

x2

Ultra-slim, 270° pivoting design to light up narrow spaces



270°

Robust, shock-resistant housing



IP20

IK07

## Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Slim X30SLIM	8719018024985	8719018024992	02498531	X30SLIMX1	6

# Xperion 3000 Zoom

Powerful LED zoom light

With its powerful bright light and non-slip grip, the Philips Xperion 3000 Zoom is an excellent versatile LED work lamp. Its zoom lens allows you to adjust your light from wide flood to focused brightness easily.



Zoom from a 130° to a 20° light angle

**ZOOM**

1000 lm

600/200 lm

Charged via USB-C and battery life indicator

USB-C

<3.5 h

Long operating time in different light modes

<9 h



Powerful magnet for hands-free use

Magnet

Flexible adjustment of the lighting module

180°

Robust, shock-resistant housing

IP54

IK07

## Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Zoom X30ZOOM	8719018025005	8719018025012	02500531	X30ZOOMX1	6

# Xperion 3000 Line

Cordless, slim professional LED lamp

The Philips Xperion 3000 Line LED hand light is ideal for quick inspection jobs and longer repairs. Its 120°-wide light beam eliminates shadows, while a 360° rotating hook and strong magnet allow hands-free working.



Bright, comfortable work light

300 lm

150 lm

Charged via USB-C

USB-C

<3 h

Long operating time in different light modes

<7.5 h



Strong magnet and 360° rotatable hook

Magnet

360°

Wide beam angle

120°

Robust, shock-resistant housing

IP54

IK07

## Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Line X30LINE	8719018024947	8719018024954	02494731	X30LINEX1	6




# Xperion 3000 Pocket

Small, handy LED pocket lamp

The Philips Xperion 3000 Pocket LED lamp is a small, rechargeable work light that slips easily into your pocket. It's perfect for quick inspection jobs and everyday use.



Pocket-sized, bright, comfortable work light




300 lm

100 lm

Charged via USB-C




Long operating time in different light modes



Magnet and 360° rotatable hook for hands-free use



Flexible adjustment of the lighting module



Robust, shock-resistant housing



## Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Pocket X30POCK	8719018024923	8719018024930	02492331	X30POCKX1	6

# Xperion 3000 Headlamp

Dual-mode LED headlight

The lightweight Philips Xperion 3000 Headlight provides bright white light wherever you need it. Two preset modes of up to 300 lumens and a comfortable headband make it a versatile, hands-free tool for everyday use.




Bright, comfortable work light with wide beam angle




300 lm

100 lm

Anti-slip elastic headband. Comfortable and easy to adjust



Handy spotlight



Flexible adjustment of the lighting module



Charged via USB-C



Robust, shock-resistant housing



## Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Headlight X30HEAD	8719018024909	8719018024916	02490931	X30HEADX1	6



# Xperion 3000 Flood

Portable LED flood light

Small but powerful, versatile yet robust, the Philips Xperion 3000 Flood LED light provides the bright white light you need to illuminate large dark areas. Enjoy up to six hours of continuous use before charging the battery.



Bright, comfortable work light with Boost, Eco and spot settings

1000 lm 500 lm 300 lm

Long operating time in different light modes

<8 h

Charged via USB-C

<5.5 h

Tiltable magnetic handle and 360° hook for hands-free use

180°

Powerbank function with USB charging port

180°

Robust, shock-resistant housing

IP65 IK08

## Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Flood X30FL	8719018025043	8719018025050	02504331	X30FLX1	6

# Xperion 3000 Flood mini

Compact LED flood light

Compact and versatile, the Philips Xperion 3000 Flood mini rechargeable LED light provides the bright white light you need for everyday use. Enjoy up to eight hours of continuous use before charging the battery.



Bright, comfortable work light with Boost, Eco and spot settings

500 lm 200 lm 300 lm

Long operating time in different light modes

<8 h

Charged via USB-C

<3.5 h

Tiltable magnetic handle and 360° hook for hands-free use

180°

Compact and light to follow you everywhere

180°

Robust, shock-resistant housing

IP65 IK08

## Ordering information



Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Flood Mini X30FLMI	8719018025029	8719018025036	02502931	X30FLMIX1	6



# Xperion 3000 Penlight

Portable LED inspection tool





Compact and ergonomic, our Philips Xperion 3000 Penlight is ideal for quick inspection jobs. Featuring a natural white light, it illuminates what's in front of you and fits easily into narrow spaces.



# Xperion 3000 Pen eco

Compact worker's companion

The ultra-compact Philips Xperion 3000 Pen eco is an everyday companion in your pocket.



### Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Penlight X30PEN	8719018024886	8719018024893	02488631	X30PENX1	6

### Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 3000 Pen Eco X30PECOB1	8719018024848	8719018024855	02484840	X30PECOB1	10
Xperion 3000 Pen Eco X30PECOX1	8719018024862	8719018024879	02486230	X30PECOX1	10







