



PHILIPS

Xperion 6000

Professional work lights



2023

Designed
with **you**
in mind

LED work light features

Light module

Maximum light output (in lumen)

Boost light

Light output during power save mode (in lumen)

Eco/dimmed light

Additional small light to reach confined spaces (in lumen)

Spotlight

Operating time during one charging cycle

Operating time

Angle of the main light beam

Beam angle

Flexibility of the work light thanks to pivoting light module

Pivoting light module

High Color Rendering Index (CRI) reveals the true colors of an object, as if seen with natural light

95 CRI

UV light helps identify leakages

UV light

Change the focus of the light beam by simply turning a knob

New: Zoom light

Smart, ergonomic design

Robust ABS* and soft rubber body to hold the work light securely

Grip

Integrated telescopic hooks extendable on both sides

Telescopic mount

Switch the light on and off by moving your hand in front of the sensor

Motion detector

The remote control accessory helps retrieve lost devices up to 10 meters

Find My Device

Slide the light module along the mount to the area you want to illuminate

Sliding light

Presence sensor that senses human activity within a 2.5-meter radius

Presence sensor

Robustness and durability

Degree of protection against intrusion from solid objects, dust, accidental contact and water

Ingress protection

Degree of protection against external impacts

Shock protection

Highly resistant to grease and workshop solvents

Grease resistance

Power options and recharging

Time needed to fully recharge the integrated battery

Charging time

Battery rechargeable via a USB Type-C or Micro USB

Micro USB

Compatibility with the Multi Dock Station** accessory for cordless charging

USB-C

Compatibility with the Multi Dock Station** accessory for cordless charging

Charging station











* Acrylonitrile-butadiene-styrene copolymer
**Accessories to buy separately




















Discover our Xperion 6000 LED work lights


















UV Pillar	Pillar
 reddot winner 2022 DESIGN AWARD 2022	 reddot winner 2022 DESIGN AWARD 2022
<div>Boost light</div> <div>500 lm</div> <div>Up to 4.5 h</div>	<div>Boost light</div> <div>500 lm</div> <div>Up to 4.5 h</div>
<div>Eco light</div> <div>250 lm</div> <div>Up to 10 h</div>	<div>Eco light</div> <div>250 lm</div> <div>Up to 10 h</div>
<div>Spotlight</div> <div>180 lm</div> <div>Up to 12 h</div>	<div>Spotlight</div> <div>180 lm</div> <div>Up to 12 h</div>
<div>Light angle/ flexibility</div> <div>100°</div> <div>90° rotatable</div>	<div>Light angle/ flexibility</div> <div>100°</div> <div>90° rotatable</div>
<div>Special light features</div> <div>UV light</div> <div>Excellent color rendition</div>	<div>Special light features</div> <div></div> <div></div>
<div>Fixture</div> <div>360° rotatable hook</div> <div>1 magnet</div>	<div>Fixture</div> <div>360° rotatable hook</div> <div>1 magnet</div>
<div>Grip/grease resistance</div> <div>ABS*, Rubber</div> <div>Garage proof</div>	<div>Grip/grease resistance</div> <div>ABS*</div> <div>Garage proof</div>
<div>Robustness</div> <div>IP65</div> <div>IK07</div>	<div>Robustness</div> <div>IP65</div> <div>IK07</div>
<div>Lithium battery power supply</div> <div><4.5 h</div> <div>USB Type-C</div>	<div>Lithium battery power supply</div> <div><4.5 h</div> <div>USB Type-C</div>
<div>Additional accessories</div> <div>Find My Device</div> <div>Multi Dock Station**</div>	<div>Additional accessories</div> <div>Find My Device**</div> <div>Multi Dock Station**</div>
<div>Philips Order Entry</div> <div>X60UVPX1</div>	<div>Philips Order Entry</div> <div>X60PILLX1</div>

* Acrylonitrile-butadiene-styrene copolymer
** Accessories to buy separately, except for the Philips Xperion 6000 UV Pillar which already includes the Find My Device function

















Flood Audio	Flood	Flood Mini	Pocket	Slim	Line
  <div>Up to 20 h audio via Bluetooth</div>	 	 	 <div>reddot winner 2022</div> <div>DESIGN AWARD 2022</div> 	 <div>reddot winner 2022</div> <div>DESIGN AWARD 2022</div> 	 <div>reddot winner 2022</div> <div>DESIGN AWARD 2022</div> 
<div>Boost light</div> <div>1000 lm</div> <div>Up to 3 h</div>	<div>Boost light</div> <div>1000 lm</div> <div>Up to 3 h</div>	<div>Boost light</div> <div>500 lm</div> <div>Up to 3 h</div>	<div>Boost light</div> <div>300 lm</div> <div>Up to 3.5 h</div>	<div>Boost light</div> <div>500 lm</div> <div>Up to 4.5 h</div>	<div>Boost light</div> <div>300 lm</div> <div>Up to 4.5 h</div>
<div>Eco light</div> <div>100 lm</div> <div>Up to 22 h</div>	<div>Eco light</div> <div>100 lm</div> <div>Up to 22 h</div>	<div>Eco light</div> <div>100 lm</div> <div>Up to 9 h</div>	<div>Eco light</div> <div>150 lm</div> <div>Up to 7 h</div>	<div>Eco light</div> <div>250 lm</div> <div>Up to 7 h</div>	<div>Eco light</div> <div>150 lm</div> <div>Up to 8 h</div>
<div>Spotlight</div> <div>250 lm</div> <div>Up to 9 h</div>	<div>Spotlight</div> <div>250 lm</div> <div>Up to 9 h</div>	<div>Spotlight</div> <div>250 lm</div> <div>Up to 5 h</div>	<div>Spotlight</div> <div>100 lm</div> <div>Up to 10 h</div>	<div>Spotlight</div> <div>150 lm</div> <div>Up to 9 h</div>	<div>Spotlight</div> <div>120 lm</div> <div>Up to 9 h</div>
<div>Light angle/light function</div> <div>100°</div> <div>Light setting memory</div>	<div>Light angle/light function</div> <div>100°</div> <div>Light setting memory</div>	<div>Light angle/light function</div> <div>100°</div> <div>Light setting memory</div>	<div>Light angle</div> <div>110°</div>	<div>Light angle/flexibility</div> <div>100°</div> <div>270° rotatable</div>	<div>Light angle</div> <div>110°</div>
<div>Special features</div> <div>Zoom light</div> <div>Motion detection</div>	<div>Special features</div> <div>Zoom light</div> <div>Motion detection</div>	<div>Special light features</div> <div>Zoom light</div> <div>Compact design</div>	<div>Special light features</div> <div>25 cm flexible hose, rotatable in all directions</div>	<div>Special light features</div> <div>180° foldable</div>	
<div>Fixture</div> <div>180° rotatable handle</div> <div>Magnetic handle</div>	<div>Fixture</div> <div>180° rotatable handle</div> <div>Magnetic handle</div>	<div>Fixture</div> <div>180° rotatable handle</div> <div>Magnetic handle</div>	<div>Fixture</div> <div>360° rotatable hook</div> <div>1 magnet</div>	<div>Fixture</div> <div>360° rotatable hook</div> <div>1 magnet</div>	<div>Fixture</div> <div>360° rotatable hook</div> <div>1 magnet</div>
<div>Grip/grease resistance</div> <div>ABS*</div> <div>Garage proof</div>	<div>Grip/grease resistance</div> <div>ABS*</div> <div>Garage proof</div>	<div>Grip/grease resistance</div> <div>ABS*</div> <div>Garage proof</div>	<div>Grip/grease resistance</div> <div>ABS*, Rubber</div> <div>Garage proof</div>	<div>Grip/grease resistance</div> <div>ABS*, Rubber</div> <div>Garage proof</div>	<div>Grip/grease resistance</div> <div>ABS*</div> <div>Garage proof</div>
<div>Robustness</div> <div>IP55</div> <div>IK07</div>	<div>Robustness</div> <div>IP65</div> <div>IK07</div>	<div>Robustness</div> <div>IP65</div> <div>IK07</div>	<div>Robustness</div> <div>IP65</div> <div>IK07</div>	<div>Robustness</div> <div>IP54</div> <div>IK07</div>	<div>Robustness</div> <div>IP65</div> <div>IK07</div>
<div>Lithium battery power supply</div> <div><5 h</div> <div>USB Type-C</div>	<div>Lithium battery power supply</div> <div><5 h</div> <div>USB Type-C</div>	<div>Lithium battery power supply</div> <div><3.5 h</div> <div>USB Type-C</div>	<div>Lithium battery power supply</div> <div><3.5 h</div> <div>USB Type-C</div>	<div>Lithium battery power supply</div> <div><4 h</div> <div>USB Type-C</div>	<div>Lithium battery power supply</div> <div><3.5 h</div> <div>USB Type-C</div>
<div>Charging features</div> <div>Multi Dock Station**</div> <div>USB power bank</div>	<div>Charging features</div> <div>Multi Dock Station**</div> <div>USB power bank</div>	<div>Additional accessories</div> <div>Find My Device**</div> <div>Multi Dock Station**</div>	<div>Additional accessories</div> <div>Multi Dock Station**</div>	<div>Additional accessories</div> <div>Find My Device**</div> <div>Multi Dock Station**</div>	
<div>Philips Order Entry</div> <div>X60FLAUX1</div>	<div>Philips Order Entry</div> <div>X60FLX1</div>	<div>Philips Order Entry</div> <div>X60FLMIX1</div>	<div>Philips Order Entry</div> <div>X60POCKX1</div>	<div>Philips Order Entry</div> <div>X60SLIMX1</div>	<div>Philips Order Entry</div> <div>X60LINEX1</div>

Penlight		
		
		
Boost light	 200 lm	 Up to 3 h
Eco light	 100 lm	 Up to 5.5 h
Spotlight	 120 lm	 Up to 3.5 h
Light angle	 80°	
Special features	 Rotating magnetic clip	
Fixture	 2 magnets	
Grip/grease resistance	 ABS*	 Garage proof
Robustness	 IP65	 IK07
Lithium battery power supply	 <1.6 h	 USB Type-C

Philips Order Entry
X60PENX1

Headlight		
		
		
Boost light	 300 lm	 Up to 2.5 h
Eco light	 150 lm	 Up to 4 h
Spotlight	 120 lm	 Up to 4.5 h
Light angle/ flexibility	 220° panoramic	 60° rotatable
Special features	 Motion detection	
Fixture	 Adjustable headband	
Grip/grease resistance	 Garage proof	
Robustness	 IP65	 IK07
Lithium battery power supply	 <2.5 h	 USB Type-C

Philips Order Entry
X60HEADX1


Under-Bonnet Light		
		
		
Boost light	 1200 lm	 Up to 3 h
Eco light	 120 lm	 Up to 20 h
Spotlight		
Light angle/ feature	 110°	5800 K
Special features	 Presence sensor	 Sliding light
Fixture	 Telescopic hooks	
Grip/grease resistance	 Rubber	 Garage proof
Robustness	 IP54	 IK07
Lithium battery power supply	 <3.5 h	 USB Type-C

Philips Order Entry
X60BONNX1

Xperion 6000 Penlight

Compact LED worker’s companion

Designed with a broad beam of 200 lumens, the compact, ergonomic Philips Xperion 6000 Penlight is ideal for all inspection work. Our Penlight is equipped with a 120-lm pointer to direct the light where needed.



3 year warranty*

*To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Penlight X60PEN	8719018021694	8719018021700	02169431	X60PENX1	6

Xperion 6000 Headlight

Dual-mode, motion-sensing LED light

The Philips Xperion 6000 Headlight projects a 300-lumen panoramic light beam in front of you. Its rotating 120-lumen spotlight allows you to see every detail. An additional motion-detection function makes it a versatile, hands-free tool.



3 year warranty*

Premium LED light with multiple outputs

300 lm
1500 lm
120 lm

220° panoramic LED light beam

220°

Motion-detection mode for hands-free use

Anti-slip elastic headband. Comfortable and easy to adjust

Fully charged within 2.5 hours, via USB-C and battery life indicator

<2.5 h

Resistant to impacts, water and solvents

IP65
IK07

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Headlight X60HEAD	8719018021731	8719018021748	02173131	X60HEADX1	6

Xperion 6000 Under-Bonnet Light

Extendable, powerful LED light

The Philips Xperion 6000 Under-Bonnet LED Light offers a seamlessly dimmable beam of up to 1200 lumens, 360° rotatability, and a telescopic mount extending up to 2.08 meters. It is for working on cars, vans, and trucks.



3 year warranty*

Seamless, premium light dimming with multiple outputs

1200 lm
120 lm

Telescopic, extendable mount up to 2.08 meters

Sliding light module along the mount

Presence sensor of human activity within a 2.5-meter radius

360° rotatable hooks covered with soft rubber

Fully charged within 3.5 hours, via USB-C and battery life indicator

<3,5 h

Resistant to impacts, water and solvents

IP54
IK07

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Under-Bonnet Light X60BONN	8719018021717	8719018021724	02171731	X60BONNX1	6

Xperion 6000 UV Pillar

Advanced lighting performance that lasts

Our premium work light, the Philips Xperion 6000 UV Pillar, is a multi-purpose work light with several powerful light sources, UV light, high CRI and long-lasting battery. Locate your work light in seconds with the Find My Device function.



Premium LED light with multiple outputs

500 lm
2500 lm
180 lm

Precision light with ergonomic design and wide beam angle

90°
100°

High CRI 95 and unique UV light

95 CRI
UV



3 year warranty**

Strong magnet and 360° rotatable hook

360°
Magnet

Compatible with the Find My Device accessory (included) and the Multi Dock Station*

Find My Device
Multi Dock Station

Resistant to impacts, water and solvents

IP65
IK07

*Accessories to buy separately
**To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 UV Pillar X60UVPI	8719018014719	8719018014726	01471931	X60UVPIX1	6

Xperion 6000 Pillar

Work all day on a single charge

The Philips Xperion 6000 Pillar LED work light lasts all day on a single charge. Its bright 250 and 500 lm main light and inbuilt 180 lm spotlight will meet multiple needs. Foldable for easy carrying and adjustable lighting angles.



Premium LED light with multiple outputs

500 lm
2500 lm
180 lm

Precision light with ergonomic design and wide beam angle

90°
100°

Long operating time in different light modes

<12 h



3 year warranty**

Strong magnet and 360° rotatable hook

360°
Magnet

Compatible with the Find My Device accessory and the Multi Dock Station*

Find My Device
Multi Dock Station

Resistant to impacts, water and solvents

IP65
IK07

*Accessories to buy separately
**To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Pillar X60PILL	8719018014696	8719018014702	01469631	X60PILLX1	6



Xperion 6000 Flood Audio

Audio LED projector light

With its 1000-lm flood light, 250-lm spot and variable beam, the Philips Xperion 6000 Flood audio-enabled projector gets the job done. The smart-zoom knob and motion sensor simplify control, while Bluetooth speakers are music to the ears.



3 year warranty*



*To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Flood Audio X60FLAU	8719018019110	8719018019127	01911031	X60FLAUX1	6




Xperion 6000 Flood

Multipurpose LED projector light

With its 1000-lm flood light and variable beam, the Philips Xperion 6000 Flood multipurpose projector gets the job done. The smart-zoom knob and motion sensor simplify control, while resistance to impacts and water guarantees durability.



3 year warranty*



*To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Flood X60FL	8719018019097	8719018019103	01909731	X60FLX1	6

Xperion 6000 Flood Mini

Compact LED projector light

With its 500-lm flood light and variable beam, the Philips Xperion 6000 Flood compact projector gets the job done. The smart-zoom knob simplifies control, while resistance to impacts and water guarantees durability.



Premium LED light with multiple outputs

Versatile attachments with integrated magnets

Compact and light to follow you everywhere

Glove proof smart-zoom knob for easy light control

Fully charged within 3.5 hours via USB-C and battery life indicator

Resistant to impacts, water and solvents

^{*}To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Flood X60FLMI	8719018019134	8719018019141	01913431	X60FLMIX1	6

Xperion 6000 Pocket

The compact but powerful light

The compact, powerful Philips Xperion 6000 Pocket is perfect for confined spaces with an ultra-flexible 100 lm, 25 cm hose spotlight. Its wide-beam light up to 300 lm in Boost mode gives you the bright light you need.



Premium LED light with multiple outputs

Precision light with flexible hose spot and wide beam angle

Long operating time in different light modes

^{**}To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Pocket X60POCK	8719018014658	8719018014665	01465831	X60POCKX1	6

Xperion 6000 Slim

Perfect for narrow spaces

The versatile Philips Xperion 6000 Slim is ideal for narrow spaces. Featuring 250 lm in Eco and 500 lm in Boost mode, its unique 270° rotating light module helps you direct the powerful beam where you need it.

Premium LED light with multiple outputs

500 lm

250 lm

150 lm

Unique 270° rotating light module and wide beam angle

270°

100°

Long operating time in different light modes

<9 h

3 year warranty**



Strong magnet and 360° rotatable hook

Compatible with the Find My Device accessory and the Multi Dock Station*

Resistant to impacts, water and solvents

IP54

IK07

*Accessories to buy separately
**To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Slim X60SLIM	8719018014672	8719018014689	01467231	X60SLIMX1	6

Xperion 6000 Line

Work on larger areas

Designed with a 110° broad beam of 150 lm in Eco and 300 lm in Boost mode, the Philips Xperion 6000 Line is ideal for lighting up larger areas. It is equipped with a 120 lm spotlight beam to direct the light where it is needed.



Premium LED light with multiple outputs

300 lm

150 lm

120 lm

Precision light with ergonomic design and wide beam angle

110°

Long operating time in different light modes

<9 h

3 year warranty*

Strong magnet and 360° rotatable hook

Fully charged within 3,5 hours via USB-C

<3,5 h

Resistant to impacts, water and solvents

IP65

IK07

*To be claimed on Philips.com/LEDworklights-warranty

Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Xperion 6000 Line X60LINE	8719018014733	8719018014740	01473331	X60LINEX1	6

Multi Dock Station

Docking station for charging multiple devices

The Philips Multi Dock Station is a cordless accessory for the Xperion LED work lights. Placed on a table, it can cordlessly charge two devices at a time or simply act as a storage point.

- LED indicator to show charging status
- Dedicated space for the Find My Device remote control
- Compatible with Philips Xperion 6000 UV Pillar, Pillar, Pocket, Slim, Flood Audio, Flood and Flood Mini.



Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Multi Dock Station ACCMUDO	8719018014757	8719018014764	01475731	ACCMUDOX1	6

Find My Device

A handy way to find misplaced devices

With the Philips Find My Device accessory, you can use the remote control to trigger an audible buzzer and a flashing light, to find lost Philips Xperion 6000 devices. It works up to 10 meters.

- Insert the plug-and-play chip into the work light's body
- Use remote control to locate your misplaced Philips Xperion 6000 UV Pillar (included), Pillar, Slim or Flood Mini (to buy separately)
- Carry the remote control on your keychain or place it on the Philips Multi Dock Station



Ordering information

Product	EAN1	EAN3	GOC	Order Entry	MOQ
Find My Device ACCFIMD	8719018014771	8719018014788	01477131	ACCFIMDX1	6



