

# Xperion 6000

## Our professional range that covers every garage need



	UV Pillar	Pillar	Flood Audio	Flood	Flood Mini	Pocket	Slim	Line	Penlight	Headlight	Under-Bonnet Light
Boost light	500 lm Up to 4.5 h	500 lm Up to 4.5 h	1000 lm Up to 3 h	1000 lm Up to 3 h	500 lm Up to 3 h	300 lm Up to 3.5 h	500 lm Up to 4.5 h	300 lm Up to 4.5 h	200 lm Up to 3 h	300 lm Up to 2.5 h	1200 lm Up to 3 h
Eco light	250 lm Up to 10 h	250 lm Up to 10 h	100 lm Up to 22 h	100 lm Up to 22 h	100 lm Up to 9 h	150 lm Up to 7 h	250 lm Up to 7 h	150 lm Up to 8 h	100 lm Up to 5.5 h	150 lm Up to 4 h	120 lm Up to 20 h
Spotlight	180 lm Up to 12 h	180 lm Up to 12 h	250 lm Up to 9 h	250 lm Up to 9 h	250 lm Up to 5 h	100 lm Up to 10 h	150 lm Up to 9 h	120 lm Up to 9 h	120 lm Up to 3.5 h	120 lm Up to 4.5 h	
Light angle/ flexibility	100° 90° rotatable	100° 90° rotatable	100° Light setting memory	100° Light setting memory	100° Light setting memory	110°	100° 270° rotatable	110°	80°	220° panoramic 60° rotatable	110° 5800 K
Special light features	UV light  Excellent color rendition		Zoom light  Motion detection	Zoom light  Motion detection	Zoom light  Compact design	25 cm flexible hose, rotatable in all directions	180° foldable		Rotating magnetic clip	Motion detection	Presence sensor  Sliding light
Fixture	360° rotatable hook  1 magnet	360° rotatable hook  1 magnet	180° rotatable handle  Magnetic handle	180° rotatable handle  Magnetic handle	180° rotatable handle  Magnetic handle	360° rotatable hook  1 magnet	360° rotatable hook  1 magnet	360° rotatable hook  1 magnet	2 magnets	Adjustable headband	Telescopic hooks
Grip/grease resistance	ABS*, Rubber  Garage proof	ABS*  Garage proof	ABS*  Garage proof	ABS*  Garage proof	ABS*  Garage proof	ABS*, Rubber  Garage proof	ABS*, Rubber  Garage proof	ABS*  Garage proof	ABS*  Garage proof	Garage proof	Rubber  Garage proof
Robustness	IP65  IK07	IP65  IK07	IP55  IK07	IP65  IK07	IP65  IK07	IP65  IK07	IP54  IK07	IP65  IK07	IP65  IK07	IP65  IK07	IP54  IK07
Lithium battery power supply	<4.5 h  USB Type-C	<4.5 h  USB Type-C	<5 h  USB Type-C	<5 h  USB Type-C	<3.5 h  USB Type-C	<3.5 h  USB Type-C	<4 h  USB Type-C	<3.5 h  USB Type-C	<1.6 h  USB Type-C	<2.5 h  USB Type-C	<3.5 h  USB Type-C
Additional accessories	Find My Device  Multi Dock Station**	Find My Device**  Multi Dock Station**	Multi Dock Station**  USB power bank	Multi Dock Station**  USB power bank	Find My Device**  Multi Dock Station**	Multi Dock Station**	Find My Device**  Multi Dock Station**				
	Philips Order Entry X60UVPIX1	Philips Order Entry X60PILLX1	Philips Order Entry X60FLAUX1	Philips Order Entry X60FLX1	Philips Order Entry X60FLMIX1	Philips Order Entry X60POCKX1	Philips Order Entry X60SLIMX1	Philips Order Entry X60LINEX1	Philips Order Entry X60PENX1	Philips Order Entry X60HEADX1	Philips Order Entry X60BONNX1

\* Acrylonitrile-butadiene-styrene copolymer  
\*\* Accessories to buy separately, except for the Philips Xperion 6000 UV Pillar which already includes the Find My Device function