

Az egyes LED izzók rendeltetése



Fényszóró	Első ködlámpák	Első parkolólámpák	Első helyzetjelzők	Műszerfalvilágítás	Belső világítás	Oldalsó irányjelzők	Kesztyűtartó-világítás	Hátsó helyzetjelzők	Hátsó irányjelzők	Hátsó ködlámpák	Csomagtartó-világítás	Rendszámlemezvilágítás	3. féklámpa	Féklámpák	Tolatólámpa	



Ultinon Pro9100 HL

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

Ultinon Pro6000 SL

SL-T10 [≈W5W]	SL-AMB [≈P21W]	SL-AMB [≈P21/5W]	SL-T10 [≈W5W]	SL-T10 [≈W5W]	SL-AMB [≈W5W]	SL-T10 [≈W5W]	SL-RED [≈P21/5W]	SL-AMB [≈P21W]	SL-RED [≈P21W]	SL-T10 [≈W5W]	SL-T10 [≈W5W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-WHITE [≈P21W]
SL-WHITE [≈R5W/R10W]	SL-AMB [≈W21W]	SL-AMB [≈W21/5W]	SL-FEST 30/38/43 mm	SL-T10 [≈W5W]	SL-FEST 30/38/43 mm	SL-RED [≈W21/5W]	SL-AMB [≈P21/5W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-FEST 30/38/43 mm	SL-FEST 30/38/43 mm	SL-RED [≈W21W]	SL-RED [≈P21/5W]	SL-RED [≈P21/5W]	SL-WHITE [≈W21W]
SL-WHITE [≈P21/5W]	SL-WHITE [≈P21/5W]		SL-WHITE [≈R5W/R10W]	SL-WHITE [≈R5W/R10W]	SL-WHITE [≈R5W/R10W]	SL-AMB [≈W21W]	SL-AMB [≈W21W]	SL-AMB [≈W21W]	SL-AMB [≈W21W]	SL-WHITE [≈R5W/R10W]	SL-WHITE [≈R5W/R10W]	SL-WHITE [≈R5W/R10W]	SL-WHITE [≈R5W/R10W]	SL-RED [≈W21W]	SL-T16 [≈W16W]
SL-WHITE [≈W21/5W]	SL-WHITE [≈W21/5W]					SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]							SL-RED [≈W21/5W]	



Ultinon Pro5100 HL

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

Ultinon Pro3000 SL

SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	SL-RED [≈P21/5W]	SL-RED [≈P21/5W]	SL-RED [≈P21W]	IL/SL-WHITE [≈W5W]	SL-WHITE [≈W5W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-WHITE [≈P21W]
SL-FEST 30/38/43 mm	SL-FEST 30/38/43 mm	SL-FEST 30/38/43 mm	SL-FEST 30/38/43 mm	SL-RED [≈W21/5W]	SL-RED [≈W21/5W]	SL-RED [≈W21W]	SL-FEST 30/38/43 mm	SL-FEST 30/38/43 mm	SL-FEST 30/38/43 mm	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-WHITE [≈W21W]



Ultinon Pro3022 HL

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

LED-adapterek

CANbus adapter HL [≈H4], [≈H7]	CANbus adapter HL [≈HB3/HB4/HIR2]	Light Repair HL [≈H7]	CANbus adapter FL [≈H8/H11/H16]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]



LED-adapterek

CANbus adapter HL [≈H4], [≈H7]	CANbus adapter HL [≈HB3/HB4/HIR2]	Light Repair HL [≈H7]	CANbus adapter FL [≈H8/H11/H16]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]