

Which LED for which function?



Headlights		Front fog lights		Front position/ parking lights		Front indicators		Dashboard lights		Interior lights		Side indicators		Glove compartment lights		Rear position/ parking lights		Rear indicators		Rear fog lights		Trunk lights		License plate lights		3 rd stop light		Stop lights		Reversing light	
Ultion Pro9100 HL																Ultion Pro6000 SI															
HL [~H1]	HL [~H3]	HL [~H4]	HL [~H7]	FL [~H8/H11/H16]	SI-T10 [~W5W]	SI-T10 [~W5W]	SI-T10 [~W5W]	SI-AMB [~P21W]	SI-AMB [~P21W]	SI-AMB [~P21W]	SI-T10 [~W5W]	SI-T10 [~W5W]	SI-T10 [~W5W]	SI-AMB [~P21W]	SI-AMB [~P21W]	SI-AMB [~P21W]	SI-T10 [~W5W]	SI-T10 [~W5W]	SI-T10 [~W5W]	SI-AMB [~P21W]	SI-AMB [~P21W]	SI-AMB [~P21W]	SI-T10 [~W5W]	SI-T10 [~W5W]	SI-T10 [~W5W]	SI-AMB [~P21W]	SI-AMB [~P21W]	SI-AMB [~P21W]	SI-T10 [~W5W]	SI-T10 [~W5W]	SI-T10 [~W5W]
HL [~HB3/HB4]	HL [~H11]	HL [~HIR2]			SI-WHITE [~R5W/R10W]	SI-WHITE [~R5W/R10W]	SI-WHITE [~R5W/R10W]	SI-AMB [~W21W]	SI-AMB [~W21W]	SI-AMB [~W21W]	SI-FEST 30/38/43 mm	SI-FEST 30/38/43 mm	SI-FEST 30/38/43 mm	SI-T10 [~W5W]	SI-T10 [~W5W]	SI-T10 [~W5W]	SI-FEST 30/38/43 mm	SI-FEST 30/38/43 mm	SI-FEST 30/38/43 mm	SI-RED [~W21W/5W]	SI-RED [~W21W/5W]	SI-RED [~W21W/5W]	SI-RED [~P21W]	SI-RED [~P21W]	SI-RED [~P21W]	SI-AMB [~P21W]	SI-AMB [~P21W]	SI-AMB [~P21W]	SI-T10 [~W5W]	SI-T10 [~W5W]	SI-T10 [~W5W]
Ultion Pro5100 HL																Ultion Pro3100 SI															
HL [~H1]	HL [~H3]	HL [~H4]	HL [~H7]	FL [~H8/H11/H16]	SI-WHITE [~P21W/5W]	SI-WHITE [~P21W/5W]	SI-WHITE [~P21W/5W]	SI-AMB [~W21W]	SI-AMB [~W21W]	SI-AMB [~W21W]	SI-FEST 30/38/43 mm	SI-FEST 30/38/43 mm	SI-FEST 30/38/43 mm	SI-T10 [~W5W]	SI-T10 [~W5W]	SI-T10 [~W5W]	SI-FEST 30/38/43 mm	SI-FEST 30/38/43 mm	SI-FEST 30/38/43 mm	SI-RED [~W21W/5W]	SI-RED [~W21W/5W]	SI-RED [~W21W/5W]	SI-RED [~P21W]	SI-RED [~P21W]	SI-RED [~P21W]	SI-AMB [~P21W]	SI-AMB [~P21W]	SI-AMB [~P21W]	SI-T10 [~W5W]	SI-T10 [~W5W]	SI-T10 [~W5W]
HL [~HB3/HB4]	HL [~H11]	HL [~HIR2]			SI-WHITE [~P21W/5W]	SI-WHITE [~P21W/5W]	SI-WHITE [~P21W/5W]	SI-AMB [~W21W]	SI-AMB [~W21W]	SI-AMB [~W21W]	SI-FEST 30/38/43 mm	SI-FEST 30/38/43 mm	SI-FEST 30/38/43 mm	SI-T10 [~W5W]	SI-T10 [~W5W]	SI-T10 [~W5W]	SI-FEST 30/38/43 mm	SI-FEST 30/38/43 mm	SI-FEST 30/38/43 mm	SI-RED [~W21W/5W]	SI-RED [~W21W/5W]	SI-RED [~W21W/5W]	SI-RED [~P21W]	SI-RED [~P21W]	SI-RED [~P21W]	SI-AMB [~P21W]	SI-AMB [~P21W]	SI-AMB [~P21W]	SI-T10 [~W5W]	SI-T10 [~W5W]	SI-T10 [~W5W]
LED adapters																LED adapters															
CANbus adapter HL [~H4], [~H7]	CANbus adapter HL [~HB3/HB4/HIR2]	Light Repair HL [~H7]	CANbus adapter FL [~H8/H11/H16]		CANbus adapter SI [~W5W]	CANbus adapter SI [~W21W]	CANbus adapter SI [~W5W]	CANbus adapter SI [~W5W]	CANbus adapter SI [~W5W]	CANbus adapter SI [~W5W]	CANbus adapter SI [~W5W]	CANbus adapter SI [~W21W]	CANbus adapter SI [~W21W]	CANbus adapter SI [~W21W]	CANbus adapter SI [~W21W]	CANbus adapter SI [~W21W]	CANbus adapter SI [~W5W]	CANbus adapter SI [~W5W]	CANbus adapter SI [~W5W]	CANbus adapter SI [~W21W]	CANbus adapter SI [~W21W]	CANbus adapter SI [~W21W]	CANbus adapter SI [~W21W]	CANbus adapter SI [~W21W]	CANbus adapter SI [~W21W]	CANbus adapter SI [~W21W]	CANbus adapter SI [~W21W]	CANbus adapter SI [~W21W]	CANbus adapter SI [~W21W]	CANbus adapter SI [~W21W]	