

# Which car lamp do you need?



## Enhanced brightness



Up to **200%**  
more brightness<sup>1</sup>

**RacingVision  
GT200**


Beam  
up to  
**+80 m<sup>2</sup>**




**Auto  
EXPRESS  
BEST BUY  
2023**



Beam performance<sup>1</sup>



Light color<sup>4</sup>



Lifetime<sup>4</sup>




Available in  
**H4, H7**

Up to **130%**  
more brightness<sup>1</sup>


**X-tremeVision  
G-force**



Beam performance<sup>1</sup>



Light color<sup>4</sup>



Lifetime<sup>4</sup>




Available in  
**H1, H4, H7<sup>3</sup>**

Up to **60%**  
more vision<sup>1</sup>


**VisionPlus**



Beam performance<sup>1</sup>



Light color<sup>4</sup>



Lifetime<sup>4</sup>




Available in  
**H1, H4, H7**

Up to **30%**  
more vision<sup>1</sup>


**Vision**



Beam performance<sup>1</sup>



Light color<sup>4</sup>



Lifetime<sup>4</sup>



Available in  
**H1, H3, H4, H7, H11,  
HB3, HB4**

## Unique style




**Sharp  
white** look

**WhiteVision  
ultra**


H4, H7  
up to  
**4200 K**



Beam performance<sup>1</sup>



Light color<sup>4</sup>



Lifetime<sup>4</sup>




Available in  
**H1, H3, H4, H7, H8, H11,  
HB3, HB4, HIR2, PSX24W**

**Ultimate  
white** light


**DiamondVision<sup>5</sup>**



Beam performance



Light color<sup>4</sup>



Lifetime<sup>4</sup>




Available in  
**H1, H3, H4, H7, H11,  
HB3, HB4**

**Bright  
white** light


**CrystalVision<sup>5</sup>**



Beam performance



Light color<sup>4</sup>



Lifetime<sup>4</sup>




Available in  
**H1, H3, H4, H7, H11,  
HB3, HB4**

## Extended lifetime




Lifetime up to  
**1500 hours<sup>4</sup>**


**LongLife  
EcoVision**




Beam performance



Light color<sup>4</sup>



Lifetime<sup>4</sup>



Available in  
**H1, H3, H4, H7, H11,  
H18, H19, HIR2**

Images for illustration purposes only. <sup>1</sup> Compared to the minimum legal standard. <sup>2</sup> Compared to derived minimum after ECE regulation, based on 1 Lux. Farthest distance from the car, applies to H4 and H7. <sup>3</sup> 10 G applies to H4 and H7. <sup>4</sup> Lifetime and color temperature differ per type, indication for H7 only. <sup>5</sup> Non-ECE homologated, for off-road only.