

PHILIPS

Xperion 6000

LED work lights




**Built for
professionals**

Discover our **Xperion 6000** LED work lights

Philips Xperion 6000 LED work lights were conceived, engineered, and built for auto service professionals.

With their state-of-the-art Philips Xperion LED chips, incredibly rugged construction, and innovative features such as 360° rotating hooks, hinged light panels, and multiple illumination modes, these lights are designed to deliver years of reliable service and brilliant illumination in shop bays and anywhere superior lighting is needed.

The Philips Xperion 6000 LED work light line includes six hand-held lights, two flood projector lights, an under hood extendable light, a wearable headlamp, a multi-dock charging station, and the Find My Device accessory.



Xperion 6000 UV Pillar

Advanced lighting performance that lasts

Our premium work light, the Philips Xperion 6000 UV Pillar, is a multi-purpose work light with exceptionally long battery life. It features three light sources – a main light that's rated CRI95 for critical color matching, a UV inspection light, and a 180 Lumens Spotlight.



Xperion 6000 Pillar

Work all day on a single charge

The Philips Xperion 6000 Pillar LED work light lasts all day on a single charge. Bright 500 Lumens in Boost mode, 250 Lumens in Eco mode and built-in 180 Lumens in Spotlight will meet multiple needs. Foldable for easy carrying and adjustable lighting angles.



Premium LED light with multiple outputs



- 500 Lumens
- 250 Lumens
- 180 Lumens

Precision light with ergonomic design and wide beam angle



- 90°
- 100°

High CRI95 main light and unique UV light for leak detection



- UV
- 95 CRI



Strong magnet and 360° rotatable hook



- 360°

Compatible with Find My Device and Multi Dock Station*



- Find My Device
- Multi Dock Station

Resistant to impacts, water, and solvents



- IP65
- IK07

*Accessories sold separately

Premium LED light with multiple outputs



- 500 Lumens
- 250 Lumens
- 180 Lumens

Precision light with ergonomic design and wide beam angle



- 90°
- 100°

Long operating time in different light modes



- <12 h



Strong magnet and 360° rotatable hook



- 360°

Compatible with Find My Device and Multi Dock Station*



- Find My Device
- Multi Dock Station

Resistant to impacts, water, and solvents



- IP65
- IK07

*Accessories sold separately

Xperion 6000 Pocket


The compact but powerful light

Its wide-beam light delivers up to 300 Lumens in Boost mode to give you the bright light you need. With an ultra-flexible 100 Lumens, 10 inch hose spotlight, the compact, powerful Philips Xperion 6000 Pocket is perfect for confined spaces.


Premium LED light with multiple outputs



Precision light with flexible hose spotlight and wide beam angle



Long operating time in different light modes



Strong magnet and 360° rotatable hook



Compatible with the Multi Dock Station*



Resistant to impacts, water, and solvents




*Accessory sold separately

Xperion 6000 Slim

Perfect for narrow spaces

The versatile Philips Xperion 6000 Slim is ideal for narrow spaces. Featuring 500 Lumens in Boost and 250 Lumens in Eco mode, its unique 270° rotating light module helps you direct the powerful beam where you need it. The spotlight delivers 150 Lumens and up to 9 hours of run time.


Premium LED light with multiple outputs



Unique 270° rotating light module and wide beam angle



Long operating time in different light modes



Strong magnet and 360° rotatable hook



Compatible with Find My Device and Multi Dock Station*



Resistant to impacts, water, and solvents



*Accessories sold separately



Xperion 6000 Line

Work on larger areas


Designed with a 110° broad beam of 300 Lumens in Boost and 150 Lumens in Eco mode, the Philips Xperion 6000 Line is ideal for lighting up larger areas. It features a main light with 20 Xperion LEDs and a 120 Lumens Spotlight beam.




Premium LED light with multiple outputs



Precision light with ergonomic design and wide beam angle



Long operating time in different light modes



Strong magnet and 360° rotatable hook



Fully charged within 3.5 hours via USB-C




Resistant to impacts, water, and solvents



Xperion 6000 Flood Audio

Audio LED projector light

With its 1000 Lumens Floodlight, 250 Lumens variable beam Spotlight, the Philips Xperion 6000 Flood audio-enabled projector gets the job done. The smart-zoom knob and motion sensor simplify control, while Bluetooth speakers are music to the ears.



Xperion 6000 Flood Mini

Compact LED projector light

With its 500 Lumens Floodlight and variable beam, the Philips Xperion 6000 Flood mini projector gets the job done. The smart-zoom knob simplifies control, while resistance to impacts and water guarantees durability.



Xperion 6000 Penlight

Premium LED penlight



The Penlight is ideal for quick inspection jobs. Small and rechargeable, it lets you work a full day without interruption. Designed with multiple light outputs, providing up to 200 Lumens in Boost mode, 120 Lumens in Spotlight, and 100 Lumens in Eco mode. The Penlight features a 45° rotatable magnetic clip as well as a battery-status indicator.



Premium LED light with multiple outputs

Precision light with a smart, ergonomic design and wide beam angle

Long operating time in different light modes



Strong magnet and 45° rotatable magnetic clip

Fully charged within 2 hours via USB-C plus battery life indicator


Resistant to impacts, water, and solvents

Xperion 6000 Headlamp

Dual mode LED headlamp



The Headlamp headband-mounted work light puts brilliant LED illumination right on the task at hand. Powered by state-of-the-art Xperion LED chips, the Headlamp features two light sources. Across the front of the headband, an LED light strip provides a broad beam of light of up to 300 Lumens in Boost mode and up to 150 Lumens in Eco mode. A spotlight mounted on the side of the headband provides a narrow, intense beam of up to 120 Lumens. The hands-free motion detection feature allows you to turn on and off the light without touching it. The Headlamp is resistant to solvents and is rated IK07/IP65 against impacts and dust and water intrusion.



LED Headlamp with multiple modes

Motion detector mode for hands-free working

Fully charged within 2.5 hours via USB-C

Comfortable headband design with a wide beam angle

Long operating time in different light modes

Resistant to impacts, water, and solvents

Xperion 6000 Under Hood Light

Versatile, flexible hood light for cars, vans, and trucks

This powerful LED light with multiple light outputs provides up to 1200 Lumens and a 5800 K color temperature. Designed with 32 top quality LEDs, the light has a bright, 120° wide beam angle that will light up the entire engine compartment. Attaches to the car from both sides with extendable mount and is equipped with motion detection.



32 high quality LEDs



Telescopic extendable mount from both sides




Resistant to impacts, water, and solvents



Motion detection function



Bright 120° wide beam angle; Dimmable light output



Multi Dock Station

Docking station for charging multiple devices

The Philips Multi Dock Station is an accessory for the Xperion 6000 LED work lights. Placed on a table, it can charge two devices at a time or simply act as a storage point.

- LED indicator to show charging status
- Dedicated spaces for the Find My Device remote control
- Compatible with Philips Xperion 6000 UV Pillar, Pillar, Pocket, Slim and Flood Mini models



Find My Device



A handy way to find misplaced devices





















With the Philips Find My Device accessory, you can trigger an audible buzzer and a flashing light, to find most lost Philips Xperion 6000 devices. It works up to 32 feet.

- Find My Device is sold separately for UV Pillar, Pillar, Slim, and Flood Mini models
- Insert the plug-and-play chip into the work light's body
- Use the Find My Device to locate your misplaced Philips Xperion UV Pillar, Pillar, Slim, and Flood Mini work lights
- Carry the remote control on your key chain or place it in the Philips Multi Dock Station























UV Pillar



Boost light	 500 Lumens	 Up to 4.5 h
Eco light	 250 Lumens	 Up to 10 h
Spotlight	 180 Lumens	 Up to 12 h
Light angle/ flexibility	 100°	 90° rotatable
Special light features	 UV	 95%
Fixture	 360° rotatable hook	 2 magnets
Grip/grease resistance	 ABS*, Rubber	 Garage proof
Robustness	 IP65	 IK07
Lithium battery power supply	 <4.5 h	 USB Type-C
Additional accessories**	 Multi Dock Station**	 Find My Device**


















Pillar



Boost light	 500 Lumens	 Up to 4.5 h
Eco light	 250 Lumens	 Up to 10 h
Spotlight	 180 Lumens	 Up to 12 h
Light angle/ flexibility	 100°	 90° rotatable
Special light features	Foldable	
Fixture	 360° rotatable hook	 2 magnets
Grip/grease resistance	 ABS*, Rubber	 Garage proof
Robustness	 IP65	 IK07
Lithium battery power supply	 <4.5 h	 USB Type-C
Additional accessories**	 Multi Dock Station**	 Find My Device**



















Pocket



Boost light	 300 Lumens	 Up to 3.5 h
Eco light	 150 Lumens	 Up to 7 h
Spotlight	 100 Lumens	 Up to 10 h
Light angle/ flexibility	 110°	
Special light features	10" flexible hose, rotatable in all directions	
Fixture	 360° rotatable hook	 1 magnet
Grip/grease resistance	 ABS*, Rubber	 Garage proof
Robustness	 IP65	 IK07
Lithium battery power supply	 <3.5 h	 USB Type-C
Additional accessories**	 Multi Dock Station**	

















Slim



Boost light	 500 Lumens	 Up to 4.5 h
Eco light	 250 Lumens	 Up to 7 h
Spotlight	 150 Lumens	 Up to 9 h
Light angle/ flexibility	 100°	 270° rotatable
Special light features	180° foldable	
Fixture	 360° rotatable hook	 2 magnets
Grip/grease resistance	 ABS*, Rubber	 Garage proof
Robustness	 IP54	 IK07
Lithium battery power supply	 <4 h	 USB Type-C
Additional accessories**	 Multi Dock Station**	 Find My Device**
















Line

Boost light	 300 Lumens	 Up to 4.5 h
Eco light	 150 Lumens	 Up to 8 h
Spotlight	 120 Lumens	 Up to 9 h
Light angle/ flexibility	 110°	
Special light features		
Fixture	 360° rotatable hook	 1 magnet
Grip/grease resistance	 ABS*	 Garage proof
Robustness	 IP65	 IK07
Lithium battery power supply	 <3.5 h	 USB Type-C

Under Hood Light


Boost light	 1200 Lumens	 Up to 3 h
Eco light	 120 Lumens	 Up to 20 h
Light angle/ flexibility	 120°	
Special light features	Dimming 2 settings	 Motion detection
Fixture	 360° rotatable hook	 1 magnet
Grip/grease resistance	 ABS* Rubber	 Garage proof
Robustness	 IP54	 IK07
Lithium battery power supply	 <5 h	 USB Type-C

Flood Audio



Floodlight			1000 Lumens	Up to 3 h
Spotlight			250 Lumens	Up to 9 h
Light angle/light function			100°	Light setting memory
Special features			Zoom light	Motion detection
Fixture			180° rotatable handle	Magnetic handle
Grip/grease resistance			ABS*	Garage proof
Robustness			IP55	IK07
Lithium battery power supply			<5 h	USB Type-C
Charging features			Multi Dock Station**	USB power bank

Flood Mini



Floodlight			500 Lumens	Up to 3 h
Spotlight			250 Lumens	Up to 5 h
Light angle/light function			100°	Light setting memory
Special light features			Zoom light	Compact design
Fixture			180° rotatable handle	Magnetic handle
Grip/grease resistance			ABS*	Garage proof
Robustness			IP65	IK07
Lithium battery power supply			<3.5 h	USB Type-C
Additional accessories			Find My Device**	Multi Dock Station**

Pen Light



Boost light			200 Lumens	Up to 3 h
Eco light			100 Lumens	Up to 5.5 h
Spotlight			120 Lumens	Up to 3.5 h
Light angle/light function			80°	
Fixture			45° rotatable pocket clip	2 magnets
Grip/grease resistance			ABS*	Garage proof
Robustness			IP65	IK07
Lithium battery power supply			<2 h	USB Type-C

Headlamp



Boost light			300 Lumens	Up to 2.5 h
Eco light			150 Lumens	Up to 4 h
Spotlight			120 Lumens	Up to 4.5 h
Light angle/light function			220°	
Special features			Motion detection	
Grip/grease resistance			ABS*	Garage proof
Robustness			IP65	IK07
Lithium battery power supply			<2.5 h	USB Type-C

LED work light features

Light module

	Maximum light output (in Lumen)		Angle of the main light beam
	Boost light		Beam angle
	Light output during power save mode (in Lumen)		Flexibility of the work light thanks to pivoting light module
	Eco/dimmed light		Pivoting light module
	Spotlight		High Color Rendering Index (CRI) reveals the true colors of an object, as if seen with natural light
	Additional small light to reach confined spaces (in Lumen)		UV light helps identify leakages
	Operating time during one charging cycle		UV light
	Operating time		

Smart, ergonomic design

	Fixture such as clips, clamps, and hooks to enable hands-free work		Magnet integrated into the work light to enable hands-free work
	The remote control accessory helps retrieve lost devices up to 32 feet		Robust ABS* and soft rubber body to hold the work light securely

Robustness and durability

	Degree of protection against intrusion from solid objects, dust, accidental contact, and water		Degree of protection against external impacts
	Highly resistant to grease and workshop solvents		

Power options and recharging

	Time needed to fully recharge the integrated battery		Rechargeable battery with a USB Type-C cable or the Multi Dock Station**
	Compatibility with the Multi Dock Station** accessory for cordless charging		



Part Number	Description	Packaged Quantity	Minimum Order Quantity
UV Pillar	Philips LED work light Xperion 6000 UV Pillar	1	6
Pillar	Philips LED work light Xperion 6000 Pillar	1	6
Slim	Philips LED work light Xperion 6000 Slim	1	6
Pocket	Philips LED work light Xperion 6000 Pocket	1	6
Line	Philips LED work light Xperion 6000 Line	1	6
Flood Audio	Philips LED work light Xperion 6000 Flood Audio	1	6
Flood Mini	Philips LED work light Xperion 6000 Flood Mini	1	6
Under Hood Light	Philips LED work light Xperion 6000 Under Hood Light	1	6
Headlamp	Philips LED work light Xperion 6000 Headlamp	1	6
Penlight	Philips LED work light Xperion 6000 Penlight	1	6
Multi Dock	Philips LED work light accessory Multi Dock Station	1	6
Find my Device	Philips LED work light accessory Find my Device	1	6

Lumileds

34119 W. Twelve Mile Road, Suite 102
 Farmington Hills, MI 48331
 Phone: 800-257-6054
www.philips.com/automotive

Xperion 6000 LED work lights