



Philips Signage Solutions
LED Display

22"
Direct View LED

SignageSolutions



22BDL7324L

Unleash your imagination even more

LED Display for every form and shape

No limits. No boundaries. Philips L-Line 7000 series is an LED signage solution for endless possibilities in shape and size. Seamless linking and multiple size options enable truly unique displays of any dimension for perfect results.

Ready for impact

- High brightness: 1200 nits / peak 1600 nits
- Dynamic contrast & color enhancement
- Forms any shape, L-shape corner, or curvature

Next level performance

- Philips Active Health Monitoring
- Dynamic Panel Connect
- Factory calibrated

Endless possibilities

- Available in 3 dimensions
- Seamless linking for perfect imagery
- Optional bevelled corners allow curved displays
- Dynamic Power Saving

PHILIPS

Highlights

L-shape corner, or curvature

The Philips L-Line 7000 series LED panels come with a height of 25 cm and are available in 50 cm, 75 cm and 100 cm widths. These displays are ready to be installed in any landscape format with no limitations to size. Also available with bevelled corners to form curved designs in both convex and concave formats.

Active Health Monitoring

Achieve perfection through precision. Active Health Monitoring makes maintenance fast, simple, and predictable by displaying the exact item of failure and location. Utilising this software that works in real-time both online and offline, replacing the relevant part becomes an efficient process, and a must for display owners with many geographical locations.

Factory calibrated

Every Philips L-Line LED panel is calibrated in our factory under perfect circumstances. That means there's no need for further calibration on location, resulting in quicker installations. Calibration and configuration files are available to ensure fast maintenance.

Dynamic Panel Connect

Mix and match each of the Philips L-Line 7000 LED panel sizes to form a single display of any

shape and dimension. Dynamic flexible alignment pins ensure a perfect fit in any circumstance - resulting in a smooth, seamless display surface. For added convenience and efficiency, each LED panel features openings on each side to allow for versatile wired connection between the LED panels and any external input connection. Openings on the top and bottom of the LED panel can be popped out in case access is only available from the top or bottom of the panel.

Optional bevelled corners

Create bezel-free displays of any shape, size or resolution. The modular design of Philips Professional LED panels means you can adapt to any space. Build vast, immersive installations or assemble intriguing patterns. Easily create displays that flow seamlessly around doorways and other openings. Even corners and curved displays become easy to create with the new Philips 7000 series.

Perfect imagery

Your Philips Professional LED Display features built-in cable wiring to keep power and data cables tidy. Display panels are daisy-chained for both power and data, allowing you to minimise clutter and speed up installation.

Dynamic Power Saving

Philips Professional LED Displays use high-performance LEDs, which are tested thoroughly, energy efficient and cost effective. Furthermore, enhanced technology allows the display to dynamically save on power consumption.

Dynamic contrast & color

Dust, dirt, fungus and moisture resistant conformal coating protects this product and enables easier maintenance. IP30 rated and certified against ingress for reduced chance of short circuit from dust and corrosion.

High brightness

Fire retardant design slows down the spread of flames in the event of fire, and help protect the structural integrity of the LED panel in case of fire. Tested and certified with European standard B1 DIN4102, British standard (BS476-7), and North-American standard UL94.

Optional easy mount brackets

Patented easy-mount brackets make installation even faster. These optional items are available for flat LED mounting, convex curved (177.5/175/172.5 degree), and L-shape 90 degree corners.

Specifications

Picture/Display

- Color temperature default: 6500±500 K
- Color temperature adjust range: 4000~9500 K (by software)
- Viewing angle (H / V): 160 / 160 degree
- Brightness uniformity: >=97%
- Calibration(brightness/color): Supported
- Refresh rate(Hz): 2100~3900 (14 bits: 3900Hz)
- Frame frequency (Hz): 50 & 60
- Aspect ratio: 2:1
- Picture enhancement: Wide color gamut display
- Placement: Landscape
- Usage: 24/7 Hrs, Indoor
- Peak brightness (nits): 1600*
- Max. brightness (nits): ±1200*
- Peak contrast ratio: 6500:1*
- Max. contrast ratio: 5000:1*
- * Note: According to IDMS standard.

Convenience

- Signal control loop through: RJ45
- Ease of installation: Guide pins, Light weight
- Power loop through: For 230V environments: 16 cabinets or less, for 110V environments: 8 cabinets or less, 10A max
- Max. daisy chain current: 10 Amp

Operating conditions

- Temperature range (operation): -20~45 °C
- Temperature range (storage): -20~50 °C
- Humidity range (operation)[RH]: 10~80%
- Humidity range (storage) [RH]: 10~85%

Power

- Input voltage: AC100~240V (50 & 60Hz)
- Max. power cons.(W): <85
- Typical power cons. (W): <20
- Black screen power cons. (W): <9

Miscellaneous

- Warranty: 2 years
- Regulatory approvals: EN55032, EN55035, EN61000-3-2, EN61000-3-3, IEC/UL60950, IEC/UL62368, IEC62471, RoHS, FCC SDOC, Part 15, Class A
- Fire retardancy certification: BS476, UL94, B1 DIN4102

Cabinet

- Cabinet size (mm): 500x250x40
- Side angle (degree): 45
- Cabinet diagonal (inch): 22"
- Cabinet resolution (W x H): 208x104
- Weight (KG): 3.19
- Cabinet pixels (Dot): 21.632
- Cabinet area (m²): 0.125
- Power connector: 3 core socket (C14 in, C13 out)
- Data connector: RJ45
- Cabinet construction: Die-Casting Aluminum
- Receiving card quantity: 1 pcs
- Receiving card spec.: A5S/A5S plus
- Receiving card brand: NovaStar

Module

- LED type: SMD 1515 Copper wire
- Pixel constitution: 1R1G1B
- LED lifetime(Hrs): 100,000 hours
- Pixel pitch (mm): 2.4
- Module resolution (WxH pixels): 104x104
- Module size (WxH in mm): 249.9*249.9

Accessories

- Power cable: 2 pcs
- LAN cable (RJ45, CAT-5): 1 pcs
- QSG: 1 pcs

Packaging Data

- Dimension of packaging (mm): 764x392x221



Issue date 2020-12-11
Owner: Dafinka
Mihaylova

Version: 0.0.0

12 NC: 8670 001 69548
EAN: 87 12581 76999 4

Test leaflet, for internal use only!
© 2020 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com